



Representative

Catalog Number: 2PG2/ELF3-LD1-M
Product ID: 7TBA133580R1284
UPC Number: 78417013989
Status: Active

Battery Unit, Battery Type: lead-calcium, Battery Wattage: 54W, Voltage DC: 6V, 120/277VAC, self-powered, Head Style: ELF3, two lamps, Lamp Type: MR16 LED, Lamp Voltage: 6V, Lamp Wattage: 4W, Housing Colour: mist-white, Battery Run Time (Minimum): 90 minutes

The PG, P12G Series battery units combine reliability, versatility, performance and cost-efficiency in an aesthetically pleasing design. This series is Ideally suited for a wide range of commercial applications.

- Automatic, temperature compensated, pulse-type charger
- High capacity, automatic, dust-tight instantaneous transfer relay
- Low voltage disconnect prevents over discharge of battery
- Automatic brownout protection is provided
- Battery lock-out prevents battery discharge during installation

North American Specifications (UNSPSC)

UNSPSC	39111709 Emergency light unit
IGCC	3940 Emergency light unit
Brand Name	Lightalarms
Type	Battery Unit
Application	Commercial
Standard	UL
Wattage	54W
Voltage Rating	120/277VAC, 6VDC
Battery	Lead-calcium
Battery Runtime	90 minutes
Lamp Type	MR16 LED
Number Of Lamps	2
Size	14-5/8 Inches Height x 12-3/4 Inches Width x 3-1/8 Inches Depth
Material	Housing: Steel
Mounting	Wall
Color	Mist-white
Lamp Wattage	4W

European Specifications (ETIM)

ETIM	EC001957 Emergency luminaire
Lamp type	LED exchangeable
Lamp power	4W
Material housing	Steel
Colour housing	White
Battery quality	Lead
Voltage type	AC/DC
Nominal voltage	120-277V
Width	323.8mm

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	16 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US
Instruction Sheet

Available on Website
Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com