



UPC Code : 078477943557

Country Of Origin : Please Contact Customer Service.

IP710-D0Z

IllumaTech Slide Dimmer for LED 0-10V Power Supplies, 1200VA, 10A LED, 120/277 VAC

1200VA, 10A LED, 120/277 VAC, IllumaTech Slide Dimmer for LED 0-10V Power Supplies - White, Ivory, & Light Almond

- INNOVATIVE – Designed for use with LED fixtures using 0-10V power supplies
- ADVANCED – No power pack required for switching
- EXCEPTIONAL – Superior quality and dimming performance
- FLEXIBLE – Can be used in a single-pole or 3-way installation (with a 3-way switch, sold separately)

Technical Information

Product Features

Action : Standard ON/OFF

Available Colors : Ivory, White, Gray, Black, Brown, Light Almond, and Red

Color : White, Ivory, Light Almond

Frequency : 60Hz

Load Rating : 10A, 1200VA, 1500VA

Load Type : 0-10V LED, 0-10V Fluorescent (120V), 0-10V Fluorescent (277V)

Ordering Notes : White, Ivory, Light Almond Color Kits

Preset : Preset

Protection : Radio/TV Filter

Standards and Certifications : cCSAus

Style Name : Illumatech

Switch Type : Single-Pole & 3-Way

Type : Slide

Voltage : 120/277 VAC

Wallplate : Order Separately

Warranty : 5-Year Limited

Features and Benefits

- Designed specifically for use with LED fixtures using 0-10V power supplies and Mark 7® 0-10V fluorescent ballasts
- Dual voltage 120V/277V; 28 mAmps maximum sink current
- No power pack required for switching
- Provides single pole or 3-way lighting control when used with a 3-way switch
- Compatible with Decora Plus™ screwless and Decora standard designer wallplates (sold separately)
- Six product options in each box with three changeable faceplates and single pole or 3-way functionality when used with a 3-way switch
- Fluid slide movement allows fine adjustment of light level with minimal effort
- Captive wraparound slide bar remains securely attached

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-
1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

