



Representative

Catalog Number: CPC150
Product ID: 7TBA005370R0005
UPC Number: 61601310706
EAN Number: 05415022256208
Status: Active

Clamp, One-Piece Cable and Pipe, EMT and Rigid Conduit Trade Size 1-1/2 Inches, Cable Outer Diameter Range 1.690-1.980 Inches, Steel

- Heavy-duty 5/16 Inch hex bolt with multi-driver head, Robertson square, Phillips cross-recess and slot, provides a full range of installation options.
- Reconfigure wiring without complete disassembly. Remove cables easily without disturbing neighboring clamps.
- Parallel hook design keeps conduits and cable square with strut.
- Works with all depths of strut - 13/16 Inch to 3 1/4 Inch

Header

3D Model Available on Website

North American Specifications (UNSPSC)

| | |
|------------------------|---|
| UNSPSC | 31162906 Hose or pipe clamps |
| IGCC | 3064 Hose or pipe clamps |
| Brand Name | Superstrut |
| Type | Pipe Straps, Pipe Clamps & Hangers (Series 700) |
| Special Features | One-piece, heavy-duty construction ready to install right out of the box, no need to break apart and re-assemble, no screws or bolts to drop. |
| Application | Attaches a full range of EMT, Rigid conduit and cable to strut channels. |
| Standard | UL E160899 |
| Material | Steel |
| Size | 1-1/2 Inch |
| Finish | GoldGalv/Standard |
| Width | 1 Inch |
| Maximum Clamp Diameter | 1.980 Inches |
| Minimum Clamp Diameter | 1.690 Inches |
| Number Of Holes | 1 |
| Thickness | 0.112 Inches |

European Specifications (ETIM)

| | |
|-----------|--|
| ETIM | EC002470 Mounting clamp for cable protection tubes |
| Material | Steel |
| Rotatable | N |

Packaging

| | |
|---------------------------|-------------------|
| Outer Quantity | 50 |
| Outer Dimensions (inches) | 10.5x7.75x7.75 |
| Weight Uom | 18.5 lbs. per 100 |

Documents / Support Tools

| | |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
| Technical Data Sheet CA | Available on Website |

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com