

# GUEB Conduit Outlet Boxes with Multiple Hubs

## Explosionproof, Dust-Ignitionproof, Raintight

### NEC/CEC:

Class I, Division 1 and 2, Groups B♦, C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III

### Applications

- To provide access to conductors for pulling, splicing, maintenance and future changes/ upgrades.
- Allows connection of straight conduit runs, branch conduit runs and 90° bends.

### Features

- 7 to 13 hubs.
- O-ring gasket provided to assure NEMA 4 rating.
- Smooth hub bushings protect insulation when pulling conductors.
- Cast-in brackets on cover for use with breaker-bar tools for tightening/loosening.
- Tapered threaded hubs (NPT)
- Supplied with close-up plugs (see table).
- Furnished with internal ground screw.

### Standard Materials

- Copperfree (4/10 of 1% max.) aluminum



### Standard Finishes



- Body and cover: aluminum enamel

### NEC/CEC Certifications and Compliances

- UL Standard: 886
- UL Listed: E-85310
- CSA Standard: C22.2 No. 30
- CSA Certified: 009795
- Fed. Spec: A-A-50563
- NEMA 4, 7BCD, 9EFG

### Dimensions in Millimeters (Inches)



	Dimensions in Millimeters (Inches)					
	Trade Size (Inches)	No. of Hubs	No. of Plus Supplied	Cover Opening	Volume dm³ (in³)	Catalog Number
<b>GUEB7</b>						
	1/2	7	4	85.9 (3.38)	0.48 (29)	<b>GUEB7-50AN4</b>
	3/4	7	4	85.9 (3.38)	0.48 (29)	<b>GUEB7-75AN4</b>
	1	7	4	85.9 (3.38)	0.48 (29)	<b>GUEB7-100AN4</b>
<b>GUEB13</b>						
	1/2	13	5	85.9 (3.38)	0.48 (29)	<b>GUEB13-50AN4</b>
	3/4	13	5	85.9 (3.38)	0.48 (29)	<b>GUEB13-75AN4</b>

♦ In Class I, Division 1, Group B atmospheres, all conduit runs must have a sealing fitting (not supplied) field-installed adjacent to the enclosure.