



DELIVERY

Hubbell's innovative delivery solutions provide customers with the flexibility to create personalized solutions for the most demanding multi-service applications. Hubbell delivers a consistent, aesthetic and functional solution for floor, wall, furniture, surface or ceiling applications. Just add an audio/video, data, power or voice connector and the delivery solution maintains a perfect and complimentary look.





DELIVERY

DELIVERY

| | |
|---|-----|
| Hubbell SystemOne Recessed Concrete Floor Boxes..... | R3 |
| Hubbell SystemOne 2-Gang Recessed Floor Boxes and Covers | R7 |
| Hubbell SystemOne 4-Gang Recessed Floor Boxes and Covers | R8 |
| Hubbell SystemOne 6-Gang Recessed Floor Boxes and Covers | R9 |
| Hubbell SystemOne 2-, 4- and 6-Gang Plates and Accessories..... | R10 |
| Hubbell SystemOne 10-Gang Recessed Floor Boxes and Covers | R11 |
| Hubbell SystemOne 10-Gang Plates and Accessories..... | R12 |
| Hubbell SystemOne Floor Boxes | R13 |
| Hubbell SystemOne Sub-Plates | R15 |
| Recessed 7- and 11-Gang Concrete Floor Boxes | R16 |
| Furniture and Work Surface Connectivity Boxes | R17 |
| Large Capacity and Gangable AV Wall Boxes..... | R22 |
| Recessed AV In-Wall Enclosures and Ceiling Enclosures..... | R23 |
| Hubbell SystemOne Recessed Fire-Rated Poke-Throughs | R24 |
| Ordering SystemOne Recessed Fire-Rated Poke-Throughs | R25 |
| Hubbell SystemOne 8" Recessed Fire-Rated Poke-Throughs..... | R26 |
| Hubbell SystemOne 8" Recessed Sub-Plates | R27 |
| Hubbell SystemOne 6" Recessed Fire-Rated Poke-Throughs..... | R28 |
| Hubbell SystemOne 6" Recessed Sub-Plates | R29 |
| Hubbell SystemOne 8" Recessed Kits..... | R30 |
| Hubbell SystemOne 6" Recessed Kits..... | R31 |
| Hubbell SystemOne 4" One-Piece Poke-Throughs | R32 |
| Hubbell SystemOne 4" Through Floor Fittings..... | R34 |
| Hubbell SystemOne 4" Sub-Plates..... | R35 |
| Hubbell SystemOne 4" Configuration Chart | R36 |
| JLOAD® Multimedia Outlet..... | R37 |
| Aluminum Service Poles..... | R38 |
| Custom Service Pole Configurations | R39 |





The family of Hubbell SystemOne floorboxes has been expanded to provide industry leading flexibility while accommodating an extensive range of applications. Hubbell SystemOne is constructed to give customers the ability to create personal solutions for their most demanding, power, data and AV requirements.

Hubbell SystemOne Recessed Floor Box Applications



2-Gang Recessed

The Hubbell SystemOne 2-gang recessed concrete floor box offers eight styles, satisfying the requirements of almost any commercial building application. Rectangular or round covers, as well as furniture feed covers, are available in a variety of finishes to blend with any existing or new décor. A parallel-device layout reduces plug interference, maximizing functionality and performance.



4-Gang Recessed

Similar to the 2-gang Recessed Concrete Floor Box, Hubbell's SystemOne 4-gang recessed concrete floor box is available with rectangular or round covers. Ten different styles make it possible to meet the electrical requirements of most commercial projects—new construction or renovation. The parallel device layout maximizes functionality which can be limited when devices are mounted 90° from one another.



6-Gang Recessed

Increased power, data, and AV capacity is what the Hubbell SystemOne 6-gang recessed concrete floor box was designed to handle. Four styles allow the floor box to work within almost any commercial application to enhance connectivity. Rectangular and round covers are available in a variety of finishes that work with any aesthetic or finish.



10-Gang Recessed

With maximum capacity in a small footprint, the 10-gang box provides a uniform look with rectangular or round covers that are available in several finishes to complement existing décor. Electrical devices are mounted vertically and are mounted to the plate prior to securing it to the box. Two inch knockouts are designed into each box allowing for simple installation of AV cables with pre-connectorized heads and specific bend radius requirements.

Cover

- 180° cover opening
- Two large cable egress doors
- Listed to UL 514A and UL scrub water compliant
- Die cast aluminum cover construction
- Available in round, rectangular and furniture feed styles
- All covers are ADA compliant
- Post pour adjustment

Box

- 16 gauge galvanized sheet metal and cast iron construction
- Optional fusion-bonded, green epoxy paint for on-grade use
- 6" solid conductor ground pigtail in each gang
- 3" deep version accepts adapter (CFBHUB2) for 2" conduit
- Pre pour adjustment
- Meets UL 514A requirements and are UL scrub water compliant
- Patent pending, labor saving, easy mount device plates



CR version is coated with fusion-bonded epoxy paint to help prevent corrosion and intended for on-grade use.

The Family Look

Hubbell SystemOne recessed floor box line offers a common look regardless of capacity or installation. This simple concept ensures a consistent look throughout a building with rectangular or round covers. Round covers lend themselves to multi-story buildings, also using fire-rated poke-through devices.



A | Covers

All SystemOne covers are ADA compliant. The doors open to 180° for maximum access. Cables and plugs are protected by recessed connections.



C | Easy Mount Device Plates

The Easy Mount device plates allow for a device to be mounted to the plate and wired outside of the floor box. The device and plate assembly are then easily installed and secured with one stud that locates the plate and one screw to secure it.

This patent pending device fastening method maximizes efficiency while reducing install time and comes standard with all device plates for 2-, 4- and 6-gang boxes.



B | One Screw, Three Fasteners

Pre-wired duplex or Style Line® receptacles with 8" stranded leads are installed into plates to allow for even more labor savings.



DELIVERY

To assist with the floor box selection process, please have the following information available:

| Electrical Requirements | Application | Cover Style |
|--|--|----------------------|
| Power (each electrical device requires one gang) Data/AV (consult manufacturers' specification for size/volume requirements), number required Add up total number to determine needed capacity. If necessary capacity is not shown, round up to next size. Example: 9-gang rounds up to a 10-gang floor box | Above-grade (AG) On-grade (OG) Minimum concrete pour depth | Round Rectangular |

Once this information is gathered, start with Capacity below:

- 1 Capacity: select necessary box
- 2 Application: select the concrete pour depth and on-grade or above-grade application
- 3 Cover style: select round or rectangular cover
- 4 Locate intersecting point of all three categories and move to right to select the appropriate catalog number

| | | Application/Minimum Pour Depth 2 | | | | | | | | | | | | | | |
|--------------------------------------|--------|----------------------------------|-------------|-------|-------|-------------|-------|--------|----|--------|----|--------|----|-------------|-----------|------------|
| | | 2 1/2" | | 3" | | 3 1/4" | | 3 3/4" | | 5 1/2" | | 6 1/4" | | | | |
| | | AG | OG | AG | OG | AG | OG | AG | OG | AG | OG | AG | OG | | | |
| Electrical Requirements - Capacity 1 | 2-Gang | | • | | | | | | | | | | | | CFB2G25 | |
| | | | | • | | | | | | | | | | | | CFB2G25CR |
| | | | | | • | | | | | | | | | | | CFB2G30 |
| | | | | | | • | | | | | | | | | | CFB2G30CR |
| | | | | | | | • | | | | | | | | | CFB2G25R |
| | | | | | | | | • | | | | | | | | CFB2G25RCR |
| | | | | | | | | | • | | | | | | | CFB2G30R |
| | | | | | | | | | | • | | | | | | CFB2G30RCR |
| | 4-Gang | | • | | | | | | | | | | | | CFB4G25 | |
| | | | | • | | | | | | | | | | | CFB4G25CR | |
| | | | | | • | | | | | | | | | | CFB4G30 | |
| | | | | | | • | | | | | | | | | CFB4G30CR | |
| | | | | | | • | | | | | | | | CFB4G25R | | |
| | | | | | | | • | | | | | | | CFB4G25RCR | | |
| | | | | | | | | • | | | | | | CFB4G30R | | |
| | | | | | | | | | • | | | | | CFB4G30RCR | | |
| 6-Gang | | | | • | | | | | | | | | | CFB6G30 | | |
| | | | | | • | | | | | | | | | CFB6G30CR | | |
| | | | | | | | • | | | | | | | CFB6G30R | | |
| | | | | | | | | • | | | | | | CFB6G30RCR | | |
| 10-Gang | | | | | | | | | • | | | | | CFB10G55 | | |
| | | | | | | | | | | • | | | | CFB10G55CR | | |
| | | | | | | | | | | | • | | | CFB10G55R | | |
| | | | | | | | | | | | | • | | CFB10G55RCR | | |
| | | Rectangular | Rectangular | Round | Round | Rectangular | Round | | | | | | | | | |
| | | Cover Style 3 | | | | | | | | | | | | | | |

Select Appropriate Catalog No. 4

Benefits and Enhancements

Safety

- Flush flange available for tile, finished concrete or terrazzo
- Surface flange available for carpeted floors with 0.15in rise meets ADA requirements
- Hideaway egress doors fold under cover while in use
- 180° opening of main door

Functionality

- Cables and connections are protected by recessed functionality
- Open architecture sub-plate design
- Common door layout regardless of flange for harmonized look
- Meets UL 514A scrub water requirements with ScrubShield® technology
- Easy selection with common look for all floor types

Value

- Enhance building décor with numerous finishes
- Increase durability and longevity with cast aluminum covers

Online Resources

- BIM models, customer drawings and technical specifications are available on www.hubbell-wiring.com



Concrete Pour Pocket Cap

This factory-installed, field-removable pour pocket cap provides a pocket in the final floor to accept the covers intended for terrazzo, tile, or finished concrete floor. The cap may not be used for carpet, wood or engineered floors.



2" Conduit Ready

To meet expanding AV and data needs, the Hubbell SystemOne Recessed Floor Box line readily accepts 2" conduits with the use of a 2" threaded conduit hub. The offset design allows for less conduit lifting while threading and the hub mounting holes are asymmetrical for installation efficiency.



Corrosion Resistant Epoxy Paint

Intended for on-grade use, the CR version is coated with fusion-bonded epoxy paint to help prevent corrosion.





DELIVERY

Dimensions Inches (mm)

| Style | Rectangular Cover | | Round Cover | |
|---|---|--|--|--|
| | | | | |
| Box Type | | | | |
| Standard On-grade (Corrosion-Resistant) | CFB2G30 CFB2G30CR | CFB2G25 CFB2G25CR | CFB2G30R CFB2G30RCR | CFB2G25R CFB2G25RCR |
| Recommended Pour Depth | 3.50" (88.9) | 3.00" (76.2) | 3.75" (95.3) | 3.25" (82.6) |
| Minimum Depth of Pour | 3.00" (76.2) | 2.50" (63.5) | 3.75" (95.3) | 3.25" (82.6) |
| Adjustability | Fully | Fully | Fully | Fully |
| Cubic Inch (cm ³) Capacity per Gang | 35in ³ (570cm ³) | 30in ³ (490cm ³) | 35in ³ (570cm ³) | 30in ³ (490cm ³) |
| Dimensions – A | 2.97" (75.3) | 2.41" (61.1) | – | – |
| Dimensions – B | 6.62" (168.2) | 6.62" (168.2) | 7.32" (185.9) | 7.32" (185.9) |
| Dimensions – C | 13.79" (350.3) | 13.79" (350.3) | 13.79" (350.3) | 13.79" (350.3) |
| Dimensions – D | – | – | 6.37" (161.7) TYP. | 6.37" (161.7) TYP. |
| Dimensions – E | 3.50" (88.9) | 3.00" (76.2) | 3.75" (95.3) | 3.25" (82.6) |
| KO Trade Size: | Front & Back Sides Bottom | (1) 1/2", 3/4" (1) 3/4", 1", 1 1/4" hub plate (2) 1/2", 3/4", 1" (4) 1/2", 3/4", 1" | (1) 1/2", 3/4", 1" (2) 1/2", 3/4", 1" (4) 1/2", 3/4", 1" | (1) 1/2", 3/4", 1" (2) 1/2", 3/4", 1" (4) 1/2", 3/4", 1" |
| Cover Family | Rectangular | Rectangular | Round | Round |
| Concrete Cover Included | ✓ | ✓ | ✓ | ✓ |
| 2" Hub Compatible | ✓ | – | ✓ | – |



Rectangular Surface Cover
24GCCVRBK



Rectangular Furniture Feed
2GCFFCVRBRZ



Rectangular Flush
24GTCVRALU



Round Flush Surface
CFBS1R6CVRALU



Round Furniture Feed
CFBS1R6FFCVRBLK

Rectangular Covers

- Compatible with CFB2G25, CFB2G25RCR, CFB2G30 and CFB2G30CR
- Two large cable egress doors and access 180° opening
- Maximum static load of 800lb with 2x safety factor*
- Surface style typical applications: carpet, VCT
- Flush style typical applications: tile, finished concrete and terrazzo floors

| Finish | Cover dimensions 11 1/16" x 7 3/16" | | | Cover dimensions 10 1/16" x 6 3/16" | | |
|----------------------------|-------------------------------------|---------------------|----------------------------------|-------------------------------------|--------------------|----------------------------------|
| | Surface | Surface with Insert | Furniture Feed (1" and 2" Plugs) | Flush | Flush with Insert | Furniture Feed (1" and 2" Plugs) |
| Aluminum Powder Coated | 24GCCVRALU | 24GCCVRALUC | 2GCFFCVRALU | 24GTCVRALU | 24GTCVRALUC | 2GTFFCVRALU |
| Black Powder Coated | 24GCCVRBK | 24GCCVRBK | 2GCFFCVRBK | 24GTCVRBK | 24GTCVRBK | 2GTFFCVRBK |
| Brass Powder Coated | 24GCCVRBRS | 24GCCVRBRSC | 2GCFFCVRBRS | 24GTCVRBRS | 24GTCVRBRSC | 2GTFFCVRBRS |
| Bronze Powder Coated | 24GCCVRBRZ | 24GCCVRBRZC | 2GCFFCVRBRZ | 24GTCVRBRZ | 24GTCVRBRZC | 2GTFFCVRBRZ |
| Satin Nickel Powder Coated | 24GCCVRNK | 24GCCVRNKC | 2GCFFCVRNK | 24GTCVRNK | 24GTCVRNKC | 2GTFFCVRNK |

Round Covers

- Compatible with CFB2G25R, CFB2G25RCR, CFB2G30R and CFB2G30RCR
- Cover has a 7 1/2" outer diameter and two large cable egress doors and access 180° opening
- Maximum static load of 1000lb with 2x safety factor*

| Finish | Flush Surface | Furniture Feed (3/4" and 2" Plugs) |
|---------------------|----------------------|------------------------------------|
| Brushed Aluminum | CFBS1R6CVRALU | CFBS1R6FFCVRALU |
| Black Powder Coated | CFBS1R6CVRBLK | CFBS1R6FFCVRBLK |
| Brass Plated | CFBS1R6CVRBRS | CFBS1R6FFCVRBRS |
| Bronze Plated | CFBS1R6CVRBRZ | CFBS1R6FFCVRBRZ |
| Satin Nickel Plated | CFBS1R6CVRNKL | CFBS1R6FFCVRNKL |

*Load applied through a 3" (76mm) mandrel in center of the cover.

ScrubShield
Complies with UL514 A & C

Dimensions Inches (mm)

| Style | Rectangular Cover | | Round Cover | | Cast Iron | |
|---|--|--|--|--|--|--|
| | | | | | | |
| Box Type | | | | | | |
| Standard On-grade (Corrosion-Resistant) Cast Iron | CFB4G30 CFB4G30CR | CFB4G25 CFB4G25CR | CFB4G30R CFB4G30RCR | CFB4G25R CFB4G25RCR | - CFB4G30CI | - CFB4G30RCI |
| Recommended Pour Depth | 3.50" (88.9) | 3.00" (76.2) | 3.75" (95.3) | 3.25" (82.6) | 4.25" (108.0) | 4.00" (101.6) |
| Min. Depth of Pour | 3.00" (76.2) | 2.50" (63.5) | 3.75" (95.3) | 3.25" (82.6) | 3.75" (95.3) | 4.00" (101.6) |
| Adjustability | Fully | Fully | Fully | Fully | Fully | |
| Cubic Inch (cm ³) Capacity per Gang | 32.5in ³ (530cm ³) | 26.5in ³ (430cm ³) | 32.5in ³ (530cm ³) | 26.5in ³ (430cm ³) | 32.5in ³ (430cm ³) | |
| Dimensions – A | 3.46" (87.8) | 2.96" (75.1) | - | - | 3.20" (81.3) | - |
| Dimensions – B | 12.08" (306.8) | 12.08" (306.8) | 12.08" (306.8) | 12.08" (306.8) | 13.19" (335.1) | 13.19" (335.1) |
| Dimensions – C | 11.20" (284.5) | 11.20" (284.5) | 11.20" (284.5) | 11.20" (284.5) | 11.44" (290.5) | 11.44" (290.5) |
| Dimensions – D | - | - | 8.37" (212.5) TYP. | 8.37" (212.5) TYP. | - | 8.37" (212.5) TYP. |
| Dimensions – E | 3.50" (88.9) | 3.00" (76.2) | 3.75" (95.3) | 3.25" (82.6) | 3.68" (93.3) | 4.00" (101.6) |
| KO Trade Size: | Front & Back Sides Bottom | (2) 3/4", 1", 1 1/4" (2) 1/2", 3/4", 1" (4) 1/2", 3/4", 1" | (2) 1/2", 3/4", 1" (2) 1/2", 3/4", 1" (4) 1/2", 3/4", 1" | (2) 3/4", 1", 1 1/4" (2) 1/2", 3/4", 1" (4) 1/2", 3/4", 1" | (2) 1/2", 3/4", 1" (2) 1/2", 3/4", 1" (4) 1/2", 3/4", 1" | (4) 1 1/2" NPT Thread (4) 3/4" NPT Thread |
| Cover Family | Rectangular | Rectangular | Round | Round | Rectangular | Round |
| Concrete Cover Included | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| 2" Hub Compatible | ✓ | - | ✓ | - | - | - |



Rectangular Surface Cover
24GCCVRBRZ



Surface Cover with Insert
24GCCVRBKC



Rectangular Flush Cover
24GTCVRLU



Flush Cover with Insert
24GTCVRBRSC



Round Flush Surface Cover
CFBS1R8CVRNKL

Rectangular Covers

- Compatible with CFB4G25, CFB4G25RCR, CFB4G30 and CFB4G30CR
- Two large cable egress doors and access 180° opening
- Maximum static load of 800lb with 2x safety factor*
- Surface style typical applications: carpet, VCT
- Flush style typical applications: tile, finished concrete and terrazzo floors

| Finish | Cover dimensions 11 1/16" x 7 3/16" | | Cover dimensions 10 1/16" x 6 3/16" | |
|----------------------------|-------------------------------------|---------------------|-------------------------------------|--------------------|
| | Surface | Surface with Insert | Flush | Flush with Insert |
| Aluminum Powder Coated | 24GCCVRLU | 24GCCVRLUC | 24GTCVRLU | 24GTCVRLUC |
| Black Powder Coated | 24GCCVRBK | 24GCCVRBKC | 24GTCVRBK | 24GTCVRBKC |
| Brass Powder Coated | 24GCCVRBRS | 24GCCVRBRSC | 24GTCVRBRS | 24GTCVRBRSC |
| Bronze Powder Coated | 24GCCVRBRZ | 24GCCVRBRZC | 24GTCVRBRZ | 24GTCVRBRZC |
| Satin Nickel Powder Coated | 24GCCVRNK | 24GCCVRNKC | 24GTCVRNK | 24GTCVRNKC |

Round Covers

- Compatible with CFB4G25R, CFB4G25RCR, CFB4G30R, CFB4G30RCR and CFB4G30RCI
- Cover has a 9 1/2" outer diameter and two large cable egress doors and access 180° opening
- Maximum static load of 1000lb with 2x safety factor*

| Finish | Flush Surface |
|---------------------|----------------------|
| Brushed Aluminum | CFBS1R8CVRALU |
| Black Powder Coated | CFBS1R8CVRBLK |
| Brass Plated | CFBS1R8CVRBRS |
| Bronze Plated | CFBS1R8CVRBRZ |
| Satin Nickel Plated | CFBS1R8CVRNKL |

*Load applied through a 3" (76mm) mandrel in center of the cover.



DELIVERY

Dimensions Inches (mm)

| Style | Rectangular Cover | | Round Cover | |
|---|--|--|--|--|
| | | | | |
| Box Type | | | | |
| Standard On-grade (Corrosion-Resistant) | CFB6G30 | CFB6G30CR | CFB6G30R | CFB6G30RCR |
| Recommended Pour Depth | 3.50" (88.9) | 3.50" (88.9) | 3.75" (95.3) | 3.75" (95.3) |
| Min. Depth of Pour | 3.00" (76.2) | 3.00" (76.2) | 3.75" (95.3) | 3.75" (95.3) |
| Adjustability | Fully | Fully | Fully | Fully |
| Cubic Inch (cm ³) Capacity per Gang | (4) 33in ³ and (2) 89in ³ (435cm ³ /1450cm ³) | (4) 33in ³ and (2) 89in ³ (435cm ³ /1450cm ³) | (4) 33in ³ and (2) 89in ³ (435cm ³ /1450cm ³) | (4) 33in ³ and (2) 89in ³ (435cm ³ /1450cm ³) |
| Dimensions – A | 3.00" (76.2) | 3.00" (76.2) | – | – |
| Dimensions – B | 17.45" (443.2) | 17.45" (443.2) | 17.45" (443.2) | 17.45" (443.2) |
| Dimensions – C | 11.60" (294.5) | 11.60" (294.5) | 11.60" (294.5) | 11.60" (294.5) |
| Dimensions – D | – | – | 8.37" (212.5) TYP. | 8.37" (212.5) TYP. |
| Dimensions – E | 3.46" (87.8) | 3.46" (87.8) | 3.75" (95.3) | 3.75" (95.3) |
| KO Trade Size: | Front & Back (2) 3/4", 1", 1 1/4", 1 1/2" Sides (4) 3/4", 1", 1 1/4" hub plate Bottom (4) 3/4", 1", 1 1/4", 1 1/2" | (2) 3/4", 1", 1 1/4", 1 1/2" (4) 3/4", 1", 1 1/4" hub plate (4) 3/4", 1", 1 1/4", 1 1/2" | (2) 3/4", 1", 1 1/4", 1 1/2" (4) 3/4", 1", 1 1/4" hub plate (4) 3/4", 1", 1 1/4", 1 1/2" | (2) 3/4", 1", 1 1/4", 1 1/2" (4) 3/4", 1", 1 1/4" hub plate (4) 3/4", 1", 1 1/4", 1 1/2" |
| Cover Family | Rectangular | Rectangular | Round | Round |
| Concrete Cover Included | ✓ | ✓ | ✓ | ✓ |
| 2" Hub Compatible | ✓ | ✓ | ✓ | ✓ |



Rectangular Surface Cover
610GCCVRALU



Surface Cover with Insert
610GCCVRBKC



Rectangular Flush Cover
610GTCVRBRS



Flush Cover with Insert
610GTCVRBRZC



Round Surface Cover
CFBS1R8CVRBRS

Rectangular Covers

- Compatible with CFB6G30 and CFB6G30CR
- Two large cable egress doors and access 180° opening
- Maximum static load of 1500lb with 2x safety factor*
- Surface style typical applications: carpet, VCT
- Flush style typical applications: tile, finished concrete and terrazzo floors

| Finish | Cover dimensions 11 1/2" x 10" | | Cover dimensions 10 1/2" x 9" | |
|----------------------------|--------------------------------|---------------------|-------------------------------|---------------------|
| | Surface | Surface with Insert | Flush | Flush with Insert |
| Aluminum Powder Coated | 610GCCVRALU | 610GCCVRALUC | 610GTCVRALU | 610GTCVRALUC |
| Black Powder Coated | 610GCCVRBK | 610GCCVRBKC | 610GTCVRBK | 610GTCVRBKC |
| Brass Powder Coated | 610GCCVRBRS | 610GCCVRBRSC | 610GTCVRBRS | 610GTCVRBRSC |
| Bronze Powder Coated | 610GCCVRBRZ | 610GCCVRBRZC | 610GTCVRBRZ | 610GTCVRBRZC |
| Satin Nickel Powder Coated | 610GCCVRNK | 610GCCVRNK | 610GTCVRNK | 610GTCVRNK |

Round Covers

- Compatible with CFB6G30R and CFB6G30RCR
- Two large cable egress doors and access 180° opening
- Maximum static load of 1000lb with 2x safety factor*

| Finish | Surface |
|---------------------|----------------------|
| Brushed Aluminum | CFBS1R8CVRALU |
| Black Powder Coated | CFBS1R8CVRBLK |
| Brass Plated | CFBS1R8CVRBRS |
| Bronze Plated | CFBS1R8CVRBRZ |
| Satin Nickel Plated | CFBS1R8CVRNKL |

*Load applied through a 3" (76mm) mandrel in center of the cover.

ScrubShield
Complies with UL514 A & C

Plates for use in 2-, 4- and 6-Gang Floor Boxes

- UL 514A listed

| | | | | |
|-------------|---|---|---|--|
| Plate Style | (1) Decorator Opening | (1) Duplex Opening | (2) Extron® MAAP Openings | (2) Extron® Openings |
| Catalog No. | FBMPREC | FBMPDUP | FBMPMAAP | FBMPAAP |
| | | | | |
| Plate Style | (2) 1U Hubbell iSTATION Openings | (1) 1.5U Hubbell iSTATION Opening | (1) Simplex Opening 1.40" Diameter | (1) Twist-Lock® Opening 1.60" Diameter |
| Catalog No. | FBMP2IM | FBMP15IM | FBMP139 | FBMP156 |
| | | | | |
| Plate Style | 1-Gang Blank | Cable Feed Through with Bushing | (1) Opening for TracJack® or Series II® | (1) Opening with Hubbell ISF6 Frame for Keystone Jacks |
| Catalog No. | FBMPBNK | FBMPFT | FBMPTRAC | FBMP6KS |
| | | | | |
| | | | | |
| | 15A Pre-Wired Duplex Plate PWFBMPCR15GRY | 20A Pre-Wired Decorator TR PWFBMPDR20GRYTR | Threaded Zinc Hub CFBHUB2 | Knock-Out Plate CFBKOPATECR |
| | | | | Wire-Way CFB4WW |

Pre-Wired Device Plates

- Reduces wiring and installation times
- 8" stranded leads mounted to the face plate

| Description | Type | 15A | 20A |
|-----------------|------------------------------|--|--|
| Duplex, Gray | Standard Tamper-Resistant | PWFBMPCR15GRY PWFBMPCR15GRYTR | PWFBMPCR20GRY PWFBMPCR20GRYTR |
| Decorator, Gray | Standard Tamper-Resistant | PWFBMPDR15GRY PWFBMPDR15GRYTR | PWFBMPDR20GRY PWFBMPDR20GRYTR |

Accessories

| Description | | Catalog No. |
|---|--|---|
| 2" threaded zinc hub for use with CFB2G30, CFB4G30 and CFB6G30 series floor boxes; replaces CFBKOPATE and CFBKOPATECR | | CFBHUB2 |
| Replacement knock-out plate | Standard Epoxy Coating | CFBKOPATE CFBKOPATECR |
| Finished floor height adjustment ring (increase post pour adjustment); use with CFB51R6 cover series | 0 - 1/4" 1/4" - 1/2" 1/2" - 3/4" | CFB6RCVRR1 CFB6RCVRR2 CFB6RCVRR3 |
| Finished floor height adjustment ring (increase post pour adjustment); use with CFB51R8 cover series | 0 - 1/4" 1/4" - 1/2" 1/2" - 3/4" | CFB8RCVRR1 CFB8RCVRR2 CFB8RCVRR3 |
| Replacement low voltage divider | | CFB46DIV |

Extron is a registered trademark of Extron Electronics. Crestron is a registered trademark of Crestron Electronics, Inc. FSR is a registered trademark of FSR Inc. TracJack, Series II and Ortronics are registered trademarks of Ortronics/Legrand.

Complies with UL514 A & C



DELIVERY

Dimensions Inches (mm)

| Style | Rectangular Cover | | Round Cover | |
|---|---|---|---|---|
| | | | | |
| Box Type | | | | |
| Standard On-grade | CFB10G55 | – CFB10G55CR | CFB10G55R | – CFB10G55RCR |
| Recommended Pour Depth | 6.00" (152.4) | 6.00" (152.4) | 6.27" (159.3) | 6.27" (159.3) |
| Min. Depth of Pour | 5.52" (140.2) | 5.52" (140.2) | 6.27" (159.3) | 6.27" (159.3) |
| Adjustability | Fully | Fully | Fully | Fully |
| Cubic Inch (cm ³) Capacity per Gang | 33in ³ /89in ³ (435cm ³ /1450cm ³) | 33in ³ /89in ³ (435cm ³ /1450cm ³) | 33in ³ /89in ³ (435cm ³ /1450cm ³) | 33in ³ /89in ³ (435cm ³ /1450cm ³) |
| Dimensions – A | 5.52" (140.2) | 5.52" (140.2) | – | – |
| Dimensions – B | 10.96" (278.4) | 10.96" (278.4) | 10.96" (278.4) | 10.96" (278.4) |
| Dimensions – C | 10.96" (278.4) | 10.96" (278.4) | 10.96" (278.4) | 10.96" (278.4) |
| Dimensions – D | – | – | 8.37" (212.5) TYP. | 8.37" (212.5) TYP. |
| Dimensions – E | 6.00" (152.4) | 6.00" (152.4) | 6.25" (158.8) | 6.25" (158.8) |
| KO Trade Size: | Front & Back Sides Bottom | | | |
| | (1) 1/2", 3/4" (1) 3/4", 1", 1 1/4", 1 1/2" (1) 1", 1 1/4", 1 1/2", 2 (2) 3/4", 1", 1 1/4", 1 1/2" (2) 1/2", 3/4" (4) 1/2", 3/4", 1", 1 1/4" | (1) 1/2", 3/4" (1) 3/4", 1", 1 1/4", 1 1/2" (1) 1", 1 1/4", 1 1/2", 2 (2) 3/4", 1", 1 1/4", 1 1/2" (2) 1/2", 3/4" (4) 1/2", 3/4", 1", 1 1/4" | (1) 1/2", 3/4" (1) 3/4", 1", 1 1/4", 1 1/2" (1) 1", 1 1/4", 1 1/2", 2 (2) 3/4", 1", 1 1/4", 1 1/2" (2) 1/2", 3/4" (4) 1/2", 3/4", 1", 1 1/4" | (1) 1/2", 3/4" (1) 3/4", 1", 1 1/4", 1 1/2" (1) 1", 1 1/4", 1 1/2", 2 (2) 3/4", 1", 1 1/4", 1 1/2" (2) 1/2", 3/4" (4) 1/2", 3/4", 1", 1 1/4" |
| Cover Family | Rectangular | Rectangular | Round | Round |
| Concrete Cover Included | ✓ | ✓ | ✓ | ✓ |
| 2" Hub Compatible | – | – | – | – |



Rectangular Surface Cover
610GCCVBRBS



Surface Cover with Insert
610GCCVRALUC



Rectangular Flush Cover
610GTCVBRNK



Flush Cover with Insert
610GTCVRBKC



Round Surface Cover
CFBS1R8CVRBRZ

Rectangular Covers

- Compatible with CFB10G55 and CFB10G55CR
- Two large cable egress doors and access 180° opening
- Maximum static load of 1500lb with 2x safety factor*
- Surface style typical applications: carpet, VCT
- Flush style typical applications: tile, finished concrete and terrazzo floors

| Finish | Cover dimensions 11 1/2" x 10" | | Cover dimensions 10 1/2" x 9" | |
|----------------------------|--------------------------------|---------------------|-------------------------------|---------------------|
| | Surface | Surface with Insert | Flush | Flush with Insert |
| Aluminum Powder Coated | 610GCCVRALU | 610GCCVRALUC | 610GTCVRALU | 610GTCVRALUC |
| Black Powder Coated | 610GCCVRBK | 610GCCVRBKC | 610GTCVRBK | 610GTCVRBKC |
| Brass Powder Coated | 610GCCVBRBS | 610GCCVBRBSC | 610GTCVBRBS | 610GTCVBRBSC |
| Bronze Powder Coated | 610GCCVBRZ | 610GCCVBRZC | 610GTCVBRZ | 610GTCVBRZC |
| Satin Nickel Powder Coated | 610GCCVRNK | 610GCCVRNK | 610GTCVRNK | 610GTCVRNK |

Round Covers

- Compatible with CFB10G55R and CFB10G55RCR
- Two large cable egress doors and access 180° opening
- Maximum static load of 1000lb with 2x safety factor*

| Finish | Surface |
|---------------------|----------------------|
| Brushed Aluminum | CFBS1R8CVRALU |
| Black Powder Coated | CFBS1R8CVRBLK |
| Brass Plated | CFBS1R8CVRBRS |
| Bronze Plated | CFBS1R8CVRBRZ |
| Satin Nickel Plated | CFBS1R8CVRNKL |

*Load applied through a 3" (76mm) mandrel in center of the cover.

ScrubShield
Complies with UL514 A & C

CFB10 Series Plates

| | | | | | |
|-------------|-----------------------|--------------------|------------------|--|--|
| Plate Style | (1) Decorator Opening | (1) Duplex Opening | Blank | Decorator Opening Plate Including Hubbell ISF6GY | (2) Openings to Accommodate (6) Ortronics TrackJack® |
| Catalog No. | FB10MPREC | FB10MPDUP | FB10MPBNK | FB10MPKEY | FB10MPTRAC |




| | | | | | |
|-------------|-----------------|--------------------------|-------------------------|-------------------------------------|------------------------------------|
| Plate Style | (2) Decorator | (4) Extron® MAAP Modules | (4) Extron® AAP Modules | For (6) 1U Hubbell iSTATION Modules | Replacement Spacer Around Wire-Way |
| Catalog No. | FB10MP2A | FB10MPMAAP | FB10MPAAP | FB10MP2B | FB10MPX |



| | | | | |
|-------------|--|--|--|---|
| Plate Style | (1) Twist-Lock® Opening 1.60 in. Dia. (Uses 2 Gangs) | (1) Simplex Opening 1.40 in. Dia. (Uses 2 Gangs) | (2) Twist-Lock® Opening 1.60 in. Dia. (Uses 3 Gangs) | (2) Simplex Opening 1.40" Dia. (Uses 3 Gangs) |
| Catalog No. | FB10TLA | FB10TLX | FB10TLB | FB10TLY |



| | | | | |
|-------------|--|--|--|---|
| Plate Style | (3) Twist-Lock® Opening 1.60 in. Dia. (Uses 5 Gangs) | (3) Simplex Opening 1.40 in. Dia. (Uses 5 Gangs) | (2) 2-Gang. Meets NEMA Spacing. Ideal for Crestron® DM –TX Product and Power | (4) Single Service Openings Utilizing NEMA Wallplate (Uses 5 Gangs) |
| Catalog No. | FB10TLC | FB10TLZ | CFB10NEMA | CFB10NEMA4G |



20A Pre-Wired Duplex Plate
PWFBMPCR20GRY



15A Pre-Wired Decorator Plate
PWFBMPDR15GRYTR



Adjustment Rings
CFB8RCVRR1, CFB8RCVRR2, CFB8RCVRR3

Pre-Wired Device Plates

- Reduces wiring and installation times
- 8" stranded leads mounted to the face plate

| Description | Type | 15A | 20A |
|-----------------|------------------------------|--|--|
| Duplex, Gray | Standard Tamper-Resistant | PWFBMPCR15GRY PWFBMPCR15GRYTR | PWFBMPCR20GRY PWFBMPCR20GRYTR |
| Decorator, Gray | Standard Tamper-Resistant | PWFBMPDR15GRY PWFBMPDR15GRYTR | PWFBMPDR20GRY PWFBMPDR20GRYTR |

Accessories

| Description | Catalog No. |
|--|-------------------------------|
| Replacement wire-way, used to pass wires from one compartment to the other, for use in CFB10G55/CR rectangular boxes | CFB10WW |
| Replacement low voltage divider | CFB10DIV |
| Finished floor height adjustment ring (increase post pour adjustment); use with CFBS1R8CVR cover series | 0 – 1/4" CFB8RCVRR1 |
| | 1/4" – 1/2" CFB8RCVRR2 |
| | 1/2" – 3/4" CFB8RCVRR3 |

Extron is a registered trademark of Extron Electronics. Crestron is a registered trademark of Crestron Electronics, Inc. FSR is a registered trademark of FSR Inc. TracJack, Series II and Ortronics are registered trademarks of Ortronics/Legrand.

ScrubShield
Complies with UL514 A & C



Non-Metallic

Non-corrosive plastic parallel conduit hubs reduce labor and material cost, facilitating easier wire pull.

Specifications



- Minimum pour depth 3" (S1PFB) or 3½" (S1CFB, S1SFB, S1SFBAY)
- Standard 1" power entry
- Approved for use in City of Chicago




Cast Iron

Corrosion resistant for on-grade applications.



Stamped Steel

Economical and light weight for above-grade applications.



Stamped Steel AV

Accommodates high-capacity multimedia applications including an oversized 1½" N.P.T. threaded data hub.



Common Theme

Same covers for both floor boxes and fire-rated poke-throughs.



Universal Wiring

Hubbell 4x4: four 20 Amp, 125 Volt receptacles and four keystone openings for category rated applications.



Low Profile

Flange meets ADA requirements; hinged doors open 180 degrees.

Floor Box Dimensions

Inches (mm)

| | Cast Iron | Steel | Steel AV | Non-Metallic |
|--|--|--|--|--|
| | | | | |
| | S1CFB* | S1SFB* | S1SFBAV* | S1PFB** |
| Min. Depth of Pour | 3.50" (89) | 3.50" (89) | 3.50" (89) | 3.00" (76) |
| Adjustability | Fully | Fully | Fully | Fully |
| Cubic Inch (cm ³) Capacity | 156.0 in ³ (2556 cm ³) | 175.7 in ³ (2879 cm ³) | 177.5 in ³ (2910 cm ³) | 100 in ³ (1639 cm ³) |
| Dimensions – A | 3.00" (76) | 3.00" (76) | 3.00" (76) | 6.00" (152) |
| Dimensions – B | 7.26" (184) | 7.50" (191) | 7.50" (191) | 5.58" (142) |
| Dimensions – C | 7.45" (189) | 7.38" (187) | 7.38" (187) | 8.76" (222) |
| Dimensions – D (Inside Diameter) | 5.00" (127) | 5.00" (127) | 5.00" (127) | 5.00" (127) |
| Power Entries | 1" N.P.T. Access Holes | ¾", 1" Concentric KO | ¾", 1" Concentric KO | 1" Conduit Hub |
| Data Entries | 1½" N.P.T. Access Holes | ¾", 1", 1¼" Concentric KO | 1½" Threaded Hub (Included) | 1½" Conduit Hub |
| Concrete Cover Included | ✓ | ✓ | ✓ | ✓ |
| Closure Plugs Included | ✓ | | ✓ | ✓ |
| Reducers | | | | ✓** |
| Accepts Hubbell SystemOne Universal Cover | ✓ | ✓ | ✓ | ✓ |
| Cover Mounting Clips Included | ✓ | ✓ | ✓ | ✓ |
| Non-Metallic Low Voltage Divider Included (S1DIV1) | ✓ | ✓ | ✓ | ✓ |


*S1CFB, S1SFB and S1SFBAV are approved for use in the City of Chicago.

**S1PFB reducers included: Qty (2) combo plug/reducers 1" to ¾"; Qty (2) reducers 1½" to 1"; Qty (2) reducers 1½" to ¾"; Qty (2) plugs 1½"

Note: UL File Number E92074; CSA File Number LR18416



Carpet Cover
S1CFCAL



Tile Cover
S1TFCAL



Abandonment Plate
S1AP4BL



Threaded Hub
S1AVHUB15



Mounting Clips
S1FBCLIP5PK

Hubbell SystemOne Covers

| Color | Carpet Catalog Number | Tile Catalog Number |
|-----------------|-----------------------|---------------------|
| Aluminum Finish | S1CFCAL | S1TFCAL |
| Brass Finish | S1FCBRS | S1TFCBRS |
| Black | S1FCBBL | S1TFCBL |
| Gray | S1FCGGY | S1TFCGY |
| Ivory | S1FCFI | S1TFCI |

Floor Box Accessories

| Description | Catalog No. |
|--|--------------------|
| Abandonment plate, black | S1AP4BL |
| Abandonment plate, gray | S1AP4GY |
| Replacement side by side divider | S1DIV1 |
| 1½" threaded hub | S1AVHUB15* |
| Replacement universal cover mounting clips | S1FBCLIP5PK |

















*For use with S1SFBAV only. Permits feed-through applications. S1SFBAV floor box includes one (1) threaded hub.



Complies with UL514 A & C



DELIVERY

| Description | Catalog No. | Description | Catalog No. | Description | Catalog No. |
|---|---|---|--|---|---|
| Style Line® Decorator/GFCI (2) Style Line decorator openings for power and/or datacom applications ③ Non-Metallic ③.5 Metal |  S1SP | Duplex/Duplex (2) duplex openings for power and/or datacom applications ③ Non-Metallic ③.5 Metal |  S1SPDU | Duplex/Style Line® Decorator (1) duplex and (1) Style Line decorator opening for power and/or datacom applications ③ Non-Metallic ③.5 Metal |  S1SPDUSL |
| Hubbell 4 X 4 (4) 20A, 125V receptacles, (4) keystone openings for Hubbell jacks or flush AV connectors; power can be wired as single or two circuit with isolated ground capability Provided with 15' wire leads Provided with 30' wire leads ④ |  S1SP4X4 S1SP4X415 S1SP4X430 | Carpet Furniture Feed Cover/Flange* (1) 3/4" and (1) 1 1/2" N.P.T. access holes for power and/or datacom applications; universal cover not required; includes carpet flange Aluminum Fin. Brass Fin. Black Gray ③ Non-Metallic ③.5 Metal |  S1SPFFAL S1SPFFBRS S1SPFFBL S1SPFFGY | Tile Furniture Feed Cover/Flange* (1) 3/4" and (1) 1 1/2" N.P.T. access holes for power and/or datacom applications; universal cover not required; includes tile flange Aluminum Fin. Brass Fin. Black Gray ③ Non-Metallic ③.5 Metal |  S1SPFFTAL S1SPFFTBR S1SPFFTBL S1SPFFTGY |
| Single Receptacle + Data Opening for 20 or 30A Twist-Lock® receptacle (1.56" OD) and (2) keystone openings for Hubbell jacks or flush AV connectors ④ |  S1SPTL | Hubbell DataCom + Power (1) 20A, 125V receptacle and 3 unit recessed Hubbell iSTATION opening for data, voice and AV applications ⑤ |  S1SP3IM | Hubbell DataCom + Duplex (1) duplex opening, (2) flush keystone openings and 1.5 unit recessed Hubbell iSTATION opening for data, voice and AV applications ⑤ |  S1SPDU2IM |
| Hubbell DataCom + Style Line® Decorator (1) Style Line decorator opening, (2) flush keystone openings and 1.5 unit recessed Hubbell iSTATION opening for data, voice and AV applications ⑤ |  S1SPSL2IM | Hubbell DataCom 1 unit flush Hubbell iSTATION opening and 3 unit recessed Hubbell iSTATION opening for data, voice and AV applications ③.5 |  S1SP4IM | Active Multimedia + Power Single 20A, 125V receptacle, (2) flush keystone openings, (1) rectangular Style Line® decorator opening to accommodate active multimedia modules or low voltage outlet frames ⑤ |  S1SPAMM20 |
| Extron® or FSR + Power (1) 20A, 125V receptacle, recessed opening for (3) single Extron® MAAP series adapter plates or FSR IPS plates ④ |  S1SPEXT1 | Extron® or FSR + Power (1) 20A, 125V receptacle, recessed opening for (1) single Extron MAAP and (2) single AAP series adapter plates or FSR IPS plates ④ |  S1SPEXT2 | Extron® or FSR Single-Service Recessed opening for (2) single Extron MAAP and (2) single AAP series adapter plates or FSR IPS plates ④.5 |  S1SPEXT3 |
| Extron® AAP + Power (1) 20A, 125V receptacle, (2) flush keystone and recessed openings for (2) single Extron AAP Series adapter plates ④ |  S1SPEXT4 | | | | |

⊖ Signifies minimum depth of concrete pour in inches for Metal Floor Boxes (S1CFB, S1SFB and S1SFBAV) and Non-Metallic Floor Box (S1PFB).
*Furnished with two screw-in flexible metal conduit connectors.



Conduit Plugs
S1FP15BL, S1FP34BL

Sub-Plate Accessories

Replacement threaded conduit plugs

| Description | Color | | | |
|-------------|-----------------|------------------|-----------------|-----------------|
| | Aluminum Finish | Brass Finish | Black | Gray |
| 1 1/2" plug | S1FP15AL | S1FP15BRS | S1FP15BL | S1FP15GY |
| 3/4" plug | S1FP34AL | S1FP34BRS | S1FP34BL | S1FP34GY |

See V12 for color chart. Used with S1SPFFxx and S1SPFFTxx only. Sub-plate is supplied with plugs.


Extron is a registered trademark of Extron Electronics.

ScrubShield®
Complies with UL514 A & C

Concrete Floor Box Dimensions

Inches (mm)

Style



CFB7G Series
7-Gang





CFB11G Series
11-Gang



| | CFB7G4 | CFB7G6 | CFB11G4 | CFB11G6 |
|--------------------------------|----------------------------|----------------------------|------------------------------|------------------------------|
| Min. Depth of Pour | 4.08" (104) | 6.08" (154) | 4.08" (104) | 6.08" (154) |
| Adjustability | Before Pour | Before Pour | Before Pour | Before Pour |
| Dimensions: | | | | |
| A | 4.08" (104) | 6.08" (154) | 4.08" (104) | 6.08" (154) |
| B | 10.0" (254) | 10.0" (254) | 13.5" (343) | 13.5" (343) |
| C | 12.2" (310) | 12.2" (310) | 12.2" (310) | 12.2" (310) |
| Trade Size Knockouts: | | (4) x 1", 1¼", 1½" Con- | | (4) x 1", 1¼", 1½" Con- |
| Sidewalls | (4) x 1", 1¼" Concentric | centric | (4) x 1", 1¼" Concentric | centric |
| Back | (3) x 1", 1¼", 1½" Concen- | (3) x 1", 1¼", 1½" Concen- | (2) ¾", 1" Concentric; | (2) ¾", 1" Concentric; |
| | tric; (1) x 2" | tric; (1) 2" | (4) 1", 1¼", 1½" Concentric, | (4) 1", 1¼", 1½" Concentric, |
| | | | (1) 2" | (1) 2" |
| Bottom | (4) x 1", 1¼", 1½" Con- | (4) x 1", 1¼", 1½" Con- | (5) 1", 1¼", 1½" Concentric; | (5) 1", 1¼", 1½" Concentric; |
| | centric | centric | (2) ¾", 1" Concentric | (2) ¾", 1" Concentric |
| Side View: | X: 1.01" | X: 2.37" | X: 1.02" | X: 2.37" |
| Depth Behind | Y: 2.41" | Y: 3.77" | Y: 2.42" | Y: 3.81" |
| Mounting | Z: 3.51" | Z: 3.65" | Z: 3.50" | Z: 3.72" |
| Plate | | | | |
| Accepts Industry Standard Size | (1) 1-Gang | (1) 1-Gang | (2) 1-Gang | (2) 1-Gang |
| Wallplates (Sold Separately) | (1) 2-Gang | (1) 2-Gang | (1) 3-Gang | (1) 3-Gang |
| | (1) 4-Gang | (1) 4-Gang | (1) 6-Gang | (1) 6-Gang |


Interior Configuration



Note: UL File Number E31999; CSA File Number LR18416



On-Grade Barrier
CFBOGPAN4



7-Gang Cover, Brass
CFB7CVRBRS



11-Gang Cover, Aluminum
CFB11CVRALU

On-Grade Barrier

Intended for use on installations at grade level; installed prior to the concrete pour and provides a barrier between the soil; **CFBOGPAN4** on-grade barrier comes with leveling feet and anchor points; pour pan dimensions are 15.75in²/4" depth

Floor Box Covers

| | CFB7G Series | | CFB11G Series | |
|-------------------------|--------------|----------|---------------|----------|
| Flange and cover; | ¼" Edging | Brass | ¼" Edging | Brass |
| Beveled edge for carpet | | Aluminum | | Aluminum |
| | | | | |
| Flange and cover; | ½" Edging | Brass | ¼" Edging | Brass |
| Square edge for tile | | Aluminum | | Aluminum |

Note: Covers provide a recess for floor covering insert.



Complies with UL514 A & C




Square Flush Mount Box
HBLSHA2



Surface Mount Box
HBLCON2



Under Desk Mount Box
HBLMAR2



Screw Type Face Plates
HBLST302SBK
HBL317SBK

DELIVERY

Square Flush Mount Boxes

| Description | Finish | Dimensions | Catalog No. |
|--|-----------------|------------------------|-------------------|
| 2-gang square flush mount box with cover | Black | 6.5"L x 6.5"W x 3.75"H | HBLSHA2 |
| 2-gang square flush mount box with cover | Stainless Steel | 6.5"L x 6.5"W x 3.75"H | HBLSHA2BSS |

Rectangular Flush Mount Boxes

| Description | Finish | Dimensions | Catalog No. |
|---|-----------------|--------------------------|-------------------|
| 2-gang rectangular flush mount with cover | Black | 10.75"L x 4.06"W x 3.5"H | HBLPHA2 |
| 2-gang rectangular flush mount with cover | Stainless Steel | 10.75"L x 4.06"W x 3.5"H | HBLPHA2BSS |
| 4-gang rectangular flush mount with cover | Black | 10.75"L x 6.5"W x 3.5"H | HBLPHA4 |
| 4-gang rectangular flush mount with cover | Stainless Steel | 10.75"L x 6.5"W x 3.5"H | HBLPHA4BSS |

Surface Mount Boxes

| Description | Finish | Dimensions | Catalog No. |
|--------------------------|--------|--------------------------|----------------|
| 2-gang surface mount box | Black | 4.19"L x 4.81"W x 2.44"H | HBLCON2 |
| 3-gang surface mount box | Black | 6.19"L x 4.81"W x 2.44"H | HBLCON3 |

Recessed Mount Boxes

| Description | Finish | Dimensions | Catalog No. |
|-----------------------|--------|---------------------------|----------------|
| 4-gang recessed mount | Black | 10.25"L x 7.0"W x 5.88"H | HBLMIR2 |
| 8-gang recessed mount | Black | 31.0"L x 10.25"W x 5.88"H | HBLMIR4 |

Under Desk Mount Boxes

| Description | Finish | Dimensions | Catalog No. |
|-------------------------|--------|--------------------------|----------------|
| 2-gang under desk mount | Black | 9.19"L x 3.0"W x 2.88"H | HBLMAR2 |
| 3-gang under desk mount | Black | 13.69"L x 3.0"W x 2.88"H | HBLMAR3 |

Screw Type Face Plates

| Description | Catalog No. |
|-------------------------------|--------------------|
| Duplex | HBLST302SBK |
| Style Line® decorator opening | HBLDE301SBK |
| Blank | HBLBL300SBK |
| 3-unit Hubbell iSTATION | HBLIMFSBK* |
| 6-port | HBL317SBK |

*See Section F for module options.



Low Voltage Table Top Box
TTBXLRBK



Pre-Wired Dual-Service Box
TTBDS1BK



Low Voltage Only

| Description | Dimensions | Black Anodized Aluminum | Clear Anodized Aluminum | Solid Brass |
|--|----------------|-------------------------|-------------------------|-----------------|
| Table top box; 2" diam. hole; (1) keystone opening; keystone modules sold separately | 2.19" Diameter | TTBKSBK | TTBKSAL | TTBKSBR |
| Table top box; 2" diam. hole; (1) XLR microphone jack installed | 2.19" Diameter | TTBXLRBK | TTBXLRAL | TTBXLRBR |

Pre-Wired Dual-Service

| Description | Dimensions | Black Anodized Aluminum | Clear Anodized Aluminum | Solid Brass |
|---|----------------|-------------------------|-------------------------|-----------------|
| Table top box; 3.5" diam. hole; (1) pre-wired 15A outlet with 9' power supply cord; (1) 3.5mm screw terminal audio jack; (1) 15-pin gender changer F/F; (2) keystone openings; keystone modules sold separately | 3.88" Diameter | TTBDS1BK | TTBDS1AL | TTBDS1BR |
| Table top box; 3.5" diam. hole; (2) pre-wired 15A outlets with 9' power supply cord; (2) keystone openings; keystone modules sold separately | 3.88" Diameter | TTBDS2BK | TTBDS2AL | TTBDS2BR |

See Section F for AV and datacom options.



Square Lift-Up Box
WSBC21UBK



Square Mini Lift-Up Box
WSBA11BK



Work Surface Mount Box
WSBD21UBK



Recessed Concealed Services Box
WSBB23UBK

Square Lift-Up Style

| Description | Finish | Dimensions | Catalog No. |
|--|-----------------|--------------------------|--------------------------------------|
| (2) pre-wired 15A outlets with 6' power supply cord; 1-unit opening for Hubbell iSTATION modules; unit rotates up when in use and down to conceal services when not in use | Black Silver | 5.75"L x 5.39"W x 4.25"H | WSBC21UBK WSBC21USV |

Square Mini Lift-Up Style

| Description | Finish | Dimensions | Catalog No. |
|---|----------------------------------|------------------------|-------------------------------------|
| (1) pre-wired 15A outlet with 9' power supply cord; (1) RJ-45 jack installed with 6' patch cord | Black Brushed Stainless Steel | 3.7"L x 3.7"W x 2.93"H | WSBA11BK WSBA11BSS |
| (2) pre-wired 15A outlets with 9' power supply cord (power only) | Black Brushed Stainless Steel | 3.7"L x 3.7"W x 2.93"H | WSBA2BK WSBA2BSS |

Under Table Mount

| Description | Finish | Dimensions | Catalog No. |
|--|--------|--------------------------|------------------|
| (2) pre-wired 15A outlets with 9' power supply cord; (1) low voltage plate included with 1-unit opening for Hubbell iSTATION modules | Black | 6.50"L x 1.75"W x 2.25"H | WSBD21UBK |

Work Surface Mount

| Description | Finish | Dimensions | Catalog No. |
|--|-----------------|--------------------------|--------------------------------------|
| (1) pre-wired 15A outlet with 9' power supply cord; (1) Hubbell keystone opening | Black Silver | 3.57"L x 2.19"W x 2.50"H | WSBE11BK WSBE11SV |
| (2) pre-wired 15A outlets with 9' power supply cord; (2) Hubbell keystone openings | Black Silver | 6.32"L x 2.19"W x 2.50"H | WSBE22BK WSBE22SV |
| (3) pre-wired 15A outlets with 9' power supply cord; (1) low voltage plate included with 1-unit opening for Hubbell iSTATION modules | Black Silver | 8.25"L x 2.19"W x 2.50"H | WSBE31UBK WSBE31USV |
| Mounting bracket with thumb screw (optional) | – | – | WSBECLAMP |

Recessed Concealed Services

| Description | Finish | Dimensions | Catalog No. |
|--|---|--------------------------|--|
| (2) pre-wired 15A outlets with 6' power supply cord; (1) low voltage plate included with 1-unit opening for Hubbell iSTATION modules; (2) additional 1-unit openings provided in base of unit | Black Brushed Anod. Alum. Brushed Stainless Steel | 8.98"L x 5.47"W x 2.97"H | WSBB23UBK WSBB23UBAL WSBB23UBSS |
| (4) pre-wired 15A outlets with 6' power supply cord; (2) 1-unit openings for Hubbell iSTATION modules provided in base of unit | Black Brushed Anod. Alum. Brushed Stainless Steel | 8.98"L x 5.47"W x 2.97"H | WSBB43UBK WSBB43UBAL WSBB43UBSS |
| Empty enclosure with (1) duplex opening, (1) low voltage plate included with 1-unit opening for Hubbell iSTATION modules; (2) additional 1-unit openings provided in base of unit; intended for field wiring | Black | 8.98"L x 5.47"W x 2.97"H | WSBBHWBK |



Grommet Style Furniture Box
WSBF22BK



Grommet Cover with Dust Shield
WSBFGROMSV



Recessed Concealed Box (Shown with Cover Open)
WSBG43USV



Pop-Up Style with Trim Ring
WSBH42U, WSBHTRBK

DELIVERY

Grommet Style

| Description | Finish | Dimensions | Catalog No. |
|--|-------------------------|--------------------------|--------------------|
| (2) pre-wired 15A outlets with 6' power supply cord; (2) Hubbell Keystone openings | Black | 8.62"L x 3.0"W x 2.25"H | WSBF22BK |
| | Silver | 8.62"L x 3.0"W x 2.25"H | WSBF22SV |
| Flush grommet cover with dust shield | Black | 5.68"L x 3.39"W x 0.96"H | WSBFGROMBK |
| | Silver | 5.68"L x 3.39"W x 0.96"H | WSBFGROMSV |
| | Brushed Aluminum | 5.68"L x 3.39"W x 0.96"H | WSBFGROMBAL |
| | Brushed Stainless Steel | 5.68"L x 3.39"W x 0.96"H | WSBFGROMBSS |

Pre-Wired Work Surface Elite Series

Recessed Concealed Services

| Description | Finish | Dimensions | Catalog No. |
|---|----------------|-------------------------|-------------------|
| (4) pre-wired 15A outlets with 6' power supply cord; (3) low voltage plates included with 1-unit opening for Hubbell iSTATION modules | Black | 15.0"L x 9.0"W x 6.25"H | WSBG43UBK |
| | Silver | 15.0"L x 9.0"W x 6.25"H | WSBG43USV |
| | Clear Anodized | 15.0"L x 9.0"W x 6.25"H | WSBG43UBAL |
| | Black Anodized | 15.0"L x 9.0"W x 6.25"H | WSBG43UBBA |

Pop-Up Style*

| | | | |
|--|-------------------------|--------------------------|------------------|
| Base unit with (4) pre-wired 15A outlets with 6' power supply cord; (2) low voltage plates included with 1-unit opening for Hubbell iSTATION modules | – | 8.90"L x 8.90"W x 13.9"H | WSBH42U* |
| Trim ring and decorative round top | Black | 5.25" Diameter | WSBHTRBK |
| Trim ring and decorative round top | Brushed Stainless Steel | 5.25" Diameter | WSBHTRBSS |

*WSBH42U is CSA Certified only.

Replacement Low Voltage Data Plates

| | | | |
|---|-------|-----------------|------------------|
| Non-metallic low voltage plate, blank | Black | 3.18"L x 1.88"W | WSBPLATE1 |
| Non-metallic low voltage plate, 1-unit Hubbell iSTATION cut-out | Black | 3.18"L x 1.88"W | WSBPLATE2 |

Pre-Wired 2X2 USB Work Surface Pop-Up Box

Hubbell's UL listed 2X2 USB Work Surface Pop-Up Box is ideal for work surfaces, such as desks, which require power for a computer and USB charging for smart devices. Developed in coordination with the hotel industry, the Hubbell Pop-Up Box utilizes a pneumatic spring for providing a smooth action for opening and closing. Available in brushed aluminum or black powder coat, the Pop-Up Box is suited for installation with any modern décor.


Installation is simple and only requires a jig-saw or similar saw plus a screwdriver. The unit is supplied with a 5 foot cord with a molded plug end allowing it to be installed with ease. Designed to be installed into existing desks or by furniture manufactures. The Hubbell 2X2 USB Work Surface Pop-Up Box is ideally suited for any work surface application.



Charging convenience at the push of a button

Features

- 15A duplex with two USB charging ports, 3A USB charging capacity
- 5 foot, pre-wired, 12 gauge, 3-wire electrical cord, making it excellent for conference rooms or classrooms that are frequently rearranged
- Tamper-resistant receptacle
- Gas-spring actuation for smooth opening and closing
- Die cast aluminum construction
- Rated for +10,000 open/close cycles
- Simple three-screw installation
- Unobtrusive low profile flange at 0.05in
- LED power-indicating light
- Easily replaceable receptacle



Electrical Specifications

- Voltage: 125V
- Current: 15A
- USB charging current: 3A
- Plug type: NEMA type 5-15P
- Cord length: 5 feet

Specifications

- cULus
- Listed to UL962A for Furniture Power Distribution Units



2X2 USB Work Surface Box,
Brushed Aluminum
WSBUSB2X2ALU



2X2 USB Work Surface Box,
Brushed Aluminum
WSBUSB2X2BLK

2X2 USB Work Surface Pop-Up Box

| Surface Dimensions | Cut Out Dimensions | Product Depth | Maximum Surface Thickness | Finish | Catalog No. |
|--------------------|--------------------|---------------|---------------------------|-------------------|---------------------|
| 5" x 5" | 4.62" x 4.62" | 3.55" | 1.125" | Brushed Aluminum | WSBUSB2X2ALU |
| | | | | Black Powder Coat | WSBUSB2X2BLK |



HBL985 and HBL986 with HBL989
Low Voltage Partition



Gangable AV Wall Box, 2-Gang
HBL985



Gangable AV Wall Box, 3-Gang
HBL986



Low Voltage Partition
HBL989

DELIVERY

Gangable AV Wall Boxes, 2- and 3-Gang

| Box | Dimensions | Knockouts Top* | Knockouts Bottom* | Knockouts Back | Catalog No. |
|--|---------------------------|---------------------------|--|-----------------|---------------|
| 2-Gang, 2" KO, 54in ³ capacity | H: 4¼" W: 4⅞" D: 4" | (2) ½" (2) ½" – ¾" TKO | (1) 1", 1¼", 1½" and 2" (1) ½" - ¾" TKO | (2) ½" – ¾" TKO | HBL985 |
| 3-Gang, 2" KO, 79in ³ capacity | H: 4¼" W: 5⅞" D: 4" | (3) ½" (3) ½" – ¾" TKO | (1) ½" (1) ½" - ¾" TKO (1) 1", 1¼", 1½" and 2" | (3) ½" – ¾" TKO | HBL986 |

Low Voltage AV Wallbox Partitions

| Compatible With | Compatible Mud Ring Depth | Description | Quantity | Catalog No. |
|-------------------|---------------------------|---------------------------|----------|------------------|
| HBL985 and HBL986 | ½", ¾" and 1¼" | Solid divider | 1 | HBL989 |
| | | With pass-thru capability | 1 | HBL989AVD |



Front



Back (Cutaway)


Cutaway images are for demonstration purposes only.



2-Gang Large Capacity Wall Box
HBL260



3-Gang Large Capacity Wall Box
HBL263



3-Gang Mud Ring
HBL792

2-Gang Large Capacity Wall Box, 66.7 Cubic Inch Capacity

| Description | Dimensions | Knockouts Sides* | Knockouts Back* | Catalog No. |
|------------------------|----------------------------|---|---------------------------|---------------|
| Square 2-gang wall box | H: 4⅞" W: 4⅞" D: 3¼" | (2) ¾" – 1" TKO; (2) 1" – 1¼" TKO; (2) 1" – 2" conc. KO | (2) ¾" – 1" TKO (2) ½" | HBL260 |

Note: Use with industry standard 4⅞" square mud rings for 1- or 2-gang applications.

3-Gang Large Capacity Wall Box, 113.3 Cubic Inch Capacity

| Description | Dimensions | Knockouts Sides* | Knockouts Back* | Catalog No. |
|------------------------------|----------------------------|---|--|---------------|
| Square 2- or 3-gang wall box | H: 4⅞" W: 7¾" D: 3¼" | (4) ½" – ¾" TKO, (4) ¾" – 1" TKO, (2) 1" – 1¼" TKO, (2) 1" – 2" conc. KO | (2) ½" – ¾" TKO, (2) ¾" – 1" TKO, (2) 1" – 1¼" TKO | HBL263 |

Note: Use with industry standard 4" square mudrings for 1- or 2-gang applications.

2-Gang Mud Rings (Compatible with HBL260)

| Description | Capacity | Catalog No. |
|-------------|---------------------|---------------|
| ⅝" height | 7.3in ³ | HBL818 |
| ¾" height | 8.8in ³ | HBL840 |
| 1" height | 12.0in ³ | HBL819 |
| 1¼" height | 15.0in ³ | HBL820 |

3-Gang Mud Rings (Compatible with HBL263)

| Description | Capacity | Catalog No. |
|-------------|---------------------|---------------|
| ½" height | 10.1in ³ | HBL792 |
| ⅝" height | 12.3in ³ | HBL793 |
| 1¼" height | 24.3in ³ | HBL794 |

Low Voltage Partitions

| Compatible With | Compatible Mud Ring Depth | Description | Quantity | Catalog No. |
|-------------------|---------------------------|---------------------------|----------|------------------|
| HBL260 and HBL263 | ½", ¾" and 1¼" | Solid divider | 1 | HBL981 |
| | | With pass-thru capability | 1 | HBL981AVD |

*TKO (Tangential Knockout)



FPTV Enclosure
NSAV62M



FPTV Enclosure Cover
NSAV6C



Surge Protected Power Kit
NSOKPS



HDMI Frame
NS801W



AV Ceiling Enclosure
AVCE1

FPTV Connection Enclosure

| Description | Color | Catalog No. |
|-------------------------------|-------|-----------------|
| 2-gang in-wall enclosure | White | NSAV62M |
| Steel cover for NSAV6 series | White | NSAV6C |
| 4-gang in-wall enclosure | White | NSAV124M |
| Steel cover for NSAV12 series | White | NSAV12C |

Power Kits

For use with NSAV62M only

| Description | Color | Catalog No. |
|---------------------------|-------|---------------|
| Standard power kit | White | NSOKP |
| Surge protected power kit | Blue | NSOKPS |

AV Connectors and Plates

| Description | Color | Catalog No. |
|-------------------------------|-------|-----------------|
| 1-gang decorator plate | White | NP26W |
| 1-gang Hubbell iSTATION plate | White | IMF1W |
| 1-gang 4-port keystone plate | White | NSP14W |
| 1-port HDMI frame | White | NS801W |
| 2-port HDMI frame | White | NS802W |
| HDMI snap fit | Black | SFHC14BK |
| F-connector snap fit | White | NSF70W |
| USB A-to-B snap fit | White | SFUSBABW |
| Cat 6 snap fit jack | White | NSJ6W |

Note: See Section F for AV and datacom options

AV Ceiling Enclosure

| Description | Color | Catalog No. |
|------------------------------------|-------|---------------|
| AV ceiling enclosure | White | AVCE1 |
| AV ceiling enclosure, plenum rated | White | AVCE1P |

Note: Enclosure includes 24" x 12" x 8" enclosure, (2) 20A duplex receptacles and 2-gang back box.



Safety

- Low profile flange, 0.150", is better than ADA requirements
- Hide-away egress door fold under cover while in use
- 180° opening of main door

Functionality

- Cables and connections are protected by recessed functionality
- Open architecture sub-plate design
- Dirt ingress reduced by egress door brushes
- Exceeds UL 514A Scrub Requirements with ScrubShield® technology
- Easy selection with common flange for all floor types



Value

- Enhance building décor with numerous finishes
- Increase durability and longevity with cast aluminum covers

Online Resources

BIM models, customer drawings and technical specifications are available on www.hubbell-wiring.com.

8" Sub-Plate Features



Center Plate Configurations:

- Allows for three duplex receptacles or up to 18 data and or audio visual jacks
- Open architecture sub-plate design accommodates FSR®, Extron®, Crestron®, etc.
- NEMA spacing between devices
- All plates can be independently wired

Outer Plate Configurations:

- Available in pre-wired 20A duplex receptacles or data/AV plates
- Multiple 20A duplex receptacles can be wired to a common circuit or independently

6" Sub-Plate Features



60/40 Device Plate Combination:

- Allows for a wide array of data and audio visual connectivity with a 20A duplex receptacle
- The two plates can be independently wired



50/50 Device Plate Combination:

- Accommodates up to two 20A duplex receptacles with eight data or audio visual connections
- The two plates can be independently wired

4" Sub-Plate Features



Plate Configurations


- Quad receptacle sub-plate, single or dual circuit wiring
- 2x2 sub plate for decorator or traditional receptacles plus two keystone jacks
- Since service decorator or traditional sub-plates

*Extron is a registered trademark of Extron Electronics.
Crestron is a registered trademark of Crestron Electronics, Inc.
FSR is a registered trademark of FSR Inc.*

STEP 1 | Select Poke Through



STEP 2 | Select Sub-Plates



Note: Furniture feed model does not use sub-plates.

STEP 3 | Select Cover Finishes



Recommended Fire-Rated Poke-Through Size Chart

To avoid over or under utilizing the capacity of the fire-rated poke-through, first determine how many gangs of power, data and AV are required for the application. The matrix below will guide you to the correct poke-through size.


| | | Recommended Fire-Rated Poke-Through Size | | | | | |
|-------------|---|--|------------------|---------------------|---------------|----|----|
| POWER GANGS | 5 | 8" | Exceeds capacity | | | | |
| | 4 | 8" | 8" | of Hubbell recessed | | | |
| | 3 | 6" | 8" | 8" | poke-throughs | | |
| | 2 | 6" | 6" | 8" | 8" | | |
| | 1 | 4" | 6" | 6" | 8" | 8" | |
| | 0 | - | 4" | 6" | 8" | 8" | 8" |
| | | 0 | 1 | 2 | 3 | 4 | 5 |
| | | DATA AND AV GANGS | | | | | |

Example: 2 gangs of power, 1 gang of AV and 1 gang of data is required. Find the intersection for 2 power gangs with 2 data/AV gangs. The highlighted intersection defines the recommended FRPT.



Features

- Step down installation
- Maintains concrete floor fire rating up to two hours
- Junction box standard
- For use in the City of Chicago applications, junction box is NOT included
- Features ScrubShield® technology that exceeds UL514A scrub water exclusion requirements



8" Fire-Rated Poke-Throughs

| Description | Catalog No. |
|--|----------------------|
| 8" Fire-Rated Poke-Through includes: (1) 3/4" power EMT plus (1) S1R8JNC1 with (1) 1" EMT and (1) 1 1/2" EMT | S1R8PTFIT1 |
| 8" Fire-Rated Poke-Through includes: (1) 3/4" power EMT plus (1) S1R8JNC2 with (2) 1" EMT | S1R8PTFIT2 |
| 8" Fire-Rated Poke-Through includes: (1) 3/4" power EMT plus (1) S1R8JNC3 with (1) 2" EMT | S1R8PTFIT3 |
| 8" Fire-Rated Poke-Through includes: (1) 3/4" power EMT plus (1) S1R8JNC1 with (2) 1inch EMT and (1) 1 1/2" EMT; no junction box or flexible metal conduit | S1R8PTFIT1CHI |
| 8" Fire-Rated Poke-Through includes: (1) 3/4" power EMT plus (1) S1R8JNC2 with (2) 1" EMT; no junction box or flexible metal conduit | S1R8PTFIT2CHI |
| 8" Fire-Rated Poke-Through includes: (1) 3/4" power EMT plus (1) S1R8JNC3 with (1) 2" EMT; no junction box or flexible metal conduit | S1R8PTFIT3CHI |

ScrubShield®
Complies with UL514 A & C



Center Plate Configurations

- Allows for 3 duplexes or up to 18 data/AV jacks. Other combinations possible
- Accepts third party AV devices (i.e. FSR®, Crestron®, Extron®)
- Standard NEMA spacing between devices

Outer Plate Configurations

- Available in pre-wired duplexes or openings to accommodate third party AV devices
- Multiple duplexes can be wired in the supplied junction box or independently



Center, Twist-Lock
S1R8CSPG



Center, Duplex
S1R8CSPJ



Center, 2-Gang Decorator
S1R8CSPM



Outer, iSTATION
S1R8PSPY



Outer, Dual 20A
S1R8PSPZ



Aluminum Cover
S1R8CVRALU



Replacement Fitting Box
S1R8JNC1

Center Sub-Plates, Single Gang

| Description | Catalog No. |
|--|-----------------|
| Blank cover plate | S1R8CSPB |
| (1) 1 unit Hubbell iSTATION opening | S1R8CSPD |
| (1) 1.60" opening for 20A and 30A Twist-Lock® | S1R8CSPG |
| (1) 1.40" opening for simplex or 15A Twist-Lock® | S1R8CSPJ |
| (2) Extron® MAAP openings | S1R8CSPC |
| (1) 1.5 unit Hubbell iSTATION opening | S1R8CSPE |
| (1) Duplex opening | S1R8CSPJ |
| (1) Style Line® Decorator opening | S1R8CSPK |

Center Sub-Plates, 2- and 3-Gang

| Description | Catalog No. |
|---|-------------------|
| Two gang; (4) Extron® AAP openings | S1R8CSPA |
| Two gang; (2) Style Line® Decorator openings | S1R8CSPM |
| Three gang; blank cover plate | S1R8CSPN |
| Two gang; 3 unit Hubbell iSTATION opening | S1R8CSPL |
| Two gang; device depth extension collar (for use with third party data up to 2.5" depth or two power receptacles) | S1R8CSPEXT |

Recessed 8" Covers

Single piece 8" FRPT cover assembly unit includes solid cast aluminum construction, carpet gasket and mounting hardware.

| Description | Catalog No. |
|----------------------|-------------------|
| Brushed Aluminum | S1R8CVRALU |
| Black Powder Coat | S1R8CVRBLK |
| Brushed Brass Plated | S1R8CVRBRS |
| Bronze Plated Finish | S1R8CVRBRZ |
| Satin Nickel Plated | S1R8CVRNKL |

Note: Rectangle sub-plates are for center compartment, crescent sub-plates are for outer compartments and are not inter-changeable. See section F for Hubbell iSTATION modules.

Extron is a registered trademark of Extron Electronics. Crestron is a registered trademark of Crestron Electronics, Inc. FSR is a registered trademark of FSR Inc.

Outer Sub-Plates

| Description | Catalog No. |
|---|-----------------|
| Blank cover plate | S1R8PSPU |
| Pull through with 1" bushing opening | S1R8PSPW |
| (1) 1 unit Hubbell iSTATION opening | S1R8PSPY |
| Single Extron® MAAP opening | S1R8PSPV |
| Single Extron® MAAP opening | S1R8PSPX |
| Dual 20A pre-wired power cubes; one circuit (Supplied with isolated ground sticker) | S1R8PSPZ |

8" Accessories

| Description | Catalog No. |
|--|-------------------|
| Pre-pour tube, includes hardware | S1R8PPT* |
| Abandonment plate, black finish | S1R8ADMTBK |
| Low voltage replacement divider | S1R8DIV |
| Power junction box, 27.0 cubic inches; (1) 3/4" and (1) 1" EMT connector | S1FRPTJB |

*Not UL Listed


Replacement Fitting Box

| Description | Catalog No. |
|-------------------------------|-----------------|
| (1) 1" and (1) 1 1/2" EMT | S1R8JNC1 |
| (2) 1" EMTs | S1R8JNC2 |
| (1) 2" EMT | S1R8JNC3 |
| (3) 1" EMTs | S1R8JNC4 |
| (1) 1 1/2" and (1) 1 1/4" EMT | S1R8JNC5 |
| (2) 1 1/4" EMTs | S1R8JNC6 |
| (1) 3/4" and (2) 1" EMTs | S1R8JNC7 |
| (1) 3/4" and (1) 1 1/4" EMT | S1R8JNC8 |
| (1) 3/4" and (2) 1 1/4" EMTs | S1R8JNC9 |



Features

- Step down installation
- Maintains concrete floor fire rating up to two hours
- Junction box standard
- Includes (1) 2" data/AV EMT and (1) 3/4" power EMT
- For use in the City of Chicago applications, junction box is NOT included
- Features ScrubShield® technology that exceeds UL514A scrub water exclusion requirements



6" Fire-Rated Poke-Throughs

| Description | Catalog No. |
|--|---------------------|
| 6" Fire-Rated Poke-Through | S1R6PTFIT |
| 6" Fire-Rated Poke-Through; for use in the City of Chicago | S1R6PTFITCHI |

ScrubShield®
Complies with UL514 A & C



Left 60%,
Decorator and MAAP
S1R6SPV



Right 40%,
20A Pre-Wired
S1R6SPZ25



Left 50%,
Decorator and Keystone
S1R6SPE



Right 50%,
Duplex
S1R6SPV



Right 50%,
20A Pre-Wired
S1R6SPV



Recessed 6" Cover
S1R6CVRBLK



Pre-Pour Tube
S1R6PPT

60/40 Device Plate Combination

- Allows for up to twelve data/AV jacks plus a 20A duplex receptacle
- Two plates which can be wired independently

50/50 Device Plate Combination

- Allows for up to eight Hubbell data jacks plus two 20A duplex receptacles
- Two plates which can be wired independently

Left 60% Sub-Plates

| Description | Catalog No. |
|---|----------------|
| (1) Style Line® decorator, (2) Extron® MAAP openings | S1R6SPV |
| (2) Style Line decorator openings | S1R6SPW |
| (1) Style Line decorator, (2) Extron AAP openings | S1R6SPX |
| (1) Style Line decorator, (2) 1.5 unit Hubbell iSTATION openings* | S1R6SPY |
| (6) Extron MAAP openings | S1R6SPT |
| (2) Extron MAAP, (2) Extron AAP openings | S1R6SPU |

Note: Left side only

Right 40% Sub-Plates

| Description | Catalog No. |
|--|------------------|
| (2) 20A pre-wired receptacles; 16" lead; one circuit (Supplied with isolated ground sticker) | S1R6SPZ |
| (2) 20A pre-wired receptacles; 25 foot lead; one circuit (Supplied with isolated ground sticker) | S1R6SPZ25 |

Note: Right side only

6" Accessories

| Description | Catalog No. | |
|--|--------------------|----------------------|
| Pre-pour tube, including hardware | S1R6PPT** | |
| Abandonment plate, black finish | S1R6ADMTBK | |
| Low voltage replacement divider | S1R6DIV | |
| Power junction box, 27.0 cubic inches; (1) 3/4" and (1) 1" EMT connector | S1FRPTJB | |
| | 2" Catalog No. | 3/4" Catalog No. |
| Replacement furniture feed fitting | S1RFFFIT2 | S1RFFFIT075 |
| Replacement plugs | | |
| Aluminum | S1RPLUG2ALU | S1RPLUG075ALU |
| Black | S1RPLUG2BLK | S1RPLUG075BLK |
| Brass | S1RPLUG2BRS | S1RPLUG075BRS |
| Bronze | S1RPLUG2BRZ | S1RPLUG075BRZ |
| Nickel | S1RPLUG2NKL | S1RPLUG075NKL |

**Not UL Listed

*See section F for Hubbell iSTATION modules.

Note: Sub-plates can not be rotated to create additional layouts. When assembled, sub-plates can not overlap. Custom plates available upon request and may be subject to minimum order quantity

Extron is a registered trademark of Extron Electronics. Crestron is a registered trademark of Crestron Electronics, Inc. FSR is a registered trademark of FSR Inc.

Left 50% Sub-Plates

| Description | Catalog No. |
|---|----------------|
| (3) Extron® AAP openings | S1R6SPA |
| (5) Extron MAAP openings | S1R6SPC |
| (1) Style Line Decorator, (2) Hubbell keystone openings | S1R6SPE |
| (3) Extron MAAP, (2) Hubbell keystone jack openings | S1R6SPL |
| Blank cover plate | S1R6SPB |
| (4) 1 unit Hubbell iSTATION openings* | S1R6SPD |
| (2) 1.5 unit Hubbell iSTATION openings* | S1R6SPF |
| (1) Style Line® decorator opening | S1R6SPM |

Note: Left side only

Right 50% Sub-Plates

| Description | Catalog No. |
|---|----------------|
| (1) 1.60" opening for 20A and 30A Twist-Lock® | S1R6SPG |
| (1) Duplex device opening | S1R6SPI |
| (1) Style Line® decorator device opening | S1R6SPK |
| (4) 20A pre-wired receptacles; 16" leads; one or two circuits (Supplied with isolated ground sticker) | S1R6SPH |
| (1) 1.4" opening for simplex or 15A Twist-Lock | S1R6SPJ |

Note: Right side only

Recessed 6" Covers

6" FRPT cover assembled unit includes solid cast aluminum construction, carpet gasket and mounting hardware.

| Description | Catalog No. | Furniture Feed Option |
|----------------------|-------------------|-----------------------|
| Brushed Aluminum | S1R6CVRALU | S1R6FFCVRALU |
| Black Powder Coat | S1R6CVRBLK | S1R6FFCVRBLK |
| Brushed Brass Plated | S1R6CVRBRS | S1R6FFCVRBRS |
| Bronze Plated Finish | S1R6CVRBRZ | S1R6FFCVRBRZ |
| Satin Nickel Plated | S1R6CVRNKL | S1R6FFCVRNKL |



DELIVERY




Pre-Wired 8" Fire-Rated Poke-Through

Unit includes:

- (1) Hubbell SystemOne 8" floor fitting (S1R8PTFIT1)
- (4) 20A, pre-wired receptacles, 18" wire lead, two pieces (S1R8PSPZ)
- (1) Fitting connection box with 1" and 1½" EMT stubs (S1R8JNC1)
- (1) 8" flange and universal cover assembly (S1R8CVRxx)

Receptacles feature single circuit wiring




| Finish | Catalog No. |
|----------------------------|---------------------|
| Brushed Aluminum | S1R8PTZZ1ALU |
| Black Powder Coat | S1R8PTZZ1BLK |
| Brass Plated | S1R8PTZZ1BRS |
| Bronze Plated (Oil rubbed) | S1R8PTZZ1BRZ |
| Nickel Plated | S1R8PTZZ1NKL |



8" Fire-Rated Poke-Through

Unit includes:

- (1) Hubbell SystemOne 8" floor fitting (S1R8PTFIT1)
- (1) Fitting connection box with 1" and 1½" EMT stubs (S1R8JNC1)
- (1) 8" flange and universal cover assembly (S1R8CVRxx)



| Finish | Catalog No. |
|----------------------------|-------------------|
| Brushed Aluminum | S1R8PT1ALU |
| Black Powder Coat | S1R8PT1BLK |
| Brass Plated | S1R8PT1BRS |
| Bronze Plated (Oil rubbed) | S1R8PT1BRZ |
| Nickel Plated | S1R8PT1NKL |




Pre-Wired 8" Fire-Rated Poke-Through

Unit includes:

- (1) Hubbell SystemOne 8" floor fitting (S1R8PTFIT2)
- (4) 20A, pre-wired receptacles, 18" wire lead, two pieces (S1R8PSPZ)
- (1) Fitting connection box with (2) 1" EMT stubs (S1R8JNC2)
- (1) 8" flange and universal cover assembly (S1R8CVRxx)

Receptacles feature single circuit wiring



| Finish | Catalog No. |
|----------------------------|---------------------|
| Brushed Aluminum | S1R8PTZZ2ALU |
| Black Powder Coat | S1R8PTZZ2BLK |
| Brass Plated | S1R8PTZZ2BRS |
| Bronze Plated (Oil rubbed) | S1R8PTZZ2BRZ |
| Nickel Plated | S1R8PTZZ2NKL |




8" Fire-Rated Poke-Through

Unit includes:

- (1) Hubbell SystemOne 8" floor fitting (S1R8PTFIT2)
- (1) Fitting connection box with (2) 1" EMT stubs (S1R8JNC2)
- (1) 8" flange and universal cover assembly (S1R8CVRxx)

| Finish | Catalog No. |
|----------------------------|-------------------|
| Brushed Aluminum | S1R8PT2ALU |
| Black Powder Coat | S1R8PT2BLK |
| Brass Plated | S1R8PT2BRS |
| Bronze Plated (Oil rubbed) | S1R8PT2BRZ |
| Nickel Plated | S1R8PT2NKL |



Pre-Wired 8" Fire-Rated Poke-Through for Data AV

Unit includes:

- (1) Hubbell SystemOne 8" floor fitting (S1R8PTFIT3)
- (4) 20A, pre-wired receptacles, 18" wire lead, two pieces (S1R8PSPZ)
- (1) Fitting connection box with one 2" EMT stubs (S1R8JNC3)
- (1) 8" flange and universal cover assembly (S1R8CVRxx)

Receptacles feature single circuit wiring

| Finish | Catalog No. |
|----------------------------|---------------------|
| Brushed Aluminum | S1R8PTZZ3ALU |
| Black Powder Coat | S1R8PTZZ3BLK |
| Brass Plated | S1R8PTZZ3BRS |
| Bronze Plated (Oil rubbed) | S1R8PTZZ3BRZ |
| Nickel Plated | S1R8PTZZ3NKL |



8" Fire-Rated Poke-Through

Unit includes:

- (1) Hubbell SystemOne 8" floor fitting (S1R8PTFIT3)
- (1) Fitting connection box with (1) 2" EMT stubs (S1R8JNC3)
- (1) 8" flange and universal cover assembly (S1R8CVRxx)

| Finish | Catalog No. |
|----------------------------|-------------------|
| Brushed Aluminum | S1R8PT3ALU |
| Black Powder Coat | S1R8PT3BLK |
| Brass Plated | S1R8PT3BRS |
| Bronze Plated (Oil rubbed) | S1R8PT3BRZ |
| Nickel Plated | S1R8PT3NKL |

Note: xx indicates finish options.



Complies with UL514 A & C



Pre-Wired 60/40 Split 6" FRPT for Data AV

Unit includes:

- (1) Hubbell SystemOne 6" floor fitting (S1R6PTFIT)
- (2) decorator opening sub-plate (S1R6SPW)
- (2) 20A, pre-wired receptacle with 18" wire leads (S1R6SPZ)
- (1) 6" flange and universal cover assembly (S1R6CVRxx)

Receptacles feature single circuit wiring.



| Finish | Catalog No. |
|----------------------------|--------------------|
| Brushed Aluminum | S1R6PTWZALU |
| Black Powder Coat | S1R6PTWZBLK |
| Brass Plated | S1R6PTWZBRS |
| Bronze Plated (Oil rubbed) | S1R6PTWZBRZ |
| Nickel Plated | S1R6PTWZNKL |



Pre-Wired 50/50 Split 6" Fire-Rated Poke-Through for Data AV

Unit includes:

- (1) Hubbell SystemOne 6" floor fitting (S1R6PTFIT)
 - (4) 1 unit Hubbell iSTATION openings (S1R6SPD)
 - (1) decorator opening and (2) keystone openings (S1R6SPE)
 - (4) 20A, pre-wired receptacles (S1R6SPH)
 - (1) 6" flange and universal cover assembly (S1R6CVRxx)
- Opening architecture keystone openings accept Hubbell modular jacks and many others. Receptacles feature single or two circuit wiring and isolated ground capability.



| | |
|----------------------------|---------------------|
| Brushed Aluminum | S1R6PTDEHALU |
| Black Powder Coat | S1R6PTDEHBLK |
| Brass Plated | S1R6PTDEHBRS |
| Bronze Plated (Oil rubbed) | S1R6PTDEHBRZ |
| Nickel Plated | S1R6PTDEHNKL |



Pre-Wired 50/50 Split 6" Fire-Rated Poke-Through for Third Party Devices

Unit includes:

- (1) Hubbell SystemOne 6" floor fitting (S1R6PTFIT)
 - (3) Extron® AAP openings (S1R6SPA)
 - (5) Extron® MAPP openings (S1R6SPC)
 - (1) decorator opening and (2) Hubbell keystone openings (S1R6SPE)
 - (4) 20A, pre-wired receptacles (S1R6SPH)
 - (1) 6" flange and universal cover assembly (S1R6CVRxx)
- Opening architecture Keystone openings accept Hubbell modular jacks and many others. Receptacles feature single or two circuit wiring and isolated ground capability.



| | |
|----------------------------|----------------------|
| Brushed Aluminum | S1R6PTACEHALU |
| Black Powder Coat | S1R6PTACEHBLK |
| Brass Plated | S1R6PTACEHBRS |
| Bronze Plated (Oil rubbed) | S1R6PTACEHBRZ |
| Nickel Plated | S1R6PTACEHNKL |



6" Fire-Rated Poke-Through with Finished Cover

Unit includes:

- (1) Hubbell SystemOne 6" floor fitting (S1R6PTFIT)
- (1) 6" flange and universal cover assembly (S1R6CVRxx)

| | |
|----------------------------|------------------|
| Brushed Aluminum | S1R6PTALU |
| Black Powder Coat | S1R6PTBLK |
| Brass Plated | S1R6PTBRS |
| Bronze Plated (Oil rubbed) | S1R6PTBRZ |
| Nickel Plated | S1R6PTNKL |



6" Fire-Rated Poke-Through for Furniture Feed Applications

Unit includes:

- (1) Hubbell SystemOne 6" floor fitting (S1R6PTFIT)
- (1) 6" furniture feed flange and cover assembly (S1R6FFCVRxx)
- (1) 2" conduit fitting (S1RFFFIT2)
- (1) 3/4" conduit fitting (S1RFFFIT075)

| | |
|----------------------------|--------------------|
| Brushed Aluminum | S1R6PTFFALU |
| Black Powder Coat | S1R6PTFFBLK |
| Brass Plated | S1R6PTFFBRS |
| Bronze Plated (Oil rubbed) | S1R6PTFFBRZ |
| Nickel Plated | S1R6PTFFNKL |



Note: xx indicates finish options.

Extron is a registered trademark of Extron Electronics.

Complies with UL514 A & C



DELIVERY



AV Inspired Fire-Rated Poke-Through

The Hubbell S1PTAVxxx offers an industry leading 1½" data/AV EMT and ¾" power EMT to maximize use of the 4" core hole.



Multiple Sub-Plates

Allow for use of most standard and third party devices.



Fire Rating

Fire barrier expands during fire conditions to maintain the floor's fire rating up to four hours.

Specifications



- UL installation spacing: minimum two feet on center, not more than one per 65 square feet of floor area in each span
- Hubbell SystemOne Fire-Rated Poke-Throughs are approved for use in the City of Chicago
- Meets ADA standards for accessible design, section 4.3.8



Unique Cover Design

Durable cast aluminum construction available in black, gray, brass, aluminum and ivory powder coat finishes.



Complies with UL514 A & C

Hubbell SystemOne 4-Inch Core Hole One-Piece Poke-Throughs

All Hubbell SystemOne 4-inch core, one-piece poke-throughs include the sub-plate and cover to simplify your order and reduce installation time. Units are also available with a power junction box installed. The junction box is also available for purchase separately.



4X4 Poke-Through
S1PT4X4



Decorator Poke-Through
S1PTAL



Modular AV Poke-Through
S1PT3IM



Furniture Feed Poke-Through
S1PTFFAL

One-Piece 4X4 Poke-Through

| Description | Color | Without Junction Box | With Junction Box* |
|---|--|---|--|
| Assembled unit includes: <ul style="list-style-type: none"> • Hubbell SystemOne 4X4 floor fitting (S1PT4X4FIT) • 4X4 sub-plate (S1SP4X4) • Finish flange and universal carpet cover assembly (S1CFCxx) • 4-hour fire classification Keystone openings accept Hubbell modular jacks, X-END connectors and flush multimedia Snap Fit connectors. Receptacles feature single or two circuit wiring and isolated ground capability. | Aluminum Finish Brass Finish Black/Brass Finish Black Gray | S1PT4X4AL S1PT4X4BRS S1PT4X4BRS3 S1PT4X4BL S1PT4X4GY | S1PT4X4ALJ S1PT4X4BRSJ S1PT4X4BRS3J S1PT4X4BLJ S1PT4X4GYJ |



One-Piece Dual Style Line® Decorator Poke-Through

| | | | |
|---|--|---|---|
| Assembled unit includes: <ul style="list-style-type: none"> • Hubbell SystemOne dual channel floor fitting (S1PTFIT) • Dual Style Line Decorator opening sub-plate (S1SP) • Finish flange and universal carpet cover assembly (S1CFCxx) • 4-hour fire classification Style Line Decorator openings accept two Style Line Decorator or one surge or GFCI receptacle and one Style Line Decorator receptacle. Outlet frames can be used to convert the application to a 6-port multi-service or a 12-port all communication solution. Fitting is 4-hr rated at 100% fill to accommodate (12) Cat 6A cables (0.330" diameter). | Aluminum Finish Brass Finish Black Gray | S1PTAL S1PTBRS S1PTBL S1PTGY | S1PTALJ S1PTBRSJ S1PTBLJ S1PTGYJ |
|---|--|---|---|



One-Piece Modular AV Poke-Through

| | | | |
|--|--|---|---|
| Assembled unit includes: <ul style="list-style-type: none"> • Hubbell SystemOne AV floor fitting (S1PTAVFIT) • 20A, 125V power and 3-unit Hubbell iSTATION sub-plate (S1SP3IM) • Finish flange and universal carpet cover assembly S1CFCxx) • 4-hour fire classification The Hubbell iSTATION recessed opening can accommodate datAVoice/audio and video solutions including 15-pin VGA, RCA, S-Video, 3.5mm stereo, X-END, HDMI and XLR microphone jacks. | Aluminum Finish Brass Finish Black Gray | S1PT3IMAL S1PT3IMBRS S1PT3IMBL S1PT3IMGY | S1PT3IMALJ S1PT3IMBRSJ S1PT3IMBLJ S1PT3IMGYJ |
|--|--|---|---|



One-Piece Furniture Feed Poke-Through

| | | | |
|--|--|---|---|
| Assembled unit includes: <ul style="list-style-type: none"> • Hubbell SystemOne AV floor fitting (S1PTAVFIT) • Hubbell SystemOne Furniture Feed Cover Plate (S1SPFFxx) • 4-hour fire classification This solution provides (1) 3/4" conduit for power and (1) 1 1/2" conduit for low-voltage; furnished with two screw-in flexible metal conduit connectors | Aluminum Finish Brass Finish Black Gray | S1PTFFAL S1PTFFBRS S1PTFFBL S1PTFFGY | S1PTFFALJ S1PTFFBRSJ S1PTFFBLJ S1PTFFGYJ |
|--|--|---|---|



Complies with UL514 A & C

*Junction box factory installed on through floor fitting.



4X4
Through Floor Fitting
S1PT4X4FIT



Dual Channel
Through Floor Fitting
S1PTFIT



AV
Through Floor Fitting
S1PTAVFIT



Hubbell SystemOne 4-Inch Core Hole, Three-Piece Units

4X4 Through Floor Fitting

| Description | Without Junction Box | With Junction Box* |
|---|----------------------|--------------------|
| Through floor fitting with two 3/4" E.M.T. for communications and one 3/4" E.M.T. for power. For use with Hubbell SystemOne universal covers and S1SP4X4 and S1SPTL series sub-plates only. Universal cover and sub-plate ordered separately. 4-hour fire classification. | S1PT4X4FIT | S1PT4X4FITJ |

Dual Channel Through Floor Fitting

| | | |
|--|----------------|-----------------|
| Through floor fitting with two 1" E.M.T. conduit stems to feed power and/or communication services. For use with Hubbell SystemOne universal covers and all Hubbell sub-plates except S1SP4X4 and S1SPTL series. Universal cover and sub-plate ordered separately. 4-hour fire classification. | S1PTFIT | S1PTFITJ |
|--|----------------|-----------------|

AV Through Floor Fitting

| | | |
|---|------------------|-------------------|
| Through floor fitting with one 3/4" E.M.T. conduit stem for power and one 1 1/2" E.M.T. conduit stem for communication services. Ideal for demanding, high capacity audio/video and data requirements. For use with Hubbell SystemOne universal covers and all Hubbell sub-plates except S1SP4X4 and S1SPTL series. Universal cover and sub-plate ordered separately. 4-hour fire classification. | S1PTAVFIT | S1PTAVFITJ |
|---|------------------|-------------------|

*Junction box factory installed on through floor fitting.



Universal Carpet Cover
S1CFCAL



Universal Tile Cover
S1TFCAL



Abandonment Plate
S1AP4BL



Fire-Rated Closure Plug
S1FRPBL



Power Junction Box
S1FRPTJB

Hubbell SystemOne Universal Covers

| Color | Carpet Catalog Number | Tile Catalog Number |
|-----------------|-----------------------|---------------------|
| Aluminum Finish | S1CFCAL | S1TFCAL |
| Brass Finish | S1CFCBRS | S1TFCBRS |
| Black | S1CFCBL | S1TFCBL |
| Gray | S1CFCGY | S1TFCGY |
| Ivory | S1CFCI | S1TFCI |

Poke-Through Accessories

| Description | Catalog No. |
|---|-----------------|
| Abandonment plate, black | S1AP4BL |
| Abandonment plate, gray | S1AP4GY |
| Fire-rated closure plug, black | S1FRP4BL |
| Fire-rated closure plug, gray | S1FRP4GY |
| Power junction box with trade size knockouts: (1) top 1", (1) bottom 3/4", (2) side 1/2", (1) side 3/4" | S1FRPTJB |



Complies with UL514 A & C

| Description | Catalog No. | Description | Catalog No. | Description | Catalog No. |
|--|--|---|---|---|--|
| Style Line® Decorator/GFCI (2) Style Line decorator openings for power and/or datacom applications | S1SP | Duplex/Duplex (2) duplex openings for power and/or datacom applications | S1SPDU | Duplex/Style Line® Decorator (1) duplex and (1) Style Line decorator opening for power and/or datacom applications | S1SPDUSL |
| Hubbell 4 X 4 (4) 20A, 125V receptacles, (4) keystone openings for Hubbell jacks or flush AV connectors; power can be wired as single or two circuit with isolated ground capability Provided with 15' wire leads Provided with 30' wire leads | S1SP4X4 S1SP4X415 S1SP4X430 | Carpet Furniture Feed Cover/Flange* (1) 3/4" and (1) 1 1/2" N.P.T. access holes for power and/or datacom applications; universal cover not required; includes carpet flange | S1SPFFAL S1SPFFBRS S1SPFFBL S1SPFFGY | Tile Furniture Feed Cover/Flange* (1) 3/4" and (1) 1 1/2" N.P.T. access holes for power and/or datacom applications; universal cover not required; includes tile flange | S1SPFFTL S1SPFFTBRS S1SPFFTBL S1SPFFTGY |
| Single Receptacle + Data Opening for 20 or 30A Twist-Lock® receptacle (1.56" OD) and (2) keystone openings for Hubbell jacks or flush AV connectors | S1SPTL | Hubbell DataCom + Power (1) 20A, 125V receptacle and 3 unit recessed Hubbell iSTATION opening for data, voice and AV applications | S1SP3IM | Hubbell DataCom + Duplex (1) duplex opening, (2) flush keystone openings and 1.5 unit recessed Hubbell iSTATION opening for data, voice and AV applications | S1SPDU2IM |
| Hubbell DataCom + Style Line® Decorator (1) Style Line decorator opening, (2) flush keystone openings and 1.5 unit recessed Hubbell iSTATION opening for data, voice and AV applications | S1SPSL2IM | Hubbell DataCom 1 unit flush Hubbell iSTATION opening and 3 unit recessed Hubbell iSTATION opening for data, voice and AV applications | S1SP4IM | Active Multimedia + Power Single 20A, 125V receptacle, (2) flush keystone openings, (1) rectangular Style Line® decorator opening to accommodate active multimedia modules or low voltage outlet frames | S1SPAMM20 |
| Extron® or FSR + Power (1) 20A, 125V receptacle, recessed opening for (3) single Extron® MAAP series adapter plates or FSR IPS plates | S1SPEXT1 | Extron® or FSR + Power (1) 20A, 125V receptacle, recessed opening for (1) single Extron MAAP and (2) single AAP series adapter plates or FSR IPS plates | S1SPEXT2 | Extron® or FSR Single-Service Recessed opening for (2) single Extron MAAP and (2) single AAP series adapter plates or FSR IPS plates | S1SPEXT3 |
| Extron® AAP + Power (1) 20A, 125V receptacle, (2) flush keystone and recessed openings for (2) single Extron AAP Series adapter plates | S1SPEXT4 | | | | |

*Furnished with two screw-in flexible metal conduit connectors. See Section F for complete offering of Hubbell jacks and frames. See page R16 for FRPT Configuration Chart.



Conduit Plugs
S1FP15BL, S1FP34BL

Sub-Plate Accessories

| Replacement threaded conduit plugs | | | | | Blank Style Line® Decorator Frame | |
|------------------------------------|-----------------|------------------|-----------------|-----------------|-----------------------------------|---------------|
| Description | Color | | | | Color | Catalog No. |
| | Aluminum Finish | Brass Finish | Black | Gray | Black | 2100BK |
| 1 1/2" plug | S1FP15AL | S1FP15BRS | S1FP15BL | S1FP15GY | | |
| 3/4" plug | S1FP34AL | S1FP34BRS | S1FP34BL | S1FP34GY | | |

See V12 for color chart. Used with S1SPFFxx and S1SPFFTxx only. Sub-plate is supplied with plugs.

Extron is a registered trademark of Extron Electronics.



Complies with UL514 A & C




DELIVERY

Approved for use in the City of Chicago (Except S1PFB)

| Sub-Plates | | Floor Boxes* | | | | 4" Core Hole Fire-Rated Poke-Throughs | | | |
|---|--|--------------|---|-----|-----|---------------------------------------|---------------------------------|--------------------------------|----------------------|
| | | Non-Metallic | Metal | | | | | | |
| | | | | | | | | | |
| | | | | | | | | | |
| S1SP | Style Line® Decorator/GFCI | | 3 | 3.5 | 3.5 | 3.5 | ✓+ (Single-Service) | ✗ | ✓ (Multi-Service) |
| S1SPDU | Duplex/Duplex | | 3 | 3.5 | 3.5 | 3.5 | ✓+ (Single-Service) | ✗ | ✓ (Multi-Service) |
| S1SPDUSL | Duplex/Style Line® Decorator | | 3 | 3.5 | 3.5 | 3.5 | ✓+ (Single-Service) | ✗ | ✓ (Multi-Service) |
| S1SP4X4 | Hubbell 4X4 | | 4 | 4 | 4 | 4 | ✗ | ✓+ | ✗ |
| S1SPTL | Twist-Lock® Receptacle + Data | | 4 | 4 | 4 | 4 | ✗ | ✓+ | ✗ |
| S1SP3IM | Hubbell DataCom + Power | | 5 | 5 | 5 | 5 | ✓ | ✗ | ✓+ |
| S1SP4IM | Hubbell DataCom | | 3.5 | 3.5 | 3.5 | 3.5 | ✓ | ✗ | ✓+ |
| S1SPDU2IM | Hubbell DataCom + Duplex | | 5 | 5 | 5 | 5 | ✓ | ✗ | ✓+ |
| S1SPSL2IM | Hubbell DataCom + Style Line® Decorator | | 5 | 5 | 5 | 5 | ✓ | ✗ | ✓+ |
| S1SPFFxx (Carpet) | Furniture Feed Cover/Flange (Replace xx with BRS (Brass Finish), AL (Aluminum Finish), BL (Black) or GY (Gray)) | | 3 | 3.5 | 3.5 | 3.5 | ✓ | ✗ | ✓+ |
| S1SPFFTxx (Tile) | | | | | | | | | |
| S1SPEXT1 | Extron® or FSR® MAAP + Power | | 4 | 4 | 4 | 4 | ✓ | ✗ | ✓+ |
| S1SPEXT2 | Extron® or FSR® AAP/MAAP + Power | | 4 | 4 | 4 | 4 | ✓ | ✗ | ✓+ |
| S1SPEXT3 | Extron or FSR® Datacom | | 4.5 | 4.5 | 4.5 | 4.5 | ✓ | ✗ | ✓+ |
| S1SPEXT4 | Extron or FSR® AAP + Flush Keystone + Power | | 4 | 4 | 4 | 4 | ✓ | ✗ | ✓+ |
| S1SPAMM20 | Active Multimedia + Flush Keystone + Power | | 5 | 5 | 5 | 5 | ✓ | ✗ | ✓+ |
| S1FCxx SystemOne Carpet Cover | Hubbell SystemOne Floor Boxes and FRPTs use SystemOne Universal Covers (Replace xx with BRS (Brass Finish), AL (Aluminum Finish), BL (Black), GY (Gray) or I (Ivory)) | | ○ Signifies minimum depth of concrete pour in inches for Hubbell SystemOne Floor Boxes. | | | | ✓+ Recommended Floor Fitting | ✓ Alternative Floor Fitting | ✗ Not Compatible |
| S1TFCxx SystemOne Tile Cover | | | Extron® is a registered trademark of Extron Electronics. FSR® is a registered trademark of FSR, Inc. | | | | | | |



Requires unique box shown below




Patented

JLOAD provides low voltage and power in the same frame

Specifications



- UL Listed tamper-resistant receptacle
- Unique mounting strap for use with RJ600 box
- Minimum spacing for power and low voltage
- RoHS compliant



JLOAD Multimedia Outlet
RJ620WTR





JLOAD with Open Ports
RJ62WTR



JLOAD Multimedia Box
RJ600

JLOAD® Multimedia Outlet

| Description | Color |   | |
|---|---|---|--|
| | | 15A 125V NEMA 5-15R UL/CSA | 20A 125V NEMA 5-20R UL/CSA |
| JLOAD multimedia outlet, specifically designed to provide power, Cat 5e and coaxial in a single gang box; requires JLOAD multimedia box RJ600; perfect for HDTV and computer use where a combination of power and data are needed; includes decorator frame, (1) Cat 5e, (1) F-connector and (1) power receptacle 125V with voltage divider | Almond Black Gray Ivory Light Almond White | RJ650ALTR RJ650BKTR RJ650GYTR RJ650ITR RJ650LATR RJ650WTR | RJ620ALTR RJ620BKTR RJ620GYTR RJ620ITR RJ620LATR RJ620WTR |
| JLOAD multimedia outlet, includes decorator frame with two open ports for custom configuration and one power receptacle 125V with voltage divider | Almond Black Gray Ivory Light Almond White | RJ65ALTR RJ65BKTR RJ65GYTR RJ65ITR RJ65LATR RJ65WTR | RJ62ALTR RJ62BKTR RJ62GYTR RJ62ITR RJ62LATR RJ62WTR |
| JLOAD multimedia box, 3" deep with seven 1/2" knockouts, non-metallic sheathed cable clamps on each side; screw in mounting to stud | Steel | RJ600 | RJ600 |



DELIVERY



With Two Receptacles
HBLPP10AI



With One IG and
One Standard Receptacle
HBLPP10IGA



With One IG Surge and
Two IG Duplex Receptacles
HBLPP10SAI



Adjustable T-Bar Assembly
ATB



Replacement Trim Kit
PPTRIM1

Aluminum Service Poles

Aluminum service poles; gray or ivory painted and clear anodized aluminum; Style Line® duplex receptacles and two Style Line® knockouts for communications; includes ceiling trim mounting plate and scuff boot

| Description | Height Feet (m) | Gray | Ivory | Clear Anodized Aluminum |
|---|--------------------|-------------------|--------------------|----------------------------|
| Three service; two 20A 125V Style Line® duplex receptacles; one circuit | 10' 2" (3.10) | HBLPP10A | HBLPP10AI | HBLPP10AAL |
| | 12' 2" (3.71) | HBLPP12A | HBLPP12AI | HBLPP12AAL |
| | 15' 2" (4.62) | HBLPP15A | HBLPP15AI | HBLPP15AAL |
| Three service; one orange isolated ground 20A 125V Style Line® duplex receptacle; one 20A 125V Style Line® duplex receptacle; two circuits | 10' 2" (3.10) | HBLPP10IGA | HBLPP10IGAI | - |
| Three service; two orange isolated ground 20A 125V Style Line® duplex receptacles; one isolated ground surge suppression 20A 125V duplex receptacle; one circuit | 10' 2" (3.10) | HBLPP10SA | HBLPP10SAI | - |
| Three service; blank pole; divider; four Style Line® device knockouts | 10' 2" (3.10) | HBLPPOA | HBLPPOAI | HBLPPOAAL |
| | 12' 2" (3.71) | HBLPPO12A | HBLPPO12AI | HBLPPO12AAL |
| | 15' 2" (4.62) | HBLPPO15A | HBLPPO15AI | HBLPPO15AAL |

Accessories

| | |
|--|----------------|
| Adjustable T-bar assembly for mounting poles in middle of ceiling tile (requires PPTRIM1 trim kit) | ATB |
| Replacement service pole trim kit, Office White | PPTRIM1 |

Note: Style Line® communication outlets, modular jacks, and data connectors are sold separately. See sections B and F.

Specifications

Material: extruded aluminum; .05" thick (1.27mm)
Finish: gray, ivory or clear anodized aluminum
Conductors: 12AWG stranded copper
Receptacles: (see drawings below)
Listing: UL Listed

| Wiring Capacity (at 40% fill) | Voice Data Channel* | | | Power Channel** |
|--|---------------------|-------|--------|-----------------|
| | Cat 5e | Cat 6 | Cat 6A | |
| HBLPP10A, HBLPP12A, HBLPP15A, HBLPP10IGA | 26 | 11 | 9 | 41 |
| HBLPP10SA, HBLPP10SAI | 8 | 6 | 3 | 41 |
| HBLPPOA, HBLPPO12A, HBLPPO15A (with barrier) | 26 | 11 | 9 | 41 |

*Pole wiring capacity (telephone fill): Cat 5 UTP (1.96ft²)

**#12 THHN stranded

Custom Poles

Using the chart below, you are able to create a custom service pole.

| | | | | | | | | | | | | | | | | |
|------------|----------|----------|----------|----------|----------|----------|----------|----------|----------|----------|-----------|-----------|-----------|-----------|-----------|----------|
| Position | | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | |
| Selections | S | P | 1 | 0 | 0 | 2 | 1 | 1 | B | B | B | X | X | X | C | I |

Example: **SP100211BBBXXCI**

10 feet 02 inches, (2) rectangular Style Line® knockouts for data, (3) HBL2162 duplex receptacles, (2) circuits (first two receptacles on Circuit #1, remaining receptacles on Circuit #2), Ivory

Worksheet

| | | | | | | | | | | | | | | | |
|------------|----------|----------|----------|----------|----------|----------|----------|----------|----------|----------|-----------|-----------|-----------|-----------|-----------|
| Position | | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 |
| Selections | S | P | | | | | | | | | | | | | |

Position 1 and 2: Height to the nearest foot 08–22'

Position 3 and 4: Height in inches up to 11" 00–11"

Position 5, 6, 7, 8, 9, 10, 11, 12:
Starting at Position 5, select datacom knockouts/device frames followed by power receptacle/power knockout options. If the service pole is power only, select receptacle options starting at Position 5. Empty positions should be filled with an "X" to designate an empty field.


Note: If power receptacles are chosen, then power knockouts may not be chosen in the same service pole.

Data Selections

- 1 - Rectangular Style Line® knockout
- 2 - ½" N.P.T. knockout (0.875" diameter)
- 3 - ¾" N.P.T. knockout (1.109" diameter)
- 4 - 2-port Style Line data frame, 1-gang, 2-port voice/data frame
- 5 - 3-port Style Line data frame, 1-gang, 3-port voice/data frame

Power Selections

- 6 - Rectangular Style Line knockout (for blank poles only)
- 7 - ½" N.P.T. knockout (0.875" diameter, for blank poles only)
- 8 - ¾" N.P.T. knockout (1.109" diameter, for blank poles only)
- A - 5362, 20A, 125V AC, duplex
- B - HBL2162, 20A, 125V AC, Style Line duplex
- C - IG5362, 20A, 125V AC, I.G. duplex
- D - IG2162, 20A, 125V AC, I.G. Style Line duplex
- G - HBL4700, 15A, 125V AC, Twist-Lock® duplex
- H - IG4700, 15A, 125V AC, I.G. Twist-Lock duplex
- I - IG2310, 20A, 125V AC, I.G. Twist-Lock single
- J - IG5361, 20A, 125V AC, I.G. single
- K - HBL5361, 20A, 125V AC, single
- L - HBL2310, 20A, 125V AC, Twist-Lock single
- M - HBL2610, 30A, 125V AC, Twist-Lock single
- N - HBL2320, 20A, 250V AC, Twist-Lock single
- O - HBL2620, 30A, 250V AC, Twist-Lock single
- Q - IG4710, 15A, 125V AC, I.G. Twist-Lock single
- R - HBL4710, 15A, 125V AC, Twist-Lock single
- S - HBL5662, 15A, 250V AC, duplex
- T - IG5662, 15A, 250V AC, I.G. duplex
- U - HBL5661, 15A, 250V AC, single
- V - IG5661, 15A, 250V AC, I.G. single
- W - HBL5462, 20A, 250V AC, duplex



Position 13: Power Circuits

- Z - No circuits (should only be selected when the service poles has ONLY data and/or power knockouts)
- A - All devices on a single circuit
- B - 2 circuits, first receptacle on Circuit #1, remaining receptacles on Circuit #2
- C - 2 circuits, first 2 receptacles on Circuit #1, remaining receptacles on Circuit #2
- D - 2 circuits, first 3 receptacles on Circuit #1, remaining receptacles on Circuit #2
- E - 2 circuits, first 4 receptacles on Circuit #1, remaining receptacles on Circuit #2
- F - 2 circuits, first 5 receptacles on Circuit #1, remaining receptacles on Circuit #2
- G - 2 circuits, first 6 receptacles on Circuit #1, remaining receptacles on Circuit #2
- H - 2 circuits, first 7 receptacles on Circuit #1, remaining receptacles on Circuit #2

Position 14: Color

- I - Ivory
- G - Gray
- W - White
- K - Black
- A - Aluminum with clear anodized finish