

# Integral Tube

# LED

## LED 4' Glass Linear Tube 5000k

### Specifications




The ETi 15 watt 1900 lumen LED 4' Glass tubes offer exceptional performance for precision lighting applications. These 4' linear LED tubes are high quality replacements for fluorescent lamps. They are UL listed for use in damp locations and are RoHS compliant with no lead or mercury. Non-dimmable. Warranty period 5 years or 60 months. Suitable for installations from -13°F to 113°F.

### KEY FEATURES & BENEFITS

- 15 watt Low Power and High Performance
- 1900 Lumens
- 80 CRI
- 5000K
- UL-Damp and Dry Location
- Rated Lifetime: 50,000 hours
- wire to one endcap

### LAMP DIMENSIONS



SKU# 54296161  
Dimension A = 1.1"  
Dimension B = 47.2"



This light source meets restrictions on hazardous substances.

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, please see www.etiled.us

### APPLICATION INFORMATION

Typical applications for the LED tubes include retrofitting existing fluorescent fixtures. Includes; homes, museums, galleries, shop windows, restaurants, meeting rooms and hotel / motel locations.



# LED 4' Glass Tube 5000k

# LED

## SPECIFICATION DATA

Project \_\_\_\_\_

Item Number \_\_\_\_\_

Prepared by \_\_\_\_\_ Date \_\_\_\_\_

## ORDERING INFORMATION

Description	Watt- age	Base Type	Input Voltage (VAC)	Average Rated Life <sup>1</sup>	Typical Lumens <sup>2</sup>	CCT <sup>3</sup>	CRI <sup>4</sup>	R9	Power Factor	DUV	90-270° Beam Angle	0-180° Spacing	90-270° Spacing
LED15w4ftT8tu be850NDIM	15	G13	120- 277V	50,000	1,900	5000k	>86	37.1	≥0.98	0.0032	180°	1.26	1.4
<sup>1</sup> Hours lifetime with 70% lumen maintenance													
<sup>2</sup> Thermally stable typical lumens (±10%)													
<sup>3</sup> Thermally stable CCT (±10%)													
<sup>4</sup> Color rendering index													

## SHIPPING INFORMATION

Model Number	Item UPC	Item Dimensions (H x L x W)	Item Weight (lbs)	Inner Pack Qty	Inner Carton Bar Code	Inner Carton Dimensions (H x L x W)	Inner Pack Weight (lbs)	Master Pack Qty	Master Carton Bar Code	Master Dimen- sions (H x L x W)	Master Pack Weight (lbs)
54296161	8366070 09609	1.4" x 49.5" x 1.4"	.65	N/A	N/A	N/A	N/A	20	50836607 009604	8" x 50.4" x 9.2"	15.7

**LED lighting facts®**  
A Program of the U.S. DOE

Light Output (Lumens) **1900**  
Watts **15**  
Lumens per Watt (Efficacy) **126.67**

Color Accuracy  
Color Rendering Index (CRI) **80**


Light Color  
Correlated Color Temperature (CCT) **5000 (Daylight)**

Warm White 2700K 3000K Bright White 4500K Daylight 6500K

All results are according to IESNA LM-79-2008. Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit [www.lightingfacts.com](http://www.lightingfacts.com) for the Label Reference Guide.

Registration Number: YN84-PXGHTK (Revised)  
Model Number: 54296161 (01-10)  
Type: Lamp - Linear



**The Americas Headquarters**  
**720 Corporate Woods PKWY**  
**Vernon Hills, IL 60061**

**855-384-7754**    [www.etissl.com](http://www.etissl.com)