

Zinc Cable and Conduit Connectors

Application:

Used to connect steel armored cable and flexible metallic conduit to a box or enclosure.

Features:

- UL Listed Locknut
- End Stopped

Standard Materials:

Zinc Die Cast




UL Listed:

E198258


CSA File No. LR57925



Set-Screw for Armored Cable and Flexible Metallic Conduit



Type C22



CATALOG NUMBER	TRADE SIZE	DIM. A MIN.	DIM. A MAX.	DIM. B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
C22	3/8"	0.38	0.63	0.84	100	1000	5	31222


These connectors are used to secure the following cable to an enclosure:

- AC Cable No. 10-2 Steel; Maximum Diameter 0.598 in.
- AC Cable No. 14-2 Steel; Minimum Diameter 0.460 in.
- MCI Cable No. 10-3 Steel; Maximum Diameter 0.600 in.
- MCI Cable No. 14-2 Steel; Minimum Diameter 0.469 in.

Two Screw for Armored Cable, Metal Clad and Flexible Metallic Conduit



Type C23C



CATALOG NUMBER	TRADE SIZE	DIM. A MIN.	DIM. A MAX.	DIM. B	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
C23C	3/8"	0.63	0.18	1.20	100	1000	6	32232

These connectors are used to secure the following cable to an enclosure:

- AC Cable No. 10-2 Steel; Maximum Diameter 0.598 in.
- AC Cable No. 14-2 Steel; Minimum Diameter 0.460 in.
- AC Cable No. 10-2 Aluminum; Maximum Diameter 0.565 in.
- AC Cable No. 14-2 Aluminum; Minimum Diameter 0.480 in.
- MCI Cable No. 10-3 Steel; Maximum Diameter 0.600 in.
- MCI Cable No. 14-2 Steel; Minimum Diameter 0.469 in.
- MCI Cable No. 10-3 Aluminum; Maximum Diameter 0.610 in.
- MCI Cable No. 14-2 Aluminum; Minimum Diameter 0.470 in.
- MCI-A Cable No. 10-3 Aluminum; Maximum Diameter 0.495 in.
- MCI-A Cable No. 14-2 Aluminum; Minimum Diameter 0.370 in.
- HCF MCI-A Cable No. 10-2 Aluminum; Maximum Diameter 0.495 in.
- HCF MCI-A Cable No. 12-2 Aluminum; Minimum Diameter 0.418 in.
- FMC

Application:

To terminate regular wall steel or aluminum flexible conduit to a 1/2" knockout in a dry box enclosure.

Features:

- UL Listed Locknut
- End Stopped
- Male Hub NPS
- Combination Head Screw

Standard Materials:

Zinc Die Cast



UL Listed:

E198258

CSA File No. LR57925

