



GE
Lighting

13743 - GE Cool White T12

F72T12/CW 15PK

Product Photo



GENERAL CHARACTERISTICS

Base Description	Single Pin
Base Type	Pin/Plug-In
Mercury Content	90 mg
Mercury-Picogram per mean lm hr	1811.6
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	12000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	Fa8
Bulb Shape	T12

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	4140 lm
Nominal Initial Lumen per Watt	82
Initial Lumens-nominal	4500 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	13743
Description	F72T12/CW 15PK
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168981163
Standard Package GTIN	00043168137430
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168137430

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.59 in
Bulb Diameter (DIA) <Min>	1.41 in
Diameter	1.5 in
End of Base Pin to Pin	69.73 in
Face to End of Opposing Pin (B) <Max>	69.65 in
Face to End of Opposing Pin (B) <Min>	69.42 in
Nominal Length	72.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (instant start) Min @ Temperature	475.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	55 W

CAUTIONS & WARNINGS


Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.





Jan 6, 2017 10:52:41 AM For additional information, visit www.gelighting.com