

Cat No.	UPC No.	Description	Qty
EK425LD011	52028 N	EK425L Crimping Tool w/CJD30 jaws w/120 volt battery charger	1
EK425LD012	52029 N	EK425L Crimping Tool w/CJD30 jaws w/12 volt battery charger	1
EK425LD022	52030 N	EK425L Crimping Tool w/CJD30 jaws w/230 volt battery charger	1
EK425LDBG11	52025 N	EK425L Crimping Tool w/CJD3BG jaws w/120 volt battery charger	1
EK425LDBG12	52026 N	EK425L Crimping Tool w/CJD3BG jaws w/12 volt battery charger	1
EK425LDBG22	52027 N	EK425L Crimping Tool w/CJD3BG jaws w/230 volt battery charger	1
EK425LK11	52034 N	EK425L Crimping Tool w/CJK jaws w/120 volt battery charger	1
EK425LK12	52035 N	EK425L Crimping Tool w/CJK jaws w/12 volt battery charger	1
EK425LK22	52036 N	EK425L Crimping Tool w/CJK jaws w/2L0 volt battery charger	1
EK425LD11	52031 N	EK425L Crimping Tool w/CJD3 jaws w/120 volt battery charger	1
EK425LD12	52032 N	EK425L Crimping Tool w/CJD3 jaws w/12 volt battery charger	1
EK425LD22	52033 N	EK425L Crimping Tool w/CJD3 jaws w/230 volt battery charger	1
EK425LB	52024 N	EK425L Crimping Tool w/2 batteries only	1
CJXPJ	84512 A	Crimping Jaw with Nicopress X, P, & J die grooves	1
CJB	84513 A	Cutting Jaw for one-time disposable lock hasps	1
CJ22	84511 A	Crimping Jaw for use with KC22 & KA22 crimping dies	1
KD6-27	10182 A	"W" style cutter dies for ACSR to 4/0 AWG	1
F020735	43136 A	Kearney "D" crimping die (adapts jaws to use "W" & "X" dies)	1
CJD30	84514 R	Crimping Jaw Unit-D ₃ and O die grooves	1
CJD3BG	84515 R	Crimping Jaw Unit-D ₃ and BG die grooves	1
CJK	04829 R	Crimping Jaw Unit for Kearney "O" dies	1
CJD3	03242 R	Crimping Jaw with single D ₃ die groove	1
52176	52176 R	18 V 3.0 Ah Li-ion battery	1
CP1	22041 R	Tool Pouch	1



CP1

DIES FOR CRIMPING COLOR-CODED COPPER & ALUMINUM LUGS & SPLICES*
6-TON CRIMPING DIE KITS* (Requires CJ22 crimping jaws)

CAT. NO.	UPC NO.	DESCRIPTION
K22S1GL	03078	Die Kit for #8-600 Copper Connectors – Includes all copper die sets listed below and carrying case
KD06AL	01631	Die Kit for #8-350 Aluminum Connectors – Includes all aluminum die sets listed below and carrying case

22 SERIES CRIMPING DIES		ALUMINUM			COPPER		
CABLE SIZE	CAT. NO.	UPC NO.	COLOR	CAT. NO.	UPC NO.	COLOR	
8 AWG	KA22-8	06744	Blue	KC22-8	03079	Red	
6 AWG	KA22-6	06745	Gray	KC22-6	03080	Blue	
4 AWG	KA22-4	06746	Green	KC22-4	03081	Gray	
2 AWG	KA22-2	06747	Pink	KC22-2	03082	Brown	
1 AWG	KA22-1	06749	Gold	KC22-1	03083	Green	
1/0 AWG	KA22-1/0	06750	Tan	KC22-1/0	03084	Pink	
2/0 AWG	KA22-2/0	06751	Olive	KC22-2/0	03085	Black	
3/0 AWG	KA22-3/0	06752	Ruby	KC22-3/0	03086	Orange	
4/0 AWG	KA22-4/0	06753	White	KC22-4/0	03087	Purple	
250 kcmil (MCM)	KA22-250	06754	Red	KC22-250	03088	Yellow	
300 kcmil (MCM)	KA22-300	06755	Blue	KC22-300	03089	White	
350 kcmil (MCM)	KA22-350	06756	Brown	KC22-350	03090	Red	
400 kcmil (MCM)	—	—	—	KC22-400	03091	Blue	
500 kcmil (MCM)	—	—	—	KC22-500	03092	Brown	
600 kcmil (MCM)	—	—	—	KC22-600	03093	Green	

*Note: Connections are UL and cUL classified for copper and aluminum, when used with Greenlee tools on Anderson®, Blackburn®, FCI Burndy®, ILSCO®, Panduit®, Thomas & Betts® and Penn-Union® color-coded lugs and splices.

DIES FOR USE WITH SERVICE ENTRANCE CONNECTORS, C-TAPS, H-TAPS, OVER-HEAD AND UNDERGROUND CONNECTORS
(Use with EK245L with CJD3, CJD3BG & CJD30 jaws. Use with EK425L with CJK jaws with F020735 adapters.)

"W"-STYLE DIES

CAT. NO.	UPC NO.	BURNDY NO.
KD6-10	10165	W-BG
KD6-11	10166	W-O
KD6-12	10167	W-C
KD6-13	10168	W-K840
KD6-14	10169	W-161
KD6-15	10170	W-162
KD6-16	10171	W-163
KD6-17	10172	W-165
KD6-18	10173	W-166
KD6-19	10174	W-243
KD6-20	10175	W-247
KD6-21	10176	W-249
KD6-22	10177	W-164
KD6-24	10179	W-237
KD6-25	10180	W-239
KD6-27	10182	W-28K

The products listed above are registered trademarks of Anderson®, Blackburn®, FCI Burndy®, ILSCO®, Panduit®, Penn-Union® and Thomas & Betts®.

N = NEW PRODUCT **R** = REPLACEMENT PART **A** = ACCESSORY

USA Tel: 800.435.0786
Fax: 800.451.2632

Canada Tel: 800.435.0786
Fax: 800.524.2853

International Tel: +1.815.397.7070
Fax: +1.815.397.9247