



Dimmers & Fan Speed Controls

Pass & Seymour




Constant memory returns lights to previous level after power failure.

Enables On/Off and full dimming control from an unlimited number of locations.

LED indicators keep you informed. Green LEDs indicate preset level and current light level. Red LED night light glows when load is off.

Easy operation — Tap up once for preset, twice for full On. Tap down once for full Off. Hold paddle up to raise lights, down to lower.



Sleek, ergonomic P&S Decorator style matches other Decorator devices.

Unobtrusive preset selection button helps prevent accidental setting changes.

Change light level without affecting preset.

Elegant fade On and Off extends bulb life. Easy on the eyes, too.

Installs easily using the same wiring as conventional 3-way switches.

D600M-LAV

Today's home and business owners want optimum control of their electrical systems. P&S Dimmers & Fan Speed Controls provide that control — along with aesthetics, durability, trouble-free installation, and technologies aimed at solving real-world problems.

Index

Device	Rating	Page Number
Product Selection Guide		M-2
Catalog Numbering System		M-3
Dimmers		
Decorator Dimmers		
Scene Director Dimmers	120VAC, 60 Hz	M-4, M-5
Leandro® Dimmers	120VAC, 60 Hz	M-6
Aumente® Dimmers	120VAC, 60 Hz	M-7
Decorator Slide Dimmers	120 & 277VAC, 60 Hz	M-8 – M-10
TradeMaster® Short Slide Dimmers	120VAC, 60 Hz	M-11
Toggle Dimmers		
TogglePlus Dimmers	120VAC, 60 Hz	M-12
TradeMaster® Toggle Dimmers	120VAC, 60 Hz	M-13
Rotary Dimmers		
Incandescent, Low-Voltage & Fluorescent Rotary Dimmers	120VAC, 60 Hz	M-14, M-15
Fan Speed Controls		
Decorator Fan Speed Controls		
Scene Director & Leandro® Fan Speed Controls	120VAC, 60 Hz	M-16
Decorator Slide Fan Speed Controls	120VAC, 60 Hz	M-17, M-18
TradeMaster® Toggle Fan Speed Controls	120VAC, 60 Hz	M-19
Rotary Fan Speed Controls	120VAC, 60 Hz	M-20, M-21
Wall Box Timers		
Rotary Wall Box Timers	125, 125-T, 250 & 277VAC, 60 Hz	M-22
Toggle Wall Box Timers	500W, 1/3 HP, 120VAC, 60 Hz	M-23

Dimmers & Fan Speed Controls Product Selection Guide



Energy concerns have created directives in some states for lighting controls in new residential construction and major renovations. In an effort to reduce electrical power consumption, California has mandated one of the most stringent energy codes in the country. California Title 24 requires high efficacy luminaires, vacancy sensors (Section L), or dimmers to be placed in certain areas of the home. The standard became effective on October 1, 2005. Other states are considering adopting similar mandates to answer their own energy concerns. Pass & Seymour/Legrand has an extensive selection of vacancy sensor and dimmer solutions to address this growing industry trend.



SC Series P&S Scene Director Dimmers and Master Controllers

- Select any lighting scene at the touch of a button.
- Easy to install and program — additional control wiring required.
- Light levels fade elegantly up and down — and the fade rate is programmable.
- Power-failure memory returns lights to programmed levels when power is restored.
- Master can control up to 30 dimmers — handles even the most complex lighting scenes.

PAGE M-4, M-5



D600-M Series P&S Multi-Location Dimmers

- Select dimming levels from any number of locations.
- Power-failure memory returns lights to programmed levels when power is restored.
- Light levels fade elegantly up and down.
- Red LED indicates when dimmer is off — plus green LEDs to indicate light level currently selected and preset level.

PAGE M-6



D600-E Series P&S Decorator Dimmers

- Preset returns lights to programmed levels after a power failure.
- Red LED makes the dimmer easy to find in the dark.
- Handsome, ergonomic design for comfortable, convenient operation.

PAGE M-7



LS, 90, 91, 92, 93, and 95 Series Decorator Slide Dimmers

- Available in a wide range of styles for incandescent and low-voltage lighting.
- Transform into an illuminated dimmer using patented Snap-In Light Module.

PAGE M-8 – M-10



T Series P&S Toggle Dimmers

- Match appearance of toggle switches.
- Available for incandescent and low-voltage lighting.
- Slide and touch preset.

PAGE M-12, M-13



90, 91, 93 and 95 Series P&S Rotary Dimmers

- Available in a wide range of styles for incandescent, fluorescent and low-voltage lighting.

PAGE M-14, M-15

Dimmers & Fan Speed Controls Catalog Numbering System

Pass & Seymour



Scene Director®, Leandro®, Aumente®, TradeMaster® & TogglePlus Dimmers & Fan Speed Controls use an easy-to-understand catalog numbering system:

TLV 600 - *

Control Type

D = Decorator
LS = Long Slide
SC = Scene Controller
SS = Short Slide
T = Toggle

Load Type

Blank = Incandescent
FB = Fluorescent Ballast
IR = Infrared Remote
LV = Low-Voltage
ELV = Electronic Low-Voltage
MC = Master Controller

DC = Dual Dimmer/De-Hummer
Speed Control
DV = Dimmer/Variable Speed
Control
DH = De-Hummer
Fan Speed Control
SC = Fan Speed Control
R = Remote

Load Size

300 = 300 Watt
600 = 600 Watt/VA
603 = 600 Watt/VA,
3-Way
1000 = 1000 Watt/VA
1003 = 1000 Watt/VA,
3-Way

3 = 3 Amps
5 = 5 Amps
15 = 1.5 Amps
16 = 1.6 Amps
25 = 2.5 Amps

Color

CL = Clear
GRY = Gray
I = Ivory
LA = Light Almond
LC = Lighted Clear
W = White

Package

Blank = Box
V = VisionPak™

Options

E = Electronic Preset
L = Lighted
M = Multilocation
P = Preset

Examples:

D600-MLAV = Decorator Dimmer, Incandescent, 600W, Multilocation, Light Almond, in a VisionPak

LS600-LA = Decorator Slide Dimmer, Incandescent, 600W, Light Almond, in a Box

SSSC5-WV = Short Slide, Fan Speed Control, 5 Amp, White, in a VisionPak



Many P&S Dimmers & Fan Speed Controls are available boxed or VisionPak™ clam-shell packaging for high-impact merchandising. Please see the Catalog Numbering System above or specific charts for ordering information.

Pass & Seymour



Dimmers & Fan Speed Controls Decorator Dimmers – Scene Director



For everything people do at home, there's a combination of light sources and levels that will work best. P&S Scene Director Controls let homeowners capture these combinations (or scenes) — and recall them whenever they want at the touch of a button. A scene can encompass one or more rooms. And it can even include control of ceiling fans and outdoor lighting.

P&S Scene Director Master

No tools or plate removal necessary for programming with our exclusive, patent-pending system. Set light levels with product fully installed.

Easy to install, program, and operate for sophisticated scene control dimming.

Constant memory returns lights to previously selected level after power failure. No need to reset.

Controls up to 30 dimmers per Master, providing the ability to control even complex, multiroom scenes.

Available infrared remote (SCIR) provides mobile control flexibility.

Buttons glow when selected — glow levels are adjustable, too.



Raises or lowers all lights in any scene simultaneously.

One-touch selection for up to five lighting environments (scenes) — plus full Off.

Programmable fade rates enable users to easily select the speed of fade-up and fade-down.

Provides powerful control via conventional wall-box wiring. Wires like a 3-way switch. Communication among devices requires just one additional conductor.

SCMC5-WV

P&S Scene Director Dimmer

Works in conjunction with a P&S Scene Director Master.

Red LED glows when dimmer is off.

Green LEDs indicate light level selected and preset level.


Can be operated individually.

Touch pad raises or lowers individual light levels without affecting preset.

Unobtrusive set button for simple programming of preset scenes.

Sleek, ergonomic P&S Decorator style matches other Decorator devices.

Constant memory returns lights to previously selected level after power failure.



SC600-LAV



Dimmers & Fan Speed Controls Decorator Dimmers – Scene Director


Pass & Seymour




Catalog Number	Description	Ratings	Color
600W Incandescent Scene Director Control Dimmers			
SC600-WV SC600-IV SC600-LAV	Preset, Controls 1 Load in a Scene	600 Watt	White Ivory Light Almond
300VA Electronic Low-Voltage Scene Director Control Dimmers			
SCELV300-WV SCELV300-IV SCELV300-LAV	Preset, Controls 1 Load in a Scene	300VA	White Ivory Light Almond
600VA Fluorescent Ballast Scene Director Control Dimmers*			
SCFB600-WV SCFB600-IV SCFB600-LAV	Preset, Controls 1 Load in a Scene	600VA	White Ivory Light Almond
5 Scene Director Master Controllers			
SCMC5-WV SCMC5-IV SCMC5-LAV	5-Button Preset Scene Controller		White Ivory Light Almond
Remote Location Control			
SCR-WV SCR-IV SCR-LAV	For Full Dimming Control of 1 Load from Two or More Locations		White Ivory Light Almond
Accessories			
SCIR SCMCK	Infrared Hand-Held Remote Preprinted Inserts for Master Controller		

*Use with Advance Mark X® dimmable fluorescent ballasts.
Note: All Dimmers on this page may be ganged without de-rating.


WIRING DIAGRAM




Add additional dimmers and remotes (up to 30) as needed to control more loads. Use same wiring practices as above.




SC600-LAV
SCELV300-LAV
SCFB600-LAV



SCMC5-WV



SCR-LAV



SCIR

Enables full dimming control from an unlimited number of locations.

Constant memory returns lights to previous level after power failure.

LED indicators keep you informed.
Green LEDs indicate preset level and current light level. Red LED night light glows when load is off.

Easy operation — Tap up once for preset, twice for full On. Tap down once for full Off. Hold paddle up to raise lights, down to lower.


Sleek, ergonomic P&S Decorator style matches other Decorator devices.

Unobtrusive preset selection button helps prevent accidental setting changes.

Elegant fade On and Off extends bulb life. Easy on the eyes, too.

Installs easily using the same wiring as conventional 3-way switches.

Change light level without affecting preset.



D600-MLAV



D600-MLAV
DFB600-MLAV
DLV600-MLAV



D1000-MLAV

Catalog Number	Description	Ratings	Color
600W Incandescent Preset Dimmers†			
D600-MWV D600-MIV D600-MLAV D600-MBKV	Preset, Single Pole and 3-Way	600 Watt	White Ivory Light Almond Black
1000W Incandescent Preset Dimmers†			
D1000-MWV D1000-MIV D1000-MLAV	Preset, Single Pole and 3-Way	1000 Watt	White Ivory Light Almond
600VA Low-Voltage Preset Dimmers**†			
DLV600-MWV DLV600-MIV DLV600-MLAV	Preset, Single Pole and 3-Way	600VA	White Ivory Light Almond
600VA Fluorescent Ballast Preset Dimmers**††			
DFB600-MWV DFB600-MIV DFB600-MLAV	Preset, Single Pole and 3-Way	600VA	White Ivory Light Almond
Remote Dimmers†			
DR-MWV DR-MIV DR-MLAV DR-MBKV	Full Dimming or Fan Speed Control from Two or More Locations		White Ivory Light Almond Black


* Use with MR16s with magnetic transformers, neon, cold cathode, general inductive loads.

** Use with Advance Mark X® dimmable fluorescent ballasts.

† All dimmers and fan controls can be dimmed from more than one location when used with DRM remotes. Uses standard 3-way wiring. See wiring diagram.


WIRING DIAGRAMS

Single Pole



* Neutral required on DLV, DFB and DDH models. (No common neutral on dimmed circuits.)

Full Dimming Control from Two or More Locations



* Neutral required on DLV, DFB and DDH models. (No common neutral on dimmed circuits.)
Can be used with up to 30 dimmers and remotes.

Max. Load Rating	Fins Removed	
	One Side	Two Side
600W/VA	No De-Rating Required	
1000W	800W	600W

De-Rating Chart

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.




Dimmers & Fan Speed Controls Decorator Dimmers – Aumente®

Pass & Seymour



Red LED night light
glows when Off.

Sleek, ergonomic
P&S Decorator
style matches other
Decorator devices.




Convenient operation –
combines On/Off preset
Decorator switch with separate
slider microswitch for separate
dimming control.


Constant memory returns lights to
previous level after power failure.

D600-ELA

Catalog Number	Description	Ratings	Color
600W Incandescent Decorator Dimmers*†			
D600-EW D600-EI D600-ELA D600-EBK	Preset, Single Pole and 3-Way	600 Watt	White Ivory Light Almond Black
1000W Incandescent Decorator Dimmers*†			
D1000-EW D1000-EI D1000-ELA	Preset, Single Pole and 3-Way	1000 Watt	White Ivory Light Almond
Decorator On/Off Remotes**††			
DR-EWV DR-EIV DR-ELAV DR-EBKV	On/Off Control from Two or More Locations		White Ivory Light Almond Black



D600-ELA



D1000-ELA

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: D600-ELAV.


**Available in VisionPak™ only.

† All dimmers and fan controls can be operated from more than one location when used with DRE remotes.
Uses standard 3-way wiring. See wiring diagram.

Max. Load Rating	Fins Removed	
	One Side	Two Side
De-Rating Chart		
600W	No De-Rating Required	
1000W	800W	650W

WIRING DIAGRAMS

Single Pole and Multilocation



Pass & Seymour



Dimmers & Fan Speed Controls Decorator Dimmers – Slide



Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.

Electromagnetic and radio-frequency interference protection built in.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Superior heat management. No derating on 600W units.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer. See Page M-17 for information.




LS600-PLA


Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster® wall plate available for all models.

Preset "On/Off" switch automatically returns controlled lights to preset level without readjusting dimmer setting.


Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.



LS600-LA



LS600-PLA



LS1000-PLA

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
NEW 600W Incandescent Slide Dimmers*				
LS600-I LS600-W LS600-LA		Non-Preset	600W max.	Ivory White Light Almond
LS600-PI LS600-PW LS600-PLA	LS603-PI LS603-PW LS603-PLA	Preset	600W max.	Ivory White Light Almond
NEW 1000W Incandescent Slide Dimmers*				
LS1000-I LS1000-W LS1000-LA		Non-Preset	1000W max.	Ivory White Light Almond
LS1000-PI LS1000-PW LS1000-PLA	LS1003-PI LS1003-PW LS1003-PLA	Preset	1000W max.	Ivory White Light Almond
NEW 600VA Low-Voltage Magnetic Slide Dimmers**				
LSLV600-I LSLV600-W LSLV600-LA		Non-Preset	600VA max.	Ivory White Light Almond
LSLV600-PI LSLV600-PW LSLV600-PLA	LSLV603-PI LSLV603-PW LSLV603-PLA	Preset	600VA max.	Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: LS600-IV.

** Available in boxed packaging only.

Catalog Number	Description	Color
Accessories		
LRK-IV LRK-WV LRK-LAV	Replacement Knobs for Decorator Dual Slides	Ivory White Light Almond
LLRK-IV LLRK-WV LLRK-LAV	Large Replacement Knobs for Decorator Single Slides	Ivory White Light Almond

Max. Load Rating	Fins Removed	
	One Side	Two Side
De-Rating Chart		
LS600, LS603	No De-Rating Required	
LS1000P, LS1003P	900W	750W
LS1000	850W	700W

For wiring diagrams, see Page U-20.

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.



Dimmers & Fan Speed Controls Decorator Dimmers – Slide

Pass & Seymour




Full-On Bypass


When the dimmer is placed in the full-On position, the dimming circuitry is bypassed by latching contacts. This feature allows for 100% lighting output and extends dimmer life by eliminating heat build-up.

Features


- Maximum ratings are for continuous full load.
- Many 1000W models fit standard Decorator plates.
- RFI suppression built in.
- Full-On bypass.
- Preset "On/Off" switch automatically returns controlled lights to preset level without readjusting dimmer setting.
- 600W maximum rated dimmers can be ganged without de-rating.




90680 90683
N90681



91180 91183
N91181



91080 91680
N91081 N91681
91083 91683



91580 92080
N91581 N92081
91583

P = Preset
N = Non-Preset


Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
600W Incandescent Specification Grade Slide Dimmers				
90680-I*	90683-I*	Preset	600W max.	Ivory White Gray Light Almond
90680-W*	90683-W*			
90680-GRY	90683-GRY			
90680-LA*	90683-LA*			
90681-I*		Non-Preset	600W max.	Ivory White Gray Light Almond
90681-W*				
90681-GRY				
90681-LA*				
1000W Incandescent Specification Grade Slide Dimmers				
91180-I	91183-I	Preset	1000W max.	Ivory White Gray Light Almond
91180-W	91183-W			
91180-GRY	91183-GRY			
91180-LA	91183-LA			
91181-I		Non-Preset	1000W max.	Ivory White Light Almond
91181-W				
91181-GRY				
91181-LA				
600, 1000, 1500 & 2000W Incandescent Specification Grade Slide Dimmers with Architectural Heat Sink				
91680-I	91683-I	Preset	600W max.	Ivory White
91680-W	91683-W			
91681-I		Non-Preset	600W max.	Ivory White
91681-W				
91080-I	91083-I	Preset	1000W max.	Ivory White Gray
91080-W	91083-W			
91080-GRY				
91081-I		Non-Preset	1000W max.	Ivory White
91081-W				
91580-I	91583-I	Preset	1500W max.	Ivory White Gray Light Almond
91580-W	91583-W			
91580-GRY	91583-GRY			
91580-LA	91583-LA			
91581-I		Non-Preset	1500W max.	Ivory White Light Almond
91581-W				
91581-LA				
92080-I		Preset	2000W max.	Ivory White Gray Light Almond
92080-W				
92080-GRY				
92080-LA				
92081-I		Non-Preset	2000W max.	Ivory White Light Almond
92081-W				
92081-LA				

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 90680-IV.

Max. Load Rating	Fins Removed	
	One Side	Two Side
De-Rating Chart		
1000W	800W	700W
1500W	1400W	1300W
2000W	1800W	1600W


Note: Each side removed reduces plate size by 3/8".

Slide Dimmer 3-Way Wiring Diagram




All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.


Pass & Seymour




95681



95181




93281 93482
93271 93472



93683 93884
93673 93874

Typical Wiring Diagram –
Fluorescent Dimming



Dimmers & Fan Speed Controls Decorator Dimmers – Slide

Full-On Bypass

When the dimmer is placed in the full-On position, the dimming circuitry is bypassed by latching contacts. This feature allows for 100% lighting output and extends dimmer life by eliminating heat build-up.

Features	
<ul style="list-style-type: none"> Maximum rating for full continuous load. Full-On bypass. 600VA dimmers may be ganged without de-rating. 	<ul style="list-style-type: none"> Compatible with Decorator wall plates. RFI suppression built-in.

Catalog Number	Description	Ratings	Color
120VAC Low-Voltage* Specification Grade Slide Dimmers			
95681-I 95681-W 95681-LA	Non-Preset/Full-On Bypass	600VA max.	Ivory White Light Almond
120VAC Low-Voltage* Specification Grade Slide Dimmers with Architectural Heat Sink			
95181-I 95181-W	Non-Preset/Full-On Bypass	1000VA max.	Ivory White

* For use with magnetic transformer supplied incandescent low-voltage lighting.

Features	
<ul style="list-style-type: none"> Use with magnetic dimming ballast. 120 or 277VAC compatible. Full-On bypass. 	<ul style="list-style-type: none"> Low end trim adjustable. RFI suppression built-in. 5A dimmers may be ganged without de-rating.

Catalog Number		Description	Ratings	Color
120VAC	277VAC			
5A Max. Fluorescent Ballast, Single Pole, Specification Grade Dimmers				
93281-I 93281-W 93281-GRY	93271-I 93271-W 93271-GRY	Preset, 2 to 12 Lamps	5A max.	Ivory White Gray
8A Max. Fluorescent Ballast, Single Pole, Specification Grade Dimmers				
93482-I 93482-W 93482-GRY	93472-I 93472-W 93472-GRY	Preset, 4 to 20 Lamps	8A max.	Ivory White Gray
12 & 16A Max. Fluorescent Ballast, Single Pole, Specification Grade Dimmers with Architectural Heat Sink				
93683-I 93683-W 93683-GRY	93673-I 93673-W 93673-GRY	Preset, 6 to 30 Lamps	12A max.	Ivory White Gray
93884-I 93884-W 93884-GRY	93874-I 93874-W 93874-GRY	Preset, 8 to 40 Lamps	16A max.	Ivory White Gray

Catalog Number	Description	Color
Accessories for Decorator Heat Sink Dimmers & Fan Speed Controls		
DAC1-I DAC1-W	Decorator 1 Gang Wall Plate for 1000W Heat Sink Devices	Ivory White
DAC2-I DAC2-W	Decorator 1 Gang Wall Plate for 1500W and 2000W Heat Sink Devices	Ivory White

Note: See ballast manufacturer's instructions for correct wiring of ballasts and lamps. Wire colors vary by manufacturer.

Max. Load Rating	Fins Removed	
	One Side	Two Side
De-Rating Chart		
1000VA	800VA	700VA
1500VA	1400VA	1300VA
2000VA	1800VA	1600VA

Max. Load Rating	Fins Removed	
	One Side	Two Side
De-Rating Chart		
4-20 Lamps	4-18 Lamps	4-14 Lamps
6-30 Lamps	6-26 Lamps	6-24 Lamps
8-40 Lamps	8-32 Lamps	8-26 Lamps

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.


Dimmers & Fan Speed Controls TradeMaster® Short Slide Dimmers

Pass & Seymour



Features

- Contemporary slide style for toggle opening.
- Tough impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.



SS600-W

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
600W Incandescent Short Slide Dimmers*				
SS600-I SS600-W SS600-LA	SS603-I SS603-W SS603-LA	Non-Preset	600W max.	Ivory White Light Almond
600W Incandescent – Lighted Short Slide Dimmers**				
SS600-LI SS600-LW SS600-LLA	SS603-LI SS603-LW SS603-LLA	Non-Preset	600W max.	Ivory White Light Almond
1000W Incandescent Short Slide Dimmers**				
SS1000-I SS1000-W SS1000-LA	SS1003-I SS1003-W SS1003-LA	Non-Preset	1000W max.	Ivory White Light Almond
1000W Incandescent – Lighted Short Slide Dimmers**				
SS1000-LI SS1000-LW SS1000-LLA	SS1003-LI SS1003-LW SS1003-LLA	Non-Preset	1000W max.	Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: SS600-LAV.

** Available in boxed packaging only.

Catalog Number	Description	Color
Accessories		
SRK-IV SRK-WV SRK-LAV	Replacement Knobs for Decorator and Short Slides	Ivory White Light Almond

Max. Load Rating	Gang Reduction	
	2 Dimmers	3+ Dimmers
600W	500W	400W
1000W	700W	650W

De-Rating Chart


Dimmers & Fan Speed Controls Toggle Dimmers – TogglePlus



More versatile than standard toggle dimmers. Provides easy On/Off. Separate preset and electronic touch pads allow convenient dimming control.

Matches appearance of standard P&S toggle switch.

Uses conventional 3-way wiring when used in conjunction with a 3-way switch.




Green LED night light glows when Off.

Double click to On position raises lights to full On automatically.

Soft start control brings lights up slowly, extends bulb life.

T600-ELA





**T600-ELA
T1000-ELA**

Catalog Number	Description	Ratings	Color
600W Incandescent Toggle Dimmers*			
T600-EW T600-EI T600-ELA	Preset, Single Pole and 3-Way	600 Watt	White Ivory Light Almond
1000W Incandescent Toggle Dimmers*			
T1000-EW T1000-EI T1000-ELA	Preset, Single Pole and 3-Way	1000 Watt	White Ivory Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: T600-ELAV.

Max. Load Rating	Fins Removed	
	One Side	Two Side
De-Rating Chart		
600W	500W	400W
1000W	800W	600W

Wiring Diagrams






Dimmers & Fan Speed Controls TradeMaster® Toggle Dimmers

Pass & Seymour



Features

- Tough impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.



T600-I

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
600W Incandescent Toggle Dimmers				
T600-I* T600-W* T600* T600-LA*	T603-I** T603-W** T603** T603-LA**	Non-Preset	600W	Ivory White Brown Light Almond
600W Incandescent – Lighted Toggle Dimmers*				
T600-LI T600-LW T600-LLA	T603-LI T603-LW T603-LLA	Non-Preset	600W	Ivory White Light Almond
1000W Incandescent Toggle Dimmers				
T1000-I* T1000-W* T1000* T1000-LA*	T1003-I** T1003-W** T1003** T1003-LA**	Non-Preset	1000W	Ivory White Brown Light Almond
1000W Incandescent – Lighted Toggle Dimmers**				
T1000-LI T1000-LW T1000-LLA	T1003-LI T1003-LW T1003-LLA	Non-Preset	1000W	Ivory White Light Almond

* Available in VisionPak™ packaging, add “V” to Catalog Number. Example: T600-LAV.

**Available in boxed packaging only.

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
600VA Low-Voltage Magnetic Toggle Dimmers*				
TLV600-I TLV600-W TLV600-LA	TLV603-I TLV603-W TLV603-LA	Non-Preset	600VA	Ivory White Light Almond
1000VA Low-Voltage Magnetic Toggle Dimmers**				
TLV1000-I TLV1000-W TLV1000-LA	TLV1003-I TLV1003-W TLV1003-LA	Non-Preset	1000VA	Ivory White Light Almond

* Available in VisionPak™ packaging, add “V” to Catalog Number. Example: TLV600-LAV.

**Available in boxed packaging only.


Max. Load Rating	Gang Reduction	
	2 Dimmers	3+ Dimmers
De-Rating Chart		
600W	500W	400W
1000W	700W	650W

Dimmers & Fan Speed Controls Rotary Dimmers




Features

- Full range rotary dimming.
- Low-voltage and fluorescent models have field adjustable trims that may be set to control minimum light level.
- Ground lead provided on all models.
- Voltage compensation circuitry in fluorescent and low-voltage model reduces lighting fluctuations.
- All models fit standard toggle wall plate.
- All dimmers on this page may be ganged without de-rating.
- RFI protected.



90601
93212
95600



90621

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
600W Max. Incandescent Specification Grade Rotary Dimmers*				
90601-L 90601-I 90601-W 90601-LA	90603-L 90603-I 90603-W 90603-LA	Preset, Push On/Off	600W max.	Lighted Clear Ivory White Light Almond
1000W Rotary Dimmers				
91022-IV 91022-WV 91022-LAV		Dial On/Off	1000W max.	Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 90601-LAV.

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
600W Max. Incandescent Specification Grade Rotary Dimmers				
90621-IV 90621-WV		Low Profile, Dial On/Off	600W max.	Ivory White

Catalog Number	Description	Ratings	Color
600VA Max. Low-Voltage Specification Grade Rotary Dimmers 120VAC Single Pole			
95600-I 95600-W	Preset, Push On/Off Preset, Push On/Off	600VA max. 600VA max.	Ivory White


For use with magnetic transformer incandescent low-voltage lighting.

Catalog Number	Description	Ratings	Color
600VA Max. Fluorescent Specification Grade Rotary Dimmers 120VAC Single Pole			
93212-I	Dial, On/Off	600VA max.	Ivory

For use with 2 to 12 rapid start 40W fluorescent lamps. Requires dimming ballast.

Catalog Number	Description	Color
Accessories for Rotary Dimmers & Fan Speed Controls		
109-004V 109-002V 109-005V	Knob Replacement for Rotary Dimmers/Fan Controls	Clear/Gold Insert Ivory/Gold Insert White/Gold Insert
109-001V 109-008V 109-003V	Knob Replacement for Rotary Dimmers/Fan Controls	Ivory Light Almond White

Rotary Dimmer 3-Way Wiring Diagram



All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.



Dimmers & Fan Speed Controls Rotary Dimmers


Pass & Seymour




Dimmers & Fan Speed Controls

Features


- Architecturally styled cover plate and knob.
- Field adjustable trim may be set to control minimum light level.
- Black anodized heat sink for greater heat dispersion and enhanced appearance.
- Easily gangable by removing scored heat sink fins.
- Voltage compensation circuitry reduces lighting fluctuations.
- Knob and cover replacements available to change colors.
- RFI suppression built-in.



91101



91000 91003
93420 95100



91500 91503
91501 92001

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
1000W Max. Incandescent Heavy Use Rotary Dimmers				
91101-I 91101-W		Dial, On/Off	1000W max.	Ivory White

Fits in standard toggle wall plate opening.

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
1000W Max. Incandescent Rotary Dimmers with Architectural Heat Sink				
91000-I 91000-W	91003-I 91003-W	Preset, Push On/Off	1000W max.	Ivory White
91001-I 91001-W		Dial, On/Off	1000W max.	Ivory White
1500W Max. Incandescent Rotary Dimmers with Architectural Heat Sink				
91500-I	91503-I 91503-W	Preset, Push On/Off	1500W max.	Ivory White
91501-I 91501-W		Dial, On/Off	1500W max.	Ivory White
2000W Max. Incandescent Rotary Dimmers with Architectural Heat Sink				
92001-I 92001-W		Dial, On/Off	2000W max.	Ivory White

Catalog Number	Description	Ratings	Color
1000VA Max. Low-Voltage Specification Grade 120VAC Single Pole Rotary Dimmer with Architectural Heat Sink			
95100-I	Dial, On/Off	1000VA max.	Ivory

For use with magnetic transformer incandescent low-voltage lighting.

Catalog Number	Description	Ratings	Color
1000VA Max. Fluorescent Specification Grade 120VAC Single Pole Rotary Dimmer with Architectural Heat Sink			
93420-I	Dial, On/Off	1000VA max.	Ivory

For use with 4 to 20 rapid start 40W fluorescent lamps. Requires dimming ballast.

Catalog Number	Description	Color
Accessories for Rotary Heat Sink Dimmers & Fan Speed Controls		
DAPK1-I DAPK1-W DAPK1	1-Gang Wall Plate – Plate and Knob Kit for Rotary Heat Sink Devices	Ivory White Brown
DAPK2-I DAPK2-W DAPK2	2-Gang Wall Plate – Plate and Knob Kit for Rotary Heat Sink Devices	Ivory White Brown

Max. Load Rating	Fins Removed	
	One Side	Two Side
1000VA	800VA	700VA
1000W	800W	700W
1500W	1400W	1300W
2000W	1800W	1600W


De-Rating Chart

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.

Rotary Dimmers

Dimmers & Fan Speed Controls


Decorator Fan Speed Controls – Scene Director & Leandro®




SCDH15-LAV



SCMC5-WV



SCR-LAV




DDH15-MLAV

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.

Catalog Number	Description	Ratings	Color
1.5A De-Hummer* Fan Speed Controllers			
SCDH15-WV SCDH15-IV SCDH15-LAV	Preset, Controls 1 Fan Load in a Scene	1.5A	White Ivory Light Almond
5 Scene Director Master Controllers			
SCMC5-WV SCMC5-IV SCMC5-LAV	5-Button Preset Scene Controller		White Ivory Light Almond
Remote Location Control			
SCR-WV SCR-IV SCR-LAV	For Full Fan Speed Control of 1 Load from Two or More Locations		White Ivory Light Almond
Accessories			
SCIR SCMCK	Infrared Hand-Held Remote Preprinted Inserts for Master Controller		


* Feature specially designed capacitive circuitry to virtually eliminate fan motor "hum."

WIRING DIAGRAM




Catalog Number	Description	Ratings	Color
1.5A De-Hummer* Fan Controls			
DDH15-MWV DDH15-MIV DDH15-MLAV	Preset, Single Pole, 3-Speed	1.5A	White Ivory Light Almond
Remote Fan Controls			
DR-MWV DR-MIV DR-MLAV	Full Dimming or Fan Speed Control from Two or More Locations		White Ivory Light Almond

* Feature specially designed capacitive circuitry to virtually eliminate fan motor "hum."
All dimmers and fan controls can be dimmed from more than one location when used with DRM remotes. Uses standard 3-way wiring. See wiring diagram.



Note: All controls on this page can be ganged without de-rating.



Neutral required on DDH model.
Can be used with up to 30 fan speed controls and remotes.

Dimmers & Fan Speed Controls


Decorator Fan Speed Controls – Slide

Pass & Seymour




Features

- Tough impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.
- Can be used with patented Snap-In Light Module (sold separately).



LSDC16-LAV



LSDC16-PLAV



TM8LMCC

Catalog Number	Description	Ratings	Color
Decorator Slide Fan Speed Controls*			
LSSC5-I LSSC5-W LSSC5-LA	Non-Preset, Single Pole, Adjustable Trim	5A	Ivory White Light Almond
LSSC5-PI LSSC5-PW LSSC5-PLA	Preset, Single Pole, Adjustable Trim	5A	Ivory White Light Almond
Decorator Slide De-Hummer Controls**			
LSDH16-IV LSDH16-WV LSDH16-LAV	Non-Preset, 4-Speed Fan Control	1.6A	Ivory White Light Almond
Dual Control Decorator Slides**			
LSDC16-IV LSDC16-WV LSDC16-LAV	Non-Preset, 3-Speed De-Hummer Fan Control With Single-Pole Dimmer	1.6A/300W	Ivory White Light Almond
LSDC16-PIV LSDC16-PWV LSDC16-PLAV	Preset, 3-Speed De-Hummer Fan Control With Single-Pole Dimmer	1.6A/300W	Ivory White Light Almond
LSDV25-IV LSDV25-WV LSDV25-LAV	Non-Preset, Variable Speed Fan Control With Single-Pole Dimmer	2.5A/300W	Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: LSSC5-IV.

** Available in VisionPak™ only.

Features

- No tool needed, module snaps-in.
- Lights when OFF.
- Uses energy-efficient 1/4 watt LED light.
- LED light will not generate heat and will last on average 47 years.


Catalog Number	Rating A. VAC	Color
Snap-In Light Module		
TM8LMCC	15 120/125	Clear

Catalog Number	Description	Color
Accessories		
LRK-IV LRK-WV LRK-LAV	Replacement Knobs for Decorator Dual Slides	Ivory White Light Almond
LLRK-IV LLRK-WV LLRK-LAV	Large Replacement Knobs for Decorator Single Slides	Ivory White Light Almond


For wiring diagrams, see Page U-20.

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.


Pass & Seymour



P94580
N94581



94881-I



94084

P = Preset
N = Non-Preset

Max. Load Rating	Gang Reduction	
	One Side	Two Side
De-Rating Chart		
8 Amps	7 Amps	6 Amps
12 Amps	11 Amps	10 Amps

Dimmers & Fan Speed Controls

Decorator Fan Speed Controls – Slide

Field Adjustable Trim

This feature allows the user to set the minimum speed level desired and helps prevent damage to motor due to stalling. Models without field adjustable trims feature factory settings for minimum anti-stall levels.

Full-On Bypass

When control is placed in the full-On position, speed control circuitry is bypassed by latching contacts. This feature allows for 100% motor output and extends speed control's life by eliminating heat build-up.

Features

- Full range speed control.
- Utilizes standard Decorator wall plates.
- 100% tested for symmetry for extended fan life.
- Ground lead provided.
- Ferrite bar coil choke for excellent RFI suppression.

Catalog Number	Description	Ratings	Color
5A Max. Slide Fan Speed Controls			
94580-I 94580-W	Preset, Full-On Bypass, Adjustable Trim May Be Ganged Without De-Rating	5A max.	Ivory White
94581-I* 94581-W* 94581-LAV**	Non-Preset, Full-On Bypass, Adjustable Trim, May Be Ganged Without De-Rating	5A max.	Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number.

**Available in VisionPak™ only.

Features

- Full range variable low to high speed control.
- Easily ganged by removing scored heat sink fins.
- Heavy-duty toroid choke for RFI suppression.
- Black anodized heat sink for greater heat dispersion and enhanced appearance.
- 100% tested for symmetry for extended fan life.
- Ground lead provided.
- Ferrite bar coil choke for excellent RFI suppression.

Catalog Number	Description	Ratings	Color
8 & 12A Max. Slide Fan Speed Controls with Architectural Heat Sink			
94881-I	Full-On Bypass, Adjustable Trim, 1 Gang Heat Sink	8A max.	Ivory
94812-I	Full-On Bypass, Adjustable Trim, 2 Gang Heat Sink	12A max.	Ivory

Catalog Number	Description	Color
Accessories for Decorator Heat Sink Dimmers & Fan Speed Controls		
DAC1-I DAC1-W	Decorator 1 Gang Wall Plate for Heat Sink Devices	Ivory White

No-Noise De-Hummers

Since the development of variable fan speed controls, many fans have made an annoying humming noise when their speed was reduced. Through the use of specially designed capacitive circuitry, these units can control fans at 3 or 4-speed levels in slide, rotary and dual styles with virtually no fan motor noise.

Catalog Number	Description	Ratings	Color
1.5A Max. No-Noise De-Hummer Specification Grade Fan Speed Controls – RFI Protected			
94084-I* 94084-W* 94084-GRY 94084-LA*	3-Speed, Single Pole	1.5A max.	Ivory White Gray Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94084-LAV.

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.


Dimmers & Fan Speed Controls TradeMaster® Short Slide & TradeMaster® Toggle Fan Speed Controls

Pass & Seymour



Features

- Contemporary slide style for toggle opening.
- Tough impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.



SSSC5-W


Catalog Number	Description	Ratings	Color
Short Slide Fan Speed Controls*			
SSSC5-I SSSC5-W SSSC5-LA	Non-Preset, Adjustable Trim	5A	Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: SSSC5-LAV.

Catalog Number	Description	Color
Accessories		
SRK-IV SRK-WV SRK-LAV	Knob Replacement for Decorator and Short Slides	Ivory White Light Almond

Features

- Tough impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.




TSC5-I

Catalog Number	Description	Ratings	Color
Toggle Fan Speed Controls*			
TSC5-I TSC5-W TSC5-LA	Non-Preset, Adjustable Trim	5A	Ivory White Light Almond


* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: TSC5-LAV.

Max. Load Rating	Gang Reduction	
	2 Controls	3+ Controls
De-Rating Chart		
1.6A	No De-Rating Required	
5A	4A	3A

Pass & Seymour



- 94301
- 94503
- 94601



■ 94121

- P = Preset
- N = Non-Preset

Max. Load Rating	Gang Reduction	
	One Side	Two Side
De-Rating Chart		
5 Amp	4 Amp	3 Amp
8 Amp	7 Amp	6 Amp
12 Amp	11 Amp	10 Amp

Dimmers & Fan Speed Controls Rotary Fan Speed Controls

Field Adjustable Trim

This feature allows the user to set the minimum speed level desired and helps prevent damage to motor due to stalling. Models without field adjustable trims feature factory settings for minimum anti-stall levels.

Full-On Bypass

When control is placed in the full-On position, speed control circuitry is bypassed by latching contacts. This feature allows for 100% motor output and extends speed control's life by eliminating heat build-up.

Features	
<ul style="list-style-type: none"> ■ Full range speed control. ■ Utilizes standard toggle wall plates. ■ 100% tested for symmetry for extended fan life. 	<ul style="list-style-type: none"> ■ Ground lead provided. ■ Ferrite bar coil choke for excellent RFI suppression.

Catalog Number	Description	Ratings	Color
3, 5 & 6A Max. Rotary Fan Speed Controls			
94301-I* 94301-WV** 94301-LA*	Dial (Non-RFI), May Be Ganged Without De-Rating	3A max.	Ivory White Light Almond
94503-I*	Preset, Push On/Off, Adjustable Trim, 3-Way May Be Ganged Without De-Rating	5A max.	Ivory
94601-I* 94601-WV**	Dial, Adjustable Trim, May Be Ganged Without De-Rating	6A max.	Ivory White

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94301-LAV.
** Available in VisionPak™ only.

Features	
<ul style="list-style-type: none"> ■ Full range variable low to high speed control. ■ Easily ganged by removing scored heat sink fins. ■ Heavy-duty toroid choke for RFI suppression. ■ Black anodized heat sink for greater heat dispersion and enhanced appearance. 	<ul style="list-style-type: none"> ■ 100% tested for symmetry for extended fan life. ■ Ground lead provided. ■ Ferrite bar coil choke for excellent RFI suppression.

Catalog Number	Description	Ratings	Color
8 & 12A Max. Rotary Fan Speed Controls with Architectural Heat Sink			
94801-I	Dial, Adjustable Trim, 1 Gang Heat Sink	8A max.	Ivory
94121-I	Dial, Adjustable Trim, 2 Gang Heat Sink	12A max.	Ivory

Catalog Number	Description	Color
Accessories for Rotary Dimmers & Fan Speed Controls		
109-004V 109-002V 109-005V	Knob Replacement for Rotary Dimmers/Fan Controls	Clear/Gold Insert Ivory/Gold Insert White/Gold Insert
109-001V 109-008V 109-003V		Ivory Light Almond White
Accessories for Rotary Heat Sink Dimmers & Fan Speed Controls		
DAPK1-I DAPK1-W DAPK1	1-Gang Wall Plate – Plate and Knob Kit for Rotary Heat Sink Devices	Ivory White Brown
DAPK2-I DAPK2-W DAPK2		Ivory White Brown
2-Gang Wall Plate – Plate and Knob Kit for Rotary Heat Sink Devices		

Dimmers & Fan Speed Controls Rotary Fan Speed Controls

Pass & Seymour



No-Noise De-Hummers

Since the development of variable fan speed controls, many fans have made an annoying humming noise when their speed was reduced. Through the use of specially designed capacitive circuitry, these units can control fans at 3 or 4-speed levels in slide, rotary and dual styles with virtually no fan motor noise.

Catalog Number	Description	Ratings	Color
1.5A Max. Specification Grade Rotary Fan Speed Controls – No-Noise De-Hummers, RFI Protected*			
94003-I 94003-W 94003-LA	3-Speed, Low-Medium-High	1.5A max.	Ivory White Light Almond
94004-CL 94004-I 94004-W 94004-LA	4-Speed, Low-High	1.5A max.	Clear Ivory White Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94003-LAV.

Dual Control Features	
<ul style="list-style-type: none"> Fits one gang box. Controls both fan speed and light level. 	<ul style="list-style-type: none"> Decorator styling.

Catalog Number	Description	Ratings	Color
1.5A/300W Max. Specification Grade Dual Controls – No-Noise De-Hummers*			
94315-I 94315-W 94315-LA	3-Speed Fan Control and 2-Level Hi/Low Dimmer	1.5A/300W max.	Ivory White Light Almond
94215-I 94215-W 94215-LA	4-Speed Fan Control and 2-Level Hi/Low Dimmer	1.5A/300W max.	Ivory White Light Almond


Requires 3 wire installation.

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94315-LAV.

Catalog Number	Description	Ratings	Color
3A/300W Max. Specification Grade Dual Controls*			
94331-I 542-433	Dial Speed Control and Dimmer	3A/300W max.	Ivory White

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94331-IV.


Catalog Number	Description	Color
Accessories for Dual Controls		
109-019V 109-020V 109-018V	Adapter Kit for Dual Fan/Light Controls	Ivory White Light Almond




Dual Control Connection Diagram

Note: All controls on this page may be ganged without de-rating.

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.



94004
94003




94215
94315
94331
542-433

Pass & Seymour



Dimmers & Fan Speed Controls Rotary Wall Box Timers

125, 125-T, 250 & 277VAC, 60 Hz



97015-I

Applications

- Lighting
- Exhaust fans
- Whirlpools and spas
- Saunas
- Heating and heatlamps
- Ventilating and air conditioning

Features

- Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.
- Turning clockwise causes unit to time load off after desired time delay.
- Quiet operation.
- Time range from 5 minutes to 12 hours.
- Available with or without hold.
- Decorator styling.
- Easily installed.
- Large head screw terminals.
- Accurate to ± 5 percent.
- Motor rated.
- Energy saving.

Catalog Number	Description	Time Range	Color
Specification Grade Decorator Rotary Timers			
No Hold			
97015-I 97015-W 97015-LA	Timeout, No Hold	15 Minutes	Ivory White Light Almond
97030-I 97030-W 97030-LA	Timeout, No Hold	30 Minutes	Ivory White Light Almond
97060-I 97060-W	Timeout, No Hold	60 Minutes	Ivory White
With Hold			
97115-I 97115-W	Timeout, With Hold	15 Minutes	Ivory White
97130-I 97130-W	Timeout, With Hold	30 Minutes	Ivory White
97160-I 97160-W	Timeout, With Hold	60 Minutes	Ivory White

Catalog Number	Color
Replacement Knobs (without plate)	
PS55A1	White
PS55B1	Ivory
PS55G1	Light Almond

VAC	Hz	Amp	HP
Ratings			
125	60	20	1
125T	60	7	
250	60	10	1
277	60	10	

Dimmers & Fan Speed Controls Wall Box Timers


500W, 1/3 & 1/6 HP, 120VAC, 60 Hz

Pass & Seymour



Applications			
■ Lighting	■ Exhaust fans	■ Store rooms	■ Garages
■ Heatlamps	■ Whirlpools and spas	■ Bathrooms	

Features	
<ul style="list-style-type: none"> ■ Contemporary design. ■ Dual switch functionality. <ul style="list-style-type: none"> - Light on or off - Fan time delay with preset ranges of 20, 40 and 60 minutes ■ Eliminates the need for two switches. 	<ul style="list-style-type: none"> ■ Easy installation – fits standard opening for easy ganging. ■ Illuminated for locating in dark areas. ■ Package includes three color overlays: Ivory, White, and Light Almond. ■ Wall plate sold separately.




DEFL44L

NEW

Catalog Number	Description	Time Range	Rating
Specification Grade Decorator-Style Electronic Fan/Light Wall Box Time Switches			
DEFL44L	Double Pole, Double Throw	20, 40 or 60 minutes	500W Incandescent, Input: 120VAC, 60Hz Output: 1/6 HP, (4.4 max)

Features	
<ul style="list-style-type: none"> ■ Eliminates the need for two switches. ■ Fits standard toggle opening for easy ganging. ■ Time range adjustable from 1-60 minutes. ■ Easily installed. ■ May control one or two loads simultaneously. 	<ul style="list-style-type: none"> ■ Motor rated. ■ Silent operation. ■ Reliable solid-state construction. ■ Energy saving.




97352-I

Catalog Number	Description	Time Range	Rating	Color
Specification Grade Toggle Time Delay Switches Center Off				
97352-I	Double Pole, Double Throw	1-60 Minutes, Adjustable	500W, 1/3 HP, 120VAC, 60 Hz	Ivory
97352-W	Double Pole, Double Throw			White

Operation: Catalog Number DEFL44L

- LED remains ON to locate in the dark.
- To turn light ON, press the area marked LIGHT.
- To turn light OFF, press the area marked LIGHT again.
- Press the area marked FAN once to operate fan for 20 minutes, twice for 40 minutes, three times for 60 minutes. The corresponding LEDs will turn ON to indicate mode of operation. Fan will shut OFF automatically.
- Press the area marked FAN a fourth time to turn OFF the timed operation.


Wiring Diagram:



Operation: Catalog Number 97352

- When toggle is up, one or two loads remain on.
- When toggle is down, load "A" is off, load "B" times-off at preset time. In the center position, both loads are off.

Wiring Diagram: Single Timed Load Application



All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.