

# General Duty Safety Switches

30-600 Amps, 240 Vac

For residential and light commercial applications



## Features & Benefits

- UL Listed and CSA Certified
- Meets or exceeds the requirements of NEMA Standard KS-1 for type General Duty
- Suitable for use as Service Equipment
- Fusible and non-fusible construction
- 100,000 RMS Amps, symmetrical IC rating on 30-200A disconnects when protected by class R fuses
- NEMA Type 1 (indoor) and Type 3R (outdoor) construction
- Integral cover interlock on 30-200A disconnects for added protection
- Lockable cover and handle (OFF position) to prevent unauthorized entry and use
- Field installable accessories available (ground lugs, neutral lugs, class R fuse rejection kits, and universal raintight hubs)



TGN3322  
with integral cover interlock

## Ordering Information

	Ampere Rating	Fusible			Non-Fusible
		2-Pole 3-Wire*	3-Pole 3-Wire	3-Pole 4-Wire*	3-Pole 3-Wire
NEMA Type 1 (indoor)	30	TG3221	—	TG4321	TGN3321
	60	TG3222	—	TG4322	TGN3322
	100	TG3223	—	TG4323	TGN3323
	200	TG3224	—	TG4324	TGN3324
	400	TG3225	TG3325	TG4325	TGN3325
	600	TG3226	TG3326	TG4326	TGN3326

\*Includes factory installed neutral lug

	Ampere Rating	Fusible			Non-Fusible
		2-Pole 3-Wire*	3-Pole 3-Wire	3-Pole 4-Wire*	3-Pole 3-Wire
NEMA Type 3R (outdoor)	30	TG3221R	—	TG4321R	TGN3321R
	60	TG3222R	—	TG4322R	TGN3322R
	100	TG3223R	—	TG4323R	TGN3323R
	200	TG3224R	—	TG4324R	TGN3324R
	400	TG3225R	TG3325R	—	—
	600	TG3226R	TG3326R	—	—

GE Energy  
41 Woodford Avenue  
Plainville, CT 06062  
www.geindustrial.com

© 2012 GE Company



Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, express or implied, that such performance will be obtained under end-use conditions.