

Malleable Iron Cable Connectors

For Armored Cable, Metal Clad and Flexible Metallic Conduit

Application:

To make a 90° termination of flexible metal conduit or cable to a knockout or unthreaded slip hole in a dry location box or enclosure.

Features:

- Male Hub Threads - NPSM
- Provided with steel locknuts
- Stamped Steel Covers

Standard Materials:

Malleable Iron / Steel Locknuts

Standard Finish:

Zinc Plated



UL Listed:
E207875

90° Duplex



Type C271

CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
C271	3/8"	1/2"	1.188	0.438	0.875	25	250	14	52713

45° Angle



Type 315M

CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
315M	3/8"	1/2"	1.750	0.438	1.125	25	250	10	31502
316M	1/2"	1/2"	1.938	0.438	1.750	25	250	12	70885
317M	3/4"	3/4"	1.938	0.500	2.000	25	250	15	70886

Application:

Connects conduit and terminates bonding conductor.

Features:

- Male Hub Threads - NPSM
- Provided with steel locknuts
- Stamped Steel Covers

Standard Materials:

Malleable Iron / Steel Locknuts

Standard Finish:

Zinc Plated



UL Listed:
E207875