


3310 Series Fan Forced Wall Heater - With Summer Fan Switch

45



Features

- Powder coated 18 Gauge steel front.
- Automatic reset thermal limit.
- Steel block fin element.
- Weight 22 lbs.
- Vane axial fan blade: 600 RPM / 175 CFM.
- Grill dimensions: 15-3/8" Wide x 20-9/64" High.
- Rough in dimensions: 14-3/16" Wide x 19-15/16" High x 4" Deep.
- Units with dual wattage, factory wired to highest wattage.
- Wattage selectable at time of installation on some models.



Manufactured in U.S.A.

Product Specifications

Typical Specifications: Furnish and install Electric Forced Air Heaters where specified. The heaters shall be constructed of a heavy gauge steel housing. The rough-in dimensions are 14-3/16" Wide x 19-5/16" High x 4" Deep. The finish shall be powder coated paint in ivory or white color. The units shall be available in ratings from 750 through 4800 Watts. The heaters shall have a low speed 600 RPM motor which drives a vane axial blower to deliver a quiet 175 CFM of down flow air. The heating element shall be of the sealed block fin type with large, parallel steel fins for quick heat transfer. Unit shall have a standard thermal overload cutoff for added safety, a fan switch for fan only operation, and is available with a single pole, or double pole built-in thermostat, or no thermostat. The in-built thermostat shall be calibrated to provide a range of 50 degrees F. to 90 degrees F. All heaters shall be listed by ETL. The heating element shall be supplied with a manufacturer's 1 year limited warranty.

Standard Models

MODELS WITH IN-BUILT DOUBLE POLE THERMOSTAT (50° - 90°F TEMPERATURE RANGE)								
IVORY		WHITE		WATTS	MAX BTU's	VOLTS	AMPS	LIST
UPC 686334	IVORY	UPC 686334	WHITE					
326063	E3312T2SRP	326209	E3312T2SRPW	1000	3413	120	8.3	498
326070	E3313T2SRP	326216	E3313T2SRPW	1500	5120		12.5	
				750	2560		6.25	
326087	F3316T2SRP	326223	F3316T2SRPW	4000	13648	208	19.2	509
326094	F3317T2SRP	326230	F3317T2SRPW	4800	16380		23	521
326124	HF3315T2SRP	326261	HF3315T2SRPW	3000 / 2250	10240	240 / 208	12.5 / 10.8	509
				1500 / 1125	5120		6.2 / 5.4	
326131	HF3316T2SRP	326278	HF3316T2SRPW	4000 / 3000	13648		16.8 / 14.4	
				2000 / 1500	6826		8.3 / 7.2	
326148	H3317T2SRP	326285	H3317T2SRPW	4800	16380	240	20.0	530

MODELS WITH IN-BUILT SINGLE POLE THERMOSTAT (50° - 90°F TEMPERATURE RANGE)								
382571	E3312TSRP	382595	E3312TSRPW	1000	3413	120	8.3	467
379618	E3313TSRP	384018	E3313TSRPW	1500	5120		12.5	
				750	2560		6.25	
377713	F3316TSRP	384025	F3316TSRPW	4000	13648	208	19.2	476
377782	F3317TSRP	384032	F3317TSRPW	4800	16380		23	488
377607	HF3315TSRP	384070	HF3315TSRPW	3000 / 2250	10240	240 / 208	12.5 / 10.8	476
				1500 / 1125	5120		6.2 / 5.4	
377690	HF3316TSRP	384087	HF3316TSRPW	4000 / 3000	13648		16.8 / 14.4	
				2000 / 1500	6826		8.3 / 7.2	
377768	H3317TSRP	384094	H3317TSRPW	4800	16380	240	20.0	497
International Models								
----	----	396480	M3315T2SRPW	3360	11468	220	15.27	509
				1680	5734		7.64	
		396493	M3316T2SRPW	4032	13761		18.33	
				2016	6881		9.16	

Note: Fan switch not available on 277V models. 277V models are available without a fan switch on previous page.

Accessories - All Models

IVORY		WHITE		DESCRIPTION	ACCESSORY TYPE	LIST
UPC 686334	MODEL	UPC 686334	MODEL			
377850	BOX3310	377850	BOX3310	ADDITIONAL BACK CAN	Field Installed	96
329958	3310EX33R	329965	3310EX33WR	SURFACE MOUNTING FRAME		85
SUFFIX D				DISCONNECT SWITCH	Factory Installed	108