

POWER-STRUT®

Quick Reference Guide

Versatile Solutions from POWER-STRUT®

- Channels, Fittings, & Accessories
- Electrical Raceway Components
- Concrete Inserts
- Brackets & Clamps®
- Available Finish Information
- Recommended installation methods




FINISHES

Power-Strut is available in multiple finishes to fit your environmental or cost requirements.


POWER-GOLD™

A Electro-galvanized zinc plate is applied with a cohesive molecular bond to the steel base metal, in compliance with the ASTM B633 standard. Yellow Dichromate is applied over the zinc and results in a gold appearance which acts as a nonporous barrier sealant.




POWER-GREEN®

Channel and parts are cleaned and phosphated. Immediately afterward, a uniform coat of rust-inhibiting acrylic enamel paint is applied by electro-deposition and thoroughly baked.




Hot Dip Galvanized

Material is coated with zinc after being roll-formed or after all manufacturing operations are completed, conforming to ASTM specification No. A123 or A153.




Electro-Galvanized

Fittings and hardware are electrolytically coated with zinc to commercial standards (ASTM-B633 Type III C1).




Pre-Galvanized

Material (steel strip) is coated with zinc by hot-dip process prior to roll-forming or press operations. The zinc coating conforms to ASTM A653, Grade 90 General Requirement for Steel Sheet, Zinc-Coated (Galvanized) by Hot Dip Process.




Stainless Steel

Material in accordance with ASTM A240 (Type 304 or type 316).




Aluminum

Channel is extruded aluminum in accordance with ASTM B221 Type 6063-T6.



Plain



Plain finish designation means that the channel retains the oiled surface applied to the raw steel during the rolling process. The fittings have the original oiled surface of the bar-stock material.





CHANNEL STYLES

Power-Strut channel shown here comes in various depths and gauges to provide a range of strength.



PS 100 – 1 5/8" x 3 1/4"





PS 210 – 1 5/8" x 1 5/8"





PS 150 – 1 5/8" x 2 7/16"





PS 300 – 1 5/8" x 1 3/8"



PS 200 – 1 5/8" x 1 5/8"





PS 400 – 1 5/8" x 1"




CHANNEL TYPE/SIZES

Power-Strut channel is made from cold-rolled steel in various depths and gauges. This roll forming produces a uniform channel section held to MFMA-2 specifications.


PS 500 – 1 5/8" x 13/16"



Standard Channel




PS 200 2T2




Welded Channel

Slotted Back (SB)

2 3/4" x 7/8" Slots on 3" Centers




PS 200 2T3




Welded Channel

PS 520 – 1 5/8" x 13/16"




Holes (H)

9/16" Holes on 1 7/8" Centers




PS 200 2T4




Welded Channel

Elongated Holes (EH)

1 1/8" x 9/16" Slots on 2" Centers





PS 200 2T5




Welded Channel


PS 560 – 1 5/8" x 13/16"



Knockouts (K06)




PS 707




Channel Closure Strip

Slotted (S)

13/32" x 3" Slots on 4" Centers



PS 6151




Channel Closure Strip

ELECTRICAL


Power-Strut offers a versatile means of supporting lighting, conduits, cable & other portions of an electrical system. Power-Strut is listed as an electrical raceway by Underwriters Laboratories as specified by the NEC

PS 649...



Electrical Joiner

PS 1500




Porcelain Insulator

PS 2625



Wiring Stud Nut

PS 2660




Junction Box

PS 655...




End Cap

PS 1510



Cable Saddle

**PS 2631,
PS 2631D**



Fixture Hanger

PS 2661




Junction Box Cover

PS 658, PS 659




Channel Hanger

PS 1610




Cable Clamp

**PS 2632,
PS 2632D**




Channel Hanger

PS 2662 A




Hub Assembly

PS 702...




Fixture Hanger

PS 1801




Cable Clamp

PS 2636




Fixed Stud Nut

PS 2800...




Inside Strut Joiner

PS 722



Porce-A- Clamp

PS 2094




Receptacle Box

PS 2637




Fixture Nut

PS 3301




Fixture Hanger

PS 791




Adapter Plate

PS 2511...



End Cap with Knock-Out

PS 2639




Outlet Box

PS 803




Fixture Wiring Nipple

PS 2560...



Connector Fitting

PS 2640




Wire Retainer

BEAM CLAMPS

Designed for every loading condition

PS 85




Rod Support

PS 86



\"C\" Clamp

PS 93



Universal \"C\" Clamp

PS 94



Wide \"C\" Clamp

PS 95




\"C\" Clamp

PS 135X




Light Duty Beam Clamp

PS 685




Beam Clamp

PS 686



Beam Clamp

PS 855



\"I\" Beam Clamp

PIPE & CONDUIT CLAMPS


from light to heavy duty.

Conduit and O.D. Tubing clamps formed from punch press dies and are available in a wide variety of sizes.

BRACKETS


Pipe, shelf, or fitting and channel brackets designed to eliminate field fabrication and to speed installation.

**PS 858,
PS 865**




Hvy. Duty Beam Clamp

PS 871




Safety Anchor Strap

**PS 907,
PS 998**




"I" Beam Clamp

PS 2622




Beam Clamp

PS 2626




Beam Clamp

PS 2651



Beam Clamp

PS 2654




Column Attachment

PS 2656




U Bolt Clamp

PS 2657




Double U Bolt Clamp

**PS 004T THRU
PS 106N**




Cush-a-Clamp

PS 1450




One Hole Clamp

PS 51




Electrical Joiner

PS 1901




2 Piece Pipe Roller

PS 52E




Par. Pipe & Conduit Clamp

PS 1902




Pipe Roller Assemb.

PS 651




Channel Bracket

PS 809




Dbl. Channel Bracket

PS 661




Channel Bracket

PS 825 R or L



Single Pipe Axle Support

PS 826




Dbl. Pipe Axle Support

PS 67




Conduit Hanger

PS 3101




Cable & Conduit Hanger

PS 732



Shelf Bracket

PS 838 R or L




Shelf Bracket

PS 69, PS 70




E-Z Grip Hanger

PS 3126



Pipe Strap

PS 808



Channel Bracket

PS 3282




Channel Bracket

PS 270




Conduit Clamp

PS 3138




Parallel Pipe Clamp

PS 1000



EMT Conduit Clamp

PS 3792




Power Wrap

FITTINGS


Power-Strut has a wide variety of Fittings to meet all of your application requirements. All Power-Strut fittings are formed in punch press dies from mild, pickled & oiled, bar or strip steel. Plain or electro-galvanized fittings meet the requirements for ASTM k575 & A-576, or ASTM A-36.

PS 601




2 Hole Splice Plate

PS 613




"U" Support

PS 669



12 Hole Triple Wing C.

PS 719




Flat Angle Plate

PS 926



Strut Brace

PS 602




3 Hole Splice Plate

PS 616




4 Hole Splice Clevis

PS 678




3 Hole "U" Support

PS 745




3 Hole Corner Angle

PS 929




"U" Support

PS 603




2 hole End Angle C.

PS 619




Square Washer

PS 679




"U" Support

PS 781




4 Hole Open Angle C.

PS 978



"U" Support

PS 604




2 Hole Corner Angle C.

PS 624




2 Hole Closed Angle C.

PS 704




Slotted Joiner

PS 793




4 Hole Closed Angle C.

PS 2119



"U" Support

PS 605




3 Hole Corner Angle C.

PS 633




2 Hole Open Angle C.

PS 710




"U" Support

PS 888




4 Hole Splice Plate

PS 2128




**L or R,
4 Hole Corner Connector**

PS 606




3 Hole Corner Angle C.

PS 665




4 Hole Dbl. Corner C.

PS 712




Cross Plate

PS 913




10 Hole Dbl. Wing C.

PS 2504




Guided Square Washer

PS 607




4 Hole Corner Angle C.

PS 667




8 Hole Dbl. Corner C.

PS 714




Tee Plate

PS 922




**L or R,
2 Hole Corner Connector**

PS 2521




2 Wheel Trolley

PS 611




Zee Support

PS 668




6 Hole Triple Wing C.

PS 718




Flat Angle Plate

PS 923



5 Hole Dbl. Wing C.

PS 2522



4 Wheel Trolley


FASTENERS

Power-Strut nuts, bolts, and threaded rod Work with all your strut needs

CHANNEL NUTS


Channel nuts are Cold Form with 6 sharp teeth, then case hardened.

PS 2528



Trolley Beam Std. Support

PS 9402



2 Hole Hinge Connector

PS 83




Hex Nut

PS 211




Lock Washer

PS LS




Clamp Nut with Long Spring

PS 2528-1




Trolley Beam Hvy. Support

PS 9403



3 Hole Hinge Connector

PS 135



Rod Coupling

PS 230




Fender Washer

PS NS




Clamp Nut no Spring

PS 2648




\"U\" Support

PS 9404



4 Hole Hinge Connector

PS 146



Threaded Rod

PS 6024




Hex Screw

PS NS S



Shallow Clamp Nut no Spring

PS 3013



Post Base

PS 202




Eyelet

PS 6064




Square Set Screw

PS RS




Clamp Nut with Long Spring

PS 3025



Post Base

PS 203



Linked Eyelet w Stud

PS 6072




Round Head Screw

PS SS




Clamp Nut with Short Spring

PS 3033



Post Base

PS 204



Linked Eyelet

PS 6075




Slotted Hex Screw

PS TG




Top Grip Nut

PS 3064



Dbl. Column Post Base

PS 205



Eyelet with Stud

PS 6108




Square Nut

PS 517



Channel Nut with Stud

PS 3373




Univ. Corner Connector

PS 209



Flat Washer

PS 3500




Seismic Rod Stiffener

CONCRETE INSERTS


A selection of heavy-duty to light-duty "continuous" & "spot" concrete inserts is available for use in pre-cast, pre-stressed or poured-in-place concrete floors, walls or ceilings.

PS 152




Insert

PS 653




Type "B" End Cap

PS 285




Lt. Weight Concrete Insert

PS 654




Type "B" End Cap

PS 349



Continuous Concrete Insert (1 5/8" x 1 3/8")

PS 449



Continuous Concrete Insert (1 5/8" x 1")

POWER-STRUT VERSATILITY, EASY AS 1, 2, 3



1
Insert the clamping nut anywhere along the continuous slot channel. A 90° clockwise turn positions the nut's grooves and teeth with the turned channel edges.



2
The Power-Strut fitting provides the connection of channels.



3
Tighten the bolt(s) to secure the connection.

VERSATILE SOLUTIONS . . .

Power-Strut with its highly rated family of framing support solutions and accessories offers you:

- A variety of channel types produced in steel, aluminum, or stainless steel
- Products available in multiple finishes
- Aickinstrut Non-Metallic Framing System also available
- Widest selection of Components
- Customer and technical support team
- A range of shipping options
- Quick Service

Here you'll learn more about Power-Strut products, accessories, and their installation.

Lets Talk Strut!

KEY PRODUCTS

Below is a list of Power-Struts key products. These products are well stocked and available on short notice.

Key Channel and Fittings

- PS200 EH - 1 5/8" x 1 5/8", 10' Channel
- PS500 EH - 1 5/8" x 1 3/16", 10' Channel
- PS RS - Clamp Nut with Long Spring
- PS603 - 2 Hole End Angle
- PS607 - 4 Hole Corner Angle
- PS9404 - 4 hole Hinge Connector

Key Brackets and Clamps

- PS 1100 - Pipe Clamps
- PS 1300 - Tubing Clamps
- PS270 - Conduit Clamp
- PS651 - Channel Bracket
- PS106N - Cush-a-Clamp Assembly U-Bolt
- PS732 - Shelf Bracket

Other Key products


- PS2094 - 4" Receptacle Box with Knock-outs
- PS2803 - "Cross" Inside Strut Joiner
- PS712 - Cross Plate
- PS349 & PS449 - Concrete Inserts
- PS3373 - Univ. Corner Connector
- PS146 - Threaded Rod

GENERAL INFORMATION

Here are some examples of easy to create support structures. Use eye and hearing protection when cutting and fitting channel.


Standard Channel and Fitting Assembly

The factory punched holes in "H" series channel allow fittings to be attached to either side.




Electrical Panel Supports

Metal framing is ideal for mounting electrical or telecommunication panels. It allows you to create a floor stand, suspend panels from an overhead beam or even attach panels to adjacent structural steel. Bracing may be added for heavier load requirements.



Floor Mounted Stand

Island stands allow you to mount equipment or piping on both sides in trenches and in service aisles.



OVERVIEW, LOAD, AND ORDERING INFORMATION

This is an reference overview only. Always contact your local representative to make sure your ordering the correct products and accessories.

Overview and Load Information

The Power-Strut metal framing system can be regarded as a basic building material. Our metal framing system is an erector set concept, using channel and fittings to solve many applications.

You can conceal metal framing in the basic structure of a building or run it along the surface of walls, ceilings and floors. An endless array of fittings provide freedom to work at virtually any angle along any surface to shape a support system that fits your exact needs. Available finishes include hot-dipped galvanized, pre-galvanized, electro-galvanized and painted, along with material choices of steel, stainless steel and aluminum.

Beyond its versatility as a basic building material, metal framing is popular for more exotic applications such as clean rooms, satellite dish supports, x-ray supports, storage racks, theater screens, tunnel stanchions and offshore platform catwalks. While the uses of metal framing are truly unlimited, they fall into three major categories.

Power-Strut is an excellent solution in;

- **Electrical Lighting and Raceway Systems**
- **Mechanical Systems That Reduce Costs**
- **Mechanical Support of HVAC**
- **Plumbing and Fire Protection Systems**
- **OEM Components and Maintenance**

With over 8000 products it would be impossible to list all load information here. Load specifications are listed in the Power-Strut Engineering Catalog or is available from you local representative.

Ordering Information

For ordering information please contact your local Power-Strut sales representative.

For our quick list of available sales representatives go to our website. The regional sales representatives are list by state and can be found at **www.alliedeg.com**.


If you can't find a local representative, or have a technical questions call us at **800-882-5543**.

OVERHEAD SUPPORTS


Here are examples of proper ways to install overhead support systems. It is recommended, for safety reasons that overhead installations should require two technicians whenever possible.

Trapeze Support System


Power-Strut metal framing is ideal for electrical and mechanical pipe support applications.




Acceptable Methods to Hang Channels




Vertical to Horizontal



Ganged Pipe Support



Overhead Multi-Use Support Systems Using Channel Attached to "I" Beams




WALL MOUNT

Wall mounting is an optional way to install Power-Strut in locations where over-head support space is limited.


Supports for Threaded Rod Attachments Between Beams

Select channel size based on load requirements.




Organize & Control

Versatile Power-Strut installation of utility piping means that expansion is just a matter of inserting another pipe clamp!




Brackets

Stock brackets are available in lengths from 6" to 36".




Multi-Shelf or Utility Support




Supports for Threaded Rod Attachments to Single Beams

Versatile Power-Strut installation of utility piping means that expansion is just a matter of inserting another pipe clamp!




Cushioned Clamps

Improperly clamped tubes/pipes invite line failure. Power-Strut's Cush-a-Clamp® cushioned clamp provides protection against vibration, shock, surge noise and temperature variations.



Wall-Mounted Single Lines




RECOMMENDED METHODS

Here are recommended methods to use when cutting and fitting channel. Please use eye and hearing protection.


Ordinary Hacksaw

Using a hacksaw is a safe and accurate way for cutting any channel to the needed length.



Electric Band Saw


A table top electric band saw is a fast and accurate way of cutting channels to size. However, use caution since the saw blade may leave slightly rough or burred edges.



Cut-Off Saw


Low RPM cut-off saws with abrasive blades provide superior cuts.

Power table saws with carbon blades are not recommended since the blades cause large burrs and make handling the channel dangerous.



Wall Anchor

NOTE: For commonly used bolts (e.g., 3/8"), most standard socket heads will fit into the channel opening. For 1/2" or larger bolts, a special socket head must be used.




WARNINGS INFORMATION

Below are a few things not to do when you are cutting or working with channel.

Torch – Do not use this method


Use of a torch for cutting channel is not recommended. This technique is not accurate and can weaken the channel.



Hole Drilling – Make sure piece securely braced

Field drilling may be necessary for certain applications.

Improper drilling (e.g., holes too large, holes too close together, holes near bends) may cause structural weakness.



POWER-STRUT®

16100 S. Lathrop Avenue, Harvey, IL 60426

Tel. 800-882-5543

Fax 708-339-0615

www.alliedeg.com/powerstrut

ALLIED ELECTRICAL™ Group

• Power-Strut® Metal & Fiberglass Framing • Allied Tube & Conduit • AFC Cable Systems® • Cope® Cable Tray

Power-Strut, Cush-A-Clamps, Power-Angle, Cope, Allied Tube & Conduit, AFC Cable Systems, and Tyco are trademarks or registered trademarks of Tyco International and/or its affiliates in the United States and in other countries. All other brand names, product names, or trademarks belong to their respective owners.