


SCREW-SHOOTER ACCESSORIES


BIT HOLDERS • SOCKETS • EXTENSIONS • BITS AND FINDERS



| DESCRIPTION | SIZE | CATALOG NUMBER |
|---|---------|----------------|
| 3" Magnetic Bit Holder w/ cap | | 48-32-3025 |
| 3" Magnetic Bit Tip Holder Stainless Steel** | | 48-32-3070 |
| 3" Magnetic Bit Holder | | 48-32-3065 |
| 2" Non-Mag. Bit Holder | | 48-32-3050 |
| 2" x 1/4" Sq. Socket Driver | | 48-32-2050 |
| 4" x 1/4" Sq. Socket Driver | | 48-32-2055 |
| Hex Sockets Only Magnetic | 1/4" | 49-66-3000 |
| | 5/16" | 49-66-3010 |
| | 3/8" | 49-66-3020 |
| 1 Pc. Hex Socket Ext. Non-Magnetic | 5/16" | 49-66-3015 |
| 1 Pc. Hex Socket Extension Magnetic | 1/4" | 49-66-3006 |
| | 5/16" | 49-66-3016 |
| | 3/8" | 49-66-3026 |
| Bit and Finder Combinations* (Slotted Screws) 3-1/2" Long | 6F-8R | 48-30-2600 |
| | 8F-10R | 48-30-2625 |
| | 10F-12R | 48-30-2650 |
| | 12F-14R | 48-30-2675 |
| | 14F-16R | 48-30-2700 |


* Finders locate screwheads—improve bit driving.

POWER BITS FOR 1/4" DRIVE SYSTEMS



| DESCRIPTION | SCREW SIZE | CATALOG NUMBER |
|---|------------|----------------|
| 1-15/16" Long Bits for Slotted Head Screws | 6F-7R | 48-30-0500 |
| | 8F-10R | 48-30-0505 |
| | 10F-12R | 48-30-0510 |
| | 12F-14R | 48-30-0515 |
| 2" Long Phillips Bit | #1 | 48-30-1510 |
| | #2 | 48-30-1520 |
| | #3 | 48-30-1500 |
| 3" Long Phillips Bit | #2 | 48-30-1525 |


INSERT SOCKET AND ADAPTER



| DESCRIPTION | SHANK | CATALOG NUMBER | FOR USE WITH |
|---------------------|-------|----------------|--------------|
| Magnetic Bit Holder | 1/4" | 48-32-3055 | 48-32-1600* |
| 1/4" Socket Adapter | 1/4" | 48-32-2060 | 48-32-1600* |

* For use with the 48-32-1600 Hand-held Driver.


INSERT BITS



| DESCRIPTION | SIZE | CATALOG NO. |
|---|--------------|-------------|
| Phillips 1" Long | #0 | 48-32-1020 |
| | #1 | 48-32-1030 |
| | #1 (QTY. 10) | 48-32-1033 |
| | #1 (QTY. 25) | 48-32-1031 |
| | #1 (QTY. 50) | 48-32-1032 |
| | #2 | 48-32-1040 |
| | #2 (QTY. 10) | 48-32-1043 |
| | #2 (QTY. 25) | 48-32-1041 |
| | #2 (QTY. 50) | 48-32-1042 |
| | #2 | 48-32-1050 |
| Phillips Bit in Quantities of 10 Come Packaged in a Reusable Vinyl Pouch. See below. | #2 (QTY. 10) | 48-32-1053 |
| | #2 (QTY. 25) | 48-32-1051 |
| | #2 (QTY. 50) | 48-32-1052 |
| | #3 | 48-32-1070 |
| #3 (QTY. 10) | 48-32-1073 | |
| Phillips 3-1/2" (90 mm) Long | #2 | 48-32-1060 |
| Slotted Screw Insert Bits 1" Long | 0F-1R | 48-32-1300 |
| | 3F-4R | 48-32-1320 |
| | 6F-8R | 48-32-1330 |
| | 5F-6R | 48-32-1340 |
| | 8F-10R | 48-32-1360 |
| | 10F-12R | 48-32-1370 |
| | 12F-14R | 48-32-1380 |
| Slotted 1-3/4" (45 mm) Long | 8F-10R | 48-32-0420 |
| Allen Head 1" Long | 5/64" | 48-32-1400 |
| | 3/32" | 48-32-1420 |
| | 7/64" | 48-32-1440 |
| | 1/8" | 48-32-1460 |
| | 9/64" | 48-32-1480 |
| Torx® 1" Long <i>Torx® is a registered tradename of CAMCAR.</i> | T10 | 48-32-1510 |
| | T15 | 48-32-1515 |
| | T20 | 48-32-1520 |
| | T25 | 48-32-1525 |
| | T30 | 48-32-1530 |
| | T40 | 48-32-1540 |
| Pozi driv® | #1 | 48-32-1120 |
| | #2 | 48-32-1125 |
| Frearson 1-1/8" Long (Reed & Prince) | #1 | 48-32-1110 |
| | #2 | 48-32-1115 |
| Square Drive (Robertson) 1" Long | #0 | 48-32-1201 |
| | #1 | 48-32-1205 |
| | #2 | 48-32-1210 |
| | #2 (QTY. 10) | 48-32-1211 |
| #3 | 48-32-1215 | |
| Magnetic Insert Socket | 1/4" | 49-66-0800 |

Reduced Diameter Insert Bits Ideal for Drywall.

ACCESSORIES



HEX SOCKET EXTENSION MAGNETIC

49-66-3005

Set includes one each of:
49-66-3006 1/4" Magnetic Socket.
49-66-3016 5/16" Magnetic Socket.
49-66-3026 3/8" Magnetic Socket.

NEW!



7-PIECE SCREWDRIVER AND 3-1/2" SLOTTED POWER BIT SET

48-30-0102

Includes No. 1, 2, & 3 Phillips 1/4" hex bits, 48-30-2601 (6-7x3-1/2" slotted bit B), 48-30-2626 (8-10x3-1/2" slotted bit) and 48-30-2651 (10-12x3-1/2" slotted bit). For use on cordless driver/drills and power screwdrivers.



PHILLIPS INSERT BITS

48-32-1033

10 Pack of #1 Phillips Insert Bits.

48-32-1043

10 Pack of #2 Phillips Reduced Shank Insert Bits.

48-32-1053

10 Pack of #2 Phillips Insert Bits.

48-32-1073

10 Pack of #3 Phillips Insert Bits.

SQUARE DRIVE INSERT BITS

48-32-1211

10 Pack of #2 Square Drive Insert Bits.



SCREWDRIVER BIT SET

48-30-0200

Includes 4 Phillips, 5 slotted, 5 hex, 4 square recess, 6 Torx®, 2 Pozidriv® bits, 1/4" adapter, magnetic bit holder and 1/4" hex driver.



HAND SCREWDRIVER
48-32-1600



NEW!

3-PIECE 3-1/2" SLOTTED POWER BIT SET

48-30-2706

Includes a 48-30-2601 (6-7x3-1/2" slotted bit B), 48-30-2626 (8-10x3-1/2" slotted bit) and 48-30-2651 (10-12x3-1/2" slotted bit). For use on cordless driver/drills and power screwdrivers.




MAGNUM® DRYWALL SCREW-SHOOTER



6749-1

5.5 AMPS
VARIABLE SPEED
0-2500 RPM



SPECIFICATIONS

| CATALOG NUMBER | VOLTS AC ONLY | AMPS | NO LOAD RPM | BIT SHANK SIZE | SPINDLE OFFSET | LENGTH | NET WGT. LBS. | SHIP. WGT. LBS. |
|----------------|---------------|------|-------------|----------------|----------------|---------|---------------|-----------------|
| 6749-1 | 120 | 5.5 | 0-2500 | 1/4" HEX | 7/8" | 11-1/2" | 3-3/4 | 5-1/2 |

STANDARD EQUIPMENT: #2 Phillips Bit 48-32-1050, Magnetic Bit Holder 48-32-3025 Magnetic Bit Holder Locator 49-26-1040 and 8' 3-Wire Quik-Lok Cord Set 48-76-4008.

TRIGGER SPEED CONTROL REVERSING MODEL

Powerful MILWAUKEE Built Motor Provides Greater Torque • All Ball and Roller Bearing Construction • Comfortable Two Finger Trigger • Four Position Hand Grip For Any Application

- **Snap-Action Positive Drive Clutch**
Prevents tip-to-tip engagement of clutch jaws at the beginning and at the end of a screw driving cycle. This reduces clutch wear, and when depth sensing nosepieces are used, greatly prolongs clutch life.
- **Quiet Operation Fan Design**
- **Lockable Trigger Switch**
- **Removable Brush Cartridge System**
Change brushes in less than one minute anywhere, with only a screwdriver.
- **3-Wire Quik-Lok® Cord Sets**
For fast secure attachment. 8' cord 48-76-4008 is standard equipment. 25' cord 48-76-4025 is also available.



GENERAL PURPOSE SCREW-SHOOTER KIT

6767-6 (KIT)

DOUBLE INSULATED

5.0 AMPS
VARIABLE SPEED
0-2500 RPM, INCLUDES THE FOLLOWING:
STEEL CARRYING CASE, SLOTTED BIT AND FINDER SET, PKG. OF 10 #2 PHILLIPS INSERT BITS, HEX SOCKET SET AND BELT CLIP




49-26-1081 Tek® Locator Assembly




49-26-1035 Drywall Pop Off Locator



49-66-3016 5/16" Magnetic Hex Socket



48-32-3070 Stepped Magnetic Insert Bit Holder



48-32-1050 #2 Phillips Insert Bit



30-37-0055 Nose Guide



48-67-0115 Belt Clip Kit

TRIGGER SPEED CONTROL REVERSING MODEL

Complete Screwdriver Package For Decking, Assembling And Drywall Projects. For The Professional Application Of Drywall, Self-Drilling/Tapping Fasteners (TEKS®), Wood And Sheet Metal Screws (TEKS Registered trademark of Illinois Tool Works, Inc.)

- **Snap-Action Drive Clutch**
- **Quiet Operation Fan Design**
- **Pop-Off Locator Nose Maintains Depth Setting When Removed And Reattached**
- **Triple Sealed Output Shaft**
- **Non-Marring Locators**
- **Powerful MILWAUKEE Built Motor**
- **Minimum Offset For Close Quarter Work**
- **Engineered For Balanced Design**
- **Impact Resistant, Non-Conductive Glass Reinforced Nylon Motor Housing And Handle**
- **Lightweight Die Cast Gear Case And Diaphragm**
- **Self-Stopping Brush Carbons**
- **Lockable Trigger Switch**
- **2-Wire Quik-Lok® Cord* Sets**
Quick detachment from tool for tangle free carrying and storage. Instant field repair. 2-wire, 10'-16 gauge rubber cord 48-76-5010. 25' cord 48-76-5025 is also available.

SPECIFICATIONS

| CATALOG NUMBER | VOLTS AC ONLY | AMPS | NO LOAD RPM | BIT SHANK SIZE | SPINDLE OFFSET | LENGTH W/TEK LOCATOR | LENGTH W/DRYWALL LOCATOR | NET WGT. LBS. | SHIP. WGT. LBS. |
|----------------|---------------|------|-------------|----------------|----------------|----------------------|--------------------------|---------------|-----------------|
| 6767-6 | 120 | 5.0 | 0-2500 | 1/4" HEX | 3/4" | 10-1/2" | 11-3/4" | 3-5/8 | 13 |

STANDARD EQUIPMENT FOR 6767-6 - 49-26-1035 and 49-26-1081 Drywall and Tek's Pop Off Locators, 5/16" Magnetic Hex Socket, Magnetic Insert Bit Holder, #2 Phillips Insert Bit, Belt Clip Kit and 10' 2-Wire Quik-Lok Cord Set 48-76-5010, Slotted Bit and Finder Set 48-30-2705, Package of 10-#2 Phillips Insert Bits 48-32-1053, Hex Socket Set 49-66-3005 and Steel Carrying Case 48-55-0711.

* 2-Wire Quik-Lok Cord is not compatible with previous 3-Wire Quik-Lok configurations.

DRYWALL SCREW-SHOOTERS

ELECTRONICS

6758-6 **DOUBLE INSULATED**

VARIABLE SPEED 0-4000 RPM

- 10' Rubber-Jacketed Cord With Separate Strain Relief
- Snap Action Clutch For Longer Clutch Life And Quiet Operation



6755-1 **DOUBLE INSULATED**

VARIABLE SPEED 0-4000 RPM

- 10', 2-Wire 16 Gauge Quik-Lok® Cord
- Snap Action Clutch For Longer Clutch Life And Quiet Operation



6747-1 **DOUBLE INSULATED**

VARIABLE SPEED 0-2500 RPM

- For framing Applications
- Snap Action Clutch
- 10' Rubber-Jacketed Cord With Separate Strain Relief



30-37-0046 Nose Guide

SPECIFICATIONS

| CATALOG NUMBER | VOLTS AC ONLY | AMPS | NO LOAD RPM | BIT SHANK SIZE | SPINDLE OFFSET | LENGTH | NET WGT. LBS. | SHIP. WGT. LBS. |
|----------------|---------------|------|-------------|----------------|----------------|---------|---------------|-----------------|
| 6758-6 | 120 | 5.0 | 0-4000 | 1/4" HEX | 3/4" | 11-3/8" | 3-1/4 | 5 |
| 6755-1 | 120 | 5.0 | 0-4000 | 1/4" HEX | 3/4" | 11-3/8" | 3-1/4 | 5 |
| 6747-1 | 120 | 5.0 | 0-2500 | 1/4" HEX | 3/4" | 11-3/4" | 3-5/8 | 5 |

STANDARD EQUIPMENT: FOR ALL MODELS - #2 Phillips Bit 48-32-1050, Magnetic Bit Holder 48-32-3065, Locator Assembly 49-26-1035 and Belt Clip 48-67-0115.

TRIGGER SPEED CONTROL REVERSING POWERFUL 5 AMP MILWAUKEE BUILT MOTOR

All Ball and Roller Bearings • Minimum Offset for Close Quarter Work


- Conveniently Located, Sealed Long-Life Reversing Switch
- Self-Stopping Long-Life Brushes
- Equipped With Lockable Trigger Switch
- Lightweight Die Cast Diaphragm And Gear Case
- Triple Sealed Output Spindle And Sealed Gear Case
- Impact Resistant, Lightweight, Glass Reinforced Nylon Motor Housing And Handle
- Slim Profile Pop-Off Locator Nose Maintains Depth Setting When Removed And Reattached
- Quiet Operation Fan Design
- High-Strength Belt Clip

6755-1 FEATURE

- **2-Wire Quik-Lok® Cord* Sets** Quick detachment from tool for tangle free carrying and storage. Instant field repair. 2-wire, 10'-16 gauge rubber cord 48-76-5010. 25' cord 48-76-5025 is also available.

* 2-wire Quik-Lok Cord is not compatible with previous 3-Wire Quik-Lok configurations.

ACCESSORIES



LOCATOR

49-26-1035

BELT CLIP

48-67-0115

TOOL HOLSTER

49-17-0200 Fits all screw-shooters.

STEEL CARRYING CASE WITH TRAY

48-55-0711 For all screw-shooters 13-1/2" long, 6" high, 8-3/4" wide.



SPECIAL SCREW-SHOOTERS



6583-1

DOUBLE INSULATED
5.0 AMPS
VARIABLE SPEED
0-1000 RPM



6783-1

DOUBLE INSULATED
5.0 AMPS
VARIABLE SPEED
0-2500 RPM



VARIABLE TRIGGER SPEED CONTROL, REVERSING MODELS

Powerful MILWAUKEE Built 5 Amp Motor

- **2-Wire Quik-Lok Cord Set**
- **Quiet Operation Fan Design**

■ **Simplified Adjustable Torque Release Clutch**

Torque output is easily changed externally by turning adjustment collar which positively holds setting. Clutch disengages and driving action stops when pre-set torque is reached.

■ **Adjustable Torque**

6583-1 10 – 120 in./lbs.
6783-1 10 – 90 in./lbs.

■ **Quick Release Bit Holding Mechanism**

■ **No Bit Guide Required**

■ **2-Wire Quik-Lok® Cord* Sets**

Quick detachment from tool for tangle free carrying and storage. Instant field repair. Tools come with 2-wire, 10'-16 gauge rubber cord No. 48-76-5010. A 25' cord No. 48-76-5025 is also available.

*2-Wire Quik-Lok Cord is not compatible with previous 3-Wire Quik-Lok configurations.

■ **6583-1 Capacity:**

- 1/4" machine screws and nuts
- 1/4" thread cutting screw
- 5/16" sheet metal screw
- Soft wood with pilot hole – to 5/16" Lag
- Soft wood without pilot hole – to #16
- Hard wood with pilot hole – to #16
- Hard wood without pilot hole – to #12

■ **6783-1 Capacity:**

- 1/4" self-drilling screw in 1/4" cold rolled steel
- #12 self-drilling screw in 1/2" cold rolled steel
- #12 wood screw
- 1/4" thread cutting screw
- 5/16" sheet metal screw
- 1/4" machine screw

SPECIFICATIONS

| CATALOG NUMBER | VOLTS AC ONLY | AMPS | NO LOAD RPM | BIT SHANK SIZE | SPINDLE OFFSET | LENGTH | NET WGT. LBS. | SHIP. WGT. LBS. |
|----------------|---------------|------|-------------|----------------|----------------|---------|---------------|-----------------|
| 6583-1 | 120 | 5.0 | 0-1000 | 1/4" HEX | 3/4" | 11-1/2" | 4 | 5-1/2 |
| 6783-1 | 120 | 5.0 | 0-2500 | 1/4" HEX | 3/4" | 11-1/2" | 4 | 5-1/2 |

STANDARD EQUIPMENT FOR 6583-1 – 6F-8R Bit and Finder No. 48-30-2600, 10F-12R Bit and Finder No. 48-30-2650, #2 Phillips Insert Bit No. 48-32-1050, Non Mag. Bit Holder No. 48-32-3050 and Belt Clip Kit No. 48-67-0115. **FOR 6783-1** – 5/16" Hex Socket Extension No. 49-66-3016 and Belt Clip Kit No. 48-67-0115.

SPECIAL SCREW-SHOOTERS

ELECTRONICS


6798-6 **DOUBLE INSULATED**
SPECIAL SCREW-SHOOTER
VARIABLE SPEED 0-2500 RPM
INCLUDES 2-WIRE, 10' RUBBER JACKETED CORD WITH SEPARATE STRAIN RELIEF

30-37-0055
 Nose Guide



6793-1
HIGH TORQUE MAGNUM®
SCREW-SHOOTER 0-2000 RPM
INCLUDES 3-WIRE, 8' QUIK-LOK CORD



6794-1
MAGNUM® SCREW-SHOOTER
0-2500 RPM
INCLUDES 3-WIRE, 8' QUIK-LOK CORD

TRIGGER SPEED CONTROL REVERSING, POWERFUL MILWAUKEE BUILT MOTOR

All Ball and Roller Bearings • For Driving Self-Drilling/Tapping TEKS® Fasteners

TEKS Registered Trademark of Illinois Tool Works, Inc.

FOR MODEL 6798-6

- **Snap-Action Drive Clutch**
Engages when pressure is applied. Driving action stops and clutch disengages when pressure is released or when locator contacts work surface. Depth control is adjustable in increments of 1/64" from outside of tool.
- **Non-Marring Locators**
- **Lightweight Die Cast Diaphragm And Gear Case**
- **New, Quiet Operating Fan Design**
- **Quiet, Long Life Operation**

FOR MODEL 6793-1

- **Lower RPM**
Provides for reduced screw point burning and 25% more torque than Model 6794-1 for fastening 1-1/8" plywood and other compressed decking materials to 1/8" steel joists using self-drilling/tapping fasteners.

EXCLUSIVE MAGNUM® FEATURES:

- **Powerful 5.5 AMP Motor**
- **Removable Brush Cartridge System**
Change brushes in less than one minute, anywhere, with only a screwdriver. Self-stopping brushes. Instant brush replacement by using spares stored in cartridge system.



- **Three-Wire Quik-Lok® Cord Sets**
 Quick detachment from tool for tangle free carrying and storage. Instant field repair. Quik-Lok with twist lock plug cord sets also available.

| 3-Wire Quik-Lok® Cord Sets | | NEMA Plug Type |
|---|---------------------------------------|----------------|
| 48-76-4008 | 3-Wire 8' Quik-Lok | 5-15P |
| 48-76-4025 | 3-Wire 25' Quik-Lok | 5-15P |
| 3-Wire Quik-Lok® Cord Sets With Twist Lock Plug | | |
| 48-76-4108 | 3-Wire 8' Quik-Lok W/Twist Lock Plug | L5-20P |
| 48-76-4125 | 3-Wire 25' Quik-Lok W/Twist Lock Plug | L5-20P |

SPECIFICATIONS

| CATALOG NUMBER | VOLTS AC ONLY | AMPS | NO LOAD RPM | BIT SHANK SIZE | SPINDLE OFFSET | LENGTH | 1/4" COLD ROLLED STEEL | 1/2" COLD ROLLED STEEL | NET WGT. LBS. | SHIP. WGT. LBS. |
|----------------|---------------|------|-------------|----------------|----------------|---------|------------------------|------------------------|---------------|-----------------|
| 6798-6 | 120 | 5.0 | 0-2500 | 1/4" HEX | 3/4" | 10-3/4" | 1/4" SCREW | NO. 12 SCREW | 3-3/4 | 5-1/2 |
| 6793-1 | 120 | 5.5 | 0-2000 | 1/4" HEX | 7/8" | 10-1/2" | 1/4" SCREW | NO. 12 SCREW | 3-3/4 | 5-1/2 |
| 6794-1 | 120 | 5.5 | 0-2500 | 1/4" HEX | 7/8" | 10-1/2" | 1/4" SCREW | NO. 12 SCREW | 3-3/4 | 5-1/2 |

STANDARD EQUIPMENT FOR 6798-6: Tek Locator Assembly 49-26-1081, 5/16" Hex One Piece Socket Extension 49-66-3016, Belt Clip Kit 48-67-0115 and 2-Wire, 10' Rubber Jacketed Cord.
FOR 6793-1 AND 6794-1: 5/16" Hex One Piece Socket Extension 49-66-3016, 1/4" Locator 49-26-0250, 5/16" Locator 49-26-0312, 3/8" Locator 49-26-0375 and 3-Wire, 8' Quik-Lok Cord Set 48-76-4008.