

POWER TOOL ACCESSORIES

CIRCULAR SAW BLADES

WOOD CUTTING CIRCULAR SAW BLADE



OVERVIEW

Milwaukee blades offer faster cutting and extra long life for contractors. Carbide teeth made of C3 grade micro ground carbide keeps the cutting edge sharper for longer periods of time. A hardened alloy steel body is used to ensure straight, accurate cuts. Specially engineered heat vents and expansions slots prevent blade distortion and increase blade life. All these features add up to a good quality blade that contractors can depend on, time and time again.

FEATURES

- Anti-Kickback Shoulder
- Precision Ground Carbide
- Expansion Slots For Truer Cuts Under Heavy Use

WOOD CUTTING CIRCULAR SAW BLADE

Diameter	Number of Teeth	Application	Hook Angle	Kerf Thickness	Tooth Grind	SKU
5-3/8"	16	Framing	20°	.051"	ATB	48-40-4105
6-1/2"	24	Framing	20°	.063"	ATB	48-40-4108
6-1/2"	40	Finish	20°	.063"	ATB	48-40-4112
7-1/4"	140	Plywood	0°	.095"	ATB	48-40-4138
7-1/4"	16	Framing	20°	.071"	ATB	48-40-4116
7-1/4"	24	Framing	20°	.071"	ATB	48-40-4120
7-1/4"	40	Finish	20°	.071"	ATB	48-40-4126
8-1/4"	18	Framing	20°	.094"	ATB	48-40-4148
8-1/4"	24	Framing	20°	.094"	ATB	48-40-4150
8-1/4"	40	Finish	20°	.094"	ATB	48-40-4152
10"	24	Ripping	20°	.094"	ATB	48-40-4160
10"	40	General Purpose	20°	.094"	ATB	48-40-4162
10"	60	Finish	15°	.094"	ATB	48-40-4164
10"	80	Finish	10°	.094"	ATB	48-40-4166
10-1/4"	28	Framing	20°	.110"	ATB	48-40-4170
10-1/4"	40	Finish	20°	.110"	ATB	48-40-4172

METAL CUTTING CIRCULAR SAW BLADES



OVERVIEW

Milwaukee metal circular saw blades were specifically designed to exceed the expectations of contractors for blade life, cut quality, and speed in the most demanding metal cutting applications – without a lubricant. A hand-tensioned, hardened alloy steel body extends blade life and delivers the highest quality cuts available. Carbide tipped teeth with Alternate Top Bevel grind shear through metal leaving burr-free, cool-to-touch cuts.

FEATURES

- Dry - No lubricant required, saving time and money with less mess
- Cool - No extreme heat buildup preserves blade life and allows handling the work piece immediately
- Clean - No burrs eliminates secondary operations saving time and money

METAL CUTTING CIRCULAR SAW BLADES

Diameter	Number of Teeth	Application	Hook Angle	Kerf Thickness	Tooth Grind	SKU
5-3/8"	30	Ferrous Metal	0°	.063"	ATB	48-40-4070
5-3/8"	50	Non-Ferrous Metal	0°	.063"	ATB	48-40-4075
6-1/2"	48	Ferrous Metal	0°	.063"	MATB	48-40-4015
6-1/2"	60	Non-Ferrous Metal	3°	.075"	MATB	48-40-4005
6-7/8"	36	Ferrous Metal	0°	.065"	MATB	48-40-4016
6-7/8"	52	Non-Ferrous Metal	10°	.071"	MATB	48-40-4006
7-1/4"		Ferrous Metal		.063"		48-40-4140
7-1/4"	48	Non-Ferrous Metal	5°	.071"	TCG	48-40-4132
8"	42	Ferrous Metal, 3/32" and thicker	0°	.073"	MATB	48-40-4515
8"	50	Ferrous Metal 3/32" and Thinner	0°	.073"	MATB	48-40-4520
8"	60	Aluminum, 1/4" - 2" Bar Stock, 1/4"-1-1/4" Flat Stock	10°	.073"	TCG	48-40-4530
8"	60	Aluminum, 1/4" and under Bar Stock and Flat Stock	0°	.073"	TCG	48-40-4540
14"	72	Ferrous Metal	0°	.086"	ATB	48-40-4505
14"	90	Stainless Steel	0°	.086"	MATB+FTG	48-40-4510

CIRCULAR SAW ACCESSORIES

CIRCULAR SAW ACCESSORIES

Description	SKU
Dust Collection Kit	49-22-8105
Extension Kit	49-22-8108
Hold Down Bar Kit	49-22-8100
Mid-Way Fence Kit	49-22-8110
Quick Stop Gauging Kit	49-22-8102
Riser Support	48-08-0360
Tool Stand	48-08-0350
Wedge Clamps	48-08-0380
Wheel Kit	49-22-8106
Work Center	48-08-0450