



Metallics



VERTICAL MOUNT THREADED ROD ANCHOR SYSTEM

SAVES TIME AND COST FROM TRADITIONAL HANGING METHODS

Drill, Drive, Done!



STOCK NO.	UPC NO.	ROD SIZE	SCREW DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
WOOD						
JSMW14201	78360	1/4-20	5/16 x 2 1/4	1.69	25	52.45/ea pkg
JSMW38161	78365	3/8-16	5/16 x 2 1/4	1.55	25	62.98/ea pkg

FOR 1/2-13 THREADED ROD SEE THE ADAPTER BELOW.



METAL						
JSM14201	78400	1/4-20	1/4-20 x 1 #3 DRILL POINT	1.43	25	68.25/ea pkg
JSM38161	78405	3/8-16	1/4-20 x 1 1/2 #3 DRILL POINT	1.77	25	68.83/ea pkg

FOR 1/2-13 THREADED ROD SEE THE ADAPTER BELOW.



CONCRETE						
JSMC14201	78370	1/4-20	5/16 x 2 1/4 1/4 DRILL SIZE	1.78	25	76.53/ea pkg
JSMC38161	78375	3/8-16	5/16 x 2 1/4 1/4 DRILL SIZE	1.64	25	65.78/ea pkg

FOR 1/2-13 THREADED ROD SEE THE ADAPTER BELOW.



**ADAPTER TO CONVERT 3/8-16 WOOD, CONCRETE AND STEEL
VERTICAL MOUNT FASTENERS TO ACCEPT 1/2-13 THREADED ROD.**

ADAPTOR						
SME270	41340	3/8-16 to 1/2-13	Threaded Rod		25	45.33/ea pkg



DRIVER						
SMDB21	78420	1/4 & 3/8	Driver	.10	1	29.70/ea

PLEASE CALL FOR TECHNICAL INFORMATION
OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST