

## PVC-Coated Conduit Bodies and Fittings

Unique sealing ring and groove design for optimum performance!

### OCAL-BLUE® Double-Coat and Stainless Steel Hubs

- Captive sealing ring won't buckle or slip during installation and provides a complete 360° seal — even when conduit isn't perpendicular to the enclosure
- Hexagonal/splined body and locknut enable fast and easy installation
- Insulated throat molded from 105° C-rated thermoplastic, UL94V0 flammability rated
- Sharper and deeper teeth provide a more penetrating bite for improved bonding to the enclosure
- Zinc or copper-free aluminum with a nominal .040" (40 mil) PVC coating bonded to exterior — in blue, white, gray or custom colors
- Pressure-sealing sleeves protect your connections
- Also available uncoated in 316-grade stainless steel




HUB1-1/4-G  
PVC-Coated Zinc Hub

STG6-G  
PVC-Coated Zinc Grounded Hub



H050GRSST  
Stainless Steel  
Grounded Hub



Cat. No.	Color
<b>HUB1 -</b>	
- = space for color identifier	G = Gray
	W = White
	B = Blue
Custom colors also available.	

### Knockout Hubs

PVC-COATED ZINC HUB CAT. NO.	PVC-COATED ALUMINUM HUB CAT. NO.	PVC-COATED ZINC GROUNDED HUB CAT. NO.	316 STAINLESS GROUNDED HUB CAT. NO.	PIPE SIZE		DIMENSIONS (UNCOATED HUB)									
				IN.	MM	A (OVERALL DIA.)		B		C		D (MAX. PANEL THICKNESS)		E (THROAT DIA.)	
						IN.	MM	IN.	MM	IN.	MM	IN.	MM	IN.	MM
HUB1/2-	HUB1/2SA-	STG1-	H050GRSST	½	16	1.44	36.58	1.56	39.62	.88	22.35	.19	4.83	.59	14.99
HUB3/4-	HUB3/4SA-	STG2-	H075GRSST	¾	21	1.44	36.58	1.59	40.39	.91	23.11	.19	4.83	.78	19.81
HUB1-	HUB1SA-	STG3-	H100GRSST	1	27	2.00	50.80	1.81	45.97	1.06	26.92	.25	6.35	1.00	25.40
HUB1-1/4-	HUB1-1/4SA-	STG4-	H125GRSST	1¼	35	2.38	60.45	1.88	47.75	1.06	26.92	.25	6.35	1.31	33.27
HUB1-1/2-	HUB1-1/2SA-	STG5-	H150GRSST	1½	41	2.75	69.85	1.88	47.75	1.06	26.92	.25	6.35	1.53	38.86
HUB2-	HUB2SA-	STG6-	H200GRSST	2	53	3.25	82.55	1.94	49.28	1.16	29.46	.25	6.35	1.97	50.04
HUB2-1/2-	HUB2-1/2SA-	STG7-	—	2½	63	3.75	95.25	2.56	65.02	1.56	39.62	.25	6.35	2.41	61.21
HUB3-	HUB3SA-	STG8-	—	3	78	4.38	111.25	2.44	61.98	1.59	40.39	.25	6.35	2.97	75.44
HUB3-1/2-	HUB3-1/2SA-	STG9-	—	3½	91	5.00	127.00	2.72	69.09	1.63	41.40	.25	6.35	3.41	86.61
HUB4-	HUB4SA-	STG10-	—	4	103	5.50	139.70	2.72	69.09	1.63	41.40	.25	6.35	3.88	98.55
HUB5-	HUB5SA-	STG11-	—	5	129	6.88	174.75	3.03	76.96	1.94	49.28	.25	6.35	4.94	125.48
HUB6-	HUB6SA-	STG12-	—	6	155	7.69	195.33	3.16	80.26	2.00	50.80	.31	7.87	6.00	152.40

### T&B® Grounding and Bonding Locknuts for Hubs

- Available in zinc, copper-free aluminum or 316 stainless steel
- UL File No. E-3060, CSA File No. 4484
- Use as replacement locknuts for the hubs featured above



ZINC CAT. NO.	ALUMINUM CAT. NO.	316 STAINLESS CAT. NO.	PIPE SIZE		DIAMETER		HEIGHT		GROUND SCREW	MAX. COND. SIZE	
			IN.	METRIC SIZE DESIGNATOR*	IN.	MM	IN.	MM		AWG	SQ. MM
L050GR-TB	L050GRA-TB	L050GRSST	½	16	1.50	38.10	.41	10.41	#10-32 x ¼"	#10	6
L075GR-TB	L075GRA-TB	L075GRSST	¾	21	1.69	42.93	.41	10.41	#10-32 x ¼"	#10	6
L100GR-TB	L100GRA-TB	L100GRSST	1	27	2.00	50.80	.41	10.41	#10-32 x ¼"	#10	6
L125GR-TB	L125GRA-TB	L125GRSST	1¼	35	2.38	60.45	.47	11.94	¼-20 x ¼"	#10	6
L150GR-TB	L150GRA-TB	L150GRSST	1½	41	2.75	69.85	.47	11.94	¼-20 x ⅝"	#8	10
L200GR-TB	L200GRA-TB	L200GRSST	2	53	3.25	82.55	.47	11.94	¼-20 x ⅝"	#8	10
L250GR-TB	L250GRA-TB	—	2½	63	3.75	95.25	.69	17.53	¼-20 x ⅝"	#6	16
L300GR-TB	L300GRA-TB	—	3	78	4.38	111.25	.72	18.29	¼-20 x ⅝"	#6	16
L350GR-TB	L350GRA-TB	—	3½	91	5.00	127.00	.72	18.29	¼-20 x ⅝"	#6	16
L400GR-TB	L400GRA-TB	—	4	103	5.50	139.70	.72	18.29	¼-20 x ⅝"	#4	25
L500GR-TB	L500GRA-TB	—	5	129	6.63	168.40	.72	18.29	⅜-16 x ⅝"	#2	35
L600GR-TB	L600GRA-TB	—	6	155	7.69	195.33	.72	18.29	⅜-16 x ⅝"	#1	50

\* Metric size designator (ANSI C80.1-1994).