


## Mounting Bases for Heavy-Duty Applications

### Designed for indoor or outdoor use and heavy-duty applications

- Quick and easy to install on existing metal framing channel
- Installs with a push and twist
- Smooth design protects cable insulation
- Takes range of cable diameters



When fastening wire bundles, cables or hoses to framing channels, you can cut costs considerably by using the Ty-Rap® cable clamp. It's made of smooth, weather-resistant nylon and designed to protect cable insulation and hoses from wear or damage, which can occur with metal clamps. The clamp may be used for both indoor or outdoor applications. It quickly installs in the framing channel with a simple push and twist. It requires no screws, nuts or tools. The clamp fits all 1-1/2 in. and 1-5/8 in. channels regardless of channel depth.



Cat. No.	Channel Size	Max. Tie Width Accom.		Std. Pkg.
	(in.)	(in.)	(mm)	
<b>Framing Channel Clamp</b>				
<b>TC5363X</b>	1-1/2 and 1-5/8	0.301	7.65	50


Made from high-impact weather-resistant black nylon.  
For use in temperatures ranging from -40°C to 85°C (-40°F to 185°F).

### Specially designed head is range-taking

- Quick, easy installation without cumbersome adhesives or epoxies
- Provides a quick, easy and dependable means of attaching cable and wires to masonry surfaces
- Installs by tapping it into a drilled hole
- It's immediately ready to accept a cable tie and wire bundle — no tedious surface preparation; no waiting for adhesives to set
- Replaces a variety of anchors, clamps, screws and adhesives
- Designed for both indoor and outdoor applications
- Only two sizes to stock — reduces inventory

Cat. No.	Hole Size in Masonry	Max. Tie Width Accom.		Std. Pkg.
	(in.)	(in.)	(mm)	
<b>Framing Channel Clamp</b>				
<b>TC5358</b>	1/4	0.190	4.83	100
<b>TC5359</b>	3/8	0.500	12.70	50

Made of a special impact and ultraviolet-resistant black nylon.  
For use in temperatures ranging from -40°C to 85°C (-40°F to 185°F).



### Weather-resistant!

- For use with lashing ties up to .500 in. width (i.e. TY5409)
- High impact



Cat. No.	Mounting Method	Tid Width Accom.		Maximum Width		Length		Std. Pkg.
		(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	
<b>Ty-Rap® Mounting Base for Lashing Tie</b>								
<b>TC5355</b>	#8 screws	0.500	12.70	0.750	19.05	1.750	44.45	25
<b>TC5356</b>	#10 screws							
<b>TC5357</b>	1/4 in. screws							

Black nylon construction.  
For use in temperatures ranging from -40°C to 85°C (-40°F to 185°F).

## Mounting Bases for Heavy-Duty Applications



The Stud Mount Cable Fastening System includes a range of bases and the custom drill bit that mounts all sizes.



During installation, the custom Stud Mount drill bit application tool ejects itself from mounting base, ensuring proper torque and preventing cracking or breaking of the mount from being overtightened.



Virtually unlimited harnessing flexibility is provided in the unique 10-position harness design of the Stud Mount base.

### A fast and simple harnessing method for neat, versatile wire management

Thomas & Betts Stud Mount Fastening System is a fast and simple harnessing method for neat, versatile, cord, cable, hose, and wire management. Using a custom drill bit for your 3/8 in. power drill, the Stud Mount base is quickly attached onto a threaded stud or bolt to the proper torque—every time. The innovative “X” design of the base reliably supports many types of cable or hose assemblies using a wide range of conventional T&B® cable ties. Designed with 10 separate lashing positions, the Stud Mount offers unlimited wire harnessing arrangements. T&B’s Stud Mount is available in four convenient stud bolt sizes.

- Great for harnessing wires, cables and hoses to truck and trailer chassis
- Fast, easy installation, using standard 3/8 in. power drill and application tool or simply hammer on
- Unlimited harnessing flexibility using conventional T&B® cable ties
- Custom drill bit quickly installs base to proper torque — won’t crack or break mounting base due to being overtightened
- Unique 4-way multi-directional design
- 10-position harness capability
- Available for 3/8 in., 1/2 in., 5/8 in., and 3/4 in. stud/bolt sizes
- Self-tapping thread design for reliable installation onto stud
- High pull-out strength of 500+ lb.

Cat. No.	Description	Stud Size (in.)	Material	Colour	Std. Pkg.
<b>Stud Mount Fastening System</b>					
<b>XMNY-375-0-D</b>	Mount Fastener	3/8	Nylon, UV Stabilized	Black	500
<b>XMNY-500-0-D</b>		1/2			
<b>XMNY-625-0-D</b>		5/8			
<b>XMNY-750-0-D</b>		3/4			
<b>WTXM</b>	Application Tool	—	Tool Steel	—	1

Material: Impact-resistant weatherable black nylon.  
For use in temperatures ranging from -40°C to 85°C (-40°F to 185°F).