


LyteCaster *Lyte* 5", Shallow Incandescent Convertible IC/Non-IC Frame-in Kit

Project:	Catalog No:	Mfg:
Location:	Fixture Type:	Qty:
Notes:		Lamps:



Ceiling Cutout: 5 3/8" Diameter

Ordering guide Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

example: 1004SIC + 1005

Frame-In Kit Series		Reflector Trims (See Individual Reflector Trim Specification Sheets)							
Catalog number		Anodized Open Downlights			Open Downlights		Eyeball	Enclosed Diffusers	Wall Washers
		Cone		Satin Cone	Baffles	Basic White			
1004SIC	LyteCaster 5" frame-in kit (with Integral Screw)	1012	1013CD	1008	1005	1071	1087	1024*	1085*
1004SICN	LyteCaster 5" frame-in kit (with Integral Nail)	1013	1013NM	1008NM	1005WH				
		1013WH	1013BKNM	1010	1005NM				
		1013BK	1013CDNM	1010NM	1005BNM				
					1076				
					1076WH				

* For Non-IC applications only.

Features

- Housing:** .032" (#20 ga.) Aluminum. UL listed convertible IC/NON-IC. 2" vertical adjustment in ceiling. Can be removed for access to junction box and ceiling plenum. 5 1/2" tall for use in 2" X 6" joist construction and shallow plenum applications. AirSeal® housing minimizes air leakage to less than 2 CFM at 1.57 PSF (or 75pa), which complies with Model Energy Code (Section 602.3.3) and Washington State Energy Code (Section 502.4) and reduces heat loss and condensation in ceiling.
- Mounting Frame:** .048" (#18 ga.) galvanized steel. Locks into position along length of mounting bars with locking spring and bendable slot. (3) slots 90° apart simplify alignment.
- Junction Box:** 2" X 4" X 3 1/2" (22 cu. in.) .032" (#22 ga.) galvanized steel. UL listed for maximum of 8 (#12 ga.) 1104SIC/N and 6 (#12 ga.) 1004SIC/N 90°C through branch circuit conductors. Cable clamp permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors.
- Mounting Bars:** .059" (#16 ga.) galvanized steel. Bars pivot for easy attachment and wire-in below ceiling line. Bars extend to accommodate 16" to 24" O.C. joist spacing. Bars can accommodate 9" O.C. joist spacing after a slight field modification (See Instruction Sheet). 1004SIC features integral self-tapping phillips screws for secure attachment to wood or metal construction. The 1004SICN features integral nails for secure attachment to wood. Both attach to T-bar ceilings without the need of accessories.
- Socket Housing:** Impact extruded aluminum or galvanized steel. Attached trim retaining spring secures trim to any height on housing wall.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 Volt 200° C) leads to junction box.
- Thermal Protector:** Meets NEC and UL requirements. Located inside housing.

Options and Accessories

AirSeal Kit: LAS56

Note: Use only if factory installed tape or knockouts are removed from vertical adjustment slots in housing wall.

Labels

UL (Type IC/NON-IC Convertible, Suitable for Damp Locations). Complies with Air Leakage Requirements stated in the Model Energy Code and the Washington State Energy Code.

Romex is a registered trademark of General Cable Industries Inc.