









Pass & Seymour



Wall Plates Toggle Switch, Duplex & Single Receptacle Openings

Junior-Jumbo & Jumbo Plastic & Metal

Description	Color	Nylon	Thermoset		Metal		
		TradeMaster® Jumbo	Junior-Jumbo	Jumbo	Material	Junior-Jumbo	Jumbo
			Smooth	Smooth		Smooth	Smooth
Toggle Switch Openings							
One Gang 	Ivory White Brown Gray Light Almond	TPJ1-I TPJ1-W TPJ1 TPJ1-GRY TPJ1-LA	SPJ1-I SPJ1-W SPJ1 SPJ1-LA	SPO1-I SPO1-W SPO1	Brass 302S/S	SBJ1 SSJ1	SBO1 SSO1
Two Gang 	Ivory White Brown Gray Light Almond	TPJ2-I TPJ2-W TPJ2 TPJ2-GRY TPJ2-LA	SPJ2-I SPJ2-W SPJ2 SPJ2-LA	SPO2-I SPO2-W SPO2	Brass 302S/S	SBJ2 SSJ2	SSO2
Three Gang 	Ivory White Brown Gray Light Almond	TPJ3-I TPJ3-W TPJ3 TPJ3-GRY TPJ3-LA	SPJ3-I SPJ3-W SPJ3 SPJ3-LA		302S/S	SSJ3	SSO3
Four Gang 	Ivory White Brown Gray Light Almond	TPJ4-I TPJ4-W TPJ4 TPJ4-GRY TPJ4-LA	SPJ4-I SPJ4-W SPJ4 SPJ4-LA		302S/S		SSO4
Duplex Receptacle Openings							
One Gang 	Ivory White Brown Gray Light Almond	TPJ8-I TPJ8-W TPJ8 TPJ8-GRY TPJ8-LA	SPJ8-I SPJ8-W SPJ8 SPJ8-LA	SPO8-I SPO8-W SPO8 SPO8-LA	Brass 302S/S	SBJ8 SSJ8	SBO8 SSO8
Two Gang 	Ivory White Brown Gray Light Almond	TPJ82-I TPJ82-W TPJ82 TPJ82-GRY TPJ82-LA	SPJ82-I SPJ82-W SPJ82 SPJ82-GRY SPJ82-LA	SPO82-I SPO82-W SPO82	302S/S	SSJ82	SSO82
Three Gang 					302S/S		SSO83
Single Receptacle Openings							
One Gang 	Ivory White Brown Gray Light Almond	TPJ7-I TPJ7-W TPJ7 TPJ7-GRY TPJ7-LA	SPJ7-I SPJ7-W SPJ7 SPJ7-LA		302S/S	SSJ7	SSO7

Wall Plates Specifications



Thermoset SP Series



Nylon TP Series



Screwless Polycarbonate SW Series

Application

Pass & Seymour/Legrand's broad line of Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour/Legrand devices.

Thermoset Plastic Wall Plates Features

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available – Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

TradeMaster® Thermoplastic Wall Plates Features

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"

Screwless Polycarbonate Wall Plates Features

- Molded of .065" thick polycarbonate with matte finish.
- Subplate made of .042" zinc-plated steel.
- Available in "SW" series, extra 1/8" width and height than Standard size plates.
- Available in Ivory, White, Gray, Black, and Light Almond.
- Oversized opening to accommodate all NEMA 26 decorator-style openings.

Metal Wall Plates Features

- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze or galvanized steel.
- Standard, Jumbo, and Tandem size plates available, as well as special Panel size plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes. Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Materials

- Type 302 Stainless Steel, non-magnetic, .032" nominal thickness, brushed finish. This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Type 430 Stainless Steel, magnetic, .032" nominal thickness, brushed finish. Less corrosion-resistant than Type 302, but ideal for general service in high abuse applications in industrial plants, commercial, and institutional buildings.
- Chrome, Brushed and Polished Brass, .040" thick. 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications. Lacquered to prevent corrosion.
- Aluminum, .040" thick. Lustrous satin finish. Lacquered to prevent corrosion.
- Galvanized Steel. Used only for Handy Box Plates.
- Brushed Bronze, .040" thick. 90% copper, 10% zinc. Lacquered to prevent corrosion.



302 Stainless Steel



Polished Brass



Brushed Brass




Aluminum

Wall Plates Specifications

Pass & Seymour




Standard Size Wall Plates					
<ul style="list-style-type: none"> Standard size wall plates for all applications. Best fit for surface mount boxes. 			<ul style="list-style-type: none"> Available in plastic and metal only. 		
Dimensions					
1 gang	2.75" x 4.5"	4 gang	8.125" x 4.5"	7 gang	13.62" x 4.5"
2 gang	4.56" x 4.5"	5 gang	10" x 4.5"	8 gang	15.44" x 4.5"
3 gang	6.375" x 4.5"	6 gang	11.812" x 4.5"		




STANDARD

TradeMaster® Wall Plates					
<ul style="list-style-type: none"> Extra 3/16" width and height than Standard size wall plates. Provide better sheet rock coverage with standard size appearance. Available in unbreakable nylon 6 construction only. Screws pre-installed in the duplex, toggle, and decorator single gang plates. 					
Dimensions					
1 gang	2.9375" x 4.6875"	3 gang	6.563" x 4.6875"	5 gang	10.188" x 4.6875"
2 gang	4.75" x 4.6875"	4 gang	8.375" x 4.6875"	6 gang	12" x 4.6875"




TRADEMASTER STANDARD

Screwless Polycarbonate Wall Plates					
<ul style="list-style-type: none"> Extra 1/8" width and height than Standard size wall plates. Provide better sheet rock coverage with standard size appearance. Molded of .065" thick polycarbonate. Subplate made of .042" zinc-plated steel. Oversized opening to accommodate all NEMA 26 decorator-style openings. 					
Wall Plate Dimensions					
1 gang	3.10" x 4.87"	3 gang	6.724" x 4.87"	5 gang	10.348" x 4.87"
2 gang	4.912" x 4.87"	4 gang	8.536" x 4.87"	6 gang	12.16" x 4.87"
Subplate Dimensions					
1 gang	2.85" x 4.62"	3 gang	6.474" x 4.62"	5 gang	10.098" x 4.62"
2 gang	4.662" x 4.62"	4 gang	8.286" x 4.62"	6 gang	11.910" x 4.62"




SCREWLESS

Junior-Jumbo Wall Plates					
<ul style="list-style-type: none"> Extra 3/8" width and height than Standard size wall plates. Additional coverage for sheet rock gaps. 			<ul style="list-style-type: none"> Available in plastic and metal only. 		
Dimensions					
1 gang	3.125" x 4.87"	3 gang	6.75" x 4.87"		
2 gang	4.93" x 4.87"	4 gang	8.56" x 4.87"		




JUNIOR-JUMBO

TradeMaster Jumbo Wall Plates					
<ul style="list-style-type: none"> Extra 3/16" width and height than Junior-Jumbo size wall plates. Provide additional coverage for sheet rock gaps, matching the appearance of the TradeMaster Plates. Available in unbreakable nylon 6 construction only. Screws pre-installed in the duplex, toggle, and decorator single gang plates. 					
Dimensions					
1 gang	3.3125" x 5.0625"	3 gang	6.9375" x 5.0625"		
2 gang	5.125" x 5.0625"	4 gang	8.75" x 5.0625"		



TRADEMASTER JUMBO

Jumbo Wall Plates					
<ul style="list-style-type: none"> Extra 3/4" width and height than Standard size wall plates. Largest size wall plates to cover larger wall damage. 			<ul style="list-style-type: none"> Available in plastic and metal only. 		
Dimensions					
1 gang	3.5" x 5.25"	3 gang	7.12" x 5.25"		
2 gang	5.31" x 5.25"	4 gang	8.93" x 5.25"		



JUMBO