



Complete Fixture consists of Frame-In Kit and Reflector Trim. Select each separately.

Uniframe™ Frame-In Kit	Uniframe™ Compact Fluorescent Performance Series Reflector Trims								
	Vertical Open	Vertical Wall Wash - Single	Vertical Wall Wash - Double	Horizontal Open	Horizontal Wall Wash - Single	Horizontal Wet Location Lensed / Diffused			Horizontal Cross Blade
1101F18U 18w Quad/Triple, GX24q-2 Base 120v – 0.17amp max 277v – 0.08amp max	1101CL	1101CLSW	1101CLDW	1101HCL	1101HCLSW	Clear Lens	Fresnel	Opal Lens	1101HACB 1101HWHC
	1101CD	1101CDSW	1101CDDW	1101HCD	1101HCDSW	1101HCLC	1101HCLF	1101HCLD	
	1101WH	1101WHSW	1101WHDW	1101HWH	1101HWHSW	1101HCDC	1101HCDF	1101HCDO 1101HWHC 1101HWHF 1101HWHO	
1101F2642U 26w Quad/Triple, GX24q-3 Base 120v – 0.24amp max 277v – 0.11amp max 32w Triple, GX24q-3 Base 120v – 0.31amp max 277v – 0.13amp max 42w Triple, GX24q-4 Base 120v – 0.38amp max 277v – 0.17amp max	Universal Series Reflector Trims (Reference Trim Spec Sheet for Recommended Lamping)								
	Performance Cone	Cone	Satin Cone	Baffle	Wall Wash	Wet Location	Cross Blade		
	1113CFL 1113CDCFL	1112* 1113* 1113BK* 1113WH 1113CD* 1145 1143 1146 / 1146CD 1144 / 1144CD	1108* 1110*	1105* 1105BNM 1105WH 1176 1176WH	1135 1135WH 1195 1196 1196CD	1121 1124 1134 1177SH 1178SH 1190	1132		

*Add NM suffix to catalog number for Natural Metal flange and finish.

Features

- Mounting Frame:** .036" (#20ga.) Galvanized Steel. Accommodates all ceilings up to 1-1/2" thick; including existing or inaccessible areas.
- Trim Clips:** "Push In / Twist Out" Stainless Steel clips hold reflector flush to ceiling.
- Junction Box:** 2" x 4" x 3-1/2" (22cu.in.) .032" (#22ga.) galvanized steel. UL Listed for maximum of 8 (#12ga.) through branch circuit conductors.
- Uniframe™ Mounting System – Grid Ceiling:** Tool free mounting in grid ceilings. .036" (20ga.) Galvanized Steel interlocking slide bars adjust to 24-1/8" long accommodating 24" O.C. Ceiling Grid. Adjustable speed clamps for positive attachment to grid ceiling systems.
- Uniframe™ Mounting System – Wood Joist Ceiling:** Integral nailing tabs, alignment guides, fastener holes and bendable strapping guides for wood joist installation. Galvanized Steel interlocking slide bars adjust from 12-15/16" to 24-1/8" long to accommodate 16" and 24" O.C. joist spacing, with or without strapping. Suitable for Steel Ceiling construction using standard 1/2" EMT, (See Instruction Sheet).
- Ballast:** 120V – 277V UL Listed Electronic Ballast, end of lamp life protection, class "P" thermally protected, class "A" sound rating. Minimum starting temperature is 0°F.
- Socket:** Four-pin base, molded thermoplastic socket, prewired with No. 18 AWM leads to ballast.
- Socket Housing:** .036" (#20ga.) Galvanized Steel housing attaches to reflector trim by spring clip for precise optic alignment.

Labels

cULus Listed. Suitable for Damp Locations.

Accessories

1967A Extra Thick Ceiling Adapter (2" thk)

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	

631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710
 We reserve the right to change details of design, materials and finish.
 www.lightolier.com © 2008 Philips Group • E0408