





HR-LED87

LEDme® Button Light

WAC LIGHTING

Responsible Lighting®



Fixture Type:

Catalog Number:

Project: _____

Location: _____

PRODUCT DESCRIPTION

Designed for recessed or surface mounted installations, delivering strong light output with the latest in LED technology.

FEATURES

- Recessed or surface mounting
- Quick and easy installation
- Includes 72" lead wire
- 3000K color temperature
- 70,000 hour rated life
- UL and CUL Listed
- 5 year WAC Lighting product warranty

FIXTURE PERFORMANCE

	Watt	Lumens	Efficacy	CRI
HR-LED87	5W	180	36 Lm/W	85
HR-LED87S	4.8W	155	32.3 Lm/W	

SPECIFICATIONS

Construction: Die-cast aluminum fixture, stamped steel housing for surface mount. Glass beam spread lens.

Wiring: Includes 72" pre-installed wires that lead out through the top.

Transformers: Class 2, 24V remote and plug-in transformers allow for up to 20 button lights to be wired together. Use a multiple terminal block to wire up to 6 fixtures in a neat under cabinet installation without the use of open splices (see below).

Light Source: Six 3000K LEDs.

Dimming: May be dimmed to 10% with an electronic low voltage (ELV) dimmer.

Mounting: *Recessed*– 2 1/8" cutout hole. Compression springs hold fixture firmly in place. *Surface*– Screw housing cover to surface, compress springs and insert into cover. **Not recommended for use in ceiling.**

Finish: Black (BK), Dark Bronze (DB) and White (WT) powder coat, electroplated Brushed Nickel (BN), Copper Bronze (CB) and Chrome (CH).

Standards: UL & cUL Damp Location Listed.


ORDER NUMBER

Model #	Color Temp	Finish
HR-LED87	BK BN CB CH DB WT
HR-LED87S	
HR-LED87-27	
HR-LED87S-27	




Example: **HR-LED87S-27-BN**

- Minimizes wiring back to transformer
- Minimal voltage drop, power supplied using a variable current
- If one fixture goes out the rest remain on



FINISHES



RETROFIT RECESSED HOUSING

Model #	Finish
HR-LED-COV	BK, BN, CB, CH, DB, WT

Use to replace low voltage HR-88 and HR-86 button lights using existing wiring and cutout.

CLASS 2 ELECTRONIC TRANSFORMERS

Type	Model	Dim	Input	Output	Power Up To	Dimensions
Remote	EN-2460-RB2	ELV	120V	24V AC/60W	12 × LED87	6 1/2" × 1 5/8" × 1 1/4"
	EN-24100-RB2	ELV	120V	24V AC/96W	20 × LED87	6 1/2" × 1 5/8" × 1 1/4"
	EN-24100-277-RB2-T	0-10V	277V	24V DC/96W	20 × LED87	12 5/8" × 3 1/4" × 2"
Plug-In	EN-2460-P-AR	ELV	120V	24V AC/60W	12 × LED87	2 3/4" X 1 5/8" X 1 3/4"


MULTIPLE TERMINAL BLOCK

Model #	Dimensions
MTB-01	L: 3 1/4" W: 1 3/4" H: 7/8"


FROSTED LENS ACCESSORY

Model #
LENS-13-FR


Round - 2700K



Round - 3000K



Square - 2700K



Square - 3000K

