


# Meter Centers

## Uni-PAK Metering: WPL Ringless Style, Lever Bypass

METER CENTERS  
2



The WPL Uni-PAK metering is available for those utilities that require a lever bypass for residential & commercial applications. WPL units provides an all-in-one solution for applications needing from 2–6 meter positions. The products are designed for easy installation and include features not found on competitors, including:

- Side mounted handles to help in lifting
- Provisions for one, two, or three incoming conductors per phase and neutral
- Hanging bracket to suspend the unit during installation
- 225 amp branch tenant provisions @ 100,000 AIC
- Full line of 2–6 position devices
- “In-line” (column) construction for 2–4 position devices
- Ability to install QP breakers in QS provisions

### Ringless Style Uni-PAK 120/240V 1 Phase, 3 Wire, Lever Bypass

Max. Tenant Main <sup>①</sup>	Bus Amperage	Meter Positions Per Pak	Old Catalog Number	NEW Catalog Number Available Sept. 2011	Breaker Provision	Max. AIC	Dimensions <sup>①</sup>			5th Jaw <sup>①</sup> Assembly	Line Lugs Wire Range
							Height	Width	Depth		
225	400	2	SP4212RJL	WPL4212RJ	QP, QPH, HQP, MP-T, MP-HT, MP-MT, QS, QSH, QSHH, HQS, HQSH	100,000	36.75	33.50	9.00	INCL.	3/8" Stud – Field installed lugs
		3	SP4312RJL	WPL4312RJ			49.75				
		4	SP4412RJL	WPL4412RJ			62.75				
	600	5	SP6512RJL	WPL6512RJ			49.75	53.38			
		6	SP6612RJL	WPL6612RJ				57.63			
		NA	WPL10612RJ								

### Lug Kits<sup>②</sup>

Catalog Number	Wire Range
H56476	3/0-800/94 kcmil
H60162	(2) 1/0-250 kcmil OR (1) #4-600 kcmil
H68752-1	(3) #6-250 kcmil
H56732-2	(2) #4-350 kcmil
H56732-M	(2) #4-500 kcmil

① Dimensions and information shown are for WPXXX units. For old style information, please see the 2008 Speedfax.

② Lug kits should be chosen based on the wire size being run to the unit. Wire should be sized according to the National Electrical Code. A total of 3 lugs are required to wire the line side of the device.