

Compact Fluorescent Lamps

Bulb Identification	5-2	Specialty	
Lamp Locator	5-2	Colored Spiral®	5-17
Base Identification	5-4	Germicidal	5-17
Introduction	5-4	Film and TV Lighting HLBX 4-Pin	5-18
Product Information	5-5	Footnotes	5-19
Section Headings	5-6	Caution Notices	5-19
Plug-in Lamps		Cross-Reference	5-21
2-Pin Low Wattage Biax®	5-7	GE Enhanced Plug-in Product Comparison	5-22
4-Pin High Lumen Biax®	5-7		
2-Pin Double Biax®	5-8		
4-Pin Double Biax®	5-8		
4-Pin Triple Biax®	5-8		
4-Pin High Output Biax®	5-9		
4-Pin 2D®	5-9		
Self-Ballasted Lamps			
Bright From The Start® A Shape	5-10		
Bright From The Start® Decorative Globes	5-10		
Bright From The Start® Reflectors	5-10		
Reveal® All Glass A Shape	5-11		
Reveal® Globes	5-11		
Reveal® Reflectors	5-11		
Reveal® Spiral® 3-Way	5-11		
Reveal® Spiral® T3	5-11		
Reveal® Bright From The Start® A Shape	5-12		
Reveal® Bright From The Start® Reflectors	5-12		
Reveal® Bright From The Start® Decorative Globes	5-12		
Spiral® T2	5-12		
Spiral® T3	5-13		
Spiral® T3 Dimming	5-15		
Spiral® T4 and T5 Hi Lumen	5-15		
Spiral® 3-Way	5-15		
Spiral® GU 24	5-15		
Reflectors/Indoor PAR	5-15		
Outdoor	5-16		
Decorative Ceiling Fan Medium Base	5-16		
Decorative Ceiling Fan Candelabra Base	5-16		
Decorative A Shapes	5-16		
Decorative Bullet	5-16		
Decorative Candle Candelabra Base	5-16		
Decorative Candle Medium Base	5-17		
Decorative Globes	5-17		

Incandescent

Halogen

High Intensity
Discharge

Fluorescent

Compact
FluorescentLED Lamps
and Systems

Stage and Studio

Miniature, Sealed
Beam and Automotive

Projection

Compact Fluorescent Lamps

Bulb Identification




NOMINAL LENGTH:
Overall length including base or pins.

Note: Lamp drawings are not drawn to scale. Be sure to check size and dimension information when identifying each lamp.






To convert inches to millimeters, multiply the dimension (in inches) by 25.4 (i.e. 1.5" x 25.4 = 38.1 mm).

Lamp Locator



Plug-in Lamps


Lamp Locator (continued)



Self-Ballasted Lamps

Compact Fluorescent Lamps

Base Identification



Introduction

- GE Compact Fluorescent lamps offer many advantages:
- Dramatic energy cost savings...up to 77% vs. incandescent lamps of comparable light output
 - Extra long life...most last 8 to 10 times longer, and some last up to 20 times longer, than standard incandescent lamps
 - High light output comparable to, and in many cases exceeding, incandescent lamps replaced
 - Excellent color rendering...rare earth tri-phosphor provides such high-quality color you won't believe it's fluorescent. Most types offer a choice of color options, from warm to cool, to let you select the tone and atmosphere you need.
 - A choice of wattages, shapes and sizes to meet your lighting needs. Designed to fit everything from table lamps to wall sconces and ceiling fixtures.
 - Many lamps use amalgam technology which provides stable lumen performance when operated in any position, over a wider range of ambient temperatures.

Compact Fluorescent Brand Name Cross-Reference

GE	OSRAM/SYLVANIA	PHILIPS
2D®	—	—
Biax®	Dulux® S	PL-S
High Lumen Biax®	Dulux® L	PL-L
Double Biax®	Dulux® D, D/E	PL-C
Triple Biax®	Dulux® T/E	PL-T
Quad Biax®	—	—
High Output Biax®	—	PL-H
Spiral®	Dulux® EL Twist	EL Twist

ATTENTION: This brand-name cross-reference chart is provided only as a quick reference. Other lamp company brand listings may only represent a near equivalent, versus an identical match to GE Lighting brands. Individual lamp manufacturers' performance specifications should be consulted. Lamp performance may be affected by environmental conditions, ballast type and/or other auxiliary equipment.

Product Information

Plug-in Lamps

2-Pin Low Wattage Biax® (pg 5-7)

- Compact size offers fixture and design flexibility
- GX23 and G23 bases are preheat lamps with internal starters
- 13-watt version also available with internal electronic starter, providing flicker-free instant on
- Available in warm and cool color temperatures
- TCLP Compliant

4-Pin High Lumen Biax® (pg 5-7)

- Available in a range of sizes and wattages for innovative compact luminaires
- High efficiency and outstanding performance in fixtures make them ideal for 2X2, 1X1 and indirect fixtures
- Available in warm to cool color temperatures; excellent color rendering

2-Pin Double Biax® (pg 5-8)

- More compact than low-wattage Biax® CFLs with higher lumen output—suitable for a broad range of applications
- Preheat lamps with starters; not suitable for use with dimming ballasts
- 26-watt version also available with internal electronic starter, providing flicker-free instant on
- Available in warm to cool color temperatures
- TCLP Compliant

4-Pin Double Biax® (pg 5-8)

- More compact than low-wattage Biax® CFLs with higher lumen output—suitable for a broad range of applications
- Dimmable and compatible with electronic ballasts
- Available in warm to cool color temperatures
- TCLP Compliant

4-Pin Triple Biax® (pg 5-8)

- GE's shortest, most compact Biax® lamp. 17-31% shorter than similar wattage Double Biax® lamps.
- 4-Pin, dimmable and compatible with electronic ballasts
- Available in a wide range of wattages: from 13 to 42 watts
- Available in warm to cool color temperatures
- TCLP Compliant

4-Pin High Output Biax® (pg 5-9)

- GE's highest light output compact fluorescent lamps
- High efficacy 72-75 LPW
- Dimmable, available in 5 colors (2,700 to 5,000K)
- Suitable for high-bay lighting
- TCLP Compliant

4-Pin 2D® (pg 5-9)

- Unique shape suitable for broad range of applications
- Uniform light distribution
- High light output – up to 200W incandescent equivalent

Self-Ballasted Lamps

Spiral® (pg 5-12)

- Long life – up to 12,000 hours or more
- One-piece unit screws directly into incandescent sockets
- Wide variety of wattages to meet application needs
- T2 & T3 Spiral® CFLs provide economical solution with small overall size
- The 42-watt T4 Spiral® CFL provides a 150W incandescent replacement in the smallest possible size (fits an 8.5" harp)
- Color-enhanced CFL Reveal® mimics the color of incandescent and halogen Reveal® lamps

3-Way (pg 5-15)

- T3 and T4 lamps available

GU 24 (pg 5-15)

- Long life – 10,000 hour rating
- Simple twist and lock design allows quick and easy lamp change
- Fits all fixtures with GU 24 base

Reflectors/Indoor PAR (pg 5-15)

- R20, R30, R40 and PAR38 glass reflectors available to meet application needs
- Medium based; fits most incandescent reflector applications
- R30 and R40 lamps available with dimming functionality

Decorative Shapes (pg 5-16)

- Variety of shapes (A-Line, Bullet, Candle, Globe, and Post) and wattages to meet all needs
- One-piece unit screws directly into incandescent sockets
- Candle-shaped CFLs available in both medium base and candelabra base

Specialty (pg 5-17)

- T3 13-watt Spiral® CFLs are available in green, red, blacklight, orange, yellow and blue

Incandescent

Halogen

High Intensity
Discharge

Fluorescent

Compact
FluorescentLED Lamps
and Systems

Stage and Studio

Miniature, Sealed
Beam and Automotive


Projection

Compact Fluorescent Lamps

Headings in this catalog section

The following terms and descriptions can help you when checking Compact Fluorescent lamp specifications and when ordering


products. Within each product line, lamps are divided into families, within these families, lamps are then listed by wattage.



Base	Watts	Nominal Length (in)	Order Code	Description	Case Qty	Volts	Rated Life (hrs)	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Fact.	THD	TCLP Compliant Plug-Ins	EOL Protection Plug-Ins	ENERGY STAR®	Additional Information	Caution Notice	Footnotes
------	-------	---------------------	------------	-------------	----------	-------	------------------	----------------	-------------	--------------	-----	-----------------------	-------------	-----	-------------------------	-------------------------	--------------	------------------------	----------------	-----------



Self-Ballasted Lamps

Spiral®																				
Med	10	4.4	15829	FLE10HT3/2/827	10	120	8000	520	420	2700	82	5	0.6	120			★	T3 Spiral®, Boxed	153	1,7,8,9,10



WHEN YOU DON'T KNOW THE LAMP DESCRIPTION

1. Identify bulb shape next to lamp information.
2. Measure bulb diameter using ruler in appendix section page D-1 to determine width in eighths of an inch.
3. Identify base type using table on page 5-4.
4. Find your lamp in the table containing the bulb shape, size and base.

Base	Watts	Nom. Length (in)	Order Code	Description	Case Qty	Rated Life (hrs)	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min Starting Temp (°F)	TCLP Compliant Plug-Ins	EOL Protection Plug-Ins	Additional Information	Caution Notice	Footnotes	
Plug-in Lamps																	
2-Pin Low Wattage Biax®																	
	G23	5	4.2	97551	F5BX/827/ECO	100	10000	265	220	2700	82	0	*		151	1,2	
		5	4.2	97553	F5BX/841/ECO	100	10000	265	220	4100	82	0	*		151	1,2	
		7	5.3	97554	F7BX/827/ECO	100	10000	425	350	2700	82	0	*		151	1,2	
		7	5.3	97556	F7BX/835/ECO	100	10000	425	350	3500	82	0	*		151	1,2	
		7	5.3	97557	F7BX/841/ECO	100	10000	425	350	4100	82	0	*		151	1,2	
		9	6.6	97558	F9BX/827/ECO	100	10000	600	500	2700	82	0	*		151	1,2	
		9	6.6	97560	F9BX/835/ECO	100	10000	600	500	3500	82	0	*		151	1,2	
	GX23	9	6.6	97561	F9BX/841/ECO	100	10000	600	500	4100	82	0	*		151	1,2	
		13	7.0	97573	F13BX/827/ECO	100	10000	825	710	2700	82	32	*		151	1,2	
		13	7.0	97574	F13BX/830/ECO	100	10000	825	710	3000	82	32	*		151	1,2	
		13	7.0	97569	F13BX/835/ECO	100	10000	825	710	3500	82	32	*		151	1,2	
		13	7.0	97571	F13BX/841/ECO	100	10000	825	710	4100	82	32	*		151	1,2	
		13	7.0	97572	F13BX/850/ECO	100	10000	784	675	5000	80	32	*		151	1,2	
		13	7.0	97562	F13BX/E/827/ECO	100	10000	825	710	2700	82	-4	*		Internal Electronic Starter	151	1,2
		13	7.0	97563	F13BX/E/830/ECO	100	10000	825	710	3000	82	-4	*		Internal Electronic Starter	151	1,2
4-Pin High Lumen Biax®																	
	2G11	18	9.0	16649	F18BX/SPX30 10PK	40	10000	1200	1080	3000	82	25			151	1,2,4,6	
		18	9.0	16053	F18BX/SPX35 10PK	40	10000	1200	1080	3500	82	25			151	1,2,4,6	
		18	9.0	16940	F18BX/SPX41 10PK	40	10000	1200	1080	4100	82	25			151	1,2,4,6	
		18	10.0	17174	F18BXSPX30RS10PK	40	20000	1250	1130	3000	82	50			151	1,2,6,13	
		18	10.5	17175	F18BXSPX35RS10PK	40	20000	1250	1130	3500	82	50			151	1,2,6,13	
		18	10.5	17176	F18BXSPX41RS10PK	40	20000	1250	1130	4100	82	50			151	1,2,6,13	
		18	10.5	12521	F18BX/SPX65/RS	40	20000	1160	1050	6500	82	50			151	1,2,6,13	
		27	12.8	16944	F27BXSPX30RS10PK	40	12000	1800	1620	3000	82	50			151	1,2,6,13	
		27	12.8	16948	F27BXSPX35RS10PK	40	12000	1800	1620	3500	82	50			151	1,2,6,13	
		27	12.8	16951	F27BXSPX41RS10PK	40	12000	1800	1620	4100	82	50			151	1,2,6,13	
		39	16.5	16538	F39BXSPX30RS10PK	40	12000	2850	2510	3000	82	50			151	1,2,6,13	
		39	16.5	15867	F39BXSPX35RS10PK	40	12000	2850	2510	3500	82	50			151	1,2,6,13	
		39	16.5	16952	F39BXSPX41RS10PK	40	12000	2850	2510	4100	82	50			151	1,2,6,13	
		40	22.5	16953	F4030BXSPX30 10P	40	20000	3150	2840	3000	82	50			151	1,2,6,13	
		40	22.5	20444	F40/30BXSPX30-36	36	20000	3150	2840	3000	82	50		Bulk Pack	151	1,2,6,13	
		40	22.5	16648	F40/30BX/SPX35	40	20000	3150	2840	3500	82	50			151	1,2,6,13	
		40	22.5	20446	F40/30BXSPX35-36	36	20000	3150	2840	3500	82	50		Bulk Pack	151	1,2,6,13	
		40	22.5	16954	F40/30BX/SPX41	40	20000	3150	2840	4100	82	50			151	1,2,6,13	
		40	22.5	20447	F40/30BXSPX41-36	36	20000	3150	2840	4100	82	50		Bulk Pack	151	1,2,6,13	
		40	22.5	10490	F40/30BX/SPX50RS	36	20000	2900	2700	5000	80	50		Bulk Pack	151	1,2,6,13	
		25	21.5	75399	F40/25BX830/IS/WM	40	20000	2600	2400	3000	82	50			151	1,2,6,13	
		25	21.5	75400	F40/25BX835/IS/WM	40	20000	2600	2400	3500	82	50			151	1,2,6,13	
		25	21.5	75401	F40/25BX840/IS/WM	40	20000	2600	2400	4100	82	50			151	1,2,6,13	
		25	21.5	75402	F40/25BX850/IS/WM	40	20000	2600	2400	5000	82	50			151	1,2,6,13	
		50	22.5	20898	F50BXSPX30RS10PK	40	20000	4000	3400	3000	82	50			151	1,2,6,13	
		50	22.5	20899	F50BXSPX35RS10PK	40	20000	4000	3400	3500	82	50			151	1,2,6,13	
		50	22.5	20900	F50BXSPX41RS10PK	40	20000	4000	3400	4100	82	50			151	1,2,6,13	
		55	20.7	31951	F55BX/830	25	20000	4800	4080	3000	82	50			151	1,2,6,13	
		55	20.7	31952	F55BX/835	25	20000	4800	4080	3500	82	50			151	1,2,6,13	
		55	20.7	31953	F55BX/840	25	20000	4800	4080	4100	82	50			151	1,2,6,13	

Compact Fluorescent Lamps

Base	Watts	Nom. Length (in)	Order Code	Description	Case Qty	Rated Life (hrs)	Rated Life @ 12 Hrs	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min Starting Temp (°F)	TCLP Compliant Plug-Ins	EOL Protection Plug-Ins	Additional Information	Caution Notice	Footnotes
Plug-in Lamps (continued)																	
2-Pin Double Biax®																	
	G23-2	9	5.5	97576	F9DBX23/827/ECO	50	12000		550	470	2700	82	*			151	1,2,17
		9	5.5	97575	F9DBX23/841/ECO	50	12000		550	470	4100	82	*			151	1,2,17
	GX23-2	13	4.7	97586	F13DBX23/827/ECO	50	12000		810	685	2700	82	*			151	1,2,17
		13	4.7	97587	F13DBX23/830/ECO	50	12000		810	685	3000	82	*			151	1,2,17
		13	4.7	97588	F13DBX23/835/ECO	50	12000		810	685	3500	82	*			151	1,2,17
		13	4.7	97589	F13DBX23/841/ECO	50	12000		810	685	4100	82	*			151	1,2,17
	G24d-1	13	5.3	97590	F13DBX/827/ECO	50	12000		900	755	2700	82	*			151	1,2,17
		13	5.3	97591	F13DBX/830/ECO	50	12000		900	755	3000	82	*			151	1,2,17
		13	5.3	97592	F13DBX/835/ECO	50	12000		900	755	3500	82	*			151	1,2,17
		13	5.3	97593	F13DBX/841/ECO	50	12000		900	755	4100	82	*			151	1,2,17
	G24d-2	18	6.1	97577	F18DBX/827/ECO	50	12000		1250	980	2700	82	*			151	1,2,5,17
		18	6.1	97578	F18DBX/830/ECO	50	12000		1250	980	3000	82	*			151	1,2,5,17
		18	6.1	97579	F18DBX/835/ECO	50	12000		1250	980	3500	82	*			151	1,2,5,17
		18	6.1	97580	F18DBX/841/ECO	50	12000		1250	980	4100	82	*			151	1,2,5,17
	G24d-3	26	6.7	97606	F26DBX/827/ECO	50	12000		1710	1460	2700	82	*			151	1,2,17
		26	6.7	97607	F26DBX/830/ECO	50	12000		1710	1460	3000	82	*			151	1,2,17
		26	6.7	97608	F26DBX/835/ECO	50	12000		1710	1460	3500	82	*			151	1,2,17
		26	6.7	97609	F26DBX/841/ECO	50	12000		1710	1460	4100	82	*			151	1,2,17
		26	6.7	97602	F26DBX/E/827/ECO	50	10000		1710	1460	2700	82	*		Internal Electronic Starter	151	1,2,15,17
		26	6.7	97604	F26DBX/E/835/ECO	50	10000		1710	1460	3500	82	*		Internal Electronic Starter	151	1,2,15,17
4-Pin Double Biax®																	
	G24q-1	13	5.0	97594	F13DBX/827/ECO4P	50	17000	20000	900	755	2700	82	*	▲		151	1,2,6,17,18
		13	5.0	97595	F13DBX/830/ECO4P	50	17000	20000	900	755	3000	82	*	▲		151	1,2,6,17,18
		13	5.0	97596	F13DBX/835/ECO4P	50	17000	20000	900	755	3500	82	*	▲		151	1,2,6,17,18
		13	5.0	97597	F13DBX/841/ECO4P	50	17000	20000	900	755	4100	82	*	▲		151	1,2,6,17,18
	G24q-2	18	5.8	97598	F18DBX/827/ECO4P	50	17000	20000	1250	970	2700	82	*	▲		151	1,2,5,6,17,18
		18	5.8	97599	F18DBX/830/ECO4P	50	17000	20000	1250	970	3000	82	*	▲		151	1,2,5,6,17,18
		18	5.8	97600	F18DBX/835/ECO4P	50	17000	20000	1250	970	3500	82	*	▲		151	1,2,5,6,17,18
		18	5.8	97601	F18DBX/841/ECO4P	50	17000	20000	1250	970	4100	82	*	▲		151	1,2,5,6,17,18
	G24q-3	26	6.4	97610	F26DBX/827/ECO4P	50	17000	20000	1800	1530	2700	82	*	▲		151	1,2,6,17,18
		26	6.4	97611	F26DBX/830/ECO4P	50	17000	20000	1800	1530	3000	82	*	▲		151	1,2,6,17,18
		26	6.4	97612	F26DBX/835/ECO4P	50	17000	20000	1800	1530	3500	82	*	▲		151	1,2,6,17,18
		26	6.4	97613	F26DBX/841/ECO4P	50	17000	20000	1800	1530	4100	82	*	▲		151	1,2,6,17,18
4-Pin Triple Biax®																	
	GX24q-1	13	4.2	97623	F13TBX/827/4P/ECO	10	17000	20000	900	755	2700	82	*	▲	Non-Amalgam	151	1,2,6,17,18
		13	4.2	97619	F13TBX/827/A/ECO	10	17000	20000	900	755	2700	82	*	▲		151	1,2,6,12,17,18
		13	4.2	97620	F13TBX/830/A/ECO	10	17000	20000	900	755	3000	82	*	▲		151	1,2,6,12,17,18
		13	4.2	97621	F13TBX/835/A/ECO	10	17000	20000	900	755	3500	82	*	▲		151	1,2,6,12,17,18
		13	4.2	97622	F13TBX/841/A/ECO	10	17000	20000	900	755	4100	82	*	▲		151	1,2,6,12,17,18
	GX24q-2	18	4.8	97628	F18TBX/827/4P/ECO	10	17000	20000	1200	1010	2700	82	*	▲	Non-Amalgam	151	1,2,6,17,18
		18	4.8	97624	F18TBX/827/A/ECO	10	17000	20000	1200	1010	2700	82	*	▲		151	1,2,6,12,17,18
		18	4.8	97625	F18TBX/830/A/ECO	10	17000	20000	1200	1010	3000	82	*	▲		151	1,2,6,12,17,18
		18	4.8	97626	F18TBX/835/A/ECO	10	17000	20000	1200	1010	3500	82	*	▲		151	1,2,6,12,17,18
		18	4.8	97627	F18TBX/841/A/ECO	10	17000	20000	1200	1020	4100	82	*	▲		151	1,2,6,12,17,18
	GX24q-3	26	5.2	97618	F26TBX/827/4P/ECO	10	17000	20000	1800	1530	2700	82	*	▲	Non-Amalgam	151	1,2,6,17,18
		26	5.2	97614	F26TBX/827/A/ECO	10	17000	20000	1800	1530	2700	82	*	▲		151	1,2,6,12,17,18
		26	5.2	97615	F26TBX/830/A/ECO	10	17000	20000	1800	1530	3000	82	*	▲		151	1,2,6,12,17,18
		26	5.2	97616	F26TBX/835/A/ECO	10	17000	20000	1800	1530	3500	82	*	▲		151	1,2,6,12,17,18
		26	5.2	97617	F26TBX/841/A/ECO	10	17000	20000	1800	1530	4100	82	*	▲		151	1,2,6,12,17,18

Base	Watts	Nom. Length (in)	Order Code	Description	Case Qty	Rated Life (hrs)	Rated Life 12 Hrs	Life In Years	Energy Cost \$/Year	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min Starting Temp (°F)	TCLP Compliant Plug-Ins	EOL Protection Plug-Ins	Additional Information	Caution Notice	Footnotes
Plug-in Lamps (continued)																			
4-Pin Triple Biax® (continued)																			
GX24q-3 	32	5.5	97629	F32TBX/827/A/ECO	10	17000	20000			2400	2040	2700	82		*	▲		151	1,2,6,12,17,18
	32	5.5	97630	F32TBX/830/A/ECO	10	17000	20000			2400	2040	3000	82		*	▲		151	1,2,6,12,17,18
	32	5.5	97631	F32TBX/835/A/ECO	10	17000	20000			2400	2040	3500	82		*	▲		151	1,2,6,12,17,18
	32	5.5	97632	F32TBX/841/A/ECO	10	17000	20000			2400	2040	4100	82		*	▲		151	1,2,6,12,17,18
	32	5.5	65337	F32TBX/850/A/ECO	10	17000	20000			2400	2040	5000	82			▲			
GX24q-4 	42	6.4	97633	F42TBX/827/A/ECO	10	17000	20000			3200	2690	2700	82		*	▲		151	1,2,6,12,17,18
	42	6.4	97634	F42TBX/830/A/ECO	10	17000	20000			3200	2690	3000	82		*	▲		151	1,2,6,12,17,18
	42	6.4	97635	F42TBX/835/A/ECO	10	17000	20000			3200	2690	3500	82		*	▲		151	1,2,6,12,17,18
	42	6.4	97636	F42TBX/841/A/ECO	10	17000	20000			3200	2690	4100	82		*	▲		151	1,2,6,12,17,18
	42	6.4	65338	F42TBX/850/A/ECO	10	17000	20000			3200	2690	5000	82			▲			
4-Pin High Output Biax®																			
GX24q-5 	57	7.1	48861	F57QBX827A4P/EOL	10	17000	20000			4300	3700	2700	82		*	▲		151	1,2,6,12,17,18
	57	7.1	48862	F57QBX830A4P/EOL	10	17000	20000			4300	3700	3000	82		*	▲		151	1,2,6,12,17,18
	57	7.1	48863	F57QBX835A4P/EOL	10	17000	20000			4300	3700	3500	82		*	▲		151	1,2,6,12,17,18
	57	7.1	48864	F57QBX841A/ECO	10	17000	20000			4300	3700	4100	82		*	▲		151	1,2,6,12,17,18
	57	5.2	93404	F57QBX850A4P/EOL	10	17000	20000			4300	3700	5000	82		*	▲		151	1,2,6,12,17,18
GX24q-6 	70	8.2	48865	F70QBX827A4P/EOL	10	17000	20000			5200	4470	2700	82		*	▲		151	1,2,6,12,17,18
	70	8.2	48866	F70QBX830A4P/EOL	10	17000	20000			5200	4470	3000	82		*	▲		151	1,2,6,12,17,18
	70	8.2	48867	F70QBX835A4P/EOL	10	17000	20000			5200	4470	3500	82		*	▲		151	1,2,6,12,17,18
	70	8.2	48868	F70QBX841A/ECO	10	17000	20000			5200	4470	4100	82		*	▲		151	1,2,6,12,17,18
	70	8.2	93406	F70QBX850A4P/EOL	10	17000	20000			5200	4470	5000	82		*	▲		151	1,2,6,12,17,18
4-Pin 2D®																			
GR10q-4 	10	3.6	21301	F102D/827/4P	60	10000				650	545	2700	82					151	1,2,3,6
	16	5.5	22169	F162D/827/4P	50	10000				1050	880	2700	82					151	1,2,3,6
	16	5.5	22177	F162D/835/4P	50	10000				1050	880	3500	82					151	1,2,3,6
	21	5.5	21303	F212D/827/4P	50	10000				1350	1135	2700	82					151	1,2,3,6
	21	5.5	22178	F212D/835/4P	50	10000				1350	1135	3500	82					151	1,2,3,6
	28	8.1	22172	F282D/827/4P	20	10000				2050	1720	2700	82					151	1,2,3,6
	28	8.1	22180	F282D/835/4P	20	10000				2050	1720	3500	82					151	1,2,3,6
	38	8.1	21305	F382D/827/4P	20	10000		9.1	\$4.58	2850	2395	2700	82		*			151	1,2,3,6
	38	8.1	22181	F382D/835/4P	20	10000				2850	2395	3500	82		*			151	1,2,3,6
GRV10q-3 	55	8.1	36358	F552D/830A/T4P/B	20	10000				4000	3400	3000	82				Torchiere Replacement Lamp	151	1,2,3,6
	55	8.1	40184	F552D/830/4P/CD	5	10000		9.1	\$6.62	4000	3400	3000	82				Torchiere Replacement Lamp, Cased	151	1,2,3,6

Compact Fluorescent Lamps

Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes
Self-Ballasted Lamps																				
Bright From The Start® A Shape																				
	9	4.4	63498	FLE9IB19/2/SWCD2	3	120	500	400	3000K	82	-5	0.5	<85	10000	9.1	\$1.08		BFTS A-Shape A19	GE2000-2946	19,20,21
	9	4.4	63497	FLE9IB19/2/SWCD	6	120	500	400	3000K	82	-5	0.5	<85	10000	9.1	\$1.08		BFTS A-Shape A19	GE2000-2946	19,20,21
	9	4.4	67455	FLE9IB19/2/SWBX	6	120	500	400	3000K	82	-5	0.5	<85	10000	9.1	\$1.08		BFTS A-Shape A19	GE2000-2946	19,20,21
	15	4.4	71046	FLE15HB19SWXLCD2	3	120	850	680	2700K	82	-15	0.5	<85	10000	9.1	\$1.84	★	BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	63505	FLE15HB19/2SWCD2	3	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	63503	FLE15HB19/2/SWCD	6	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	64158	FLE15HBSWBX2-LTP	6	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	64159	FLE15HBSWBX2-TP	6	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	71045	FLE15HB19SWXLCD	6	120	850	680	2700K	82	-15	0.5	<85	10000	9.1	\$1.84	★	BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	13572	FLE15HB19/2SWWB2	3	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	67456	FLE15HB19/2/SWBX	6	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	70968	FLE15HB19WMSWCD	6	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	69807	FLE15HB19/2/D/CD	6	120	800	640	6500K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	14106	FLE15HB19/2/D/WB	6	120	800	640	6500K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	15	4.4	70971	FLE15HB19WM/D/CD	6	120	800	640	6500K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS A-Shape A19	GE2023-6025	19,20,21
	20	5.2	63504	FLE20HB21/2SWWB2	6	120	1100	880	2700K	82	-15	0.5	<85	8000	7.3	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	64160	FLE20HBSWBX2-LTP	6	120	1100	880	2700K	82	-15	0.5	<85	8000	7.3	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	63506	FLE20HB21/2SWCD2	3	120	1100	880	2700K	82	-15	0.5	<85	8000	7.3	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	71054	FLE20HB21SWXLCD2	3	120	1150	920	2700K	82	-15	0.5	<85	10000	9.1	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	71047	FLE20HB21SWXLCD	6	120	1150	920	2700K	82	-15	0.5	<85	10000	9.1	\$2.45	★	BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	13585	FLE20HB21/2SWWB2	3	120	1100	880	2700K	82	-15	0.5	<85	8000	7.3	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	64161	FLE20HBSWBX2-TP	6	120	1100	880	2700K	82	-15	0.5	<85	8000	7.3	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	67457	FLE20HB21/2/SWBX	6	120	1100	880	2700K	82	-15	0.5	<85	8000	7.3	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	69808	FLE20HB21/2/D/CD	6	120	1100	880	6500K	82	-15	0.5	<85	8000	7.3	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	20	5.2	14107	FLE20HB21/2/D/WB	6	120	1100	880	6500K	82	-15	0.5	<85	8000	7.3	\$2.45		BFTS A-Shape A21	GE2023-6025	19,20,21
	25	5.8	13608	FLE25HBA23SW/WB	6	120	1600	1280	2700K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
	25	5.8	60309	FLE25HBA23SW/CD	6	120	1600	1280	2700K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
	25	5.8	87460	FLE25HBA23SWCD2	3	120	1600	1280	2700K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
	25	5.8	87416	FLE25HBA23/SWBX	12	120	1600	1280	2700K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
	25	5.8	87459	FLE25HBA23/SWCD	6	120	1600	1280	2700K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
	25	5.8	90757	FLE25/HBA23SWBX	6	120	1600	1280	2700K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
	25	5.8	13599	FLE25HBA23D/WB	6	120	1500	1200	6500K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
	25	5.8	60308	FLE25HBA23D/CD	6	120	1500	1200	6500K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
	25	5.8	90801	FLE25/HBA23D/BX	6	120	1500	1200	6500K	82	-15	0.5	<85	6000	5.5	\$3.07		BFTS A-Shape A23	GE2023-6025	19,20,21
Bright From The Start® Decorative Globes																				
	11	4.6	13588	FLE11HBG25SW/WB	6	120	500	400	2700K	82	-15	0.5	<85	8000	7.3	\$1.35		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	11	4.6	60310	FLE11HBG25SW	6	120	500	400	2700K	82	-15	0.5	<85	8000	7.3	\$1.35		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	11	4.6	87463	FLE11HBG25SWXLCD	6	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.35		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	11	4.6	87420	FLE11HBG25SWXLBX	12	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.35	★	BFTS Decorative Globe G25	GE2023-6025	19,20,21
	11	4.6	90802	FLE11HBG25SWBX	6	120	500	400	2700K	82	-15	0.5	<85	8000	7.3	\$1.35		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	11	4.6	13589	FLE11HBG25/D/WB	6	120	450	360	6500K	82	-15	0.5	<85	8000	7.3	\$1.35		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	11	4.6	60311	FLE11HBG25/D	6	120	450	360	6500K	82	-15	0.5	<85	8000	7.3	\$1.35		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	11	4.6	90804	FLE11/HBG25/D/BX	6	120	450	360	6500K	82	-15	0.5	<85	8000	7.3	\$1.35		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	15	4.6	13595	FLE15HBG25SW/WB	6	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	15	4.6	87432	FLE15HBG25SW	6	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Decorative Globe G25	GE2023-6025	19,20,21
	15	4.6	90805	FLE15HBG25SWBX	6	120	800	640	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Decorative Globe G25	GE2023-6025	19,20,21
Bright From The Start® Reflectors																				
	15	5.1	13451	FLE15HBR30/SW/WB	3	120	750	600	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Reflector R30	GE2023-6025	19,20,21
	15	5.1	87422	FLE15HBR30SWXLBX	6	120	750	600	2700K	82	-15	0.5	<85	10000	9.1	\$1.84		BFTS Reflector R30	GE2024-7456	19,20,21
	15	5.1	87465	FLE15HBR30SWXLCD	3	120	750	600	2700K	82	-15	0.5	<85	10000	9.1	\$1.84		BFTS Reflector R30	GE2024-7456	19,20,21
	15	5.1	60312	FLE15HBR30/SW	3	120	750	600	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Reflector R30	GE2023-6025	19,20,21
	15	5.1	90806	FLE15HBR30SWBX	4	120	750	600	2700K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Reflector R30	GE2023-6025	19,20,21
	15	5.1	13454	FLE15HBR30/D/WB	3	120	650	520	6500K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Reflector R30	GE2023-6025	19,20,21
	15	5.1	60313	FLE15HBR30/D	3	120	650	520	6500K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Reflector R30	GE2023-6025	19,20,21
	15	5.1	90811	FLE15/HBR30/D/BX	4	120	650	520	6500K	82	-15	0.5	<85	8000	7.3	\$1.84		BFTS Reflector R30	GE2023-6025	19,20,21

Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes
Self-Ballasted Lamps (continued)																				
Bright From The Start® Reflectors (continued)																				
	26	6.5	13458	FLE26HBR40/SW/WB	3	120	1300	1040	2700K	82	-15	0.5	<85	8000	7.3	\$3.19		BFTS Reflector R40	GE2024-7456	19,20,21
	26	6.5	60314	FLE26HBR40/SW	3	120	1300	1040	2700K	82	-15	0.5	<85	8000	7.3	\$3.19		BFTS Reflector R40	GE2024-7456	19,20,21
	26	6.5	87467	FLE26HBR40SWXLCD	3	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$3.19		BFTS Reflector R40	GE2024-7456	19,20,21
	26	6.5	90813	FLE26HBR40SWBX	4	120	1300	1040	2700K	82	-15	0.5	<85	8000	7.3	\$3.19		BFTS Reflector R40	GE2024-7456	19,20,21
	26	6.5	87428	FLE26HBR40SWXLBX	5	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$3.19		BFTS Reflector R40	GE2024-7456	19,20,21
	26	6.5	13459	FLE26HBR40/D/WB	3	120	1250	1000	6500K	82	-15	0.5	<85	8000	7.3	\$3.19		BFTS Reflector R40	GE2024-7456	19,20,21
	26	6.5	60315	FLE26HBR40/D	3	120	1250	1000	6500K	82	-15	0.5	<85	8000	7.3	\$3.19		BFTS Reflector R40	GE2024-7456	19,20,21
	26	6.5	90814	FLE26HBR40/D/BX	4	120	1250	1000	6500K	82	-15	0.5	<85	8000	7.3	\$3.19		BFTS Reflector R40	GE2024-7456	19,20,21
Reveal® All Glass A Shape																				
	9	4.4	63502	FLE9IB19/2RVLCD2	3	120	430	344	2490K	70	-5	0.5	<85	8000	7.3	\$1.08		Reveal® All Glass A19	GE2000-2946	19,20,21
	9	4.4	63499	FLE9IB19/2RVLCD	6	120	430	344	2490K	70	-5	0.5	<85	8000	7.3	\$1.08		Reveal® All Glass A19	GE2000-2946	19,20,21
	9	4.4	67458	FLE9IB19/2RVLBX	6	120	430	344	2490K	70	-5	0.5	<85	8000	7.3	\$1.08		Reveal® All Glass A19	GE2000-2946	19,20,21
Reveal® Globes																				
	11	4.6	61353	FLEG25XLRVLT6	6	120	450	360	2490K	70	-15	0.5	<85	10000	9.1	\$1.32		Reveal® Globe G25	GE2000-2946	1,8,10,12,19,20,21
	11	4.6	67464	FLE11G25XLRV/LBX	6	120	450	360	2490K	70	-15	0.5	<85	10000	9.1	\$1.32		Reveal® Globe G25	GE2000-2946	19,20,21
Reveal® Reflectors																				
	11	4.7	61354	FLE11R20XLRVLT6	6	120	340	272	2490K	70	-10	0.5	<85	10000	9.1	\$1.32		Reveal® Reflector R20	GE2000-2946	1,8,10,12,19,20,21
	11	4.7	67463	FLE11R20XLRV/LBX	6	120	340	272	2490K	70	-10	0.5	<85	10000	9.1	\$1.32		Reveal® Reflector R20	GE2024-7456	19,20,21
	15	5.3	61164	FLE15R30/RVL-TP6	6	120	620	496	2490K	70	-15	0.5	<85	10000	9.1	\$1.81		Reveal® Reflector R30	GE2000-2946	1,8,10,12,19,20,21
	15	5.3	84319	FLE15R30/RVL/CD2	3	120	620	496	2490K	70	-15	0.5	<85	10000	9.1	\$1.81		Reveal® Reflector R30	GE2024-7456	19,20,21
	15	5.3	69724	FLE15R30/RVL/CD2	3	120	620	496	2490K	70	-15	0.5	<85	10000	9.1	\$1.81		Reveal® Reflector R30	GE2024-7456	19,20,21
	15	5.3	89859	FLE15R30RVLBXT6	4	120	620	496	2490K	70	-15	0.5	<85	10000	9.1	\$1.81		Reveal® Reflector R30	GE2024-7456	19,20,21
	15	5.3	67461	FLE15R30/RVL/BX	4	120	620	496	2490K	70	-15	0.5	<85	10000	9.1	\$1.81		Reveal® Reflector R30	GE2024-7456	19,20,21
	15	5.3	62270	FLE15R30RVC2TP6	6	120	620	496	2490K	70	-15	0.5	<85	10000	9.1	\$1.81		Reveal® Reflector R30	GE2024-7456	19,20,21
	15	5.5	63522	FLE15/DVR30RVLCD	3	120	500	400	2490K	70	-5	0.5	<85	8000	7.3	\$1.81		Reveal® Reflector R30 Dimming	GE2025-1509	19,21
	15	5.5	67462	FLE15/DVR30RVLBX	4	120	500	400	2490K	70	-5	0.5	<85	8000	7.3	\$1.81		Reveal® Reflector R30 Dimming	GE2025-1509	19,21
	26	6.5	61355	FLE26R40XLRVLT6	6	120	1150	920	2490K	70	-10	0.5	<85	10000	9.1	\$3.13		Reveal® Reflector R40	GE2000-2946	1,8,10,12,19,20,21
	26	6.5	84324	FLE26R40RVL10HBX	4	120	1150	920	2490K	70	-10	0.5	<85	10000	9.1	\$3.13		Reveal® Reflector R40	GE2024-7456	19,20,21
	26	6.5	64874	FLE26R40XLRV-LTP	6	120	1150	920	2490K	70	-10	0.5	<85	10000	9.1	\$3.13		Reveal® Reflector R40	GE2024-7456	19,20,21
	26	6.5	62953	FLE26R40RVL10HBX	4	120	1150	920	2490K	70	-10	0.5	<85	10000	9.1	\$3.13		Reveal® Reflector R40	GE2024-7456	19,20,21
	26	6.5	89860	FLE26R40RVLBXT6	4	120	1150	920	2490K	70	-10	0.5	<85	10000	9.1	\$3.13		Reveal® Reflector R40	GE2024-7456	19,20,21
	26	6.6	67467	FLE26R40RVL/BXHH	4	120	1100	880	2490K	70	-15	0.5	<85	8000	7.3	\$3.13		Reveal® Reflector R40	GE2025-1509	19,20,21
	26	6.6	66668	FLE26/DMR40RVLCD	3	120	1100	880	2490K	70	-15	0.5	<85	8000	7.3	\$3.13		Reveal® Reflector R40 Dimming	GE2025-1509	19,21
Reveal® Spiral® 3-Way																				
	32	6.0	67466	FLE32HT3D3RVL/BX	6	120	540/1440/1935	1548	2490K	70	-15	0.5	<85	8000	7.3	\$3.85/\$3.01/\$1.93		Reveal® T3 3-Way	GE2000-0950	19,20,21
	32	6.0	35002	FLE32HT3D3RVL/BX	6	120	540/1440/1935	1548	2490K	70	-15	0.5	<85	8000	7.3	\$1.93/\$3.01/\$3.85		Reveal® T3 3-Way	GE2000-0950	19,20,21
	32	6.0	62908	FLE32HTD3RVL/CD	6	120	540/1440/1935	1548	2490K	70	-15	0.5	<85	8000	7.3	\$1.93/\$3.01/\$3.85		Reveal® T3 3-Way Shorter Design	GE2000-0948	1,8,9,16,19,20,21,22
Reveal® Spiral® T3																				
	10	4.1	75405	FLE10HT3/2/RVL/CD	3	120	450	360	2490K	70	-15	0.6	<85	8000	7.3	\$1.20		Reveal® T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
	10	4.1	67451	FLE10HT3/2RVLBX2	6	120	450	360	2490K	70	-15	0.5	<85	8000	7.3	\$1.20		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	10	4.1	75409	FLE10HT3/2RVLCD2	3	120	450	360	2490K	70	-15	0.5	<85	8000	7.3	\$1.20		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	10	4.1	84249	FLE10HT3/2RVLBX2	6	120	450	360	2490K	70	-15	0.5	<85	8000	7.3	\$1.20		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	13	4.1	75406	FLE13HT3/2/RVL/CD	3	120	800	640	2490K	70	-15	0.6	<85	8000	7.3	\$1.57		Reveal® T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
	13	4.1	84251	FLE13HT3/2RVLBX2	6	120	800	640	2490K	70	-15	0.5	<85	8000	7.3	\$1.57		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	13	4.1	67452	FLE13HT3/2RVLBX2	6	120	800	640	2490K	70	-15	0.5	<85	8000	7.3	\$1.57		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	13	4.1	62906	FLE13HT3/2RVLBX4	6	120	800	640	2490K	70	-15	0.5	<85	8000	7.3	\$1.57		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	13	4.1	75411	FLE13HT3/2RVLCD2	3	120	800	640	2490K	70	-15	0.5	<85	8000	7.3	\$1.57		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	13	4.1	15764	FLE13HT3RVL2/HD	6	120	800	640	2490K	70	-15	0.5	<85	8000	7.3	\$1.57		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	13	4.1	84254	FLE13HT3/2RVLBX4	6	120	800	640	2490K	70	-15	0.5	<85	8000	7.3	\$1.57		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	13	4.1	75407	FLE20HT3/2/RVL/CD	3	120	1200	960	2490K	70	-15	0.6	<85	8000	7.3	\$2.41		Reveal® T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
	20	4.7	75407	FLE20HT3/2RVLBX2	6	120	1200	960	2490K	70	-15	0.5	<85	8000	7.3	\$2.41		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	20	4.7	84252	FLE20HT3/2RVLBX2	6	120	1200	960	2490K	70	-15	0.5	<85	8000	7.3	\$2.41		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	20	4.7	67453	FLE20HT3/2RVLBX4	3	120	1200	960	2490K	70	-15	0.5	<85	8000	7.3	\$2.41		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
	20	4.7	75412	FLE20HT3/2RVLCD2	3	120	1200	960	2490K	70	-15	0.5	<85	8000	7.3	\$2.41		Reveal® T3 Spiral®	GE2000-2709	19,20,21,22

Compact Fluorescent Lamps

Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes
Self-Ballasted Lamps (continued)																				
Reveal® Spiral® T3 (continued)																				
	Med	26	5.2	75408	FLE26HT3/2/RVL/CD	3	120	1570	1256	2490K	70	-15	0.6	<85	8000	7.3	\$3.13	Reveal® T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		26	5.2	84262	FLE26HT3/2/RVL/BX4	3	120	1570	1256	2490K	70	-15	0.5	<85	8000	7.3	\$3.13	Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
		26	5.2	67454	FLE26HT3/2/RVL/BX2	6	120	1570	1256	2490K	70	-15	0.5	<85	8000	7.3	\$3.13	Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
		26	5.2	66354	FLE26HT3/2/RVL/BX4	3	120	1570	1256	2490K	70	-15	0.5	<85	8000	7.3	\$3.13	Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
		26	5.2	75413	FLE26HT3/2/RVL/CD2	3	120	1570	1256	2490K	70	-15	0.5	<85	8000	7.3	\$3.13	Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
		26	5.2	15862	FLE26HT3/RVL2/HD	6	120	1570	1256	2490K	70	-15	0.5	<85	8000	7.3	\$3.13	Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
		26	5.2	84253	FLE26HT3/2/RVL/BX2	6	120	1570	1256	2490K	70	-15	0.5	<85	8000	7.3	\$3.13	Reveal® T3 Spiral®	GE2000-2709	19,20,21,22
		14	5.1	63520	FLE14HT3/DVR/LCD	3	120	800	640	2490K	70	-10	0.5	<85	8000	7.3	\$1.69	Reveal® T3 Spiral® Dimming	GE2000-0951	19,21,22
		14	5.1	67465	FLE14HT3/DMRVL/BX	4	120	800	640	2490K	70	-10	0.5	<85	8000	7.3	\$1.69	Reveal® T3 Spiral® Dimming	GE2000-0951	19,21,22
		26	5.7	63521	FLE26HT3/DMRVL/CD	3	120	1560	1248	2490K	70	-5	0.5	<85	10000	9.1	\$3.13	Reveal® T3 Spiral® Dimming	GE2000-0951	19,21,22
		26	5.7	67468	FLE26HT3/DMRVL/BX	4	120	1560	1248	2490K	70	-5	0.5	<85	10000	9.1	\$3.13	Reveal® T3 Spiral® Dimming	GE2000-0951	19,21,22
Reveal® Bright From The Start® A Shape																				
	Med	15	4.4	63510	FLE15HB19/2/RVCD2	3	120	740	592	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS A shape A19	GE2023-6025	19,20,21
		15	4.4	64163	FLE15HBRVBX2-TP	6	120	740	592	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS A shape A19	GE2023-6025	19,20,21
		15	4.4	64162	FLE15HBRVBX2-LTP	6	120	740	592	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS A shape A19	GE2023-6025	19,20,21
		15	4.4	84244	FLE15HB19/2/RVCD2	3	120	740	592	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS A shape A19	GE2023-6025	19,20,21
		15	4.4	63508	FLE15HB19/2/RVLCD	6	120	740	592	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS A shape A19	GE2023-6025	19,20,21
		15	4.4	70972	FLE15HB19WMRVLCD	6	120	740	592	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS A shape A19	GE2023-6025	19,20,21
		15	4.4	67459	FLE15HB19/2/RVL/BX	6	120	740	592	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS A shape A19	GE2023-6025	19,20,21
		19	5.2	63511	FLE19HB21/2/RVCD2	3	120	950	760	2490K	70	-15	0.5	<85	8000	7.3	\$2.33	Reveal BFTS A shape A21	GE2023-6025	19,20,21
		19	5.2	63509	FLE19HB21/2/RVLCD	6	120	950	760	2490K	70	-15	0.5	<85	8000	7.3	\$2.33	Reveal BFTS A shape A21	GE2023-6025	19,20,21
		19	5.2	67460	FLE19HB21/2/RVL/BX	6	120	950	760	2490K	70	-15	0.5	<85	8000	7.3	\$2.33	Reveal BFTS A shape A21	GE2023-6025	19,20,21
		25	5.8	87462	FLE25HBA23/RVCD2	3	120	1375	1100	2490K	70	-15	0.5	<85	6000	5.5	\$3.07	Reveal BFTS A shape A23	GE2023-6025	19,20,21
		25	5.8	95143	FLE25HBA23/RVLWB	6	120	1375	1100	2490K	70	-15	0.5	<85	6000	5.5	\$3.07	Reveal BFTS A shape A23	GE2023-6025	19,20,21
		25	5.8	87461	FLE25HBA23/RVLCD	6	120	1375	1100	2490K	70	-15	0.5	<85	6000	5.5	\$3.07	Reveal BFTS A shape A23	GE2023-6025	19,20,21
		25	5.8	87419	FLE25HBA23/RVL/BX	12	120	1375	1100	2490K	70	-15	0.5	<85	6000	5.5	\$3.07	Reveal BFTS A shape A23	GE2023-6025	19,20,21
		25	5.8	90758	FLE25HBA23/RVL/BX	6	120	1375	1100	2490K	70	-15	0.5	<85	6000	5.5	\$3.07	Reveal BFTS A shape A23	GE2023-6025	19,20,21
Reveal® Bright From The Start® Reflectors																				
	Med	15	5.1	87466	FLE15HBR30/RVLCD	3	120	660	528	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS Reflector R30	GE2024-7456	19,20,21
		15	5.1	87427	FLE15HBR30/RVL/BX	6	120	660	528	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS Reflector R30	GE2024-7456	19,20,21
		15	5.1	90807	FLE15HBR30/RVL/BX	4	120	660	528	2490K	70	-15	0.5	<85	8000	7.3	\$1.84	Reveal BFTS Reflector R30	GE2024-7456	19,20,21
Reveal® Bright From The Start® Decorative Globes																				
	Med	11	4.6	87464	FLE11HBG25/RVLCD	6	120	450	360	2490K	70	-15	0.5	<85	8000	7.3	\$1.35	Reveal BFTS Decorative Globe G25	GE2023-6025	19,20,21
		11	4.6	87421	FLE11HBG25/RVL/BX	12	120	450	360	2490K	70	-15	0.5	<85	8000	7.3	\$1.35	Reveal BFTS Decorative Globe G25	GE2023-6025	19,20,21
		11	4.6	90803	FLE11HBG25/RVL/BX	6	120	450	360	2490K	70	-15	0.5	<85	8000	7.3	\$1.35	Reveal BFTS Decorative Globe G25	GE2023-6025	19,20,21
		11	4.6	84286	FLE11HBG25/RVLCD	6	120	450	360	2490K	70	-15	0.5	<85	8000	7.3	\$1.35	Reveal BFTS Decorative Globe G25	GE2023-6025	19,20,21
Spiral® T2																				
Cand	13	4.3	75368	FLE13HT2/2/CAND2P		120	850	680	2700K	82	-15	0.6	<85	8000	7.3	\$1.57		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
	Med	10	3.5	86241	FLE10HT2/2/827	10	120	580	464	2700K	82	-10	0.5	<85	12000	11.0	\$1.20	T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		10	3.5	85382	FLE10HT2/2/SW/CD	3	120	580	464	2700K	82	-10	0.5	<85	12000	11.0	\$1.20	T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		10	3.5	68504	FLE10HT2SWXL/BX3	4	120	580	464	2700K	82	-10	0.5	<85	12000	11.0	\$1.20	★ T2 Spiral®	GE2000-2709	19,20,21,22,25
		10	3.5	68510	FLE10HT2SWXL/BX6	4	120	580	464	2700K	82	-10	0.5	<85	12000	11.0	\$1.20	★ T2 Spiral®	GE2000-2709	19,20,21,22,25
		10	3.5	85389	FLE10HT2/2/SW2PK	3	120	580	464	2700K	82	-10	0.5	<85	12000	11.0	\$1.20	★ T2 Spiral®	GE2000-2709	19,20,21,22,25

Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes	
Self-Ballasted Lamps (continued)																					
Spiral® T2 (continued)																					
	Med	10	3.7	72468	FLE10HT2/6H/CWCD	3	120	580	464	4000K	82	-10	0.5	<85	8000	7.3	\$1.20		T2 Spiral®	GE2000-2709	19,20,21,22
		10	3.5	68518	FLE10HT2D/XL/BX3	4	120	550	440	5000K	82	-10	0.5	<85	12000	11.0	\$1.20	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		10	3.5	62948	FLE10HT2/12H/DCD	6	120	550	440	5000K	82	-10	0.5	<85	12000	11.0	\$1.20	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		10	3.7	72471	FLE10HT2/6H/D/CD	3	120	550	440	6500K	82	-10	0.5	<85	8000	7.3	\$1.20		T2 Spiral®	GE2000-2709	19,20,21,22
	Med	13	3.9	86256	FLE13HT2/2/827	10	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		13	3.9	85383	FLE13HT2/2/SW/CD	3	120	870	696	2700K	82	-10	0.6	<85	12000	11.0	\$1.57		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		13	3.9	62949	FLE13HT2/12H/DCD	10	120	850	680	5000K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		13	3.9	68505	FLE13HT2SWXL/BX3	4	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	68511	FLE13HT2SWXL/BX6	4	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	70909	FLE13HT2SWXL/B10	5	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	70776	FLE13HT2SWXL/BX4	3	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	85390	FLE13HT2/2/SW2PK	3	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	72466	FLE13HT2/6H/SWCD	3	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.8	72469	FLE13HT2/6H/CWCD	3	120	870	696	4000K	82	-10	0.5	<85	8000	7.3	\$1.57		T2 Spiral®	GE2000-2709	19,20,21,22
		13	3.9	68519	FLE13HT2D/XL/BX3	4	120	825	660	6500K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	70830	FLE13HT2DYL/BX4	3	120	825	660	6500K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.8	72472	FLE13HT2/6H/D/CD	3	120	825	660	6500K	82	-10	0.5	<85	8000	7.3	\$1.57		T2 Spiral®	GE2000-2709	19,20,21,22
		20	4.1	72880	FLE20HT2/2/XL/CD	3	120	1300	1040	2700K	82	-10	0.6	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
	Med	20	4.1	62951	FLE20HT2/12H/DCD	3	120	1300	1040	5000K	82	-10	0.6	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		20	4.1	68512	FLE20HT2SWXL/BX6	4	120	1300	1040	2700K	82	-10	0.5	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.1	68506	FLE20HT2SWXL/BX3	4	120	1300	1040	2700K	82	-10	0.5	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.1	72875	FLE20HT2/2/XL/2P	3	120	1300	1040	2700K	82	-10	0.5	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.1	68520	FLE20HT2D/XL/BX3	4	120	1300	1040	5000K	82	-10	0.5	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		23	4.5	72881	FLE26HT2/2/XL/CD	3	120	1600	1280	2700K	82	-15	0.6	<85	12000	11.0	\$2.77		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
	Med	23	4.5	68513	FLE23HT2SWXL/BX6	4	120	1600	1280	2700K	82	-15	0.5	<85	12000	11.0	\$2.77		T2 Spiral®	GE2000-2709	19,20,21,22
		23	4.5	68507	FLE23HT2SWXL/BX3	4	120	1600	1280	2700K	82	-15	0.5	<85	12000	11.0	\$2.77		T2 Spiral®	GE2000-2709	19,20,21,22
		23	4.5	72877	FLE23HT2/2/XL/2P	3	120	1600	1280	2700K	82	-15	0.5	<85	12000	11.0	\$2.77		T2 Spiral®	GE2000-2709	19,20,21,22
		26	4.8	62952	FLE26HT2/12H/DCD	3	120	1600	1280	6500K	82	-15	0.6	<85	12000	11.0	\$3.13		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		26	4.8	68521	FLE26HT2D/XL/BX3	4	120	1600	1280	6500K	82	-15	0.5	<85	12000	11.0	\$3.13		T2 Spiral®	GE2000-2709	19,20,21,22
		26	4.8	73633	FLE26HT2/6H/DCD	3	120	1600	1280	6500K	82	-15	0.5	<85	8000	7.3	\$3.13		T2 Spiral®	GE2000-2709	19,20,21,22
Spiral® T3																					
	Med	9	4.2	42165	FLE9HT3/2/827	10	120	520	416	2700K	82	-15	0.6	<85	10000	9.1	\$1.08	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.2	42171	FLE9HT3/2/841	10	120	520	416	4100K	82	-15	0.6	<85	10000	9.1	\$1.08	★	T3 Spiral®	GE2024-7455	1,7,8,9,11,19,20,21,22
		9	4.0	49906	FLE10HT3/2/SW/CD FLE9HT3/2/SW/CD	12	120	520	416	2700K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.0	49907	FLE10HT32SWCD2PK FLE9HT32SWCD2PK	3	120	520	416	2700K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	5.0	89082	FLE10HT3/2/D/CD FLE10HT3/2/D/CD	12	120	500	400	6500K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.0	65670	FLE9HT3/2SW/BX4	3	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	72931	FLE10HT3/2/SW6PK	4	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	76991	FLE9HT3/2/CB/BX	10	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	49807	FLE9HT32SWCD3PK	3	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	74196	FLE9HT3/2/SW/BX	10	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	97688	FLE9HT3/2/SWBX3	4	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	74197	FLE9HT3/2/BX/2P	6	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	73156	FLE9HT3/2/SW5PK	5	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	67448	FLE9HT3/41BX4HH	3	120	550	440	4100K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	67444	FLE9HT3/41BX2HH	6	120	550	440	4100K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	64004	FLE9HT3/2DBX2/6	6	120	500	400	6500K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		10	4.4	80936	FLE10HT3/2/XL	10	120	550	440	2700K	80	-15	0.6	<85	12000	11.0	\$1.20		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		10	4.4	69658	FLE10HT3XXLL/5BX	3	120	500	400	2700K	82	-10	0.5	<85	15000	13.7	\$1.20		T3 Spiral®	GE2000-2709	19,20,21,22
		10	4.4	69654	FLE10HT3XXLL/2BX	3	120	500	400	2700K	82	-10	0.5	<85	15000	13.7	\$1.20		T3 Spiral®	GE2000-2709	19,20,21,22
		10	4.4	24967	FLE10HT3XXLL/2BX	3	120	500	400	2700K	82	-10	0.5	<85	15000	13.7	\$1.20		T3 Spiral®	GE2000-2709	19,20,21,22
	Med	13	4.5	16460	FLE13HT3/2/SW/CD	12	120	825	660	2700K	82	-15	0.6	<85	10000	9.1	\$1.57		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		13	4.5	16459	FLE13HT3/2/SW/2P	3	120	825	660	2700K	82	-15	0.6	<85	10000	9.1	\$1.57		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		13	4.1	71763	FLE13HT3/2/65TP	6	120	855	684	5000K	82	-15	0.6	<85	8000	7.3	\$1.57		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		13	4.5	74198	FLE13HT3/2/SW/BX	10	120	825	660	2700K	82	-15	0.6	<85	10000	9.1	\$1.57		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		13	4.4	42159	FLE13HT/3/2/827	10	120	825	660	2700K	82	-15	0.6	<85	10000	9.1	\$1.57	★	T3 Spiral®	GE2024-7455	1,7,8,9,11,19,20,21,22</

Compact Fluorescent Lamps

Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes	
Self-Ballasted Lamps (continued)																					
Spiral® T3 (continued)																					
	Med	13	4.5	97659	FLE13HT3/2/SW6PK	4	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.57		T3 Spiral®	GE2024-7455	19,20,21,22
		13	4.5	65671	FLE13HT3/2SW/BX4	3	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.57		T3 Spiral®	GE2024-7455	19,20,21,22
		13	4.5	76992	FLE13HT3/2/CB/BX	10	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.57		T3 Spiral®	GE2024-7455	19,20,21,22
		13	4.5	97133	FLE13HT3/2SW/PRO	10	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.57		T3 Spiral®	GE2024-7455	19,20,21,22
		13	4.5	97689	FLE13HT3/2/SWBX3	4	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.57		T3 Spiral®	GE2024-7455	19,20,21,22
		13	4.5	49586	FLE13HT32SWCD3PK	3	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.57		T3 Spiral®	GE2024-7455	19,20,21,22
		13	4.5	74199	FLE13HT3/2/BX/2P	6	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.57		T3 Spiral®	GE2024-7455	19,20,21,22
	Med	14	4.5	94543	FLE14HT3/2/827	10	120	950	760	2700K	82	-10	0.6	<85	10000	9.1	\$1.69	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		14	4.5	94542	FLE14HT3/2/841	10	120	950	760	4100K	82	-10	0.6	<85	10000	9.1	\$1.69	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		14	4.5	89091	FLE15HT3/2/D/CD FLE14HT3/2/D/CD	3	120	900	720	5000K	82	-10	0.6	<85	10000	9.1	\$1.69	★	T3 Spiral®		19,20,21,22,25
		14	4.5	65425	FLE14HT3/2-PK4/6	6	120	950	760	4100K	82	-10	0.5	<85	10000	9.1	\$1.69	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		14	4.5	67445	FLE14HT3/41BX2HH	6	120	950	760	4100K	82	-10	0.5	<85	10000	9.1	\$1.69	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		14	4.5	64005	FLE14HT3/2DBX2/6	6	120	900	720	5000K	82	-10	0.5	<85	10000	9.1	\$1.69	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		15	4.8	80937	FLE15HT3/2/XL/SW	10	120	950	760	2700K	80	-15	0.6	<85	12000	11.0	\$1.81		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		15	4.8	47435	FLE15HT3/2/XL/CD	12	120	950	760	2700K	80	-15	0.6	<85	12000	11.0	\$1.81		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		15	4.9	64801	FLE15HT3/2SX/827	6	120	975	780	2700K	82	-15	0.5	<85	15000	13.7	\$1.81	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		15	4.9	69659	FLE15HT3XXLL/5BX	3	120	975	780	2700K	82	-15	0.5	<85	15000	13.7	\$1.81	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		15	4.9	69655	FLE15HT3XXLL/2BX	3	120	975	780	2700K	82	-15	0.5	<85	15000	13.7	\$1.81	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
	15	4.9	24968	FLE15HT3XXLL/2BX	3	120	975	780	2700K	82	-15	0.5	<85	15000	13.7	\$1.81	★	T3 Spiral®	GE2000-2709	19,20,21,22,25	
	Med	20	4.4	15834	FLE20HT3/2/827	10	120	1300	1040	2700K	82	-15	0.6	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		20	4.4	15516	FLE20HT3/2/SW/CD	12	120	1300	1040	2700K	82	-15	0.6	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		20	4.4	15518	FLE20HT3/2/SW/2P	3	120	1300	1040	2700K	82	-15	0.6	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		20	4.4	25186	FLE20HT3/2/841	10	120	1300	1040	4100K	82	-15	0.6	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		20	5.3	80888	FLE20HT3/2/XL827	10	120	1200	960	2700K	80	-15	0.6	<85	12000	11.0	\$2.41		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		20	4.8	64802	FLE20HT3/2SX/827	6	120	1300	1040	2700K	82	-15	0.5	<85	15000	13.7	\$2.41	★	T3 Spiral®	GE2000-0948	1,7,8,9,11,19,20,21,22,25
		20	4.7	71764	FLE20HT3/2/6S/TP	6	120	1235	988	5000K	82	-15	0.6	<85	8000	7.3	\$2.41		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		20	4.4	89094	FLE20HT3/2/D/CD	12	120	1300	1040	5000K	82	-15	0.6	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		20	4.8	47442	FLE20HT3/2/XL/CD	12	120	1200	960	2700K	80	-15	0.6	<85	12000	11.0	\$2.41		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		20	4.8	69683	FLE20HT3XXLL/5BX	3	120	1300	1040	2700K	82	-15	0.5	<85	15000	13.7	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	74201	FLE20HT3/2/BX2PK	6	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.8	69656	FLE20HT3XXLL/2BX	3	120	1300	1040	2700K	82	-15	0.5	<85	15000	13.7	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	71284	FLE20HT3/2/SW6PK	6	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	65672	FLE20HT3/2SW/BX4	3	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	74200	FLE20HT3/2/SW/BX	10	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	76993	FLE20HT3/2/CB/BX	10	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	69245	FLE20T3SW/4BX-TP	6	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	97249	FLE20HT3/2/SW5PK	5	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	97690	FLE20HT3/2/SWBX3	4	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.4	49587	FLE20HT32SWCD3PK	3	120	1300	1040	2700K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25
	20	4.4	67449	FLE20HT3/41BX4HH	3	120	1300	1040	4100K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25	
	20	4.4	67446	FLE20HT3/41BX2HH	6	120	1300	1040	4100K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25	
	20	4.4	64006	FLE20HT3/2DBX2/6	6	120	1300	1040	5000K	82	-15	0.5	<85	10000	9.1	\$2.41	★	T3 Spiral®	GE2000-2709	19,20,21,22,25	
	Med	23	5.1	80889	FLE23HT3/2/XL827	10	120	1600	1280	2700K	80	-15	0.6	<85	12000	11.0	\$2.77		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		23	4.7	42164	FLE23HT3/2/827	10	120	1650	1320	2700K	82	-15	0.6	<85	10000	9.1	\$2.77	★	T3 Spiral®	GE2000-0948	1,7,8,9,11,19,20,21,22
		23	4.8	15517	FLE23HT3/2/SW/CD	12	120	1600	1280	2700K	82	-15	0.6	<85	10000	9.1	\$2.77		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		23	4.8	94546	FLE23HT3/2/841	10	120	1600	1280	4000K	82	-15	0.6	<85	10000	9.1	\$2.77		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		23	4.8	89095	FLE26HT3/2/D/CD	12	120	1600	1280	6500K	82	-15	0.6	<85	10000	9.1	\$2.77		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		23	4.8	15519	FLE26HT3/2/SW/2P	3	120	1600	1280	2700K	82	-15	0.6	<85	10000	9.1	\$2.77		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		23	5.1	69693	FLE23HT3XXLL/5BX	3	120	1600	1280	2700K	82	-15	0.5	<85	15000	13.7	\$2.77		T3 Spiral®	GE2000-2709	19,20,21,22
		23	5.1	69657	FLE23HT3XXLL/2BX	3	120	1600	1280	2700K	82	-15	0.5	<85	15000	13.7	\$2.77		T3 Spiral®	GE2000-2709	19,20,21,22
		23	4.8	65673	FLE23HT3/2SW/BX4	3	120	1650	1320	2700K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2024-7455	19,20,21,22
		23	4.8	71285	FLE23HT3/2/SW6PK	6	120	1650	1320	2700K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2024-7455	19,20,21,22
		23	4.8	76994	FLE23HT3/2/CB/BX	10	120	1650	1320	2700K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2024-7455	19,20,21,22

Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes	
Self-Ballasted Lamps (continued)																					
Spiral® T3 (continued)																					
	Med	23	4.8	97134	FLE23HT3/2SW/PRO	10	120	1650	1320	2700K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2024-7455	19,20,21,22
		23	4.8	97250	FLE23HT3/2/SW5PK	5	120	1650	1320	2700K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2024-7455	19,20,21,22
		23	4.8	74202	FLE23HT3/2/SW/BX	10	120	1650	1320	2700K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2024-7455	19,20,21,22
		23	4.8	74203	FLE23HT3/2/BX2PK	6	120	1650	1320	2700K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2024-7455	19,20,21,22
		23	4.8	97691	FLE23HT3/2/SWBX3	4	120	1650	1320	2700K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2024-7455	19,20,21,22
		23	4.8	67450	FLE23HT3/41BX4HH	3	120	1600	1280	4000K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2000-2709	19,20,21,22
		23	4.8	67447	FLE23HT3/41BX2HH	6	120	1600	1280	4000K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2000-2709	19,20,21,22
	Med	23	4.8	64007	FLE23HT3/2DBX2/6	6	120	1600	1280	6500K	82	-15	0.5	<85	10000	9.1	\$2.77		T3 Spiral®	GE2000-2709	19,20,21,22
		26	5.2	74874	FLE26HT3/2/R30	10	120	1750	1400	3000K	82	-15	0.6	<85	10000	9.1	\$3.13		T3 Spiral®	GE2000-0948	1,7,8,9,11,19,20,21,22
		26	5.0	42167	FLE26HT3/2/2/R30	10	120	1750	1400	3000K	82	-15	0.6	<85	10000	9.1	\$3.13	★	T3 Spiral®	GE2000-0948	1,7,8,9,11,19,20,21,22
		26	5.2	71765	FLE26HT3/2/6STP	6	120	1660	1328	5000K	82	-15	0.6	<85	8000	7.3	\$3.13		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		26	4.7	80890	FLE26HT3/2/XL827	10	120	1700	1360	2700K	80	-15	0.6	<85	12000	11.0	\$3.13		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
	26	4.7	47446	FLE26HT3/2/XL/CD	12	120	1700	1360	2700K	80	-15	0.6	<85	12000	11.0	\$3.13		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22	
Spiral® T3 Dimming																					
	Med	14	5.0	66662	FLE14HT3/2DM/BX	3	120	950	760	2700K	82	-10	0.5	<85	10000	9.1	\$1.69	★	T3 Spiral® Dimming	GE2000-0951	19,21,22,25
		26	5.7	66663	FLE26HT3/2DM/BX	3	120	1700	1360	2700K	82	-10	0.5	<85	10000	9.1	\$3.13	★	T3 Spiral® Dimming	GE2010-9353	19,21,22,24
Spiral® T4 and T5 Hi Lumen																					
	Med	29	5.2	81514	FLE29HLX/2XL/827	10	120	2200	1760	2700K	80	-15	0.6	<85	12000	11.0	\$3.49		T4 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		32	6.3	24684	FLE32HLX/2/SW/BX	12	120	2100	1680	2700K	80	-15	0.5	<85	8000	7.3	\$3.85		T4 Spiral®	GE2000-2709	19,20,21,22
		42	7.0	80891	FLE42HLX/2/XL827	10	120	2730	2184	2700K	82	-15	0.6	<85	12000	11.0	\$5.06	★	T4 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		42	7.0	47452	FLE42HLX/2/XL/CD	12	120	2730	2184	2700K	82	-15	0.6	<85	12000	11.0	\$5.06	★	T4 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		42	7.0	97728	FLE42HLX/2/SW/BX	4	120	2730	2184	2700K	82	-15	0.5	<85	12000	11.0	\$5.06	★	T4 Spiral®	GE2000-2709	19,20,21,22,25
		55	5.5	78965	FLE55HT5/2/SW/BX	4	120	3800	3040	2700K	82	-15	0.6	<85	8000	7.3	\$6.62		T5 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
Spiral® 3-Way																					
	Med	26	5.7	77123	FLE26HT3/2D/3BX	6	120	1750/1150/600	1400	2700K	80	-15	0.6	<85	10000	9.1	\$1.57/\$2.29/\$3.13		T3 Spiral®, 3-way	GE2000-0948	1,7,8,9,10,19,20,21,22
		26	5.7	77124	FLE26HT3/2D3CD	3	120	1750/1150/600	1400	2700K	80	-15	0.6	<85	10000	9.1	\$1.57/\$2.29/\$3.13		T3 Spiral®, 3-way	GE2000-0948	1,7,8,9,10,19,20,21,22
	Med	32	5.8	78952	FLE32HT3/2D3/BX	6	120	600/1600/2150	1720	2700K	82	-15	0.5	<85	10000	9.1	\$1.93/\$3.01/\$3.85	★	T3 Spiral®, 3-way	GE2000-0948	1,8,9,16,19,20,21,22,25
		32	6.0	62070	FLE32HT3/2D3CWBX	6	120	600/1600/2150	1720	4000K	82	-15	0.5	<85	8000	7.3	\$1.93/\$3.01/\$3.85		T3 Spiral®, 3-way	GE2000-0948	1,7,9,10,19,20,21,22
		32	6.0	63517	FLE32HT3/2D3/DBX	6	120	540/1440/1935	1548	6500K	70	-15	0.5	<85	8000	7.3	\$1.93/\$3.01/\$3.85		T3 Spiral®, 3-way	GE2000-0950	19,20,21,22
		32	5.8	63482	FLE32HT3/2D3/CD	6	120	600/1600/2150	1720	2700K	82	-15	0.5	<85	10000	9.1	\$1.93/\$3.01/\$3.85	★	T3 Spiral®, 3-way	GE2000-0950	19,20,21,25
Spiral® GU 24																					
	Med	10	3.5	76135	FLE10HT3/2GU24CD	3	120	550	440	2700K	80	-15	0.6	<85	10000	9.1	\$1.20		T3 GU 24 Base	GE2000-0948	1,8,9,10,19,20,21,22
		15	4.1	75367	FLE15HT3/2GU24CD	3	120	1000	800	2700K	82	-15	0.6	<85	10000	9.1	\$1.81		T3 GU 24 Base	GE2000-0948	1,8,9,10,19,20,21,22
		20	4.1	76136	FLE20HT3/2GU24CD	3	120	1200	960	2700K	80	-15	0.6	<85	10000	9.1	\$2.41		T3 GU 24 Base	GE2000-0948	1,8,9,10,19,20,21,22
		26	4.6	76137	FLE26HT3/2GU24CD	3	120	1750	1400	2700K	80	-15	0.6	<85	10000	9.1	\$3.13		T3 GU 24 Base	GE2000-0948	1,8,9,10,19,20,21,22
Reflectors/Indoor PAR																					
	Med	26	6.6	66667	FLE26PAR38DM/BX	3	120	1300	1040	2700K	82	-15	0.5	<85	8000	7.3	\$3.13		PAR38 Dimming	GE2025-1509	19,21,23
		11	4.2	78948	FLE11/2/R20/D/CD	3	120	370	296	6500K	82	-15	0.6	<85	10000	9.1	\$1.32		Relector R20	GE2000-2946	1,8,9,10,12,19,20,21
		11	4.7	80892	FLE11/2/R20XL827	10	120	400	320	2700K	80	-10	0.6	<85	10000	9.1	\$1.32		Relector R20	GE2000-2946	1,8,9,10,12,19,20,21
		11	4.7	47477	FLE11/2/R20XL/CD	12	120	400	320	2700K	80	-10	0.6	<85	10000	9.1	\$1.32		Relector R20	GE2000-2946	1,8,9,10,12,19,20,21
		11	4.7	24691	FLE11/2R20XLSWCD	3	120	400	320	2700K	80	-10	0.5	<85	10000	9.1	\$1.32		Relector R20	GE2024-7456	19,20,21
		11	4.7	85278	FLE11/2/R20SW/BX	6	120	400	320	2700K	80	-10	0.5	<85	10000	9.1	\$1.32		Relector R20	GE2024-7456	19,20,21
		11	4.7	76131	FLE11/2/R20XL/2P	3	120	400	320	2700K	80	-10	0.5	<85	10000	9.1	\$1.32		Relector R20	GE2024-7456	19,20,21
		11	4.2	85279	FLE11/2/R20D/BX	6	120	370	296	6500K	82	-15	0.5	<85	10000	9.1	\$1.32		Relector R20	GE2000-2946	19,20,21
	Med	15	5.3	78950	FLE15/2/R30/D/CD	3	120	650	520	6500K	82	-15	0.6	<85	10000	9.1	\$1.81		Reflector R30	GE2000-2946	1,8,9,10,12,19,20,21
		15	5.3	78951	FLE15/2/R30/D/3P	3	120	650	520	6500K	82	-15	0.6	<85	10000	9.1	\$1.81		Reflector R30	GE2000-2946	1,8,9,10,12,19,20,21
		15	5.3	85023	FLE15/2/R30/D/BX	6	120	650	520	6500K	82	-15	0.5	<85	10000	9.1	\$1.81		Reflector R30	GE2000-2946	19,20,21
		16	5.3	20708	FLE15/2/R30/SWCD	12	120	750	600	2700K	80	-15	0.6	<85	10000	9.1	\$1.93		Reflector R30	GE2024-7456	1,8,9,10,12,19,20,21
		16	5.3	80893	FLE16/2/R30XL827	10	120	750	600	2700K	80	-15	0.6	<85	10000	9.1	\$1.93		Reflector R30	GE2000-2946	1,8,9,10,12,19,20,21
		16	5.3	47478	FLE16/2/R30XL/CD	12	120	750	600	2700K	80	-15	0.6	<85	10000	9.1	\$1.93		Reflector R30	GE2000-2946	1,8,9,10,12,19,20,21
		16	5.3	72984	FLE16/2/R30/2P	3	120	750	600	2700K	80	-15	0.5	<85	10000	9.1	\$1.93		Reflector R30	GE2024-7456	19,20,21

Compact Fluorescent Lamps


Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes
Self-Ballasted Lamps (continued)																				
Reflectors/Indoor PAR (continued)																				
	16	5.3	85022	FLE16/2/R30/SWBX	6	120	750	600	2700K	80	-15	0.5	<85	10000	9.1	\$1.93		Reflector R30	GE2024-7456	19,20,21
	15	5.5	74411	FLE15/2DMR30-LTP	6	120	750	600	2700K	82	-15	0.5	<85	8000	7.3	\$1.81		Reflector R30 Dimming	GE2025-1509	19,21
	15	5.5	66665	FLE15DMR30ES/BX	3	120	750	600	2700K	82	-15	0.5	<85	8000	7.3	\$1.81		Reflector R30 Dimming	GE2025-1509	19,21
	15	5.5	66664	FLE15/2DMR30/BX	3	120	550	440	3000K	82	-5	0.5	<85	8000	7.3	\$1.81		Reflector R30 Dimming	GE2025-1509	19,21
	26	6.5	80894	FLE26/2/R40XL827	6	120	1300	1040	2700K	80	-10	0.6	<85	10000	9.1	\$3.13		Reflector R40	GE2000-2946	1,8,9,10,12,19,20,21
	26	6.5	47479	FLE26/2/R40XL/CD	3	120	1300	1040	2700K	80	-10	0.6	<85	10000	9.1	\$3.13		Reflector R40	GE2000-2946	1,8,9,10,12,19,20,21
	26	6.5	69635	FLE26/2/R40XLNBX	3	120	1300	1040	2700K	80	-10	0.5	<85	10000	9.1	\$3.13		Reflector R40	GE2024-7456	19,20,21
	26	6.5	81676	FLE26/2/R40XL/BX	6	120	1300	1040	2700K	80	-10	0.5	<85	10000	9.1	\$3.13		Reflector R40	GE2024-7456	19,20,21
	26	6.5	63518	FLE26/2R40XL/DBX	6	120	1170	936	6500K	80	-10	0.5	<85	10000	9.1	\$3.13		Reflector R40	GE2024-7456	19,20,21
	26	6.6	66666	FLE26/2DMR40/BX	3	120	1300	1040	2700K	82	-15	0.5	<85	8000	7.3	\$3.13		Reflector R40 Dimming	GE2025-1509	19,21
	26	6.6	69251	FLE26/2DMR40-TP	3	120	1300	1040	2700K	82	-15	0.5	<85	8000	7.3	\$3.13		Reflector R40 Dimming	GE2025-1509	19,21
	26	6.6	69251	FLE26/2DMR40-TP	3	120	1300	1040	2700K	82	-15	0.5	<85	8000	7.3	\$3.13		Reflector R40 Dimming	GE2025-1509	19,21
Outdoor																				
	14	5.1	49894	FLE11/2TC14SWCD FLE14/2TC16SW/CD	3	120	750	600	2700K	82	-15	0.6	<85	10000	9.1	\$1.69		Post Light	GE2000-2946	1,8,10,12,19,20,21
	14	4.9	49895	FLE11/2TC14BUGCD FLE14/2TC16BUGCD	3	120	750	600	2700K	80	-15	0.6	<85	10000	9.1	\$1.69		Bug Yellow Post Light	GE2000-2946	1,8,10,12,19,20,21
	14	4.9	47464	FLE14/2/TC16/BUG	12	120	750	600	2700K	80	-15	0.5	<85	10000	9.1	\$1.69		Bug Yellow Post Light	GE2000-2946	1,8,10,12,19,20,21
	14	5.1	85384	FLE14/2/TC16SW/CD	12	120	750	600	2700K	82	-15	0.5	<85	10000	9.1	\$1.69		Bullet Shape	GE2000-2946	1,8,10,12,19,20,21
	24	5.4	78964	FLE24/2PAR38FLCD	3	120	1185	948	2700K	80	-15	0.6	<85	10000	9.1	\$2.89		Par 38 Flat Lens	GE2010-3449	1,8,9,12,16,19,20,21
	24	5.4	61227	FLE24/2/PAR38FL	6	120	1185	948	2700K	80	-15	0.6	<85	10000	9.1	\$2.89		Par 38 Flat Lens	GE2010-3449	1,8,9,12,16,19,20,21
	24	4.0	64871	FLE24/2PAR38LTP6	6	120	1140	912	2700K	80	-15	0.5	<85	10000	9.1	\$2.89		Par 38 Glass Reflector	GE2010-3449	19,20,21,23
	24	4.0	61165	FLE24PAR38X3TP3	3	120	1140	912	2700K	80	-15	0.5	<85	10000	9.1	\$2.89		Par 38 Glass Reflector	GE2010-3449	19,20,21,23
	26	5.9	21739	FLE26/2/PAR38/CD	3	120	1300	1040	2700K	80	-10	0.6	<85	10000	9.1	\$3.13		Par 38 Glass Reflector	GE2010-3449	1,8,9,12,16,19,20,21
	26	5.9	80895	FLE26/2/PAR38/XL	6	120	1300	1040	2700K	80	-10	0.6	<85	10000	9.1	\$3.13		Par 38 Glass Reflector	GE2010-3449	1,8,9,12,16,19,20,21
	26	5.9	47483	FLE26/2PAR38XCD	3	120	1300	1040	2700K	80	-10	0.6	<85	10000	9.1	\$3.13		Par 38 Glass Reflector	GE2010-3449	1,8,9,12,16,19,20,21
	26	5.9	82004	FLE26/2PAR38/BX	6	120	1300	1040	2700K	80	-10	0.5	<85	10000	9.1	\$3.13		Par 38 Glass Reflector	GE2010-3449	19,20,21,23
	26	5.9	73157	FLE26/2/PAR382P	3	120	1300	1040	2700K	80	-10	0.5	<85	10000	9.1	\$3.13		Par 38 Glass Reflector	GE2010-3449	19,20,21,23
	26	5.9	73157	FLE26/2/PAR382P	3	120	1300	1040	2700K	80	-10	0.5	<85	10000	9.1	\$3.13		Par 38 Glass Reflector	GE2010-3449	19,20,21,23
Decorative Ceiling Fan Medium Base																				
	11	4.4	78939	FLE11/2/A17/D/CD	3	120	460	368	6500K	80	-15	0.6	<85	10000	9.1	\$1.32		A-Line Shape A17	GE2000-2946	1,8,10,12,19,20,21
	11	4.4	78940	FLE11/2/A17/D/3P	3	120	460	368	6500K	80	-15	0.6	<85	10000	9.1	\$1.32		A-Line Shape A17	GE2000-2946	1,8,10,12,19,20,21
	11	4.4	47486	FLE11/2/A17XL/CD	12	120	500	400	2700K	82	-15	0.6	<85	10000	9.1	\$1.32	★	A-Line Shape A17	GE2000-2946	1,8,10,12,19,20,21
	11	4.4	71992	FLE11/2/A17XL3PK	3	120	500	400	2700K	82	-15	0.5	<85	10000	9.1	\$1.32		A-Line Shape A17	GE2000-2946	19,20,21
	11	4.4	49687	FLE11/2/A17XL2PK	3	120	500	400	2700K	82	-15	0.5	<85	10000	9.1	\$1.32		A-Line Shape A17	GE2000-2946	19,20,21
Decorative Ceiling Fan Candelabra Base																				
	11	4.4	78937	FLE11/2/A17CB/CD	3	120	500	400	2700K	82	-15	0.6	<85	10000	9.1	\$1.32	★	A-Line Shape A17, Candelabra Base	GE2000-2946	1,8,10,12,19,20,21
	11	4.4	78938	FLE11/2/A17CB/3P	3	120	500	400	2700K	82	-15	0.6	<85	10000	9.1	\$1.32	★	A-Line Shape A17, Candelabra Base	GE2000-2946	1,8,10,12,19,20,21
	11	4.3	78941	FLE11/2A17CBD/CD	3	120	460	368	6500K	82	-15	0.6	<85	10000	9.1	\$1.32		A-Line Shape A17, Candelabra Base	GE2000-2946	1,8,10,12,19,20,21
	11	4.3	78942	FLE11/2A17CBD/3P	3	120	460	368	6500K	82	-15	0.6	<85	10000	9.1	\$1.32		A-Line Shape A17, Candelabra Base	GE2000-2946	1,8,10,12,19,20,21
Decorative A Shapes																				
	11	4.1	89622	FLE11/2/A19XL	10	120	500	400	2700K	82	-15	0.6	<85	10000	9.1	\$1.32		A-Line Shape A19	GE2000-2946	1,8,10,12,19,20,21
	15	4.5	89632	FLE15/2/A19XL	10	120	825	660	2700K	82	-15	0.6	<85	10000	9.1	\$1.81		A-Line Shape A19	GE2000-2946	1,8,10,12,19,20,21
	15	4.5	72609	FLE15A19XL/CD3PK	3	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.81		A-Line Shape A19	GE2000-2946	19,20,21
	15	4.5	74878	FLE15/2/A19XLCF	3	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.81		A-Line Shape A19	GE2000-2946	19,20,21
	15	4.5	71876	FLE15/2/A19XL/CD	3	120	825	660	2700K	82	-15	0.5	<85	10000	9.1	\$1.81		A-Line Shape A19	GE2000-2946	19,20,21
	20	5.6	89634	FLE20/2/A19XL	10	120	1100	880	2700K	82	-15	0.6	<85	10000	9.1	\$2.41		A-Line Shape A19	GE2024-7456	1,8,10,12,19,20,21
	15	4.8	47487	FLE15/2/A21XL/CD	12	120	800	640	2700K	80	-15	0.6	<85	10000	9.1	\$1.81		A-Line Shape A21	GE2000-2946	1,8,10,12,19,20,21
	15	4.8	47487	FLE15/2/A21XL/CD	12	120	800	640	2700K	80	-15	0.6	<85	10000	9.1	\$1.81		A-Line Shape A21	GE2000-2946	1,8,10,12,19,20,21
Decorative Bullet																				
	20	5.3	89635	FLE20/2/T19XL	10	120	1100	880	2700K	82	-15	0.6	<85	8000	7.3	\$2.41		Bullet Shape	GE2000-2946	1,8,10,12,19,20,21
	26	5.9	89636	FLE26/2/T21XL	10	120	1350	1080	2700K	82	-15	0.6	<85	10000	9.1	\$3.13		Bullet Shape	GE2000-2946	1,8,10,12,19,20,21
Decorative Candle Candelabra Base																				
	9	5.5	85388	FLE9/2/CAC/SW/CD	12	120	400	320	2700K	82	-15	0.6	<85	10000	9.1	\$1.08		Candle Shape, Candelabra Base	GE2000-2946	1,8,10,12,19,20,21
	9	5.5	16105	FLE9/2CAC/XL/827	10	120	400	320	2700K	82	-15	0.6	<85	10000	9.1	\$1.08		Candle Shape, Candelabra Base	GE2000-2946	1,8,10,12,19,20,21
	9	4.3	60299	FLE9/3/CAC/SWBX3	4	120	380	304	2700K	82	-10	0.5	<85	8000	7.3	\$1.08		Candle Shape, Candelabra Base	GE2000-2946	19,20,21

Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes
Self-Ballasted Lamps (continued)																				
Decorative Candle Candelabra Base (continued)																				
	9	4.3	60295	FLE9/3/CAC/SSBX3	4	120	380	304	5000K	82	-10	0.5	<85	8000	7.3	\$1.08		Candle Shape, Candelabra Base	GE2000-2946	19,20,21
	14	5.2	60300	FLE14/3/CACSWBX3	4	120	650	520	2700K	82	-10	0.5	<85	8000	7.3	\$1.69		Candle Shape, Candelabra Base	GE2000-2946	19,20,21
	14	5.2	60296	FLE14/3/CACSSBX3	4	120	650	520	5000K	82	-10	0.5	<85	8000	7.3	\$1.69		Candle Shape, Candelabra Base	GE2000-2946	19,20,21
Decorative Candle Medium Base																				
	9	5.4	47488	FLE9/2/CAM/XL/CD	12	120	430	344	2700K	80	-15	0.6	<85	10000	9.1	\$1.08		Candle Shape, Med Base	GE2000-2946	1,8,10,12,19,20,21
	9	5.4	16106	FLE9/2/CAM/827	10	120	430	344	2700K	82	-15	0.6	<85	6000	5.5	\$1.08		Candle Shape, Med Base	GE2000-2946	1,8,10,12,19,20,21
	9	4.8	60297	FLE9/3/CAM/SWBX3	4	120	380	304	2700K	82	-10	0.5	<85	8000	7.3	\$1.08		Candle Shape, Med Base	GE2000-2946	19,20,21
	9	4.8	60292	FLE9/3/CAM/SSBX3	4	120	380	304	5000K	82	-10	0.5	<85	8000	7.3	\$1.08		Candle Shape, Med Base	GE2000-2946	19,20,21
	9	5.4	24692	FLE9/2/CAM/SW/CD	12	120	430	344	2700K	82	-15	0.5	<85	6000	5.5	\$1.08		Candle Shape, Med Base	GE2000-2946	19,20,21
	9	5.5	79068	FLE9/2/CAC/XL2PK	3	120	430	344	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		Candle Shape, Med Base	GE2000-2946	19,20,21
	9	5.4	49688	FLE9/2/CAM/XL2PK	3	120	430	344	2700K	80	-15	0.5	<85	10000	9.1	\$1.08		Candle Shape, Med Base	GE2000-2946	19,20,21
	14	5.4	60298	FLE14/3/CAMSWBX3	4	120	650	520	2700K	82	-10	0.5	<85	8000	7.3	\$1.69		Candle Shape, Med Base	GE2000-2946	19,20,21
	14	5.4	60294	FLE14/3/CAMSSBX3	4	120	650	520	5000K	82	-10	0.5	<85	8000	7.3	\$1.69		Candle Shape, Med Base	GE2000-2946	19,20,21
Decorative Globes																				
	9	3.2	74587	FLE9/3/G18/3PK	3	120	360	288	2700K	80	0	0.5	<85	8000	7.3	\$1.08		Globe G18	GE2000-2946	19,20,21
	9	3.2	74586	FLE9/3/G18/CD	3	120	360	288	2700K	80	0	0.5	<85	8000	7.3	\$1.08		Globe G18	GE2000-2946	19,20,21
	11	4.6	89629	FLE11/2/G25XL	10	120	500	400	2700K	82	-15	0.6	<85	10000	9.1	\$1.32		Globe G25	GE2000-2946	1,8,10,12,19,20,21
	11	4.6	47484	FLE11/2/G25XL/CD	12	120	500	400	2700K	82	-15	0.6	<85	10000	9.1	\$1.32		Globe G25	GE2000-2946	1,8,10,12,19,20,21
	11	4.6	78946	FLE11/2/G25/D/CD	3	120	450	360	6500K	82	-15	0.6	<85	10000	9.1	\$1.32		Globe G25	GE2000-2946	1,8,10,12,19,20,21
	11	4.6	78947	FLE11/2/G25/D/3P	3	120	450	360	6500K	82	-15	0.6	<85	10000	9.1	\$1.32		Globe G25	GE2000-2946	1,8,10,12,19,20,21
	11	4.6	85392	FLE11/2/G25XL3PK	3	120	500	400	2700K	82	-15	0.5	<85	10000	9.1	\$1.32		Globe G25	GE2000-2946	19,20,21
	11	4.6	89096	FLE11/2/G25XL2PK	3	120	500	400	2700K	82	-15	0.5	<85	10000	9.1	\$1.32		Globe G25	GE2000-2946	19,20,21
	15	4.6	89633	FLE15/2/G25XL	10	120	800	640	2700K	82	-15	0.5	<85	10000	9.1	\$1.81		Globe G25	GE2000-2946	1,8,10,12,19,20,21
	15	4.6	47485	FLE15/2/G25XL/CD	12	120	800	640	2700K	82	-15	0.6	<85	10000	9.1	\$1.81		Globe G25	GE2000-2946	1,8,10,12,19,20,21
	15	4.6	69633	FLE15/2/G25XLCD2	3	120	800	640	2700K	82	-15	0.5	<85	10000	9.1	\$1.81		Globe G25	GE2000-2946	19,20,21
	15	4.6	76132	FLE15/2/G25XL3P	3	120	800	640	2700K	82	-15	0.5	<85	10000	9.1	\$1.81		Globe G25	GE2000-2946	19,20,21
Specialty																				
Colored Spiral®																				
	13	4.9	78955	FLE13HT3/2/GREEN	6	120	NA	NA	NA	NA	5	0.6	<85	8000	7.3	\$1.57		T3, Green, Boxed	GE2000-0948	1,8,9,10
	13	4.9	78956	FLE13HT3/2/RED	6	120	NA	NA	NA	NA	5	0.6	<85	8000	7.3	\$1.57		T3, Red, Boxed	GE2000-0948	1,8,9,10
	13	4.9	78957	FLE13HT3/2/BL	6	120	NA	NA	NA	NA	5	0.6	<85	8000	7.3	\$1.57		T3, Blacklight, Boxed	GE2000-0948	1,8,9,10
	13	4.9	78958	FLE13HT3/2/ORANGE	6	120	NA	NA	NA	NA	5	0.6	<85	8000	7.3	\$1.57		T3, Orange, Boxed	GE2000-0948	1,8,9,10
	13	4.9	78959	FLE13HT3/2/YELLOW	6	120	NA	NA	NA	NA	5	0.6	<85	8000	7.3	\$1.57		T3, Yellow, Boxed	GE2000-0948	1,8,9,10
	13	4.9	78960	FLE13HT3/2/BLUE	6	120	NA	NA	NA	NA	5	0.6	<85	8000	7.3	\$1.57		T3, Blue, Boxed	GE2000-0948	1,8,9,10
Germicidal																				
2G11	60	16.3	72301	GBX60/UVC	25									8000				Clear, 4-Pin UVC Source. WARNING: Risk group 3 (High Risk): UV emitted from this lamp. Avoid exposure of eyes and skin to unshielded lamp. Skin or eye injury will result. Life rating is based on UV maintenance curve and is measured at 80% of initial (100 hr) UVC output.		

Compact Fluorescent Lamps

Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes
Film and TV Lighting HLBX 4-Pin																				
	55	20.7	41873	F55BX/STUDIOBX56	40		4100		5600	89				10000				High color rendering. Ideal for TV studios, live broadcasts. Color tuned to match tungsten and daylight light sources.		
	55	20.7	41903	F55BX/CINPLUS/32	40		2400		3200	92				2000				High color rendering. Soft light used in film applications. GEL free light source. Matches the color spectrum of film. LB and CC +/-5.		
	55	20.7	41911	F55BX/CINPLUS/55	40		2400		5500	95				2000				High color rendering. Soft light used in film applications. GEL free light source. Matches the color spectrum of film. LB and CC +/-5.		

Footnotes

- 1 Fluorescent lamp lumens decline during life.
- 2 Based on 60Hz reference circuit.
- 3  10-watt, 16-watt and 28-watt 2D® lamps may be operated in any position. 21-watt, 38-watt, 39-watt and 55-watt 2D® lamps must be used with the leg marked (a) in the diagram below the bend (b), in order to avoid overheating the end of the cap marked (c).
- 4 Life ratings for the F18BX preheat lamps are based on operating the lamp at 3 hrs. per start on a preheat type circuit. Operation on rapid start and instant start ballasts is not recommended.
- 5 Cold cathode resistance is approximately 6.0 Ohms.
- 6 4-Pin lamp minimum starting temperature is a function of the ballast. Most ballasts are rated with a minimum starting temperature of 50°F (10°C). Ballasts are also available that provide reliable starting to 0°F (-18°C) and -20°F (-29°C).
- 7 Most one-piece self-ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades.
- 8 Lumens on one-piece self-ballasted lamp systems are measured base up.
- 9 Best performance if operated base up and at 77°F (25°C) ambient temperature.
- 10 Use only on 120V, 60Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.
- 11 Adapters rated at 40,000 hours life.
- 12 Amalgam products experience stable brightness over a wider temperature range and in various operating positions.
- 13 Life ratings are based on operating the lamp at 3 hrs. per start on a rapid start type ballast. Life rating on a preheat or instant start ballast is 25% lower.
- 14 Use only on 120V, 60Hz circuits. Do not use on with photocells or timers. Do not use in wet locations.
- 15 These lamps are only recommended for use with single-lamp ballasts or parallel-wired 2-lamp ballasts.
- 16 UL Listed for wet locations. Use only on 120V, 60Hz circuits. Do not use on dimming circuits, photocells or timers.
- 17 Max. bulb wall temperature not to exceed 180°C. Consult GE sales representative for further information.
- 18 Life ratings are based on operating the lamp on a high frequency electronic rapid start type ballast.
- 19 This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45 - 30 MHz. Not intended for use with emergency exit fixtures or lights.
Use only on 120V 60 Hz circuits.
When using CFL with motion sensor, preset "on" time on the device as long as possible to avoid frequent switching. (Otherwise lamp life will be decreased significantly)
- 20 Not intended for use with dimmers. Some electronic timer and photosensor devices contain dimming circuitry, so before using them, check with its manufacturer to ensure compatibility with CFL bulbs.

21 RISK OF ELECTRICK SHOCK

DO NOT USE WHERE DIRECTLY EXPOSED TO WATER

Do not open - no user serviceable parts inside

22 Lamp may shatter and cause injury if broken

Remove and install by grasping only plastic portion of the lamp

23 SUITABLE FOR WET LOCATION

24 SUITABLE FOR USE IN ENCLOSED LUMINAIRES

25 NOT FOR USE IN ENCLOSED FIXTURE

Caution Notices

151

⚠ CAUTION

Lamp may shatter and cause injury if broken

- Remove and install by grasping only plastic portion of the lamp

GE2000-0948

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open—no user serviceable parts inside

Lamp may shatter and cause injury if broken

- Remove and install by grasping only plastic portion of the lamp

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45-30 MHz. Not intended for use with emergency exit fixture or lights, electronic timers, photocells, or with dimmers

GE2000-0950

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open—no user serviceable parts inside

Lamp may shatter and cause injury if broken

- Remove and install by grasping only plastic portion of the lamp

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45 - 30 MHz. Not intended for use with emergency exit fixtures or lights, or with dimmers. Not for use in enclosed fixtures.

GE2000-0951

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open—no user serviceable parts inside

Lamp may shatter and cause injury if broken

- Remove and install by grasping only plastic portion of the lamp

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45 - 30 MHz. Not intended for use with emergency exit fixtures or lights, or with dimmers. Not for use in enclosed fixtures.

Incandescent

Halogen

High Intensity Discharge

Fluorescent

Compact Fluorescent

LED Lamps and Systems

Stage and Studio

Miniature, Sealed Beam and Automotive

Projection

Compact Fluorescent Lamps

Caution Notices (continued)

GE2000-2709

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open - no user serviceable parts inside

Lamp may shatter and cause injury if broken

- Remove and install by grasping only plastic portion of the lamp

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45 - 30 MHz. Not intended for use with emergency exit fixtures or lights, or with dimmers. Not for use in enclosed fixtures.

GE2000-2946

⚠ CAUTION

Risk of electric shock

- Do not open—no user serviceable parts inside
- Do not use where directly exposed to water or outdoors without an enclosed fixture

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45-30 MHz. Not intended for use with emergency exit fixtures or lights, electronic timers, photocells, or with dimmers.

GE2010-3449

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open—no user serviceable parts inside
- Use indoors only

Lamp may shatter and cause injury if broken

- Remove and install by grasping only plastic portion of the lamp

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45-30 MHz. Not intended for use with emergency exit fixtures or lights, in totally enclosed recessed fixtures, or with dimmers. Added weight may cause instability of free-standing portable lamps. Use only with portable lamps in which the distance from the bottom of the base to the top of the lamp holder does not exceed three times the base width. Use only with portable lamps which are provided with lamp shades.

GE2010-9353

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open - no user serviceable parts inside

Lamp may shatter and cause injury if broken

- Remove and install by grasping only plastic portion of the lamp

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45 - 30 MHz. Not intended for use with emergency exit fixtures or lights, or with dimmers. Not for use in enclosed fixtures.

GE2023-6025

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open - no user serviceable parts inside

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45 - 30 MHz. Not intended for use with emergency exit fixtures or lights, or with dimmers. Not for use in enclosed fixtures.

GE2024-7455

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open - no user serviceable parts inside

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45 - 30 MHz. Not intended for use with emergency exit fixtures or lights, or with dimmers.

GE2024-7456

⚠ CAUTION

Risk of electric shock

- Do not open—no user serviceable parts inside
- Do not use where directly exposed to water or outdoors without an enclosed fixture

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45-30 MHz. Not intended for use with emergency exit fixtures or lights, electronic timers, photocells, dimmers, or in totally enclosed recessed fixtures.

GE2025-1509

⚠ CAUTION

Risk of electric shock

- Do not use where directly exposed to water
- Do not open - no user serviceable parts inside

This product complies with Part 18 of the FCC Rules, but may cause interference to radios, televisions, wireless telephones, and remote controls. Avoid placing this product near these devices. If interference occurs, move the product away from the device or plug either into a different outlet. Do not install this product near maritime safety equipment or other critical navigation or communication equipment operating between 0.45 - 30 MHz. Not intended for use with emergency exit fixtures or lights. Performance ratings are based on base up orientation.

Do not operate this product in ambient temperatures exceeding xx°C

Cross-Reference

GE Description	GE Product Code	Generic Description	Osram/Sylvania Description	Philips Description
Order This GE Lamp		If you currently use these lamps		

Low Wattage Biax® 2-Pin

F58X/827/ECO	97551	CFT5W/G23/827	CF5DS/827/ECO	PL-S 5W/827/2P/Alto
F58X/841/ECO	97553	CFT5W/G23/841	CF5DS/841/ECO	PL-S 5W/841/2P/Alto
F78X/827/ECO	97554	CFT7W/G23/827	CF7DS/827/ECO	PL-S 7W/827/2P/Alto
F78X/835/ECO	97556	CFT7W/G23/835	CF7DS/835/ECO	PL-S 7W/835/2P/Alto
F78X/841/ECO	97557	CFT7W/G23/841	CF7DS/841/ECO	PL-S 7W/841/2P/Alto
F98X/827/ECO	97558	CFT9W/G23/827	CF9DS/827/ECO	PL-S 9W/827/2P/Alto
F98X/835/ECO	97560	CFT9W/G23/835	CF9DS/835/ECO	PL-S 9W/835/2P/Alto
F98X/841/ECO	97561	CFT9W/G23/841	CF9DS/841/ECO	PL-S 9W/841/2P/Alto
F138X/827/ECO	97573	CFT13W/GX23/827	CF13DS/827/ECO	PL-S 13W/827/2P/Alto
F138X/830/ECO	97574	CFT13W/GX23/830	CF13DS/830/ECO	PL-S 13W/830/2P/Alto
F138X/835/ECO	97569	CFT13W/GX23/835	CF13DS/835/ECO	PL-S 13W/835/2P/Alto
F138X/841/ECO	97571	CFT13W/GX23/841	CF13DS/841/ECO	PL-S 13W/841/2P/Alto
F138X/850/ECO	97572	CFT13W/GX23/850	CF13DS/850/ECO	PL-S 13W/850/2P/Alto
F138X/E/827/ECO	97562	CFT13W/GX23/827	CF13WDS/EC/827/ECO	—
F138X/E/830/ECO	97563	CFT13W/GX23/830	CF13WDS/EC/830/ECO	—

High Lumen Biax® 4-Pin

F188X/SPX30	16649	FT18W/2G11/830	FT18DL/830	PL-L 18W/830
F188X/SPX35	16053	FT18W/2G11/835	FT18DL/835	PL-L 18W/835
F188X/SPX41	16940	FT18W/2G11/841	FT18DL/841	PL-L 18W/841
F188X/SPX30/RS	17174	FT18W/2G11/RS/830	FT18DL/830/RS	—
F188X/SPX35/RS	17175	FT18W/2G11/RS/835	FT18DL/835/RS	—
F188X/SPX41/RS	17176	FT18W/2G11/RS/841	FT18DL/841/RS	—
F188X/SPX65/RS	12521	FT18W/2G11/RS/865	—	—
F278X/SPX30/RS	16944	FT24W/2G11/830	FT24DL/830	PL-L 24W/830
F278X/SPX35/RS	16948	FT24W/2G11/835	FT24DL/835	PL-L 24W/835
F278X/SPX41/RS	16951	FT24W/2G11/841	FT24DL/841	PL-L 24W/841
F398X/SPX30/RS	16538	FT36W/2G11/830	FT36DL/830	PL-L 36W/830
F398X/SPX35/RS	15867	FT36W/2G11/835	FT36DL/835	PL-L 36W/835
F398X/SPX41/RS	16952	FT36W/2G11/841	FT36DL/841	PL-L 36W/841
F40Q/25/BX830/IS/WM	75399	FT40W/2G11/IS/830	F40DL/28W/830/SS/IS/ECO	PL-L 40W/830/XEW/4P/IS 25W
F40Q/25/BX835/IS/WM	75400	FT40W/2G11/IS/835	F40DL/28W/835/SS/IS/ECO	PL-L 40W/835/XEW/4P/IS 25W
F40Q/25/BX841/IS/WM	75401	FT40W/2G11/IS/841	F40DL/28W/841/SS/IS/ECO	PL-L 40W/841/XEW/4P/IS 25W
F40Q/25/BX850/IS/WM	75402	FT40W/2G11/IS/850	—	—
F40Q/308X/SPX30	16953	FT40W/2G11/RS/830	FT40DL/830/RS	PL-L 40W/830/RS/IS
F40Q/308X/SPX35	16648	FT40W/2G11/RS/835	FT40DL/835/RS	PL-L 40W/835/RS/IS
F40Q/308X/SPX41	16954	FT40W/2G11/RS/841	FT40DL/841/RS	PL-L 40W/841/RS/IS
F40Q/308X/SPX50/RS	10490	FT40W/2G11/RS/850	FT40DL/850/RS	—
F508XSPX30RS	20898	FT50W/2G11/RS/830	—	PL-L 50W/830/RS
F508XSPX35RS	20899	FT50W/2G11/RS/835	—	PL-L 50W/835/RS
F508XSPX41RS	20900	FT50W/2G11/RS/841	—	PL-L 50W/841/RS
F558X/830	31951	FT55W/2G11/RS/830	FT55DL/830	—
F558X/835	31952	FT55W/2G11/RS/835	FT55DL/835	—
F558X/841	31953	FT55W/2G11/RS/841	FT55DL/841	—

Double Biax® 2-Pin

F9DBX23/827/ECO	97576	CFQ9W/G23/827	CF9DD/827	—
F9DBX23/841/ECO	97575	CFQ9W/G23/841	—	—
F13DBX23/827/ECO	97586	CFQ13W/GX23/827	CF13DD/827	PL-C 13W/827/USA/Alto
F13DBX23/830/ECO	97587	CFQ13W/GX23/830	CF13DD/830	PL-C 13W/830/USA/Alto
F13DBX23/835/ECO	97588	CFQ13W/GX23/835	CF13DD/835	PL-C 13W/835/USA/Alto
F13DBX23/841/ECO	97589	CFQ13W/GX23/841	CF13DD/841	PL-C 13W/841/USA/Alto
F13DBX/827/ECO	97590	CFQ13W/G24d/827	—	PL-C 13W/827/Alto
F13DBX/830/ECO	97591	CFQ13W/G24d/830	—	PL-C 13W/830/Alto
F13DBX/835/ECO	97592	CFQ13W/G24d/835	—	—
F13DBX/841/ECO	97593	CFQ13W/G24d/841	—	—
F18DBX/827/ECO	97577	CFQ18W/G24d/827	CF18DD/827	PL-C 18W/827/Alto
F18DBX/830/ECO	97578	CFQ18W/G24d/830	CF18DD/830	PL-C 18W/830/Alto
F18DBX/835/ECO	97579	CFQ18W/G24d/835	CF18DD/835	PL-C 18W/835/Alto
F18DBX/841/ECO	97580	CFQ18W/G24d/841	CF18DD/841	PL-C 18W/841/Alto
F26DBX/827/ECO	97606	CFQ26W/G24d/827	CF26DD/827	PL-C 26W/827/Alto

GE Description	GE Product Code	Generic Description	Osram/Sylvania Description	Philips Description
Order This GE Lamp		If you currently use these lamps		

Double Biax® 2-Pin (continued)

F26DBX/830/ECO	97607	CFQ26W/G24d/830	CF26DD/830	PL-C 26W/830/Alto
F26DBX/835/ECO	97608	CFQ26W/G24d/835	CF26DD/835	PL-C 26W/835/Alto
F26DBX/841/ECO	97609	CFQ26W/G24d/841	CF26DD/841	PL-C 26W/841/Alto
F26DBX/E/827/ECO	97602	CFQ26W/G24d/827	—	—
F26DBX/E/835/ECO	97604	CFQ26W/G24d/835	—	—

Double Biax® 4-Pin

F13DBX/827/ECO4P	97594	CFQ13W/G24q/827	CF13DD/E/827	PL-C 13W/827/4P/Alto
F13DBX/830/ECO4P	97595	CFQ13W/G24q/830	CF13DD/E/830	PL-C 13W/830/4P/Alto
F13DBX/835/ECO4P	97596	CFQ13W/G24q/835	CF13DD/E/835	PL-C 13W/835/4P/Alto
F13DBX/841/ECO4P	97597	CFQ13W/G24q/841	CF13DD/E/841	PL-C 13W/841/4P/Alto
F18DBX/827/ECO4P	97598	CFQ18W/G24q/827	CF18DD/E/827	PL-C 18W/827/4P/Alto
F18DBX/830/ECO4P	97599	CFQ18W/G24q/830	CF18DD/E/830	PL-C 18W/830/4P/Alto
F18DBX/835/ECO4P	97600	CFQ18W/G24q/835	CF18DD/E/835	PL-C 18W/835/4P/Alto
F18DBX/841/ECO4P	97601	CFQ18W/G24q/841	CF18DD/E/841	PL-C 18W/841/4P/Alto
F26DBX/827/ECO4P	97610	CFQ26W/G24q/827	CF26DD/E/827	PL-C 26W/827/4P/Alto
F26DBX/830/ECO4P	97611	CFQ26W/G24q/830	CF26DD/E/830	PL-C 26W/830/4P/Alto
F26DBX/835/ECO4P	97612	CFQ26W/G24q/835	CF26DD/E/835	PL-C 26W/835/4P/Alto
F26DBX/841/ECO4P	97613	CFQ26W/G24q/841	CF26DD/E/841	PL-C 26W/841/4P/Alto

Triple Biax® 4-Pin

F13TBX827/4P/ECO	97623	CFTR13W/GX24q/827	CF13DT/E/827	PL-T 13W/827/X/4P/Alto
F13TBX/827/A/ECO	97519	CFTR13W/GX24q/827	—	—
F13TBX/830/A/ECO	97620	CFTR13W/GX24q/830	—	—
F13TBX/835/A/ECO	97621	CFTR13W/GX24q/835	—	—
F13TBX/841/A/ECO	97622	CFTR13W/GX24q/841	—	—
F18TBX827/4P/ECO	97628	CFTR18W/GX24q/827	CF18DT/E/827	PL-T 18W/827/X/4P/Alto
F18TBX/827/A/ECO	97624	CFTR18W/GX24q/827	CF18DT/E/IN/827	PL-T 18W/827/4P/Alto
F18TBX/830/A/ECO	97625	CFTR18W/GX24q/830	CF18DT/E/IN/830	PL-T 18W/830/4P/Alto
F18TBX/835/A/ECO	97626	CFTR18W/GX24q/835	CF18DT/E/IN/835	PL-T 18W/835/4P/Alto
F18TBX/841/A/ECO	97627	CFTR18W/GX24q/841	CF18DT/E/IN/841	PL-T 18W/841/4P/Alto
F26TBX827/4P/ECO	97618	CFTR26W/GX24q/827	CF26DT/E/827	PL-T 26W/827/X/4P/Alto
F26TBX/827/A/ECO	97614	CFTR26W/GX24q/827	CF26DT/E/IN/827	PL-T 26W/827/4P/Alto
F26TBX/830/A/ECO	97615	CFTR26W/GX24q/830	CF26DT/E/IN/830	PL-T 26W/830/4P/Alto
F26TBX/835/A/ECO	97616	CFTR26W/GX24q/835	CF26DT/E/IN/835	PL-T 26W/835/4P/Alto
F26TBX/841/A/ECO	97617	CFTR26W/GX24q/841	CF26DT/E/IN/841	PL-T 26W/841/4P/Alto
F32TBX/827/A/ECO	97629	CFTR32W/GX24q/827	CF32DT/E/IN/827	PL-T 32W/827/4P/Alto
F32TBX/830/A/ECO	97630	CFTR32W/GX24q/830	CF32DT/E/IN/830	PL-T 32W/830/4P/Alto
F32TBX/835/A/ECO	97631	CFTR32W/GX24q/835	CF32DT/E/IN/835	PL-T 32W/835/4P/Alto
F32TBX/841/A/ECO	97632	CFTR32W/GX24q/841	CF32DT/E/IN/841	PL-T 32W/841/4P/Alto
F42TBX/827/A/ECO	97633	CFTR42W/GX24q/827	CF42DT/E/IN/827	PL-T 42W/827/4P/Alto
F42TBX/830/A/ECO	97634	CFTR42W/GX24q/830	CF42DT/E/IN/830	PL-T 42W/830/4P/Alto
F42TBX/835/A/ECO	97635	CFTR42W/GX24q/835	CF42DT/E/IN/835	PL-T 42W/835/4P/Alto
F42TBX/841/A/ECO	97636	CFTR42W/GX24q/841	CF42DT/E/IN/841	PL-T 42W/841/4P/Alto

High Output Biax® 4-Pin

F57QBX827A4P/EOL	48861	CFM57W/GX24q/827	CF57DT/E/IN/827	—
F57QBX830A4P/EOL	48862	CFM57W/GX24q/830	CF57DT/E/IN/830	PL-T 57W/830/4P/A
F57QBX835A4P/EOL	48863	CFM57W/GX24q/835	CF57DT/E/IN/835	PL-T 57W/835/4P/A
F57QBX841A4P/EOL	48864	CFM57W/GX24q/841	CF57DT/E/IN/841	PL-T 57W/841/4P/A
F57QBX850A4P/EOL	93404	CFM57W/GX24q/850	—	—
F70QBX827A4P/EOL	48865	CFM70W/GX24q/827	—	—
F70QBX830A4P/EOL	48866	CFM70W/GX24q/830	—	—
F70QBX835A4P/EOL	48867	CFM70W/GX24q/835	—	—
F70QBX841A4P/EOL	48868	CFM70W/GX24q/841	—	—
F70QBX850A4P/EOL	93406	CFM70W/GX24q/850	—	—

Compact Fluorescent Lamps

GE Enhanced Plug-in Product Conversion

PC	PC Description	New PC	New Description
If you used to order GE product:		Now order GE product:	
37654	F5BX/SPX27/827	97551	F5BX/827/ECO
37661	F5BX/SPX41/840	97553	F5BX/841/ECO
37846	F7BX/SPX27/827	97554	F7BX/827/ECO
37659	F7BX/SPX35/835	97556	F7BX/835/ECO
37660	F7BX/SPX41/840	97557	F7BX/841/ECO
37651	F9BX/SPX27/827	97558	F9BX/827/ECO
37652	F9BX/SPX35/835	97560	F9BX/835/ECO
37653	F9BX/SPX41/840	97561	F9BX/841/ECO
41645	F13BX/E/827	97562	F13BX/E/827/ECO
41646	F13BX/E/830	97563	F13BX/E/830/ECO
17048	F13BX/SPX35/835	97569	F13BX/835/ECO
20434	F13BX/SPX41/840	97571	F13BX/841/ECO
11671	F13BX/SPX50	97572	F13BX/850/ECO
14650	F13BX/SPX27/827	97573	F13BX/827/ECO
17612	F13BX/SPX30/830	97574	F13BX/830/ECO
42065	F9DBX23T4/841	97575	F9DBX23/841/ECO
12409	F9DBX23T4SPX27/8	97576	F9DBX23/827/ECO
18844	F13DBX23T4/SPX27	97586	F13DBX23/827/ECO
10574	F13DBX23T4/SPX30	97587	F13DBX23/830/ECO
18556	F13DBX23T4/SPX35	97588	F13DBX23/835/ECO
20531	F13DBX23T4/SPX41	97589	F13DBX23/841/ECO
18557	F13DBXT4/SPX27	97590	F13DBX/827/ECO
12956	F13DBXT4/SPX30	97591	F13DBX/830/ECO
18559	F13DBXT4/SPX35	97592	F13DBX/835/ECO
20532	F13DBXT4/SPX41	97593	F13DBX/841/ECO
30035	F13DBX/SPX27/4P	97594	F13DBX/827/ECO4P
10580	F13DBX/SPX30/4P	97595	F13DBX/830/ECO4P
30037	F13DBX/SPX35/4P	97596	F13DBX/835/ECO4P
30038	F13DBX/SPX41/4P	97597	F13DBX/841/ECO4P
12860	F18DBXT4/SPX27	97577	F18DBX/827/ECO
12861	F18DBXT4/SPX30	97578	F18DBX/830/ECO
12863	F18DBXT4/SPX35	97579	F18DBX/835/ECO
12864	F18DBXT4/SPX41	97580	F18DBX/841/ECO
12865	F18DBX/SPX27/4P	97598	F18DBX/827/ECO4P
12866	F18DBX/SPX30/4P	97599	F18DBX/830/ECO4P
12869	F18DBX/SPX35/4P	97600	F18DBX/835/ECO4P
12870	F18DBX/SPX41/4P	97601	F18DBX/841/ECO4P
46290	F26DBX/E/827	97602	F26DBX/E/827/ECO
46292	F26DBX/E/835	97604	F26DBX/E/835/ECO
35250	F26DBXT4/SPX27	97606	F26DBX/827/ECO
35237	F26DBXT4/SPX30	97607	F26DBX/830/ECO
35251	F26DBXT4/SPX35	97608	F26DBX/835/ECO
35252	F26DBXT4/SPX41	97609	F26DBX/841/ECO
35247	F26DBXT4SPX27/4P	97610	F26DBX/827/ECO4P
35235	F26DBXT4SPX30/4P	97611	F26DBX/830/ECO4P
35248	F26DBXT4SPX35/4P	97612	F26DBX/835/ECO4P
35236	F26DBXT4SPX41/4P	97613	F26DBX/841/ECO4P
34391	F13TBX/SPX27/A/4	97619	F13TBX/827/A/ECO
34395	F13TBX/SPX30/A/4	97620	F13TBX/830/A/ECO
34400	F13TBX/SPX35/A/4	97621	F13TBX/835/A/ECO
34387	F13TBX/SPX41/A/4	97622	F13TBX/841/A/ECO
47696	F13TBX827/4P/EOL	97623	F13TBX827/4P/ECO
34392	F18TBX/SPX27/A/4	97624	F18TBX/827/A/ECO
34396	F18TBX/SPX30/A/4	97625	F18TBX/830/A/ECO
34405	F18TBX/SPX35/A/4	97626	F18TBX/835/A/ECO
34385	F18TBX/SPX41/A/4	97627	F18TBX/841/A/ECO
48869	F18TBX827/4P/EOL	97628	F18TBX827/4P/ECO
34393	F26TBX/SPX27/A/4	97614	F26TBX/827/A/ECO
34397	F26TBX/SPX30/A/4	97615	F26TBX/830/A/ECO
34406	F26TBX/SPX35/A/4	97616	F26TBX/835/A/ECO
34381	F26TBX/SPX41/A/4	97617	F26TBX/841/A/ECO
48870	F26TBX827/4P/EOL	97618	F26TBX827/4P/ECO
39377	F32TBX/SPX27/A/4P	97629	F32TBX/827/A/ECO

PC	PC Description	New PC	New Description
If you used to order GE product:		Now order GE product:	
39378	F32TBX/SPX30A/4P	97630	F32TBX/830/A/ECO
39379	F32TBX/SPX35A/4P	97631	F32TBX/835/A/ECO
39380	F32TBX/SPX41A/4P	97632	F32TBX/841/A/ECO
46312	F42TBX827A4P/EOL	97633	F42TBX/827/A/ECO
46313	F42TBX830A4P/EOL	97634	F42TBX/830/A/ECO
46314	F42TBX835A4P/EOL	97635	F42TBX/835/A/ECO
46315	F42TBX841A4P/EOL	97636	F42TBX/841/A/ECO
48861	F57QBX/827/A/4P/EOL	48861	F57QBX/827/A/ECO
48862	F57QBX/830/A/4P/EOL	48862	F57QBX/830/A/ECO
48863	F57QBX/835/A/4P/EOL	48863	F57QBX/835/A/ECO
48864	F57QBX/841/A/4P/EOL	48864	F57QBX/841/A/ECO
93404	F57QBX/850/A/4P/EOL	93404	F57QBX/850/A/ECO
48865	F70QBX/827/A/4P/EOL	48865	F70QBX/827/A/ECO
48866	F70QBX/830/A/4P/EOL	48866	F70QBX/830/A/ECO
48867	F70QBX/835/A/4P/EOL	48867	F70QBX/835/A/ECO
48868	F70QBX/841/A/4P/EOL	48868	F70QBX/841/A/ECO
93406	F70QBX/850/A/4P/EOL	93406	F70QBX/850/A/ECO