

MINITERMS

Nylon Ring Terminals

R Series

SPECIFICATIONS

- Nylon: Electro tin plated copper with brazed seam, easy-entry Nylon, 600V, 105 °C.

FEATURES

- Nylon Ring Terminal have Basic tongue type ring terminal. Safe and reliable connections, because it cannot be disconnected unless the screw is completely removed.



FIG. NO.	INSULATION TYPE	WIRE RANGE	STUD SIZE	RATINGS	LENGTH (L) (IN.)	WIDTH (W) (IN.)	SEAM TYPE	STD PACKS		BULK PACKS	
								CAT. NO.	QTY	CAT. NO.	QTY
1	Nylon	22-18	1/4	UL	1.094	0.456	Butted	R22-14N	100	R22-14N-BULK	1000
1	Nylon	22-18	5/16	UL	1.094	0.456	Butted	R22-56N	100	R22-56N-BULK	1000
1	Nylon	22-18	3/8	UL	1.248	0.535	Butted	R22-38N	100	R22-38N-BULK	1000
1	Nylon	22-18	#10	UL	0.866	0.314	Butted	R22-10N	100	R22-10N-BULK	1000
1	Nylon	22-18	#4	UL	0.953	0.264	Butted	R22-4N	100	R22-4N-BULK	1000
1	Nylon	22-18	#6	cULus	0.866	0.314	Butted	R22-6N	100	R22-6N-BULK	1000
1	Nylon	22-18	#8	UL	0.866	0.314	Butted	R22-8N	100	R22-8N-BULK	1000
2	Nylon	16-14	1/4	UL	1.102	0.472	Butted	R16-14N	100	R16-14N-BULK	1000
2	Nylon	16-14	5/16	UL	0.807	0.529	Butted	R16-56N	100	R16-56N-BULK	1000
2	Nylon	16-14	3/8	UL	1.248	0.535	Butted	R16-38N	100	R16-38N-BULK	1000
2	Nylon	16-14	1/2	—	1.44	0.755	Butted	R16-50N	100	R16-50N-BULK	1000
2	Nylon	16-14	#10	cULus	0.905	0.334	Butted	R16-10N	100	R16-10N-BULK	1000
2	Nylon	16-14	#6	UL	0.995	0.31	Butted	R16-6N	100	R16-6N-BULK	1000
2	Nylon	16-14	#8	cULus	0.905	0.334	Butted	R16-8N	100	R16-8N-BULK	1000
3	Nylon	12-10	1/4	cULus	1.161	0.472	Butted	R12-14N	50	R12-14N-BULK	500
3	Nylon	12-10	5/16	UL	1.346	0.59	Butted	R12-56N	50	R12-56N-BULK	500
3	Nylon	12-10	3/8	UL	1.346	0.59	Butted	R12-38N	50	R12-38N-BULK	500
3	Nylon	12-10	1/2	—	1.519	0.755	Butted	R12-50N	50	R12-50N-BULK	500
3	Nylon	12-10	#10	cULus	1.023	0.374	Butted	R12-10N	50	R12-10N-BULK	500
3	Nylon	12-10	#6	UL	1.023	0.374	Butted	R12-6N	50	R12-6N-BULK	500
3	Nylon	12-10	#8	UL	1.023	0.374	Butted	R12-8N	50	R12-8N-BULK	500
4	Nylon	8	1/4	UL	1.39	0.468	Butted	R8-14N	50	R8-14N-BULK	250
4	Nylon	8	5/16	UL	1.39	0.468	Butted	R8-56N	50	R8-56N-BULK	250
4	Nylon	8	3/8	UL	1.51	0.588	Butted	R8-38N	50	R8-38N-BULK	250
4	Nylon	8	#10	UL	1.39	0.468	Butted	R8-10N	50	R8-10N-BULK	500
5	Nylon	#6	1/4	UL	1.355	0.48	Butted	R6-14N	50	R6-14N-BULK	250
5	Nylon	#6	5/16	UL	1.355	0.64	Butted	R6-56N	50	R6-56N-BULK	250
5	Nylon	#6	3/8	UL	1.355	0.64	Butted	R6-38N	50	R6-38N-BULK	250
5	Nylon	#6	1/2	—	1.447	0.832	Butted	R6-50N	50	R6-50N-BULK	250
6	Nylon	#4	1/4	UL	1.85	0.475	Butted	R4-14N	25	R4-14N-BULK	100
6	Nylon	#4	5/16	UL	1.85	0.475	Butted	R4-56N	25	R4-56N-BULK	100
6	Nylon	#4	3/8	UL	1.95	0.668	Butted	R4-38N	25	R4-38N-BULK	100
6	Nylon	#4	1/2	UL	1.95	0.668	Butted	R4-50N	25	R4-50N-BULK	100
7	Nylon	#2	1/4	UL	1.821	0.645	Butted	R2-14N	25	R2-14N-BULK	100
7	Nylon	#2	5/16	UL	1.821	0.645	Butted	R2-56N	25	R2-56N-BULK	100
7	Nylon	#2	3/8	UL	1.821	0.645	Butted	R2-38N	25	R2-38N-BULK	100
7	Nylon	#2	1/2	—	2.202	0.863	Butted	R2-50N	25	R2-50N-BULK	100