Cover more applications with the most versatile Weatherproof Covers on the market







Our durable line-up of Die-cast and Plastic Weatherproof Covers offers long-lasting protection in all types of rugged applications: industrial, commercial, manufacturing, residential, and more! Time-saving features and resilient construction make these weatherproof covers the most versatile around.

#### STAY COMPLIANT 2014 NEC Code 406.9 (B1)


Intermatic Weatherproof Covers meet or exceed the latest NEC requirements for extra-duty applications and wet locations.

- For the 2014 NEC, all 15 and 20-ampere, 125 and 250 volt receptacles installed in a wet location still must have an enclosure and covers that are weatherproof whether an attachment plug cap is inserted or not.
- A revision now requires all enclosures and covers installed in wet locations for 15 and 20 ampere, 125 and 250 volt
  receptacles to be listed, and of the "extra duty" type, not just boxes supported from grade.
- This requirement is now also required at dwelling units as well. The requirement for weather-resistant type receptacles in wet locations is still applicable in the 2014 NEC. This change also provoked changes at 590.4(D)(2) for extra duty covers for all 15 and 20 ampere, 125 and 250 volt receptacles installed at temporary installations in a wet location.
- Exceeds the CEC Rule 26-702.

# **Features**

UL, CSA Listed, NEMA 3R, 2014 NEC® 406.9 (B1) Compliant, and CEC Rule 26-702

# **Extra-Duty Die-Cast Aluminum**



All covers come with Flexi-Guard Inserts, see page 7.



# WP5000 Extra-Duty Plastic Series

Extra-Duty Plastic Weatherproof Covers are easy to install and shipped with an adhered gasket, mounting screws, base, cover assembly, and inserts for a variety of applications.







#### **FEATURES**

- Complies with 2014 Article 406.9(B)(1) for wet locations and extra-duty applications
- Meets requirements for cold impact testing: -60° F (-51° C)
- 5000, 5100, 5200 Series available in 10 different colors
- 5500 Series available in Clear, Gray, and Yellow
- Heavy-duty UV stabilized polycarbonate construction ensures long-lasting durability
- Lockable hasp: All models accept up to 0.25" dia shank
- Impact rated: 12 lb impact test to ensure cover remains intact
- Single gang covers mount vertically or horizontally
- Single Gang Models:
  - 3 inserts provided with all models that allow each model to meet multiple installations (up to 16 configurations)
- Double Gang Models:
  - 6 inserts provided with all models that allow each model to meet multiple installations (up to 70 configurations)
  - 2 round inserts accommodate from 1.375" to 2.656" plugs for the 30/50 amp applications (4-3/4" depth)
- Reinforced hinge pin designed to exceed 40 lb hinge hang/stress test

# RATINGS

#### Cover

UV stabilized polycarbonate

UL Certified for Type 3R

Outdoor Enclosures:

Single Gang:

Horizontal – 3 cord outlets 0.5" wide by 0.9" high

Vertical – 1 cord outlet 0.75" wide by 0.9" high

Double Gang:

- 1 cord outlet 1.50" wide by 1.25" high 30/50 amp
- 1 cord outlet 1.1" wide by 3.0" high

### Mounting Base and Inserts:

UV stabilized polycarbonate

#### Gasket:

Neoprene – 1/8" (4.8 mm) thick with slits for mounting screws

#### Max Cord Size:

Single Gang – (2) 14 gauge or (1) 12 gauge

Double Gang – (2) 12 gauge or (1) 10 gauge

30/50 Amp Double Gang – (1) 6 gauge (3 wire ground)

Warranty: Limited 1 year

## **Extra-Duty Plastic Weatherproof Covers Ordering**





















Clear/Gray Single Gang

Gray Single Gang

Black Single Gang

White Single Gang

Green Single Gang

Clear/Gray Double Gang

Gray Double Gang

Black Double Gang

White Double Gang

Green Double Gang

						Standard Colors		Additional Colors		
Depth	Height	Width	Туре	Hinge	Flexi-Guard Inserts	Clear/Gray	Gray	Black	White	Green
2.25	6.5	4.75	Single Gang	Vertical/Horiz	WP17	WP5000C	WP5000G	WP5000BL	WP5000W	WP5000GN
2.75	6.5	4.75	Single Gang	Vertical/Horiz	WP17	WP5100C	WP5100G	WP5100BL	WP5100W	WP5100GN
3.625	6.5	4.75	Single Gang	Vertical/Horiz	WP17	WP5110C	WP5110G	WP5110BL	WP5110W	WP5110GN
2.25	6.5	6.5	Double Gang	Vertical	WP217	WP5220C	WP5220G	WP5220BL	WP5220W	WP5220GN
2.75	6.5	6.5	Double Gang	Vertical	WP217	WP5225C	WP5225G	WP5225BL	WP5225W	WP5225GN
3.625	6.5	6.5	Double Gang	Vertical	WP217	WP5240C	WP5240G	WP5240BL	WP5240W	WP5240GN
30/50 AMP*	6.5	6.5	Double Gang	Vertical	WP107, WP213	WP5500C	WP5500G	_	_	_

<sup>\* 30/50</sup> AMP = 4-3/4" depth























Beige Single Gang

Single Gang

Red

Yellow Single Gang Single Gang

Orange Single Gang

Beige Double Gang

Bronze Double Gang

Red Double Gang

Yellow Double Gang

Orange Double Gang

						Building Facade Colors			Safety Colors	
Depth	Height	Width	Туре	Hinge	Flexi-Guard Inserts	Beige	Bronze	Red	Yellow	Orange
2.25	6.5	4.75	Single Gang	Vertical/Horiz	WP17	WP5000B	WP5000BR	WP5000R	WP5000Y	WP50000R
2.75	6.5	4.75	Single Gang	Vertical/Horiz	WP17	WP5100B	WP5100BR	WP5100R	WP5100Y	WP51000R
3.625	6.5	4.75	Single Gang	Vertical/Horiz	WP17	WP5110B	WP5110BR	WP5110R	WP5110Y	WP51100R
2.25	6.5	6.5	Double Gang	Vertical	WP217	WP5220B	WP5220BR	WP5220R	WP5220Y	WP52200R
2.75	6.5	6.5	Double Gang	Vertical	WP217	WP5225B	WP5225BR	WP5225R	WP5225Y	WP52250R
3.625	6.5	6.5	Double Gang	Vertical	WP217	WP5240B	WP5240BR	WP5240R	WP5240Y	WP52400R
30/50 AMP*	6.5	6.5	Double Gang	Vertical	WP107, WP213	_	_	_	WP5500Y	_

<sup>\* 30/50</sup> AMP = 4-3/4" depth

#### Additional skus available:

- WP5103C WP5100C with round adapter plate
- WP5221C 2-1/4" depth double gang with WP101 (double gang duplex) and WP102 (double gang GFCI) inserts
- WP10HP 10/pack stainless steel hinge pins

# WP Extra-Duty Die-Cast Series

Die-Cast Aluminum Weatherproof Covers are easy to install and shipped with a gasket, mounting screws, base, cover assembly, and inserts for a variety of applications.



### **Die-Cast Aluminum Weatherproof Covers Ordering**

Part #	Туре	Depth	Height	Width	Flexi-Guard Inserts
WP3110MXD	Single Gang	2.75	6.37	3.87	WP17
WP1010MXD	Single Gang	3.125	6.37	3.87	WP17
WP1010HMXD	Single Gang*	3.125	4.37	5.75	WP17

<sup>\*</sup> Note: WP1010HMXD is horizontal

Part #	Туре	Depth	Height	Width	Flexi-Guard Inserts
WP1030MXD	Double Gang	3.125	6.37	5.75	WP217
WP1250MVXD	Single Gang	4.625	6.37	3.87	WP17
WP1250MXD	Double Gang	4.625	6.37	5.75	WP17

### **FEATURES**

- Complies with 2014 Article 406.9(B)(1) for wet locations and extra-duty applications
- Meets requirements for cold impact testing: -60° F (-51° C)
- Heavy-duty die-cast aluminum construction ensures long-lasting durability
- Lockable hasp: All models accept up to 0.25" dia shank
- Impact rated: 12 lb impact test to ensure cover remains intact
- Single Gang Models:
  - 3 inserts provided with all models that allow each model to meet multiple installations (up to 16 configurations)
- Double Gang Models:
  - 6 inserts provided with all models that allow each model to meet multiple installations (up to 70 configurations)
- Reinforced hinge pin designed to exceed 40 lb hinge hang/stress test

#### RATINGS

#### Cover:

Die-Cast Aluminum
UL Certified for Type 3R
Outdoor Enclosures

#### **Mounting Base:**

Die-Cast Aluminum

#### Gasket:

Neoprene – 1/8" (4.8 mm) thick with slits for mounting screws

#### Max Cord Size:

Single Gang – 12 gauge or higher cord sets Double Gang – 12 gauge or higher cord sets


Warranty: Limited 1 year

# Flexi-Guard Inserts


All Weatherproof Covers come with Flexi-Guard Inserts and mounting screws. Select an insert, rotate to fit, and snap into cover.


## WP17 Single Gang Flexi-Guard Inserts - 16 Configurations in One!

- Three separate inserts can be configured into 16 different receptacles or switches
- Converts to either toggle or round receptacles in 1.375, 1.625, 1.75, or 2.125"











## WP217 Double Gang Flexi-Guard Inserts – 70 Configurations in One!

- Six standard inserts combine to make 70 possible configurations
- Converts to either toggle or round receptacles in 1.375 or 1.625"





#### Plus, additional inserts available:

- WP101 Double Gang Duplex
- WP102 Double Gang GFCI
- WP107 Double Gang Round 1.375, 1.625, 1.75"
- WP213 Double Gang Round 2.156, 2.656"









WP102

WP107

WP213

# Stock up today!

Intermatic

7777 Winn Road Spring Grove, IL 60081 (815) 675-2321

©2014 Intermatic 300WP10082

NTERMATIC®

Intermatic.com