

MALLEABLE IRON THREADED CONDUIT BODIES

FOR THREADED RIGID CONDUIT AND IMC

APPLICATION

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

FEATURES

- Tapered threaded hubs (NPT)
- Flat back design for easy mounting close to walls
- Suitable for use in concrete

STANDARD MATERIALS


Malleable Iron

STANDARD FINISH

Zinc Plated



TYPE LL1




CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAX WIRE SIZE	VOL. CU.IN.	UNIT PACK	MASTER PACK	LBS. / 100 PCS.	UPC #
LL TYPE										
LL1	1/2"	4.688	2.063	1.375	N/A	4.50	10	50	76	41011
LL2	3/4"	5.375	2.250	1.688	3 #6 AWG	7.50	10	50	95	41021
LL3	1"	6.188	2.625	1.875	3 #4 AWG	12.50	5	25	138	41031
LL4	1-1/4"	8.125	2.750	2.750	3 #2 AWG	32.30	—	10	309	41041
LL5	1-1/2"	8.125	3.500	2.813	3 #1/0 AWG	35.30	—	10	332	41051
LL6	2"	10.500	4.125	3.313	3 #4/0 AWG	73.00	—	5	497	41061
LL7	2-1/2"	13.625	4.688	3.875	3 #300 MCM	138.00	—	1	1105	41071
LL8	3"	13.875	5.875	4.750	3 #350 MCM	170.00	—	1	1437	41081
LL9	3-1/2"	16.250	6.125	5.625	3 #350 MCM	300.00	—	1	2321	41091
LL10	4"	16.250	6.938	5.625	3 #350 MCM	328.00	—	1	2431	41101

OPTIONAL FINISH

For additional corrosion protection, specify Hot Dipped Galvanized. Add suffix 'G' to Malleable Iron catalog number. Example LL1G. For more information, see page 12.



TYPE LR1



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MAX WIRE SIZE	VOL. CU.IN.	UNIT PACK	MASTER PACK	LBS. / 100 PCS.	UPC #
LR TYPE										
LR1	1/2"	4.688	2.063	1.375	N/A	4.50	10	50	71	42011
LR2	3/4"	5.375	2.250	1.688	3 #6 AWG	7.50	10	50	100	42021
LR3	1"	6.188	2.625	1.875	3 #4 AWG	12.50	5	25	157	42031
LR4	1-1/4"	8.125	2.750	2.750	3 #2 AWG	32.30	—	10	332	42041
LR5	1-1/2"	8.125	2.813	2.813	3 #1/0 AWG	35.30	—	10	345	42051
LR6	2"	10.500	4.438	3.313	3 #4/0 AWG	73.00	—	5	626	42061
LR7	2-1/2"	13.625	5.375	3.875	3 #300 MCM	138.00	—	1	1105	42071
LR8	3"	13.875	5.875	4.750	3 #350 MCM	170.00	—	1	1437	42081
LR9	3-1/2"	16.250	6.875	5.625	3 #350 MCM	300.00	—	1	2321	42091
LR10	4"	16.625	7.188	5.625	3 #350 MCM	328.00	—	1	2500	42101