

BUILDING WIRE -600 Volt

THHN -THWN-2
90C -600 Volt



CONSTRUCTION	
Conductor	- Solid or stranded annealed copper
Insulation	- Extruded layer of heat, moisture, and flame resistant PVC with an extrusion of high heat and light stabilized nylon

Applications:

- May be installed in conduit, duct, or other recognized raceways in wet or dry locations
- Small diameter of the wire permits additional circuits or larger conductors without exceeding maximum fill limitations
- Tray cable rated and sunlight-resistant available upon request, sizes 1/0 AWG and larger

Features:

- Smooth outer jacket for easy pulling
- May be used as:
- Fluorescent Ballast
- Machine tool wire (MTW) -Stranded only, 90C dry, 60C wet
- 90C wet and dry
- 75C in oil or coolants
- RoHS compliant

Standards:

- UL 83 -THHN/THWN
- UL 1063 -Machine Tool Wire
- UL 758 -Appliance Wiring Material
- VW-1

Additional Information:

- All colors Can be striped
- Can be provided in twisted configurations

Part #	AWG	Stranding	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
M514SO-XX	14	Solid	.015"	.004"	.102"	16
M514ST-XX	14	19	.015"	.004"	.112"	16
M512SO-XX	12	Solid	.015"	.004"	.119"	24
M512ST-XX	12	19	.015"	.004"	.131"	24
M510SO-XX	10	Solid	.020"	.004"	.150"	37
M510ST-XX	10	19	.020"	.004"	.160"	37
M508ST-XX	8	19	.030"	.005"	.220"	64
M506ST-XX	6	19	.030"	.005"	.260"	96
M504ST-XX	4	19	.040"	.006"	.330"	155
M503ST-XX	3	19	.040"	.006"	.345"	190
M502ST-XX	2	19	.040"	.006"	.388"	235
M501ST-XX	1	19	.050"	.007"	.440"	300
M51/0ST-XX	1/0	19	.050"	.007"	.477"	370
M52/0ST-XX	2/0	19	.050"	.007"	.520"	465
M53/0ST-XX	3/0	19	.050"	.007"	.571"	570
M54/0ST-XX	4/0	19	.050"	.007"	.640"	720
M5250ST-XX	250	37	.060"	.008"	.711"	850
M5300ST-XX	300	37	.060"	.008"	.766"	1011
M5350ST-XX	350	37	.060"	.008"	.817"	1172
M5400ST-XX	400	37	.060"	.008"	.864"	1333

Part #	AWG	Stranding	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
M5500ST-XX	500	37	.060"	.008"	.949"	1653
M5600ST-XX	600	61	.070"	.009"	1.051"	1985
M5750ST-XX	750	61	.070"	.009"	1.126"	2462

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

Insert the color number in the -XX location:

- 01 = Black
- 02 = White
- 03 = Red
- 04 = Green
- 05 = Blue
- 06 = Gray
- 07 = Orange
- 08 = Yellow
- 09 = Purple
- 10 = Brown
- 11 = Pink
- 12 = Tan