


5262, 5362

Long-term durability for hard use applications.

Corrosion-resistant plated steel straps and high-strength nylon faces make these receptacles perfect for any hard use application. They feature one-piece, triple-wipe brass contacts for lasting retention. And screw-pressure-plate back wiring makes installation fast and easy.



Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.


Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

Corrosion-resistant plated steel strap.

Auto-ground clip assures positive ground.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Tri-drive brass terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for more wiring flexibility.



5362-LA

Field Uses/Vertical Markets

■ Health Care

■ Education

■ Institutional



Pass & Seymour

Straight Blade Receptacles Hard Use

15 & 20A, 125V

Ordering Information

Catalog Number	Rating A. V.	Color	NEMA Config. No.
Duplex Receptacles Back & Side Wire			
5262-I	15 125	Ivory	5-15R
5262-W	15 125	White	5-15R
5262	15 125	Brown	5-15R
5262-GRY	15 125	Gray	5-15R
5262-BK	15 125	Black	5-15R
5262-RED	15 125	Red	5-15R
5262-LA	15 125	Light Almond	5-15R
5262-BL	15 125	Blue	5-15R
5362-I	20 125	Ivory	5-20R
5362-W	20 125	White	5-20R
5362	20 125	Brown	5-20R
5362-GRY	20 125	Gray	5-20R
5362-BK	20 125	Black	5-20R
5362-RED	20 125	Red	5-20R
5362-LA	20 125	Light Almond	5-20R
5362-BL	20 125	Blue	5-20R



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Product Guide or visit our web site.

SF310R1 — Updated November 2005 — For latest specs visit www.legrand.us/passandseymour

Straight Blade Receptacles Hard Use 15 & 20A, 125V




Pass & Seymour

Technical Specifications

3rd Party Compliance
UL Listed, File Number E140596, Standard UL498. Federal Specification WC596. CSA Certified File Number LR16063, Standard CSA-C22.2 No. 42 General Use Receptacles. Conforms to NEMA WD-1 and WD-6.

Performance	
Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



**Dimensions for
15 & 20 Amp**

Materials			
Face	Nylon	Terminal Screws	#8 Tri-Drive Brass
Back Body	PVC		(Neutral = Nickel-Plated Steel)
Line Contacts	.032 688 Brass	Ground Screw	#8 Hex Tri-Drive Brass
Mounting Strap	.042" Plated Steel	Assembly Drive Screw	Zinc-Plated Steel
Ground Contacts	.040 688 Brass	Auto-Ground Clip	Stainless Steel
Pressure Plate	.080 Steel	Mounting Screws	Tri-Drive Steel

Warranty


1 Year

Complementary Devices & Accessories




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




PLUGTAIL™ DEVICES

- Spec Grade
- Decorator
- Hospital Grade
- Tamper-Resistant
- Isolated Ground




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



GFCIs

- Specification Grade
- Hospital Grade
- Dead Front



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
 P.O. Box 4822
 Syracuse, NY 13221-4822
 800-223-4185

North America Headquarters
 60 Woodlawn Street
 West Hartford, CT 06110
 Phone: 1.877.BY.LEGRAND (295.3472)
 Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
 570 Applewood Crescent
 Vaughan, ON, L4K 4B4
 Phone: 905.738.9195
 Fax: 905.738.9721
www.legrand.ca