


DECORA PLUS™ HEAVY-DUTY SPEC GRADE RECEPTACLES

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA		 5-15R	 5-20R	 6-15R	 6-20R
Rating		15A-125V	20A-125V	15A-250V	20A-250V
Duplex	White	16262-W	16362-W	16662-W	16462-W
	Ivory	16262-I	16362-I	16662-I	16462-I
	Light Almond	16262-T	16362-T	—	—
	Gray	16262-GY	16362-GY	—	—
	Black	16262-E	16362-E	—	—
	Brown	16262	16362	—	—
Duplex, with 6" wire leads	White	16252-LW	16352-LW	—	—
	Ivory	16252-LI	16352-LI	—	—
	Almond	16252-LA	16352-LA	—	—
	Gray	16252-LGY	16352-LGY	—	—
	Black	16252-LE	16352LE	—	—
	Brown	16252-L	16352-L	—	—



16262-W

TESTING AND CODE COMPLIANCE

Meets all NEMA WD 6, UL 498 and ANSI C-73 requirements

- UL Listed (File #E-13399)
- CSA Certified (File #152105)
- NOM Certified (#057)

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated V2

Operating Temperature: -40°C to 60°C

MECHANICAL

Terminal I.D.: Brass-Hot, White-Neutral, Green-Grounding

Terminal Accom.: #14-#10 AWG

Product I.D.: Ratings are permanently stamped on device

ELECTRICAL

Dielectric Voltage: Withstands 2000V for UL 498

Current Interr.: Full rated current

Temp. Rise: Max 30°C after 250 cycles at 200% of rated current

HORSEPOWER

15A - 125V — 1½

15A - 250V — 1½

20A - 125V — 1


20A - 250V — 2

Industrial Grade


Spec Grade Receptacles, Back and Side Wired/Wire Lead

Specifications and Features

- Impact-resistant thermoplastic nylon cover and body
- Smooth face does not collect dirt
- Four corner latches securely fasten face
- Single-piece brass mounting strap on Extra Heavy-Duty devices, multi-piece steel strap on Heavy-Duty devices
- Large, triple-wipe, brass "T" contacts for superior contact and conductivity
- Back and side-wiring options
- Brass terminal screws to reduce conductor oxidation
- Break-off tabs for easy two-circuit conversion
- Apron barrier to prevent accidental contact between terminal screw heads and metal box
- Exclusive V-shaped, serrated back-wiring clamps for superior contact and conductivity
- Wire lead receptacles for fast and easy installation
- Backed by a Limited 10-Year Warranty



5262-W




5362-SW


Back and Side Wired, Self-Grounding, Fed Spec

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Extra Heavy-Duty Duplex, Brass Strap with Integral Ground Contacts	White	5262-W	—	5362-W	—
	Ivory	5262-I	5662-I	5362-I	5462-I
	Gray	5262-GY	—	5632-GY	5462-GY
	Black	5262-E	—	5362-E	—
	Brown	5262	5662	5362	5462
	Red	5262-R	—	5362-R	—
Heavy-Duty Single	White	5261-W	—	5361-W	5461-W
	Ivory	5261-I	5661-I	5361-I	5461-I
	Light Almond	—	—	5361-T	5461-T
	Gray	5261-GY	—	5361-GY	5461-GY
	Black	—	—	5361-E	—
	Brown	5261	5661	5361	5461
	Red	5261-R	—	5361-R	5461-R
	Blue	5261-BU	—	5361-BU	—
Heavy-Duty Duplex	White	5252-W	—	5352-W	—
	Ivory	5252-I	—	5352-I	—
	Light Almond	5252-T	—	5352-T	—
	Gray	5252-GY	—	5352-GY	—
	Black	5252-E	—	5352-E	—
	Brown	5252	—	5352	—
	Red	5252-R	—	5352-R	—
	Blue	5252-BU	—	5352-BU	—
	Stainless Steel	5261-CH	—	5361-CH	—
Single, Clock Hanger	Stainless Steel	5261-CH	—	5361-CH	—

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Heavy-Duty Spec Grade Duplex	White	5262-SW	—	5362-SW	—
	Ivory	5262-SI	—	5362-SI	—
	Almond	5262-SA	—	5362-SA	—
	Light Almond	5262-ST	—	5362-ST	—
	Grey	5262-SGY	—	5362-SGY	—
	Black	5262-SE	—	5362-SE	—
	Brown	5262-S	—	5362-S	—
	Red	5262-SR	—	5362-SR	—
	Blue	5262-SBU	—	5362-SBU	—
Heavy-Duty Spec Grade, Duplex, with 6" wire leads	White	5262-LW	—	5362-LW	—
	Ivory	5262-LI	—	5362-LI	—
	Light Almond	—	—	5362-LT	—
	Grey	5262-LGY	—	5362-LGY	—
	Black	5262-LE	—	5362-LE	—
	Brown	5262-L	—	5362-L	—
	Red	5262-LR	—	5362-LR	—
Heavy-Duty Spec Grade Duplex, with 6" wire leads, no ground led and self grounding clip	White	5262-CW	—	5362-CW	—
	Ivory	5262-CI	—	5362-CI	—
	Grey	5262-CG	—	5362-CG	—



5362-IG



5242-W

Back and Side Wired, Isolated Ground, Fed Spec

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Heavy-Duty Spec Grade, Duplex	White	5262-IGW	—	5362-IGW	—
	Ivory	5262-IGI	—	5362-IGI	—
	Light Almond	5262-IGT	—	5362-IGT	—
	Gray	5262-IGG	—	5362-IGG	—
	Brown	5262-IGB	—	5362-IGB	—
	Red	5262-IGR	—	5362-IGR	—
	Blue	—	—	5362-BIG	—
	Orange	5262-IG	5662-IG	5362-IG	5462-IG
Single	Orange	5261-IG	—	5361-IG	—

Decora Plus™ Receptacles


Specifications and Features

- Back Wire and Side Wire terminal options
- Heavy-gauge zinc-plated steel locked-in wraparound strap
- Back wire terminals accept up to No. 10 copper or copper-clad wire, solid or stranded
- Brass staked on self-grounding clip
- Heavy-duty triple-wipe brass contacts for long service life
- Impact-resistant thermoplastic construction


DECORA PLUS

Heavy-Duty Back and Side Wired, Self-Grounding

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Duplex, Tamper Resistant	White	TDR15-W		TDR20-W	
	Ivory	TDR15-I		TDR20-I	
	Light Almond	TDR15-T		TDR20-T	
	Grey	TDR15-GY		TDR20-GY	
	Black	TDR15-E		TDR20-E	
	Brown	TDR15		TDR20	
Duplex	White	16252-W	16662-W	16352-W	16462-W
	Ivory	16252-I	16662-I	16352-I	16462-I
	Light Almond	16252-T	—	16352-T	—
	Grey	16252-GY	—	16352-GY	—
	Black	16252-E	—	16352-E	—
	Brown	16252	—	16352	—
Single	White	16251-W	16651-W	16351-W	16451-W
	Ivory	16251-I	16651-I	16351-I	16451-I
	Brown	16251	—	16351	—
NEMA					
		5-15R	6-15R		
Rating		15A-125V/15A-250V			
Duplex,	White	16292-W			
Dual Voltage	Ivory	16292-I			



Commercial Grade



DECORA PLUS™ SPEC GRADE RECEPTACLES

Side Wired, Self-Grounding

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Duplex, Tamper Resistant	White	DR15S-W	—	—	—
	Ivory	DR15S-I	—	—	—
	Light Almond	DR15S-T	—	—	—
	Grey	DR15S-GY	—	—	—
	Black	DR15S-E	—	—	—
	Brown	DR15S	—	—	—
Duplex	White	16242-W	—	16342-W	—
	Ivory	16242-I	—	16342-I	—
	Grey	—	—	16342-GY	—
	Black	16242-E	—	16342-E	—
	Brown	16242	—	16342	—
Single	White	16241-W	16641-W	16341-W	16441-W
	Ivory	16241-I	16641-I	16341-I	16441-I
	Light Almond	—	—	16341-T	16441-R
	Grey	—	—	16341-GY	—
	Black	—	—	16341-E	—
	Brown	—	—	16341	—

† Self-grounding when installed in a properly grounded metal wallbox.

TESTING AND CODE COMPLIANCE

Meets all NEMA WD 6, UL 498 and ANSI C-73 requirements

- UL Listed (File #E-13399)
- CSA Certified (File #152105)
- NOM Certified (#057)

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated V2
Operating Temperature: -40°C to 60°C

MECHANICAL

Terminal I.D.: Brass-Hot, White-Neutral, Green-Grounding
Terminal Accom.: #14-#10 AWG
Product I.D.: Ratings are permanently stamped on device

ELECTRICAL

Dielectric Voltage: Withstands 2000V for UL 498

Current Interr.: Full rated current

Temp. Rise: Max 30°C at full rated current after 250 cycles overload at 200% of rated current

HORSEPOWER

15A - 125V — 1½
15A - 250V — 1½
20A - 125V — 1
20A - 250V — 2


Commercial Spec Grade Receptacles

Specifications and Features

- Large-head, triple-drive terminal screws, backed out and staked, accept No. 10 copper or copper clad wire
- Back-wiring clamps accept up to No. 10 copper or copper-clad wire
- Heavy-Duty brass power contacts for maximum conductivity and plug retention
- Heavy-gauge, rust-resistant steel mounting strap
- Shallow design for maximum wiring room in box
- Convenient washer-type break-off plaster ears for best flush alignment
- Captive mounting screws for fast installation
- Break-off tabs on duplex receptacles for easy two circuit conversion
- Backed by a Limited Ten-Year Warranty

Back and Side Wired, Self-Grounding

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Duplex, Tamper Resistant	White	TBR15-W	—	TBR20-W	—
	Ivory	TBR15-I	—	TBR20-I	—
	Light Almond	TBR15-T	—	TBR20-T	—
	Grey	TBR15-GY	—	TBR20-GY	—
	Black	TBR15-E	—	TBR20-E	—
	Brown	TBR15	—	TBR20	—
Duplex	White	BR15-W	—	BR20-W	—
	Ivory	BR15-I	—	BR20-I	5824-I
	Light Almond	BR15-T	—	BR20-T	—
	Grey	BR15-GY	—	BR20-GY	—
	Black	BR15-E	—	BR20-E	—
	Brown	BR15	—	BR20	5824
Duplex, Weather Resistant	White	WBR15-W	—	WBR20-W	—
	Yellow	—	—	WBR20-Y	—
Single	White	—	—	5891-W	—
	Ivory	5088-I	5089-I	—	5823-I
	Brown	5088	—	5891	5823



BR15-W

Dual Voltage, Back and Side Wired, Self-Grounding

Description	Color	Cat. No.
NEMA		 
		5-20R 6-20R
Rating		20A-125V/20A-250V
Duplex	Ivory	5844-I
	Brown	5844

Commercial Spec Grade

Specifications and Features

- Large-head terminal screws, backed out and staked, accept No. 10 copper or copper-clad wire
- Heavy-Duty brass power contacts for maximum conductivity and plug retention
- Heavy-gauge, rust-resistant steel mounting strap
- Shallow design for maximum wiring room in box
- Convenient washer-type break-off plaster ears for best flush alignment
- Captive mounting screws for fast installation where applicable


Side Wired, Self-Grounding

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Duplex, Tamper Resistant	White	CR15S-GW	—	—	—
	Ivory	CR15S-GI	—	—	—
	Light Almond	CR15S-GT	—	—	—
	Grey	CR15S-GG	—	—	—
	Brown	CR15S-G	—	—	—
Duplex, Tamper and Weather Resistant	White	TWR15-W	—	TWR20-W	—
	Gray	TWR15-GY	—	TWR20-GY	—
Duplex	White	CR15-W	—	CR20-W	5822-W
	Ivory	CR15-I	5028-I	CR20-I	5822-I
	Light Almond	CR15-T	—	CR20-T	—
	Grey	CR15-GY	—	CR20-GY	—
	Black	CR15-E	—	CR20-E	—
	Brown	CR15	5028	CR20	5822
Duplex, Smooth Face	White	CR015-W	—	CR020-W	—
	Ivory	CR015-I	—	CR020-I	—
	Grey	CR015-GY	—	CR020-GY	—
	Black	CR015-E	—	CR020-E	—
	Brown	CR015	—	CR020	—
Duplex, on 4" Cover*	Zinc Plated	5042	—	—	—
Duplex, with Pigtail Leads*	White	5040-W	—	5340-W	—
	Ivory	5040-I	—	5340-I	—
	Grey	—	—	5340-GY	—
	Brown	—	—	5340	—
Duplex, with 6" wire leads, no ground lead and self-grounding clip	White	5040-CW	—	5340-CW	—
	Ivory	5040-CI	—	5340-CI	—
	Grey	5040-CG	—	5340-CG	—


CSA certified except where indicated by *

Cross Reference to Power Devices Section for Side Wired, Non-Grounding Single (Double Swipe) Receptacle 5032 with matching plug 9151-N.

Continued On Next Page >



CR15-W



CR20-GY

Commercial Grade

Continued From Previous Page >

Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
NEMA					
		5-15R	6-15R	5-20R	6-20R
Rating		15A-125V	15A-250V	20A-125V	20A-250V
Single, Tamper Resistant	White	T5015-W	—	T5020-W	—
	Ivory	T5015-I	—	T5020-I	—
	Light Almond	T5015-T	—	T5020-T	—
	Grey	T5015-GY	—	T5020-GY	—
	Black	T5015-E	—	T5020-E	—
	Brown	T5015	—	T5020	—
Single	White	5015-W	5029-W	5801-W	5821-W
	Ivory	5015-I	5029-I	5801-I	5821-I
	Light Almond	5015-T	—	5801-T	5821-T
	Brown	5015	5029	5801	5821
Single, on 4" Cover	Zinc Plated	5059	—	—	—
Single, short strap, 8-32 tapped mounting holes on 1 ³ / ₄ " Centers	Black	5258-SS	5658-SS	5558-SS	5458-SS

CSA certified except where indicated by *.

Cross Reference to Power Devices Section for Side Wired, Non-Grounding Single (Double Swipe) Receptacle 5032 with matching plug 9151-N.

TESTING AND CODE COMPLIANCE

Meets all NEMA WD 6, UL 498 and ANSI C-73 requirements

- UL Listed (File #E-13399)
- CSA Certified (File #152105)
- NOM Certified (#057)

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated V2

Operating Temperature: -40°C to 60°C

MECHANICAL

Terminal I.D.: Brass-Hot, White-Neutral, Green-Grounding

Terminal Accom.: #14-#10 AWG

Product I.D.: Ratings are permanently stamped on device

ELECTRICAL

Dielectric Voltage: Withstands 2000V for UL 498

Current Interr.: Full rated current

Temp. Rise: Max 30°C at full rated current after 100 cycles overload at 150% of rated current for both AC and DC as per UL 498

HORSEPOWER

15A - 125V — 1¹/₂,

15A - 250V — 1¹/₂,


20A - 125V — 1

20A - 250V — 2


DECORA QUICKWIRE AND SIDE WIRED RECEPTACLES

Description	Color	Cat. No.	Cat. No.
NEMA			
		5-15R	5-20R
Rating		15A-125V	20A-125V
Duplex, Tamper Resistant	White	T5325-W	
	Ivory	T5325-I	
	Almond	T5325-A	
	Light Almond	T5325-T	
	Grey	T5325-GY	
	Black	T5325-E	
	Brown	T5325	
Duplex, Tamper Resistant, self-grounding*	White	T5325-SW	
	Ivory	T5325-SI	
	Light Almond	T5325-ST	
Duplex	White	5325-W	
	Ivory	5325-I	
	Almond	5325-A	
	Light Almond	5325-T	
	Grey	5325-GY	
	Black	5325-E	
	Brown	5325	
Duplex, self-grounding*	White	5325-SW	
	Ivory	5325-SI	
	Light Almond	5325-ST	
Duplex, 8-hole Quickwire	White	5328-W	
	Ivory	5328-I	
	Almond	5328-A	
Duplex Tamper Resistant, Self-grounding*, No Quickwire	White		T5825-W
	Ivory		T5825-I
	Light Almond		T5825-T
	Grey		T5825-GY
	Black		T5825-E
	Brown		T5825

*Self-grounding when installed in a properly grounded metal wallbox.



T5325-W



5325-SW



5328-W

TESTING AND CODE COMPLIANCE

- UL Listed (File# E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (File #057)


MATERIAL CHARACTERISTICS

Environmental: Flammability, UL-94, Rated V2
Operating Temperature: -40°C to 60°C


QUICKWIRE PUSH-IN AND SIDE WIRED RECEPTACLES

Description NEMA	Color	Cat. No.	Cat. No.
		 5-15R	 5-20R
Rating		15A-125V	20-125V
Duplex, Tamper-Resistant	White	T5320-W	
	Ivory	T5320-I	
	Almond	T5320-A	
	Light Almond	T5320-T	
	Black	T5320-E	
	Brown	T5320	
Duplex, Tamper Resistant, self-grounding*	White	T5320-SW	
	Ivory	T5320-SI	
	Light Almond	T5320-ST	
Duplex, Tamper Resistant and Weather Resistant	White	W5320-TW	
	Gray	W5320-TG	
Duplex	White	5320-W	
	Ivory	5320-I	
	Almond	5320-A	
	Light Almond	5320-T	
	Black	5320-E	
	Brown	5320	
Duplex, self-grounding*	White	5320-SW	
	Ivory	5320-SI	
	Almond	5320-SA	
	Light Almond	5320-ST	
	Brown	5320-S	
Duplex, 8-hole Quickwire with ground screw	White	5248-W	
	Ivory	5248-I	
	Brown	5248	
Duplex Tamper Resistant, Self-grounding*, No Quickwire	White		T5820-W
	Ivory		T5820-I
	Light Almond		T5820-T
	Grey		T5820-GY
	Black		T5820-E


*Self-grounding when installed in a properly grounded metal wallbox.
CSA Certified except where indicated by†.
NOTE: Please consult factory for duplex receptacles, less plaster ears.



T5320-WR



W5320-WR



5248-W