

September 2007

Enclosures

Type 1 Enclosures

Table 12-82. Type 1 Enclosures — NEMA, IEC (Freedom and /T. Type)

Starter Type	Box Number	NEMA Size AN16	Catalog Number
Non-reversing Starter	1	00 – 1	C799B11 ①
	1	—	C799B12 ①
	2	2	C799B13
	4	3 – 4	C799B15
	10	5	C799B17
Non-reversing Starter with Space for CPT	3	00 – 2	C799B14 ②
	4	3 – 4	C799B15 ③
Reversing Starter	2	00 – 0	C799B13
	3	1 – 2	C799B14
	4	3	C799B15
	9	4	C799B16
	10	5	C799B17



Type 1

① In order to install cover control kits for NEMA Sizes 00 – 2 the starter must be provided with a **side mounted** auxiliary contact or a separately ordered Dummy Contact Block **C320KGSD**, to serve as a mounting base. **Note:** NEMA Size 00 open type devices **are not** supplied as standard with side mounted auxiliaries.

② Sub panel drilled for 50 – 200 VA CPTs.

③ Enclosure drilled for 150 – 300 VA CPTs.

Box 1 will **not** accept devices with top mounted auxiliaries. Box 2 will accept NEMA Sizes 00 and 0 starters with top mounted auxiliaries.

Type 3R, 4X and 12 Enclosures

Table 12-83. Type 3R, 4X and 12 Enclosures — NEMA, IEC (Freedom and /T. Type)

Starter Type	Box Number	NEMA Size AN16	Type 3R	Type 12	Type 4X
			Catalog Number	Catalog Number	Catalog Number
Non-reversing Starter	5	00 – 1	C799B21	C799B81	C799B41
	6	2	C799B24	C799B84	C799B43
	6	—	C799B25	C799B85	C799B44
	8	3	C799B210	C799B810	C799B47
	8	—	C799B212	C799B812	C799B49
	8	4	C799B211	C799B811	C799B48
Non-reversing Starter with Space for CPT	10	5	C799B218	C799B818	C799B413
	6	00 – 2	C799B24	C799B84	C799B43
	6	—	C799B25	C799B85	C799B44
	8	3	C799B210	C799B810	C799B47
	8	—	C799B212	C799B812	C799B49
Reversing Starter	8	4	C799B211	C799B811	C799B48
	10	5	C799B218	C799B818	C799B413
	6	00 – 2	C799B24	C799B84	C799B43
	6	—	C799B25	C799B85	C799B44
	8	3	C799B210	C799B810	C799B47
Multispeed	8	—	C799B212	C799B812	C799B49
	9	4	C799B215	C799B815	C799B411
	10	5	C799B218	C799B818	C799B413
Multispeed	7 ①	0 – 2	C799B223	C799B823	C799B417



Type 3R

① Blank cover provided.

Note: Combination enclosures not available for sale as enclosures only.