

WIREMOLD® Surface Style Poke-Thru Devices

Bring Power & Communication Services Directly to the Workstation



Protection from water, dirt, and debris.

Flush Style Poke-Thru Devices are an excellent solution for bringing power, communication, and audio/video services to the workstation in an open space, above-grade floor environment. All Wiremold Flush Style Poke-Thru Devices come with built-in TopGuard™ protection, an industry-leading design that meets and exceeds UL scrub water exclusion requirements for tile and carpet floors. Topguard protection prevents water, dirt, or debris from entering not just the power devices, but also the communication devices.

All Wiremold Flush Style Poke-Thru Devices can be installed on tile, carpet, or wood covered floors. Each of these devices provides an excellent solution for both new or retrofit construction, with typical applications that include office buildings, airports, malls, shopping centers, libraries, and schools.







AV3 Series



RC4 Series



AMD8 Series

FEATURES & BENEFITS

- AV3 Series is specifically designed to meet the growing needs of the audio and video market. AV3 Series accepts Extron[®] MAAP Series mini architectural adapter plates. The MAAP line includes passive A/V connector plates that support a wide variety of video, audio, control, voice and data connectors, as well as active modules such as VGA line drivers, audio buffers and twisted pair transmitters. (Extron devices sold separately only through authorized Extron dealers.)
- AMD8 Series is designed to meet the growing need for more communication capacity at the workstation. AMD8 Series is a large capacity all communication poke-thru device, providing up to 8-ports for communication devices. AMD8 is a flush style device with individual slide covers to prevent water, dirt and debris from entering the communication devices.
- TopGuard Protection. Integral design component that prevents water, dirt and debris from entering power and communication compartments. Whenever you see the TopGuard protection icon on any Wiremold product, you'll know it meets and exceeds UL scrub water exclusion requirements for tile and carpet floors.
- UL Listed and UL Fire Classified to U.S. and Canadian safety standards for tile and terrazzo. Includes the new UL requirements under UL514A and UL 514C for the scrub water exclusion test for carpet and wood covered floors.
- Multiple service capability. RC7, AV3, and RC4 Series provide power and communication services. The AV3 and RC4 Series provide for use of flush or recessed fiber optic devices. Eliminates the cost of a second poke-thru to accommodate additional services.

- Provides flexibility with a single poke-thru unit. 20A duplex receptacle in the AV3, and the RC7 Series can be wired as standard or isolated ground receptacle. Two 20A duplex power receptacles in the RC4 Series are wired with a 6-wire system with individual neutral and ground wires, and can be wired for standard or isolated ground. RC9 quad 15A receptacle can also be wired as standard or isolated ground receptacle.
- Individual slide covers. Protects power and communication devices. Power slide covers snap back into place when receptacle is not in use. Activate either power or communication services, simultaneously or individually. RC9AMD and AMD8 Series Poke-Thru Devices are the only all communication pokethru devices available with slide cover protection.
- Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point-of-use.
- "Step-on-it" installation. Quick and easy installation without the need for additional fasteners or a second installer.
- Suitable for use in air handling plenums. In accordance with Sec 300-22(C) of the National Electrical Code.
- Meets ADA Accessibility Guidelines. Wide trim flange on the product is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.
- Fire rated for up to 2-hour rated floors. Maintains the fire classification of the floor.

Flush Poke-Thru Device Specifications

3" Diameter Hole									
POKE-THRU SERIES	F	RC7 Seri	ies		RC9 Seri	es	RC9	AMD Se	ries
HOLE SIZE	Minimum: Maximum:	3 1/16" 3 1/8"	(78mm) (79mm)	Minimum: Maximum:	3 1/16" 3 1/8"	(78mm) (79mm)	Minimum: Maximum:	3 1/16" 3 1/8"	(78mm) (79mm)
UL FIRE CLASSIFICATION	1-, 1	1/2- & 2-	-hrs	1-, 1	1/2- & 2-	-hrs	1-, 1	1/2- & 2	-hrs
UL SCRUBWATER PROTECTION	To	opGuard ⁻	м	Т	opGuard"	м	To	opGuard ¹	м
CAPACITY	Recept	s (1) 20A [acle, (2) Po inication D	orts of	Receptac	gs (1) 15A (le, (2) Oper cation Pass	nings for		ngs (4) Por unication D	
POWER*	, ·) #12 AWG q. in. (9.91 :) #12 AWG q. in. (9.91 s			N/A	
POWER* COMMUNICATIONS*		at 6A/Chai . in. (2.58 so			at 6A/Char . in. (2.58 so			at 6A/Cha i . in. (10.324	
POWER	3/4	" Trade Siz	ze	3/4	" Trade Siz	ze		N/A	
POWER COMMUNICATIONS		ade Size/Cl annels per			ade Size/Ch annels per		2"	Trade Size	е
COVER SIZE	7	" (178mm)		7	" (178mm)		7	" (178mm)	
COVER COLORS	,	Brass, Alun Bray, Ivory	ninum,	,	Brass, Alum Gray, Ivory	ninum,		Brass, Alun Gray, Ivory	ninum,
APPROVED CONCRETE FLOOR COVERINGS	Carpe	et, Tile & W	ood/	Carpo	et, Tile & W	ood	Carpe	et, Tile & W	lood
FLOOR COVERING THICKNESS	Minimum: Maximum:	1/8" 3/4"	(3.2mm) (19.1mm)	Minimum: Maximum:	1/8" 3/4"	(3.2mm) (19.1mm)	Minimum: Maximum:	1/8" 3/4"	(3.2mm) (19.1mm)

4" Diameter Hole												
POKE-THRU SERIES	AV3	Serie:	S	Α	MD8 S	eries	RC	4 Serie	s	RC	3 Serie	es
HOLE SIZE	Minimum: Maximum: 4	,	102mm) 105mm)	Minimum: Maximum:	4" 4 1/8"	(102mm) (105mm)	Minimum: Maximum:	4" 4 1/8"	(102mm) (105mm)	Minimum: Maximum:	4" 4 1/8"	(102mm) (105mm)
UL FIRE CLASSIFICATION	1-, 1 1/2	2- & 2-h	ırs	1-, 1	1/2- & 2	-hrs	1-, 1	1/2- & 2	-hrs	1-, 1	1/2- & 2	?-hrs
UL SCRUBWATER PROTECTION	TopG	auard™		To	pGuard'	м	To	pGuard'	гм	То	pGuard	тм
CAPACITY	2 Gangs (1) Receptacle, (3 Extron MAAP Ports of Cor	3) Single Devices	Width or (4)	1 Gang All (8) Ports fo			Receptacle	s (2) 20A I es, and (4) nication D) ports of	Receptacle	s (1) 20A e, and (4) nication o	Ports for
POWER*	(3) #1: .01536 Sq. in.	2 AWG . (9.91 sq	. mm)		N/A		(6) .03072 Sq.	# 12 AW (in. (19.82		(3) .01536 Sq	# 12 AW (. in. (9.91	
COMMUNICATIONS*	(6) Cat 6/ .01938 Sq. in.			(10) Ca .03474 Sq.	at 6A/Cha in. (22.412			at 6/Char in. (5.16 s			at 6/Chai in. (5.16 s	
POWER COMMUNICATIONS	3/4" Tra	ade Size		3/4'	Trade Si	ze	3/4'	Trade Si	ze	3/4"	Trade S	ize
COMMUNICATIONS	1 1/4" Trade	Size/Ch	annel	1 1/4" Tra	ade Size/(Channel	3/4" Trade Oval SI	e Size (Eq naped Op		3/4" Trade Oval Sh	e Size (Ed naped Op	
COVER SIZE	8 1/4" ((210mm)		8 1/	4" (210mı	m)	8 1/	'4" (210mı	m)	7 1/	2" (191m	m)
COVER COLORS	Black, Bras Gray	s, Alumir , Ivory	num,	,	rass, Alur ray, Ivory	,	,	rass, Alur ray, Ivory	,	,	rass, Aluı ray, İvory	,
APPROVED CONCRETE FLOOR COVERINGS	Carpet, T	ile & Wo	od	Carpe	t, Tile & W	/ood	Carpe	t, Tile & W	lood	Carpe	t, Tile & V	Vood
FLOOR COVERING THICKNESS	Minimum: Maximum:	1/8" 3/4"	(3.2mm) (19.1mm)	Minimum: Maximum:	1/8" 3/4"	(3.2mm) (19.1mm)	Minimum: Maximum:	1/8" 3/4"	(3.2mm) (19.1mm)	Minimum: Maximum:	1/8" 3/4"	(3.2mm) (19.1mm)

^{*} The above maximum copper fill values are the maximum amount of copper to maintain fire classification and are for each individual power and communication compartments. Do not add values together for any one compartment.

Flush Poke-Thru Device Specifications

Copper Cross Section:

The copper cross-sectional area determines the amount of wire fill capacity in a poke-thru device. Unlike other wire and cable management systems that utilize wire fill capacity, a poke-thru device is UL tested under fire conditions to determine the maximum amount of copper conductors that will pass through a poke-thru device, while maintaining the fire-rating of the floor assembly. All Walker Flush Style Devices are UL Classified to U.S. and Canadian safety standards.

Copper Cross Sectional Area of Commonly Used Conductors						
Size	Sol	Solid				
#24	.00032 sq. in.	(.206mm²)				
#23	.00040 sq. in.	(.258mm²)				
#22	.00050 sq. in.	(.322mm²)				
#14	.00323 sq. in.	(2.083mm²)				
#12	.00512 sq. in.	(3.303mm ²)				
#10	.00815 sq. in.	(5.258mm²)				
# 8	.01296 sq. in.	(8.361mm²)				


NOTE: Use above values for solid or stranded conductors.

Concrete Thickness Min/Max:

- 1-HOUR RATED FLOOR 2 1/4" (57mm) min over top of deck (or 3" (76mm) thick reinforced concrete slab) to a maximum of 7 1/2" (191mm).
- 2-HOUR RATED FLOOR 3 1/4" (83mm) min over top of deck (or 4" (102mm) thick reinforced concrete slab) to a maximum of 7 1/2" (191mm).

Floor Coverings:

The poke-thru device is fire rated for carpet and wood covered concrete floors, and tile floor coverings 1/8" to 3/4" (3.2mm to 19.1mm) thickness. For floor coverings not listed above, consult factory.



CAUTION: These devices are suitable for 1, 1 1/2, and 2 hour rated floor assemblies as described in the UL Fire Resistance directory for each service.

These devices meet all UL scrub water requirements, but are not suitable for wet or damp locations, or other areas subject to saturation with water or other liquids such as commercial kitchens.



Download this product's PEP ecopasport® environmental product declaration at www.legrand.us/resources-and-downloads. This declaration conforms with ISO 14025 and 14040 and is in alignment with EN 15804.

Poke-Thru Devices and abandonment fitting are for use with 1-, 1 1/2-, or 2-hour rated unprotecteed reinforced concrete floor and 1-, 1 1/2- or 2-hour rated floors employing unprotected steel floor units and concrete topping (D900-Series Designs), or concrete floors with suspended ceilings. (Fire resistive designs with suspended ceilings should have provisions for accessibility in the ceiling area below the Poke-Thru Fittings). The assembled Poke-Thru stem and service fitting or the abandonment fittings will not reduce the ratings of the

The assembled Poke-Thru stem and service fitting or the abandonment fittings will not reduce the ratings of the floor assembly when the thickness and type of concrete (required for the specific rating) are within the specified limits and the fittings are installed as specified:


- **1. Spacing** Minimum of 2' (610mm) OC and not more than one unit per 65 square feet (6 square meters) of floor area in each span.
- 2. Concrete Minimum thickness of structural concrete topping of 2 1/4" (57mm) over metal deck or a minimum 3" thick reinforced concrete slab. Unit weight of concrete to be 110 to 155 pcf.
- 3. Installation Mounted in a 4" (102mm) diameter core drilled hole in concrete per installation instructions accompanying the fittings or abandonment fittings. For use with power circuits, data and/or telephone cables as tabulated below.

NOTE: The material that is used in Wiremold® Poke-Thru devices is not listed under the directory for Fire Stopping Material because the poke-thru device is UL Classified as "Outlet Boxes and Fittings Classified For Fire Resistance (CEYY)". The pass/fail criteria comes from UL263. The pass criteria is that the poke-thru unit cannot exceed 325° F. above ambient before the concrete slab (or deck) reaches this same temperature. Some poke-thru devices are tested for 2 hours while others are tested for 4 hours. The intumescent material has never been tested as a fire-stopping material as a stand-alone device. This material is designed to work as a unit with the entire poke-thru device.

RC7 Series Ordering Information

Catalog No./Item


Description/Specifications



Insert Assembly with Disposable Plate – Use with RC7C Series Covers to complete installation.

RC7CTCGY* RC7CTCBK* RC7CTCBS* RC7CTCVY* RC7CTCAB* RC7CTCAA*


(178mm)



CAUTI

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

RC7KTCGY* RC7KTCBK* RC7KTCAL* RC7KTCBS*



Retrofit Kit - Used to upgrade existing installations of RC7 Poke-Thru Devices on carpet floors to meet scrub water requirements. Includes 20A duplex receptacle that can be wired as a standard duplex or isolated ground, two Category 6 TechChoice™ discrete keystone connectors, and two Ortronics TracJack mounting bezels. Also includes scrub water finish flange and slide holder assembly. Kit also includes duplex receptacle barrier. Old barrier must be replaced with new. See installation instructions with retrofit kit for complete installation details.


- * Poke-Thru Devices on this page are available in some or all of the following cover color options as indicated by the part numbers:
 - GY Gray painted flange with gray nonmetallic cover,
 - BK Black painted flange with black nonmetallic cover,
 - VY Ivory painted flange with ivory nonmetallic cover,
 - AL Brushed Aluminum flange with black nonmetallic cover
 - BS Brushed Brass flange with black nonmetallic cover
 - AA Brushed Aluminum flange with aluminum-colored nonmetallic cover
 - AB Brushed Brass flange with brass-colored nonmetallic cover Where applicable, slide covers match the cover color.

Catalog No./Item

Description/Specifications

Catalog Number Explanation RC7ATCAL					
RC7	Α	TC	AL		
Identifies Poke-Thru Series	Identifies Assembled Unit (A) or Cover (C)	Identifies that Unit is approved for Tile and Carpet Floors	Identifies Color of Cover Assembly (See below)		


RC7ATCGY* RC7ATCBK* RC7ATCAL* RC7ATCBS* RC7ATCVY* RC7ATCAB* RC7ATCAA*



Assembled Unit - Prewired 20A duplex receptacle can be wired as standard duplex or isolated ground. Wiremold Open System unloaded inserts to accept two discrete keystone connectors from most manufacturers are provided. Includes 2 Cat 6 TechChoice™ discrete keystone connectors and Ortronics® TracJack bezels.


CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

RC7SHTCBK RC7SHTCGY RC7SHTCBS RC7SHTCVY Nonmetallic Slide Holder Assembly – Available in black (BK), gray (GY), ivory (VY), and nonmetallic brass (BS).



NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

RC7SHTCBKCR RC7SHTCBSCR RC7SHTCGYCR RC7SHTCAACR RC7SHTCVYCR




Poke-Thru Controlled Receptacle – Nonmetallic Slide Holder Assembly with Controlled Receptacle Markings. Markings are located in a recess pad and are permanent indicating the duplex receptacle below has been wired up to comply with 2014 NEC®, CA Title 24 and ASHRAE Energy Efficiency Standard 90.1. Available in black (BK), brass (BS), gray (GY), aluminum (AA) and. ivory (VY). Slide holder to be used with RC7ATC and RC7CTC units.

RC7 Series Ordering Information (Continued)

Catalog No./Item

Description/Specifications

ABPLUG3




Abandonment Plug Assembly -

Complete plug assembly for (178mm) abandoning an open 3" (76mm) cored-hole. Assembly includes intumescent fire-stop material to maintain the fire-classification of the floor, integral retainer ring to prevent the unit from pulling up through the floor, and a black die-cast aluminum cover.

RC7APTCBK RC7APTCGY

Abandonment Plate -

Abandonment available in black (BK), gray (GY).



NOTE: To abandon the RC7 Series Poke-Thru Device, the internal gasket, duplex receptacle, and communication modules must not be removed in order to maintain UL Classification. Also the stem must remain in the coredrilled hole.

COM₅₀ **COM75**

Communication Adapter -

For two 1/2" trade size conduit connections (COM50). For two 3/4" trade size conduit connections (COM75).



NOTE: No additional capacity with COM75.

NOTE: See page 3 for specifications.

Catalog No./Item

Description/Specifications

RC37REC RC37REC-25



Replacement Receptacle -Prewired snap-in 20A receptacle can be wired as standard duplex or isolated ground. Available only in black. See installation instructions with replacement receptacle for complete

installation details. The RC37REC-25 is available with 25 foot leads and can be wired as standard duplex or isolated ground.


NOTE: The 20A duplex receptacle supplied with the new scrub water version RC7 Poke-Thru Device is proprietary and can only be replaced with the RC37REC or RC37REC-25.

RC9 Series Ordering Information

Catalog No./Item

Description/Specifications


RC9STC



Insert Assembly with Disposable Plate - Includes prewired 15A quad receptacle. use with RC9C Series Covers to complete installation.

RC9CTCGY* RC9CTCBK* RC9CTCAL* **RC9CTCBS* RC9CTCAB*** RC9CTCVY*

Finish Flange & Slide Holder **Assembly** – Cover assembly includes two openings for pass-through capability for one 4-pair Category 5e or Category 6 cable per opening.




NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

	Catalog Number Explanation RC9A15TCGY					
RC9	Α	15	TC	GY		
Identifies Poke-Thru Series	Identifies Assembled Unit (A) or Cover (C)	Identifies 15A Quad Power Receptacle	Identifies that Unit is Approved for Tile and Carpet Floors	Identifies Color of Cover Assembly (See below for details)		

RC9A15TCGY* RC9A15TCBK* RC9A15TCAL* RC9A15TCBS* RC9A15TCAB* RC9A15TCVY*

Poke-Thru Assembly - Prewired 15A quad receptacle can be wired as standard quad receptacle or isolated ground. Unit also includes two openings for pass-through capability for one 4-pair Category 5e or Category 6 cable per opening.




NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

- Poke-Thru Devices on this page are available in some or all of the following cover color options as indicated by the part numbers:
 - GY Gray painted flange with gray nonmetallic cover,
 - BK Black painted flange with black nonmetallic cover,
 - VY Ivory painted flange with ivory nonmetallic cover,
 - AL Brushed aluminum flange with black nonmetallic cover
 - BS Brushed brass flange with black nonmetallic cover
 - AA Brushed aluminum flange with aluminum-colored nonmetallic cover
 - AB Brushed brass flange with brass-colored nonmetallic cover Where applicable, slide covers match the cover color.

Catalog No./Item

RC9SHTCBKCR RC9SHTCBSCR RC9SHTCGYCR RC9SHTCAACR RC9SHTCVYCR




Description/Specifications

Poke-Thru Slide Controlled Receptacle - Nonmetallic Slide Holder Assembly with Controlled Receptacle Markings. Markings are located in a recess pad and are permanent indicating the quad receptacle below has been wired up to comply with 2014 NEC®, CA Title 24 and ASHRAE Energy Efficiency Standard 90.1. Available in black (BK), brass (BS), gray (GY), aluminum (AA) and ivory (VY). Slide holder to be used with RC9A15TC and RC9CTC units

RC9SHTCGY RC9SHTCBK **RC9SHTCBS** RC9SHTCVY

Nonmetallic Slide Holder Assembly - Available in gray

(GY), black (BK), ivory (VY), and nonmetallic brass (BS).



NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

RC9APTCBK


(127mm)

Abandonment Plate -

Abandonment available in black (BK).

NOTE: To abandon the RC9 Series Poke-Thru Device, the internal gasket and quad receptacle must not be removed in order to maintain UL Classification. Also, the stem must remain in the core-drilled hole.


RC9REC



Replacement Receptacle -

Prewired 15A quad receptacle can be wired as standard receptacle or isolated ground. Available only in black. See installation instructions with replacement receptacle for complete installation details.

ABPLUG3



Abandonment Plug Assembly -


Complete plug assembly for abandoning an open 3" (76mm) cored-hole. Assembly includes intumescent fire-stop material to maintain the fire-classification of the floor, integral retainer ring to prevent the unit from pulling up through the floor, and a black die-cast aluminum cover.

RC9AMD Series Ordering Information

Catalog No./Item

Description/Specifications

RC9AM2STC




Insert Flange with Disposable Plate – Use with RC9C and RC9CMD,Series Covers to complete installation.

RC9CMDTCGY* RC9CMDTCBK* RC9CMDTCAL* RC9CMDTCBS* RC9CMDTCAB* RC9CMDTCVY*

Finish Flange & Slide Holder Assembly –

Includes adapters to accept four (4) Ortronics® TracJack modular jacks,two (2) Series II modular jacks (Devices sold separately) and Wiremold Open System inserts.




NOTE: Assembled with scrub water gasket. For use on tile or

carpet floors

NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

RC9SHMDTCBY RC9SHMDTCBK RC9SHMDTCBS RC9SHMDTCVY Nonmetallic Slide Holder Assembly– available in black (BK), gray (GY), ivory (VY), and nonmetallic brass (BS).



- Poke-Thru Devices on this page are available in some or all of the following cover color options as indicated by the part numbers:
- GY Gray painted flange with gray nonmetallic cover,
- BK Black painted flange with black nonmetallic cover,
- VY Ivory painted flange with ivory nonmetallic cover,
- AL Brushed Aluminum flange with black nonmetallic cover
- BS Brushed Brass flange with black nonmetallic cover
- AA Brushed Aluminum flange with aluminum-colored nonmetallic cover
- AB Brushed Brass flange with brass-colored nonmetallic cover Where applicable, slide covers match the cover color.


Catalog No./Item

Description/Specifications

Catalog Number Explanation RC9AMDTCGY					
RC9	Α	TC	GY		
Identifies Poke-Thru Series	Identifies Assembled Unit (A) or Cover (C)	Identifies that Unit is approved for Tile and Carpet Floors	Identifies Color of Cover Assembly (See below)		

RC9AMDTCGY*
RC9AMDTCAL*
RC9AMDTCBS*
RC9AMDTCAB*
RC9AMDTCAB*
RC9AMDTCVY*
RC9AMDTCAA*

Poke-Thru Assembly – All communication device accepts up to four UTP connectors. Includes with bezels to accept four (4) Ortronics® TracJack modular jacks and two (2) Series II modular jacks (Devices sold separately) and Wiremold Open System Inserts.



NOTE: Assembled with scrub water gasket. For use on tile or


gasket. For use on tile or carpet floors

NOTE: Modular Jacks

sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

RC9APTCBK



Abandonment Plate -


Abandonment available in black (BK).

NOTE: To abandon the RC9
Series Poke-Thru Device,
the internal gasket and
quad receptacle must not be
removed in order to maintain UL

Classification, Also, the stem

must remain in the coredrilled hole.

ABPLUG3



Abandonment Plug Assembly -

Complete plug assembly for abandoning an open 3" (76mm) cored-hole. Assembly includes intumescent fire-stop material to maintain the fire-classification of the floor, integral retainer ring to prevent the unit from pulling up through the floor, and a black die-cast aluminum cover.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

AV3 Series Ordering Information

AV3STC Insert Assembly with Disposable Plate – Use with AV3C Series covers to complete installation. 16 5/8" (422mm)

AV3CTCBK* AV3CTCAL* AV3CTCAA* AV3CTCBS* AV3CTCAB*



Finish Flange & Slide Holder
Assembly – Includes one prewired
20A duplex receptacle which can
be wired as a standard receptacle
or isolated ground. Includes one
Extron adapter to accept Extron
MAAP mini architectural adapter
plates. (Extron devices sold
separately, only through authorized
Extron dealers). Includes Ortronics®
TracJack and Series II mounting
adapters and.Wiremold Open
System adapters and inserts.

NOTE: Assembled with scrub water gasket. For use on


tile or carpet floors.

NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

Cata	Catalog Number Explanation AV3ATCAL					
AV3	Α	TC	AL			
Identifies Poke-Thru Series	Identifies Assembled Unit (A) or Cover (C)	Identifies that Unit is approved for Tile and Carpet Floors	Identifies Color of Cover Assembly (See below)			

AV3ATCGY* AV3ATCBK* AV3ATCAL* AV3ATCAS* AV3ATCBS* AV3ATCAB* AV3ATCVY*



Assembled Unit - A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground. Includes one Extron bezel to accept Extron MAAP mini architectural adapter plates. (Extron devices sold separately, only through authorized Extron dealers). Includes Ortronics® TracJack and Series II mounting adapters and Wiremold Open System adapters and inserts.

(432mm) NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.


NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

NOTE: See page 3 for specifications.

AV3SHTCBKCR AV3SHTCBSCR AV3SHTCGYCR AV3SHTCAACR AV3SHTCVYCR

Catalog No./Item



Description/Specifications

Poke-Thru Controlled Receptacle – Nonmetallic Slide Holder Assembly with Controlled Receptacle Markings. Markings are located in a recess pad and are permanent indicating the duplex receptacle below has been wired up to comply with 2014 NEC®, CA Title 24 and ASHRAE Energy Efficiency Standard 90.1. Available in black (BK), brass (BS), gray (GY), aluminum (AA) and. ivory (VY). Slide holder to be used with the AV3ATC and AV3CTC units.


AV3SHTCGY AV3SHTCBK AV3SHTCAL AV3SHTCBS AV3SHTCVY



Nonmetallic Slide Holder Assembly – Available in gray (GY), black (BK), ivory (VY), aluminum colored (AL), brass colored (BS).

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.





Abandonment plate – Abandonment available in black (BK) and gray (GY).

RC37REC RC37REC-25



Replacement Receptacle –

Prewired snap-in 20A receptacle can be wired as standard duplex or isolated ground. Available only in black. See installation instructions with replacement receptacle for complete installation details. The RC37REC-25 is available with 25 foot leads and can be wired as standard duplex or isolated ground.

NOTE: The 20A duplex receptacle supplied with the scrub water version AV3 Poke-Thru Device is proprietary and can only be replaced with the RC37REC or RC37REC-25.


- * Poke-Thru Devices on this page are available in some or all of the following cover color options as indicated by the part numbers:
 - GY Gray painted flange with gray nonmetallic cover,
 - BK Black painted flange with black nonmetallic cover, VY Ivory painted flange with ivory nonmetallic cover,
 - AL Brushed Aluminum flange with black nonmetallic cover
 - BS Brushed Brass flange with black nonmetallic cover
 - AA Brushed Aluminum flange with aluminum-colored nonmetallic cover
 - AB Brushed Brass flange with brass-colored nonmetallic cover Where applicable, slide covers match the cover color.

AMD8 Series Ordering Information

Catalog No./Item

Description/Specifications


ABPLUG4



Abandonment Plug Assembly – Complete plug assembly for abandoning an open 4" (102mm) cored-hole. Assembly includes intumescent fire-stop material to maintain the fire-classification of the floor, integral retainer ring to prevent the unit from pulling up through the floor, and a black die-cast aluminum cover.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.


AMD8STC



Insert Assembly with Disposable Plate – Use with AMD8C Series Covers to complete installation.

AMD8CTCGY*
AMD8CTCBK*
AMD8CTCAL*
AMD8CTCAA*
AMD8CTCBS*
AMD8CTCAB*
AMD8CTCY*

Finish Flange & Slide Holder Assembly – Includes adapters to accept eight (8) Ortronics® TracJack inserts and four (4) Series II inserts (Devices sold separately) and Wiremold Open System adapters and inserts.




NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

AMD8SHTCGY AMD8SHTCBK AMD8SHTCAL AMD8SHTCBS AMD8SHTCVY



Nonmetallic Slide Holder Assembly – Available in gray (GY), black (BK), ivory (VY), aluminum colored (AL), brass colored (BS).

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.


Catalog No./Item

Description/Specifications

Catalog Number Explanation AMD8ATCAL					
AMD8	Α	TC	AL		
Identifies Poke-Thru Series	Identifies Assembled Unit (A) or Cover (C)	Identifies that Unit is approved for Tile and Carpet Floors	Identifies Color of Cover Assembly (See below)		

AMD8ATCGY*
AMD8ATCBK*
AMD8ATCAL*
AMD8ATCAA*
AMD8ATCBS*
AMD8ATCAB*
AMD8ATCVY*

Poke-Thru Assembly – All communication device accepts up to eight (8) UTP, fiber optic, audio, or video connectors. Includes adapters to accept eight (8) Ortronics® TracJack inserts and four (4) Series II inserts (Devices sold separately) and Wiremold Open System adapters and inserts.




NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.


ABPLUG4



Abandonment Plug Assembly -

Complete plug assembly for abandoning an open 4" (102mm) cored-hole. Assembly includes intumescent fire-stop material to maintain the fire-classification of the floor, integral retainer ring to prevent the unit from pulling up through the floor, and a black die-cast aluminum cover.

AMD8APTCGY AMD8APTCBK



Abandonment plate -

Abandonment available in black (BK) and gray (GY).


- * Poke-Thru Devices on this page are available in some or all of the following cover color options as indicated by the part numbers:
 - GY Gray painted flange with gray nonmetallic cover,
 - BK Black painted flange with black nonmetallic cover,
 - VY Ivory painted flange with ivory nonmetallic cover,
 - AL Brushed Aluminum flange with black nonmetallic cover
 - BS Brushed Brass flange with black nonmetallic cover

 AA Brushed Aluminum flange with aluminum-colored nonmetallic cover
 - AB Brushed Brass flange with brass-colored nonmetallic cover Where applicable, slide covers match the cover color.

RC4 Series Ordering Information

Catalog No./Item Description/Specifications Insert Assembly with Disposable Plate – Comes complete with four prewired 20A receptacles. Use RC4STC with RC4C Series Covers. 16 3/8" (416mm)

RC4CTCGY*
RC4CTCBK*
RC4CTCBS*
RC4CTCBS*
RC4CTCAB*
RC4CTCVY*



Finish Flange and Slide Holder Assembly –

Wiremold open system unloaded inserts to accept four discrete keystone connectors from most manufacturers are provided. Includes Ortronics® TracJack mounting adapter and Series II communication housing. (Devices sold separately.)

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.


NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use

on polished concrete or terrazzo floor applications.

RC4SHTCBK RC4SHTCGY RC4SHTCBS RC4SHTCVY





NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

* Poke-Thru Devices on this page are available in some or all of the following cover color options as indicated by the part numbers:

- GY Gray painted flange with gray nonmetallic cover,
- BK Black painted flange with black nonmetallic cover,
- VY Ivory painted flange with ivory nonmetallic cover,
- AL Brushed Aluminum flange with black nonmetallic cover
- BS Brushed Brass flange with black nonmetallic cover
- AA Brushed Aluminum flange with aluminum-colored nonmetallic cover
- AB Brushed Brass flange with brass-colored nonmetallic cover Where applicable, slide covers match the cover color.


Catalog No./Item

Description/Specifications

Catalog Number Explanation RC4ATCAL					
RC4	Α	TC	AL		
Identifies Poke-Thru Series	Identifies Assembled Unit (A) or Cover (C)	Identifies that Unit is approved for Tile and Carpet Floors	Identifies Color of Cover Assembly (See below)		

RC4ATCGY* RC4ATCBK* RC4ATCAL* RC4ATCBS* RC4ATCVY* RC4ATCAB* RC4ATCAA*

8 1/4" (210mm) Assembled Unit – Unit includes four prewired 20A receptacles. Each duplex receptacle is wired as a separate circuit. The duplex can be wired as a standard receptacle or isolated ground. Wiremold Open System unloaded inserts to accept four discrete keystone connectors from most manufacturers are included. Includes Ortronics® TracJack mounting adapter and Series II communication housing. (Devices sold separately.)




16 3/8" (416mm)

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

RC4KTCBK RC4KTCGY RC4KTCAL RC4KTCBS RC4KTCAB RC4KTCVY




Retrofit Kit - Used to upgrade existing installations of RC4 Poke-Thru Devices on carpet floors to meet scrub water requirements. Includes two 20A duplex receptacles that can be wired as a standard duplex or isolated ground. Also includes scrub water finish flange and slide holder assembly. Flange available in painted black (BK), gray (GY), ivory (VY), and brushed metal finishes in aluminum (AL), and brass (BS). See installation instructions with retrofit kit for complete installation details.

RC4 Series Ordering Information (Continued)

Catalog No./Item


Description/Specifications

RC4SHTCBK2CR RC4SHTCBS2CR RC4SHTCGY2CR RC4SHTCAA2CR RC4SHTCVY2CR




Poke-Thru Controlled Receptacle – Nonmetallic Slide Holder Assembly with Controlled Receptacle Markings. Markings are located in a recess pad and are permanent indicating the duplex receptacle below has been wired up to comply with 2014 NEC®, CA Title 24 and ASHRAE Energy Efficiency Standard 90.1. Available in, black (BK) brass (BS), gray (GY), aluminum (AA) and. ivory (VY). On circuit "A" duplex receptacles are controlled. Slide holder to be used with the RC4ATC & RC4CTC units.

RC4SHTCBK4CR RC4SHTCBS4CR RC4SHTCGY4CR RC4SHTCAA4CR RC4SHTCVY4CR



Poke-Thru Controlled Receptacle – Nonmetallic Slide Holder Assembly with Controlled Receptacle Markings. Markings are located in a recess pad and are permanent indicating both of the duplex receptacles below have been wired up to comply with 2014 NEC®, CA Title 24 and ASHRAE Energy Efficiency Standard 90.1. Available in black (BK), brass (BS), gray (GY), aluminum (AA) and. ivory (VY). Both circuit duplex receptacles are controlled. Slide holder to be used with the RC4ATC & RC4CTC units.

RC4APTCBK RC4APTCGY RC4APTCAB RC4APTCVY **Abandonment Plate** – Available in black (BK), gray (GY), painted brass (AB), and ivory (VY).




NOTE: To abandon the RC4 Series
Poke-Thru Device, the internal
gasket, duplex receptacle, and
communication modules must
not be removed in order to
maintain UL Classification. Also
the stem must remain in the
core-drilled hole.

NOTE: See page 3 for specifications.

Catalog No./Item

Description/Specifications

RC4REC2 RC4REC2-25



Replacement Receptacle – Two prewired 20A duplex receptacles can be wired as standard duplex or isolated ground. Available only in black. See installation instructions with replacement receptacle for complete installation details. RC4REC2-25 is available with 25 foot leads and can be wired as standard duplex or isolated ground.

NOTE: The 20A duplex receptacle supplied with the scrub water version RC4 Poke-Thru Device is proprietary and can only be replaced with the RC4REC2 or RC4REC2-25.


ABPLUG4



Abandonment Plug Assembly – Complete plug assembly for abandoning an open 4" (102mm) cored-hole. Assembly includes intumescent fire-stop material to maintain the fire-classification of the floor, integral retainer ring to prevent the unit from pulling up through the floor, and a black die-cast aluminum cover.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

COM50 COM75



Communication Adapter –

For two 1/2" trade size conduit connections (COM50). For two 3/4" trade size conduit connections (COM75).

NOTE: No additional capacity with COM75.

RC3 Series Ordering Information

RC3STC Insert Assembly with Disposable Plate – Use with RC3C Series Covers to complete installation.

16 11/16"

RC3CTCGY*
RC3CTCBK*
RC3CTCAL*
RC3CTCBS*
RC3CTCAB*
RC3CTCVY*
RC3CTCAA*




Finish Flange and Slide
Holder Assembly – Prewired 20A
duplex receptacle can be wired
as standard duplex or isolated
ground. Wiremold Open System
unloaded inserts to accept four
discrete keystone connectors from
most manufacturers are provided.
Includes two (2) Ortronics®
TracJack mounting adapters and
two (2) Series II adapters. (Devices
sold separately.)

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

RC3SHTCBK RC3SHTCBY RC3SHTCBS RC3SHTCVY Nonmetallic Slide Holder Assembly – Available in black (BK), gray (GY), ivory (VY), and nonmetallic brass (BS).



NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.


- Poke-Thru Devices on this page are available in some or all of the following cover color options as indicated by the part numbers:
 - GY Gray painted flange with gray nonmetallic cover,
 - BK Black painted flange with black nonmetallic cover,
 - VY Ivory painted flange with ivory nonmetallic cover,
 - AL Brushed Aluminum flange with black nonmetallic cover
 - BS Brushed Brass flange with black nonmetallic cover
 - AA Brushed Aluminum flange with aluminum-colored nonmetallic cover
 - AB Brushed Brass flange with brass-colored nonmetallic cover Where applicable, slide covers match the cover color.

Catalog No./Item

Description/Specifications

Catalog Number Explanation RC3ATCAL					
RC3	Α	TC	AL		
Identifies Poke-Thru Series	Identifies Assembled Unit (A) or Cover (C)	Identifies that Unit is approved for Tile and Carpet Floors	Identifies Color of Cover Assembly (See below)		

RC3ATCGY RC3ATCBK RC3ATCAL RC3ATCBS RC3ATCVY RC3ATCAB RC3ATCAA Assembled Unit – Prewired 20A duplex receptacle can be wired as standard duplex or isolated ground. Wiremold Open System unloaded inserts to accept four discrete keystone connectors from most manufacturers are provided. Includes two (2) Ortronics® TracJack mounting adapters and two (2) Ortronics Series II adapters. (Devices sold separately.)




NOTE: Assembled with scrub water gasket. For use on

tile or carpet floors.

NOTE: Modular Jacks sold separately.

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

RC3KTCBK RC3KTCAL RC3KTCBS RC3KTCVY




Retrofit Kit - Used to upgrade existing installations of RC3 Poke-Thru Devices on carpet floors to meet scrub water requirements. Includes 20A duplex receptacle that can be wired as a standard duplex or isolated ground. Also includes scrub water finish flange and slide holder assembly. Flange available in painted black (BK), gray (GY), ivory (VY), and brushed metal finishes in aluminum (AL), and brass (BS). Kit also includes duplex receptacle barrier. Old barrier must be replaced with new. See installation instructions with retrofit kit for complete installation details.

RC3 Series Ordering Information (Continued)

Catalog No./Item

Description/Specifications

RC3SHTCBKCR RC3SHTCBSCR **RC3SHTCGYCR RC3SHTCAACR** RC3SHTCVYCR




Poke-Thru Controlled Receptacle -Nonmetallic Slide Holder Assembly with Controlled Receptacle Markings. Markings are located in a recess pad and are permanent indicating the duplex receptacle below has been wired up to comply with 2014 NEC®, CA Title 24 and ASHRAE Energy Efficiency Standard 90.1. Available in black (BK), brass (BS), gray (GY), aluminum (AA) and. ivory (VY). Slide holder to be used with the RC3ATC and RC3CTC units.

RC3APTCBK RC3APTCGY

Abandonment Plate -

Abandonment available in black (BK), gray (GY).



NOTE: To abandon the RC3 Series Poke-Thru Device, the internal gasket, duplex receptacle, and communication modules must not be removed in order to maintain UL Classific ation. Also the stem must remain in the core-drilled hole.

RC37REC RC37REC-25

Replacement Receptacle -

Prewired snap-in 20A receptacle can be wired as standard duplex or isolated ground. Available only in black. See installation instructions with replacement receptacle for complete installation details. The RC37REC-25 is available with 25 foot leads and can be wired as standard duplex or isolated ground.


NOTE: The 20A duplex receptacle supplied with the scrub water version RC3 Poke-Thru Device is proprietary and can only be replaced with the RC37REC or RC37REC-25.

NOTE: See page 3 for specifications.

Catalog No./Item

Description/Specifications

ABPLUG4



Abandonment Plug Assembly -Complete plug assembly for abandoning an open 4" (102mm) cored-hole. Assembly includes intumescent fire-stop material to maintain the fire-classification of the floor, integral retainer ring to prevent the unit from pulling up through the floor, and a black

CAUTION: Not intended for use on polished concrete or terrazzo floor applications.

die-cast aluminum cover.

COM50 **COM75**



Communication Adapter -

For two 1/2" trade size conduit connections (COM50). For two 3/4" trade size conduit connections (COM75).

NOTE: No additional capacity with COM75.

NOTES

NOTES

NOTES

NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Electrical Wiring Systems

60 Woodlawn Street West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295-3472) www.legrand.us

570 Applewood Crescent Vaughan, Ontario L4K 4B4 Phone:905.738.9195 www.legrand.ca

