



Tie wire is used for many purposes, among them tying down PVC conduit in trenches before pouring concrete, as well as drop ceiling applications.

- 16 1/2 Gauge
- 400 Ft. (3 1/2#)
- Black Annealed or Galvanized

CAT NO	UPC	STD	MSTR	WT/STD	UNIT
<b>Black Annealed   PC 5030</b>					
TY164	28170	20	20	71.10#	Ea
<b>Galvanized   PC 5035</b>					
VTYG	28180	20	20	68.35#	Ea

Reducing Bushings • Steel / Malleable | PC 5430



Reducing bushings are used with rigid/IMC conduit to reduce the size of a threaded opening to accept a smaller size conduit.

- Zinc Plated Steel
- High Strength Malleable Iron

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
R351	30500	<b>Steel</b> 1/2 x 3/8"	100	500	2.40#	C
R352	30505	3/4 x 1/2"	100	500	5.00#	C
R353	30510	1 x 1/2"	50	250	5.88#	C
R354	30515	1 x 3/4"	50	250	6.77#	C
R355	30520	1-1/4 x 1/2"	25	125	3.44#	C
R356	30525	1-1/4 x 3/4"	25	125	5.33#	C
R357	30530	1-1/4 x 1"	25	125	3.70#	C
R358	30535	1-1/2 x 1/2"	25	125	10.06#	C
R359	30540	1-1/2 x 3/4"	25	125	8.25#	C
R360	30545	1-1/2 x 1"	25	125	6.45#	C
R361	30550	1-1/2 x 1-1/4"	25	125	2.78#	C
R362	30555	2 x 1/2"	10	50	8.18#	C
R363	30560	2 x 3/4"	10	50	7.34#	C
R364	30565	2 x 1"	10	50	6.50#	C
R365	30570	2 x 1-1/4"	10	50	4.81#	C
R366	30575	2 x 1-1/2"	10	50	3.27#	C
R367	30576	<b>Malleable</b> 2-1/2 x 2"	1	10	0.60#	C
R368	30577	3 x 2"	1	10	1.04#	C
R369	30578	3 x 2-1/2"	1	10	1.22#	C
R370	30579	3-1/2 x 2"	1	10	1.39#	C
R371	30580	3-1/2 x 2-1/2"	1	10	1.48#	C
R372	30581	3-1/2 x 3"	1	10	1.17#	C
R373	30582	4 x 2"	1	10	3.62#	C
R374	30583	4 x 2-1/2"	1	10	1.95#	C
R375	30584	4 x 3"	1	10	1.64#	C
R376	30585	4 x 3-1/2"	1	10	1.28#	C

Anti-Short Bushings | PC 5680



Anti-Short bushings are used to protect wire insulation from the jagged or sharp cut edges of BX or flex. Priced per 100 pieces.

- Plastic
- Fits Armored Cable
- Prevents Shorts

CAT NO	UPC	FLEX	CABLE SIZE	PKG	STD	MSTR	WT/STD	UNIT
0	11600	5/16"	14/2, 14/3, 12/2	35	875	875	0.75#	C
1	11601	3/8"	14/4, 6/1,4/1,12/3	35	350	350	0.30#	C
2	11602	7/16"	12/4,10/2,10/3,2/1	35	350	350	0.35#	C
3	11603	1/2"	10/4, 8/2, 8/3,1/1	20	200	200	0.40#	C
4	11604	3/4"	8/4, 6/2, 6/3, 4/2, 4/3	16	160	160	0.40#	C

