



703-SPL




704-SPL




705-SPL




706-SPL




707-SPL



708-SPL



709-SPL




710-SPL


Multi-Gang Boxes and Partitions

Cat. No.	Specifications	Cu. In. Capacity	Std. Pkg.	Wt./Lbs. Per Pkg.
703-SPL	<p>A Three Gang Box 1-13/16" Deep—4-9/16" Long—8-3/4" Wide Three 1/2" K.O.'s and two 3/4" K.O.'s in each side, two 1/2" K.O.'s in each end, and three 1/2" K.O.'s in a line in bottom with two 3/4" K.O.'s at opposite ends in bottom. Furnished with four 8/32 screws. For use with either Bowers 803 and SB-3, 804 and SB-4, or just GB-3 rings and covers.</p>	65.0	5	8
704-SPL	<p>A Four Gang Box 1-13/16" Deep—4-9/16" Long—10-9/16" Wide Four 1/2" K.O.'s and two 3/4" K.O.'s in each side, two 1/2" K.O.'s in each end, and six 1/2" K.O.'s with four 3/4" K.O.'s in bottom. Furnished with four 8/32 screws. For use with either Bowers 804 and SB-4, 805 and SB-5, or just GB-4 rings and covers.</p>	79.0	5	10
705-SPL	<p>A Five Gang Box 1-13/16" Deep—4-9/16" Long—12-15/16" Wide Three 1/2" K.O.'s and four 3/4" K.O.'s in each side, two 1/2" K.O.'s in each end, and six 1/2" K.O.'s with four 3/4" K.O.'s in bottom. Furnished with four 8/32 screws. For use with either Bowers 805 and SB-5, 806 and SB-6, or just GB-5 rings and covers.</p>	94.3	1	2
706-SPL	<p>A Six Gang Box 1-13/16" Deep—4-9/16" Long—14-1/8" Wide Four 1/2" K.O.'s and four 3/4" K.O.'s in each side, two 1/2" K.O.'s in each end, and six 1/2" K.O.'s with four 3/4" K.O.'s in bottom. Furnished with four 8/32 screws. Requires 806, 807, or GB-6 Cover. For use with either Bowers 806 and SB-6, 807 and SB-7, or just GB-6 rings and covers.</p>	110.8	1	2
707-SPL	<p>A Seven Gang Box 1-13/16" Deep—4-9/16" Long—15-15/16" Wide Five 1/2" K.O.'s and four 3/4" K.O.'s in each side, two 1/2" K.O.'s in each end, and nine 1/2" K.O.'s with six 3/4" K.O.'s in bottom. Furnished with four 8/32 screws. For use with either Bowers 807 and SB-7, 808 and SB-8, or just GB-7 rings and covers.</p>	126.5	1	3
708-SPL	<p>An Eight Gang Box 1-13/16" Deep—4-9/16" Long—17-3/4" Wide Six 1/2" K.O.'s and four 3/4" K.O.'s in each side, two 1/2" K.O.'s in each end, and nine 1/2" K.O.'s with six 3/4" K.O.'s in bottom. Furnished with four 8/32 screws. For use with either Bowers 808 and SB-8, 809 and SB-9, or just GB-8 rings and covers.</p>	141.3	1	3
709-SPL	<p>A Nine Gang Box 1-13/16" Deep—4-9/16" Long—19-9/16" Wide Six 1/2" and five 3/4" K.O.'s in each side and two 1/2" K.O.'s in each end, and nine 1/2" K.O.'s with six 3/4" K.O.'s in bottom. Furnished with four 8/32 screws. For use with either Bowers 809 and SB-9, 810 and SB-10, or just GB-9 rings and covers.</p>	155.8	1	4
710-SPL	<p>A Ten Gang Box 1-13/16" Deep—4-9/16" Long—21-3/8" Wide Six 1/2" K.O.'s and six 3/4" K.O.'s in each side, two 1/2" K.O.'s in each end and nine 1/2" K.O.'s with six 3/4" K.O.'s in bottom. Furnished with four 8/32 screws. For use with either Bowers 810 and SB-10, or just GB-10 rings and covers.</p>	170.5	1	5


Cable Clamps



"L" Clamp
Used with pancake boxes.




"LC" Loom Clamp
For nonmetallic sheathed cable. Leg holds clamp off the box for easy cable insertion.




"MXN" Clamp
For use with MC (metal clad) and AC (armored) cable—steel and aluminum #10 to #14 conductors. Also may be used with nonmetallic sheathed cable #10 to #14.

Plaster Ears

Plaster ears are included on many switch boxes. They are set forward 1/16" in the "old work" position. Two-screw ears are supplied on shallow boxes and one-screw ears on 52-Loom Boxes.



One-screw ear



Two-screw ear

INDUSTRY STANDARD SPECIFICATIONS

Steel Products

- *Underwriters Laboratory Inc. File Number**
 - E-2969 Metallic Outlet Box (QCIT)
 - E-5476 Outlet Bushings & Fittings (QCRV)
 - E-19851 Grounding & Bonding Equipment (KDER)
- Federal Specifications**
 - W-J-800E – 1984
- ANSI/NEMA Standard**
 - OS-1 – 1998

UL LISTED PER STANDARD 514A AND B, METALLIC BOXES AND FITTINGS, GROUNDING AND BONDING EQUIPMENT AND OUTLET BUSHINGS AND FITTINGS.

CONFORM TO UBC (UNIFORM BUILDING CODE) SECTION 4304(f) FOR USE IN FIRE RATED WALLS AND PARTITIONS WITH BOXES HAVING MAXIMUM OF 16 SQUARE INCHES AND NOT MORE THAN 100 SQUARE INCHES OF OPENING FOR ANY 100 SQUARE FEET OF WALL OR PARTITION. OUTLET BOXES ON OPPOSITE SIDES OF WALL MUST BE SEPARATED BY A HORIZONTAL DISTANCE OF AT LEAST 24 INCHES.

Nonmetallic Products

- *Underwriters Laboratory Inc. File Number**
 - E-11461 Nonmetallic Outlet Box (QCMZ)
 - R-9140 Outlet Boxes and Fittings
 - Classified for Fire Resistance (CEYY)
- ANSI/NEMA Standard**
 - OS-2 – 1998
- ICBO Fire Rating Wall & Ceiling**
 - Report #3626 – 2 Hour

UL LISTED PER STANDARD 514C NONMETALLIC OUTLET BOXES, FLUSH DEVICE BOXES AND COVERS, UL CONTROL NO. 271 K UL CLASSIFIED FOR FIRE RESISTANCE PER STANDARD FIRE TESTS OF BUILDING CONSTRUCTION AND MATERIALS UL 263, UL CONTROL NO. 764 Y, THIS STANDARD IS ALSO KNOWN AS ANSI AZ 1 ASTM E119 AND NFPA 251 RATED FOR 2 HOURS OR LESS IN FIRE-RESISTANT WALLS CONSISTING OF BEARING OR NON-BEARING WOOD OR NON-BEARING STEEL STUDS AND GYPSUM. ANY LISTED PLASTIC OR STEEL FACE PLATE MAY BE USED.

*For Underwriters Laboratory Inc., (UL) and Canadian Standards Association (C.S.A.) listing marks, see Bowers products & carton labels.