

Hub swings 360° for ease of alignment.



- Pipe clamping portion identical to “JA” clamp
- Pressure-bar type conduit hub adjusts to fit ½" or ¾" EMT or ½" rigid conduit
- Brass washer provides positive contact with grounding conductor
- Furnished with zinc-plated screws

Type JPT — Cast Bronze Clamps for Conduit

CAT. NO.	CONDUIT SIZE	WATER PIPE SIZE	CONDUCTOR RANGE	
			MAX.	MIN.
JPT		½" to 1"		
JPT2	½" or ¾" EMT ½" Rigid	1¼" to 2"	6 Sol.	10 Sol.
JPT4		2½" to 4"		



Conduit Hubs

CAT. NO.	GROUND WIRE SIZE AWG	CONDUIT SIZE
3930	#8 to #2	½" Conduit
3940	#8 to #2	¾" Conduit
3950	#8 to #3/0	1" Conduit
3951	#8 to #4/0	1¼" Conduit

Material: Malleable iron

Provides positive connection between rigid conduit and water system.



- Used in conjunction with “J” clamp
- Rugged cast-bronze threaded hub

Type CH — Bronze Conduit Hubs

CAT. NO.	CONDUIT SIZE (IN.)	CONDUCTOR RANGE	
		MAX.	MIN.
CH12	½	6 Sol.	10 Sol.
CH34	¾	2/0 Str.	10 Sol.
CH1BB	1	3/0 Str.	10 Sol.