



**Sawzall®  
Ultimate 12-Piece  
Demolition Blade Set**

Includes Two 6-inch Wrecker blades, two 6-inch Torch, two 6-inch Axe, three 9-inch Torch, and three 9-inch Axe blades.


No.	Wt.	Each
Ⓢ 49-22-1129	1	24.17

**JIG SAW BLADES  
5 Pack "U" Shank Blade Assortment**

Includes Bi-Metal Blades:

48-42-2120	Metal Cutting
48-42-2160	Metal Cutting
48-42-2190	Metal Cutting
48-42-2300	General Purpose
48-42-2310	General Purpose

No.	Wt.	Each
Ⓢ 49-22-1168	1	7.70



**SUPER MILWAUKEE SUPER SAWZALL BLADES SUPER**

**Milwaukee Ice Edge™  
Super SAWZALL Blades**



Bi-Metal Material  
Made with 8% Cobalt.  
Milwaukee's Longest Lasting Blades.

No.	Teeth/Inch	Length	Height	Thickness	Recommended for cutting:	Wt.	Per 5
48-00-4091	8/12	6"	3/4"	.050"	Wood, nail embedded wood, composition material, plastic, ferrous & non-ferrous metals and cast iron.	1	11.48
48-00-4182	14	6"	3/4"	.035"	3/16 in. to 1/4 in. conduit, tubing, channels, pipe, rubber, and fibers.	1	11.48
48-00-4184	18	6"	3/4"	.035"	1/8 in. to 3/16 in. conduit, tubing, channels, pipe, rubber, and fiber.	1	11.48
48-00-4187	14	9"	3/4"	.035"	3/16 in. to 1/4 in. conduit, tubing, channels, pipe, rubber, and fiber.	1	14.04
48-00-4188	18	9"	3/4"	.035"	1/8 in. to 3/16 in. conduit, tubing, channels, pipe, rubber, and fiber.	1	14.04

**Milwaukee Ice Edge™  
Torch SAWZALL Blades**



Bi-Metal Material  
Made with 8% Cobalt.  
Milwaukee's Longest Lasting Blades.

No.	Teeth/Inch	Length	Height	Thickness	Recommended for cutting:	Wt.	Per 5
48-00-4712	10	6"	1"	.042"	Metal 1/4 in. to 3/8 in. channels, metal pipe and cast iron, demolition, rescue and remodeling.	1	15.26
48-00-4713	10	9"	1"	.042"	Metal 3/16 in. to 1/4 in. channels, metal pipe and cast iron, demolition, rescue and remodeling.	1	20.32
48-00-4782	14	6"	1"	.042"	Metal 3/16 in. to 1/4 in. channels, metal pipe and cast iron, demolition, rescue and remodeling.	1	15.26
48-00-4784	18	6"	1"	.042"	Metal 1/8 in. to 3/16 in., conduit, tubing, channels, metal pipe, demolition, rescue and remodeling.	1	15.26
48-00-4787	14	9"	1"	.042"	Metal 3/16 in. to 1/4 in. channels, metal pipe, cast iron, demolition, rescue and remodeling.	1	20.32
48-00-4788	18	9"	1"	.042"	Metal 1/8 in. to 3/16 in., conduit, tubing, channels, metal pipe, demolition, rescue and remodeling.	1	20.32

**WOOD CUTTING BLADES**



No.	Teeth/Inch	Length	Width	Thickness	Recommended for cutting:	Wt.	Per 5
Ⓢ 48-00-5035	6	6"	3/4"	.050	Very Fast Cut, Nail Embedded	1	10.40
Ⓢ 48-00-5036	6	9"	3/4"	.050	Very Fast Cut, Nail Embedded	1	13.70
Ⓢ 48-00-5037	6	12"	3/4"	.050	Very Fast Cut, Nail Embedded	1	15.59
Ⓢ 48-00-5041	4/6	6"	1/2"	.050	Shearing Action Circles, Contours	1	11.34

**METAL CUTTING BLADES  
For Cutting Metal, Scroll Cutting.**



No.	Teeth/Inch	Length	Width	Thickness	Recommended for cutting:	Wt.	Per 5
Ⓢ 48-00-5161	10	3-5/8"	5/16	.035	Wood Scroll, Contours, Nails, Plastic	1	8.91
Ⓢ 48-00-5162	14	3-5/8"	5/16	.035	Metal Scroll - Heavy gauge metal, hard rubber, fiber.	1	8.91

**ALL PURPOSE BLADES  
For Cutting Wood, Nail Embedded,  
Plastics, Fiberglass, Metals, Cast Iron.**



No.	Teeth/Inch	Length	Width	Thickness	Recommended for cutting:	Wt.	Per 5
Ⓢ 48-00-5090	10	4"	3/4	.035	All Wood, Compressed Material, non-ferrous	1	6.41
Ⓢ 48-00-5091	8/12	6"	3/4	.050	Composition material/Non-ferrous metal	1	8.78
Ⓢ 48-00-5092	10	6"	3/4	.035	Light Gauge non-ferrous metal	1	8.78
Ⓢ 48-00-5093	8/12	8"	3/4	.050	Composition material/Non-ferrous metal	1	11.34
Ⓢ 48-00-5094	8/12	12"	3/4	.050	Composition material/Non-ferrous metal	1	17.15
Ⓢ 48-00-5193	10/14	8"	5/8	.035	All Wood, Plastic, Light Gauge non-ferrous	1	10.80
Ⓢ 48-00-5194	10/14	12"	5/8	.035	All Wood, Nail Embedded, Light Gauge non-ferrous	1	15.59

**METAL CUTTING BLADES  
For Heavy Gauge Metal, Fiberglass.**



No.	Teeth/Inch	Length	Width	Thickness	Recommended for cutting:	Wt.	Per 5
Ⓢ 48-00-5181	14	4"	3/4	.035	Metal 3/16 - 1/4, Conduit, Tubing, Channel, Rubber	1	6.41
Ⓢ 48-00-5182	14	6"	3/4	.035	Sheet Metal, Bar Stock 1/8" & up	1	8.78
Ⓢ 48-00-5183	18	4"	3/4	.035	Metal 1/8 - 3/16, Conduit, Tubing, Channel, Pipe	1	6.41
Ⓢ 48-00-5184	18	6"	3/4	.035	Conduit, Tubing, Channels	1	8.78
Ⓢ 48-00-5185	24	4"	3/4	.035	Metal less than 1/8", Tubing, Pipe, Trim	1	6.41
Ⓢ 48-00-5186	24	6"	3/4	.035	Pipe 18 gauge & less, Trim Tubing	1	8.78
Ⓢ 48-00-5187	14	9"	3/4	.035	Metal 3/16" - 1/4", conduit, tubing, channels, pipe	1	10.80
Ⓢ 48-00-5188	18	9"	3/4	.035	Metal 1/8" - 3/16", conduit, tubing, channels, pipe	1	10.80
Ⓢ 48-00-5189	18	12"	3/4	.035	Metal 1/8" - 3/16", conduit, tubing, channels, pipe	1	13.43
Ⓢ 48-00-5282	14	6"	5/8	.035	Same as 48-00-5182 but 5/8 wide	1	7.97

**PLASTER CUTTING BLADE**



No.	Teeth/Inch	Length	Width	Thickness	Recommended for cutting:	Wt.	Per 5
Ⓢ 48-00-5052	6	5"	3/4	.050	Plaster, Plaster Board. Cuts on Forward and Backward Stroke.	1	7.70

**TUNGSTEN CARBIDE BLADE**



No.	Grit	Length	Width	Thickness	Recommended for cutting:	Wt.	Per 3
Ⓢ 48-00-1420	Medium	6"	3/4	.032	Hardwood flooring, cast iron, stainless steel, fiberglass, ceramic tile, stone, slate, clay pipe, carbon, brick, plaster, marble and chalkboard.	1	10.94



170 Broad St., P.O. Box 305  
Glens Falls, NY 12801-0305

www.dale-electric.com  
email: info@dale-electric.com

TOLL FREE 1-800-462-7733  
LOCAL 518-793-4927  
FAX 518-793-4467