

SCREWS

TEK SELF-DRILLING & TAPPING SCREWS PHILLIPS PAN HEAD

STEEL ZINC CHROMATE ECONOMICAL SWAGED POINT



STOCK NO.	JAR UPC NO.	DIAMETER	LENGTH	WT. PER PKG.	STD. PKG/ MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER 100
JTEK10P	80333	6	1/2	.24	100/500	6.13/c
JTEK11P	80334	6	3/4	.26	100/500	6.89/c
JTEK12P	80335	6	1	.29	100/500	7.36/c
JTEK1P	80336	8	1/2	.39	100/500	6.43/c
JTEK2P	80337	8	3/4	.49	100/500	6.89/c
JTEK14P	80338	8	1	.48	100/500	7.63/c
JTEK15P	80339	8	1 1/2	.67	100/500	10.11/c
JTEK4P	80340	10	1/2	.51	100/500	8.88/c
JTEK3P	80341	10	3/4	.57	100/500	9.97/c
JTEK7P	80342	10	1	.72	100/500	10.74/c
JTEK18P	80343	10	1 1/4	.87	100/500	12.10/c
JTEK19P	80344	10	1 1/2	1.02	100/500	13.03/c


OTHER SIZES AVAILABLE BY REQUEST

NOTE: 6 HAS A #1 POINT; 8 THRU 10 HAS A #2 POINT



TEK SELF-DRILLING & TAPPING SCREWS HEX WASHER HEAD

STEEL ZINC CHROMATE ECONOMICAL SWAGED POINT



STOCK NO.	JAR UPC NO.	DIAMETER	LENGTH	WT. PER PKG.	STD. PKG/ MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER 100
8-10 HAS A #2 TEK 1/4" HEAD—USE MT208B CHUCK, SEE P. 152						
JTEKD1	80345	8	1/2	.39	100/500	6.59/c
JTEKD16	80346	8	5/8	.35	100/500	6.76/c
JTEKD2	80347	8	3/4	.50	100/500	7.19/c
JTEKD14	80348	8	1	.59	100/500	7.63/c
JTEKD15	80349	8	1 1/2	.67	100/500	9.59/c
JTEKD4	80350	10	1/2	.44	100/500	8.15/c
JTEKD3	80351	10	3/4	.56	100/500	8.23/c
8-10 HAS A #2 TEK 5/16" HEAD—USE MT210B CHUCK, SEE P. 152						
JTEKD5	80352	10	1/2	.58	100/500	8.12/c
JTEKD17	80353	10	5/8	.54	100/500	8.75/c
JTEKD6	80354	10	3/4	.70	100/500	9.51/c
JTEKD7	80355	10	1	.87	100/500	9.89/c
JTEKD18	80356	10	1 1/4	.99	100/500	10.57/c
JTEKD19	80357	10	1 1/2	1.14	100/500	11.66/c
12-14 HAS A #3 TEK 5/16" HEAD—USE MT210B CHUCK, SEE P. 152						
JTEKD12	80358	10	3/4	.70	100/500	10.25/c
JTEKD13	80359	10	1	.76	100/500	11.17/c
JTEKD22	80360	10	2	1.31	100/500	16.32/c
JTEKD20	80361	12	3/4	.88	100/500	12.73/c
JTEKD8	80362	12	1	1.01	100/500	14.42/c
JTEKD21	80363	12	1 1/2	1.35	100/500	16.68/c
JTEKD32	80364	12	2	1.75	100/500	18.69/c
12-14 HAS A #3 TEK 3/8" HEAD—USE MT212B CHUCK, SEE P. 152						
JTEKD9	80365	14	3/4	1.11	100/500	16.57/c
JTEKD10	80366	14	1	1.30	100/500	18.86/c
JTEKD11	80367	14	1 1/2	1.75	100/500	21.15/c
JTEKD34	80368	14	2	2.50	100	33.57/c

OTHER SIZES AVAILABLE BY REQUEST

Not recommended for structural steel or bar joist. See Traxx™ Heavy Duty TEK Screws. [Stainless steel available by request.](#)