# Thin Wall Conduit Fittings (for EMT Conduit)

Compression Type Fittings – Steel

#### **COMPRESSION TYPE FITTINGS – STEEL**

## **Applications:**

Thin wall conduit fittings are used:

- To join EMT to a box or enclosure
- To couple two ends of EMT conduit

#### Features:

- · Compression type
- Threadless
- Male hub threads NPSM
- Steel locknuts
- · Heavy steel walls
- Standard material: steel
- Standard finish: zinc plated

#### Concrete Tight Straight Connectors - Insulated

UL File No. E-22132







Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100	
1650	1/2"	50	11	
1651	3/4"	25	16	
1652	1"	25	25	
1653	11/4"	10	43	
1654	11/2"	10	54	
1655	2"	5	76	
1656	21/2"	2	190	
1657	3"	1	300	
1658	31/2 "	1	330	
1650	Λ"	1	360	

### Straight Connectors - Non-insulated

UL File No. E-22132







Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
650S	1/2"	50	9
651S	3/4"	25	16
652	1"	25	25
653	11/4"	10	43
654	11/2"	10	54
655	2"	5	76
656	21/2"	2	190
657	3"	1	300
658	31/2 "	1	280
659	4"	1	360

#### **Couplings**

UL File No. E-22132







Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
660S	1/2"	50	12
661S	3/4"	25	18
662	1"	25	27
663	11/4"	10	46
664	11/2"	10	63
665	2"	5	92
666	21/2"	2	250
667	3"	1	410
668	31/2 "	1	390
669	4"	1	485

## Available in 7 Colors

Painted EMT Fittings are available in seven colors to accommodate a wide range of circuit identification. Typical applications for using color for identification include: fire alarm circuits, low voltage, intrinsically safe circuits, voice and data, and additional voltages. In addition to circuit identification, these can also be used in architectural design to better match look and feel to architectural specifications and preference.















## Part Number Example: 650SGreen

Red Blue 652 11/4 653 Yellow 11/2 654 Orange 21/2 656 657 To order, simply add the 31/2 658 name of the color needed after the catalog number.

Red

White

Blue Yellow

Orange



Black

