


Cover more applications with
the most versatile Weatherproof Covers
on the market



Intermatic.com





Our durable line-up of Die-cast and Plastic Weatherproof Covers offers long-lasting protection in all types of rugged applications: industrial, commercial, manufacturing, residential and more! Time-saving features and resilient construction make these weatherproof covers the most versatile around.

STAY COMPLIANT 2014 NEC Code, Article 406.9 (B)(1)


Intermatic Weatherproof Covers meet or exceed the latest NEC requirements for extra-duty applications and wet locations.

- For the 2014 NEC, all 15 and 20 ampere, 125 and 250 volt receptacles installed in a wet location still must have an enclosure and covers that are weatherproof whether an attachment plug cap is inserted or not.
- A revision now requires all enclosures and covers installed in wet locations for 15 and 20 ampere, 125 and 250 volt receptacles to be listed, and of the "extra-duty" type, not just boxes supported from grade.
- This requirement is now also required for dwelling units as well. The requirement for weather-resistant type receptacles in wet locations is still applicable in the 2014 NEC. This change also provoked changes to Article 590.4(D)(2) for extra-duty covers for all 15 and 20 ampere, 125 and 250 volt receptacles installed at temporary installations in a wet location.
- Exceeds the CEC Section 26-702.

Features

UL, CSA Listed, NEMA 3R, 2014 NEC® 406.9 (B)(1) Compliant and CEC Section 26-702

Extra-Duty Die-Cast Aluminum



Sleek industrial design

Reinforced hinge
(40 lbf stress test)

Impact rated
(withstands destructive forces)

Lockable hasp
accepts up to
.285 in dia. shank

Concealed
hinge

Easy
to open

Heavy-duty metal

Faster installation,
no GFCI insert required

Heavy-duty
polycarbonate construction
ensures long-lasting durability

Extra-Duty Plastic

Keyhole slots and
adhered gaskets make
installs quick and easy

Comprehensive range of sizes
accommodates 2-1/4" Single-Gang
up to 30/50 Amp Double-Gang installations
(4-3/4" depth)

Single-Gang covers
mount vertically or
horizontally



All covers come with Flexi-Guard Inserts, see page 7.



WP5000 Extra-Duty Plastic Series

Extra-Duty Plastic Weatherproof Covers are easy to install and shipped with an adhered gasket, mounting screws, base, cover assembly and inserts for a variety of applications.



WP5100C

WP5225C

WP5500C

FEATURES

- Complies with 2014 Article 406.9(B)(1) for wet locations and extra-duty applications
- Meets requirements for cold impact testing: -60° F (-51° C)
- 5100 and 5220 Series available in 10 different colors
- 5500 Series available in Clear, Gray and Yellow
- Heavy-duty UV stabilized polycarbonate construction ensures long-lasting durability
- Lockable hasp: All models accept up to 0.25" dia shank
- Impact rated: 12 lbf impact test to ensure cover remains intact
- Single-Gang covers mount vertically or horizontally
- Single-Gang Models:
 - NEW Faster Installation, Pre-Set for GFCI, No insert required
 - Two inserts provided with all models that allow each model to meet multiple installations (up to 16 configurations)
- Double-Gang Models:
 - Six inserts provided with all models that allow each model to meet multiple installations (up to 70 configurations)
 - Two round inserts accommodate from 1.375" to 2.656" plugs for the 30/50 amp applications (4-3/4" depth)
- Reinforced hinge pin – designed to exceed 40 lbf hinge hang/stress test

RATINGS

Cover:

UV stabilized polycarbonate
UL Listed for Type 3R

Outdoor Enclosures:

Single-Gang:

Horizontal – Three cord outlets 0.5" wide by 0.9" high
Vertical – One cord outlet 0.75" wide by 0.9" high

Double-Gang:

– One cord outlet 1.1" wide by 3.0" high
– 5500 Series- One cord outlet 1.50" wide by 1.25" high 30/50 amp

Mounting Base and Inserts:

UV stabilized polycarbonate

Gasket:

Neoprene – 1/8" (4.8 mm) thick with slits for mounting screws

Max Cord Size:

Single-Gang – (2) 14 gauge or (1) 12 gauge
Double-Gang – (2) 12 gauge or (1) 10 gauge
30/50 Amp Double-Gang – (1) 6 gauge (3 wire ground)

Warranty: 1-year Limited

One Less Step During Installation

Now Pre-Set for GFCI

NEW Faster Installation!

- Single-gang, Extra-duty plastic covers
- Pre-Set for GFCI – no insert required!
- Can be mounted vertical or horizontal
- 16 configurations in one



GFCI Insert No Longer Required!



Extra-Duty Plastic Weatherproof Covers Ordering



Clear/Gray	Gray	Black	Yellow	Orange	White	Green	Beige	Bronze	Red	Depth	Flexi-Guard Inserts
Single-Gang											
WP5000C	WP5000G	WP5000BL	—	—	WP5000W	—	WP5000B	WP5000BR	—	2.25	WP17
WP5100C	WP5100G	WP5100BL	WP5100Y	WP5100OR	WP5100W	WP5100GN	WP5100B	WP5100BR	WP5100R	2.75	WP17
WP5103C	—	—	—	—	—	—	—	—	—	2.75	WP17
WP5110C	WP5110G	—	—	—	WP5110W	—	—	—	—	3.625	WP17
Double-Gang											
WP5220C	WP5220G	WP5220BL	WP5220Y	WP5220OR	WP5220W	WP5220GN	WP5220B	WP5220BR	WP5220R	2.25	WP217
WP5221C	—	—	—	—	—	—	—	—	—	2.25	WP101, WP102
WP5225C	WP5225G	WP5225BL	—	—	WP5225W	—	—	—	—	2.75	WP217
WP5240C	WP5240G	—	—	—	WP5240W	—	—	—	—	3.625	WP217
WP5500C	WP5500G	—	WP5500Y	—	—	—	—	—	—	30/50 AMP*	WP107, WP213

* 30/50 AMP = 4.75" depth

Additional SKUs available:

- **WP5103C** – **WP5100C** with round adapter plate
- **WP5221C** – 2.25" depth Double-Gang with WP101 (Double-Gang duplex) and WP102 (Double-Gang GFCI) inserts
- **WP10HP** – 10/pack hinge pins

WP Extra-Duty Die-Cast Series

Die-Cast Aluminum Weatherproof Covers are easy to install and shipped with a gasket, mounting screws, base, cover assembly and inserts for a variety of applications.



WP3110MXD

WP1010MXD

WP1010HMXD

WP1030MXD

WP1250MVXD

WP1250MXD

Die-Cast Aluminum Weatherproof Covers Ordering

Part #	Type	Depth	Height	Width	Flexi-Guard Inserts
WP3110MXD	Single-Gang	2.75	6.37	3.87	WP17
WP1010MXD	Single-Gang	3.125	6.37	3.87	WP17
WP1010HMXD	Single-Gang*	3.125	4.37	5.75	WP17

* Note: WP1010HMXD is horizontal

Part #	Type	Depth	Height	Width	Flexi-Guard Inserts
WP1030MXD	Double-Gang	3.125	6.37	5.75	WP217
WP1250MVXD	Single-Gang	4.625	6.37	3.87	WP17
WP1250MXD	Double-Gang	4.625	6.37	5.75	WP17

FEATURES

- Complies with 2014 Article 406.9(B)(1) for wet locations and extra-duty applications
- Meets requirements for cold impact testing: -60° F (-51° C)
- Heavy-duty die-cast aluminum construction ensures long-lasting durability
- Lockable hasp: All models accept up to 0.25" dia shank
- Impact rated: 12 lbf impact test to ensure cover remains intact
- Single-Gang Models:
 - Three inserts provided with all models that allow each model to meet multiple installations (up to eight configurations)
- Double-Gang Models:
 - Six inserts provided with all models that allow each model to meet multiple installations (up to 70 configurations)
- Reinforced hinge pin – designed to exceed 40 lbf hinge hang/stress test

RATINGS

Cover:

Die-Cast Aluminum
UL Listed for Type 3R
Outdoor Enclosures

Mounting Base:

Die-Cast Aluminum

Gasket:

Neoprene – 1/8" (4.8 mm) thick with slits for mounting screws

Max Cord Size:

Single-Gang – 12 gauge or higher cord sets
Double-Gang – 12 gauge or higher cord sets


Warranty: 1-year Limited

Flexi-Guard Inserts

All Weatherproof Covers come with Flexi-Guard Inserts and mounting screws.
Select an insert, rotate to fit and snap into cover.


WP17 Single-Gang Flexi-Guard Inserts – 16 Configurations in One!

- Three separate inserts can be configured into 16 different receptacles or switches
- Converts to either toggle or round receptacles in 1.375", 1.625", 1.75" or 2.125"




WP217 Double-Gang Flexi-Guard Inserts – 70 Configurations in One!

- Six standard inserts combine to make 70 possible configurations
- Converts to either toggle or round receptacles in 1.375" or 1.625"



Plus, additional inserts available:

- **WP101** Double-Gang Duplex
- **WP102** Double-Gang GFCI
- **WP107** Double-Gang Round 1.375", 1.625" or 1.75"
- **WP213** Double-Gang Round 2.156" or 2.656"



Stock up today!

Intermatic

7777 Winn Road
Spring Grove, IL 60081
(815) 675-7000

©2017 Intermatic 300WP10085

Intermatic.com

