

WP Extra-Duty Die-Cast Series Weatherproof Receptacle Covers

WP Extra-Duty Die-Cast Series

The extra-duty die-cast aluminum Series While-In-Use Covers are easy to install and shipped with a gasket, mounting screws, base and cover assembly, and inserts for a variety of applications.

Features

- Complies with 2014 Article 406.9(B)(1) for Wet Locations and Extra-Duty Applications
- Heavy-Duty die-cast Aluminum construction ensures long-lasting durability
- Single-Gang Models:

 3 inserts provided with all models that allow each model to meet multiple installations (up to 16 configurations)

- Double-Gang Models:
 - 6 inserts provided with all models that allow each model to meet multiple installations (up to 70 configurations)
 - 2 round inserts accommodate from 1.375". to 2.656" plugs for the 30/50 amp applications.
- Reinforced Hinge Pin designed to exceed 40lb Hinge Hang/Stress Test
- Impact Rated: 12 lb impact test to ensure cover remains in-tact
- Lockable Hasp: All models accept up to 0.25" Dia Shank
- Meets requirements for cold impact testing: -60°F (-51°C)

Ratings

Cover:

Die-Cast Aluminum UL Certified for Type 3R **Outdoor Enclosures** Single-Gang : WP3110MXD - 2 cord outlets 0.6" high by 1.1" wide WP1010MXD - 2 cord outlets .6" high by 1.1" wide WP1010HMXD – 2 cord outlets 0.6" high by 2.1" wide WP1250MVXD - 2 cord outlets 0.6" high by 1.1" wide Double-Gang : WP1030MXD - 2 cord outlets 0.6" high by 0.8" wide WP1250MXD - 2 cord outlets 0.6" high by 2.0" wide

- Mounting Base: Die-Cast Aluminum
- UV stabilized polycarbonate Inserts:
- Gasket: Neoprene - 1/8" (4.8 mm) thick with slits for mounting screws
- Max Cord Size: Single-Gang (2) 14 Gauge or (2) 12 Gauge Double-Gang - (2) 14 Gauge or (2) 12 Gauge
- Warranty: Limited 1 year

Project:

Location:

Product Type:

Contact/Phone:

Model #:









WP Extra-Duty Die-Cast Series



| Model Number | Туре | FlexiGuard Insert # | Depth (in) |
|--------------|------------------------|---------------------|------------|
| WP3110MXD | Single-Gang | WP17 | 2 3⁄4 |
| WP1010MXD | Single-Gang | WP17 | 3 1/8 |
| WP1010HMXD | Single-Gang/Horizontal | WP17 | 3 1/8 |
| WP1030MXD | Double-Gang | WP217 | 3 1⁄8 |
| WP1250MVXD | Single-Gange/Vertical | WP17 | 4 1/8 |
| WP1250MXD | Double-Gang | WP217 | 4 1/8 |

Specification for Single-Gang

The weatherproof cover shall be designed to mount on a single-gang ______, junction box to ensure while in use weather protection for a standard receptacle. The cover shall mount on indoor or outdoor junction boxes and shall include a weatherproof cover/base assembly, a gasket, three universal inserts, and mounting hardware. The outlet cover shall meet UL requirements for wet locations. The weatherproof cover shall be designed to meet requirements of with 2014 NEC Article 406.9(B)(1) for wet locations and extra-duty applications and shall be UL Type 3R listed. The weatherproof cover shall be constructed entirely of die cast aluminum. The cover, which encloses the cord set, shall be gray. The cover shall meet agency requirements for cold impact at -60°F (-51°C). The cover shall provide usable inside depth of ______ (2 $\frac{3}{4}$ ")(3 $\frac{1}{8}$ "). The weatherproof cover shall be Intermatic model ______ (See Model Numbers Listed).

Specification for Double-Gang

The weatherproof cover shall be designed to mount on a double-gang______ (Vertical), junction box to ensure weather protection for a standard receptacle. The cover shall mount on indoor or outdoor junction boxes and shall include a weatherproof cover/base assembly, a gasket, six universal inserts, and mounting hardware. The inserts must provide flexibility for mounting at any angle including: 90°, 180°, or 270°. The outlet cover shall meet UL requirements for wet locations. The weatherproof cover shall be designed to meet requirements of 2014 NEC Article 406.8(B)(1) for wet locations and extra-duty applications and shall be UL Type 3R listed. The weatherproof cover and base shall be constructed entirely of die cast aluminum. The cover, which encloses the cord set, shall be gray. The cover shall meet agency requirements for cold impact at -60°F (-51°C). The cover shall provide a usable inside depth of _______(3 1/s")(4 5/s"). The weatherproof cover shall be Intermatic model ________(5 0.0000) (5 0.00000000).

Diagrams

