

Heavy Duty Commercial and Hospital Grade Tamper-Resistant GFCI Receptacles with Auto Grounding

15 and 20 Ampere, 125 Volts AC
2 Pole, 3 Wire Grounding



GFTR20I

10kA Short Circuit Current Rating

Limits improper access to energized contacts
 • Patented shutter design for tamper resistant protection

No power at face if reverse wired
 • Open circuit condition eliminates false assumption of protection at face

Ground fault indicator
 • Flashing **RED** indicates device has lost capability to provide protection

Accepts fork terminals
 • Open terminal design

Installation ease
 • Internal back wiring
 • Automatic grounding feature
 • Captive mounting screws

Circuit Guard® GFCI Receptacles Tamper-Resistant, Weather Resistant



Description	Rating	Color	Catalog Number	
Flush, nylon face, back and side wired, multiple drive screws, automatic grounding clip.	15 and 20A 125V AC	Almond	GFTR15AL	GFTR20AL
		Black	GFTR15BK	GFTR20BK
		Brown	GFTR15	GFTR20
		Gray	GFTR15GY	GFTR20GY
		Ivory	GFTR15I	GFTR20I
		Light Almond	GFTR15LA	GFTR20LA
		Office White	GFTR15OW	GFTR20OW
		Red	GFTR15R	GFTR20R
		White	GFTR15W	GFTR20W



GFTR20I

Circuit Guard® GFCI Receptacles Tamper-Resistant, Weather Resistant



Description	Rating	Color	Catalog Number	
Hospital Grade ● Flush, nylon face, back and side wired, multiple drive screws, automatic grounding clip.	15 and 20A 125V AC	Almond	GFR8200HALTR	GFR8300HALTR
		Black	GFR8200HBKTR	GFR8300HBKTR
		Brown	GFR8200HTR	GFR8300HTR
		Gray	GFR8200HGYTR	GFR8300HGYTR
		Ivory	GFR8200HITR	GFR8300HITR
		Light Almond	GFR8200HLATR	GFR8300HLATR
		Office White	GFR8200HOWTR	GFR8300HOWTR
		Red	GFR8200HRTR	GFR8300HRTR
		White	GFR8200HWTR	GFR8300HWTR




GFR8300HITR

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with a matching color nylon wallplate. 20 amp feed-through capability.
 * See Section X, page X-10 for TR and WR descriptions.

Ground Fault Products Heavy Duty Commercial and Hospital Grade GFCI Receptacles with Auto Grounding

15 and 20 Ampere, 125 Volts AC
2 Pole, 3 Wire Grounding



GF15ILA

10kA Short Circuit Current Rating

Comprehensive diagnostics

- When test button is actuated, both the electronic components and mechanical trip mechanism are functionally tested

Ground fault indicator

- Flashing **RED** indicates device has lost capability to provide protection

No power at face if reverse wired

- Open circuit condition eliminates false assumption of protection at face

Installation ease

- Internal back wiring
- Automatic grounding feature
- Captive mounting screws



GF15ILA



GF20WLA



GFR8200HOWLA

Circuit Guard® GFCI Receptacles



15A 125V
NEMA 5-15R



20A 125V
NEMA 5-20R

Description	Rating	Color	Catalog Number	
Flush, nylon face, back and side wired, multiple drive screws, automatic grounding clip.	15 and 20A 125V AC	Almond	GF15ALLA	GF20ALLA
		Black	GF15BKLA	GF20BKLA
	Brown	GF15LA	GF20LA	
	Gray	GF15GYLA	GF20GYLA	
	Ivory	GF15ILA	GF20ILA	
	Light Almond	GF15LALA	GF20LALA	
	Office White	GF15OWLA	GF20OWLA	
	Red	GF15RLA	GF20RLA	
	White	GF15WLA	GF20WLA	

Hospital Grade ● Circuit Guard® GFCI Receptacles



15A 125V
NEMA 5-15R



20A 125V
NEMA 5-20R

Description	Rating	Color	Catalog Number	
Flush, nylon face, back and side wired, multiple drive screws, automatic grounding clip.	15 and 20A 125V AC	Almond	GFR8200HALLA	GFR8300HALLA
		Black	GFR8200HBKLA	GFR8300HBKLA
	Brown	GFR8200HILA	GFR8300HILA	
	Gray	GFR8200HGYLA	GFR8300HGYLA	
	Ivory	GFR8200HILA	GFR8300HILA	
	Light Almond	GFR8200HLAA	GFR8300HLAA	
	Office White	GFR8200HOWLA	GFR8300HOWLA	
	Red	GFR8200HRLA	GFR8300HRLA	
	White	GFR8200HWLA	GFR8300HWLA	

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with a matching color nylon wallplate. 20 amp feed-through capability.

Ground Fault Products

Heavy Duty Commercial GFCI Receptacles with Auto Grounding

15 and 20 Ampere, 125 Volts AC
2 Pole, 3 Wire Grounding



Meets UL Standard 943
Class A GFCI



Circuit Guard® Bulk Pack GFCI Receptacles

Description	Rating	Color	Catalog Number	
Flush, nylon face, back and side wired, multiple drive screws, automatic grounding clip. Bulk packed, (50 pieces without wallplate).	15 and 20A 125V AC	Almond	GF15ALLABULK	GF20ALLABULK
		Black	GF15BKLABULK	GF20BKLABULK
		Brown	GF15LABULK	GF20LABULK
		Gray	GF15GYLABULK	GF20GYLABULK
		Ivory	GF15ILABULK	GF20ILABULK
		Light Almond	GF15LALABULK	GF20LALABULK
		Office White	GF15OWLABULK	GF20OWLABULK
		Red	GF15RLABULK	GF20RLABULK
		White	GF15WLABULK	GF20WLABULK



GF15BKLABULK



GF15LABULK



GF20GYLABULK



GF15LABULK

Circuit Guard® Faceless GFCI

Description	Rating	Color	Catalog Number
Faceless, nylon top, back and side wired, multiple drive screws, automatic grounding clip.	20A 125V AC	Almond	GFBF20ALLA
		Black	GFBF20BKLA
		Brown	GFBF20LA
		Gray	GFBF20GYLA
		Ivory	GFBF20ILA
		Light Almond	GFBF20LALA
		Office White	GFBF20OWLA
		Red	GFBF20RLA
		White	GFBF20WLA

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with a matching color nylon wallplate.

GFCI Receptacle Specifications per GFCI Products Listed (Pages H-2 to H-9)

Trip Level	4 to 6 mA.
Trip Time	.025 sec. nominal.
Frequency	60 Hz.
Voltage	120V AC +10% - 15%.
Amperage	15A/20A, 20A Feed Thru.
Maximum Interrupting Capacity	10,000A.
Operating Temperature	-35°C to 66°C or -30°F to 150°F.
Maximum Humidity	95%.
Listings and Standards	Meets UL498 for receptacles, UL943 Class A for GFCIs UL File E41978. CSA Certified.
Codes	Meets all NEC® and CEC requirements.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).

Ground Fault Products Pre-Wired/Leaded LED Heavy Duty Commercial GFCI Receptacles

15 and 20 Ampere, 125 Volts AC
2 Pole, 3 Wire Grounding



Applications



GFCI LED Pre-Wired/Leaded, #12 Solid Wire, 8 Inch Leads



Description	Rating	Color*	Catalog Number	
Impact resistant flush nylon face, automatic grounding clip, LED, 8" solid wire leads.	15 and 20A 125VAC	Gray	GF15GYLAP1	GF20GYLAP1
		Ivory	GF15ILAP1	GF20ILAP1
		White	GF15WLAP1	GF20WLAP1

Note: * Consult factory for additional colors.



GFCI LED Pre-Wired/Leaded, #12 Stranded Wire, 8 Inch Leads



Description	Rating	Color*	Catalog Number	
Impact resistant flush nylon face, automatic grounding clip, LED, 8" stranded wire leads.	15 and 20A 125VAC	Gray	GF15GYLAP2	GF20GYLAP2
		Ivory	GF15ILAP2	GF20ILAP2
		White	GF15WLAP2	GF20WLAP2

Note: * Consult factory for additional colors.



GFCI LED Tamper and Weather Resistant Pre-Wired/Leaded, #12 Solid Wire, 8 Inch Leads



Description	Rating	Color*	Catalog Number	
* Tamper and Weather Resistant, impact resistant flush nylon face, automatic grounding clip, LED, 8" solid wire leads.	15 and 20A 125VAC	Gray	GFTR15GYP1	GFTR20GYP1
		Ivory	GFTR15IP1	GFTR20IP1
		White	GFTR15WP1	GFTR20WP1

Note: * Consult factory for additional colors.



GFCI LED Tamper and Weather Resistant Pre-Wired/Leaded, #12 Stranded Wire, 8 Inch Leads



Description	Rating	Color*	Catalog Number	
* Tamper and Weather Resistant, impact resistant flush nylon face, automatic grounding clip, LED, 8" stranded wire leads.	15 and 20A 125VAC	Gray	GFTR15GYP2	GFTR20GYP2
		Ivory	GFTR15IP2	GFTR20IP2
		White	GFTR15WP2	GFTR20WP2

Note: * Consult factory for additional colors.



Ground Fault Products

“Buy American” LED Heavy Duty Commercial, Hospital Grade and Tamper-Resistant

15 and 20 Ampere, 125 Volts AC
2 Pole, 3 Wire Grounding



Meets UL Standard 943
Class A GFCI

Applications



GFCI LED “Buy American” Compliant, “U.S.A. Domestic End Product”



Description	Rating	Color	Catalog Number	
Impact resistant flush nylon face, back and side wired, automatic grounding clip, LED, assembled in the U.S.A.	15 and 20A 125VAC	Almond	GF15ALLU	GF20ALLU
		Black	GF15BKLU	GF20BKLU
		Brown	GF15LU	GF20LU
		Gray	GF15GYLU	GF20GYLU
		Ivory	GF15ILU	GF20ILU
		Light Almond	GF15LALU	GF20LALU
		Red	GF15RLU	GF20RLU
		White	GF15WLU	GF20WLU



GF15GYLU

GFCI LED Hospital Grade ● “Buy American” Compliant, “U.S.A. Domestic End Product”



Description	Rating	Color	Catalog Number	
Hospital Grade ●, impact resistant flush nylon face, back and side wired, automatic grounding clip, LED, assembled in the U.S.A.	15 and 20A 125VAC	Almond	GFR8200HALLU	GFR8300HALLU
		Black	GFR8200HBKLU	GFR8300HBKLU
		Brown	GFR8200HLU	GFR8300HLU
		Gray	GFR8200HGYLU	GFR8300HGYLU
		Ivory	GFR8200HILU	GFR8300HILU
		Light Almond	GFR8200HLALU	GFR8300HLALU
		Red	GFR8200HRLU	GFR8300HRLU
		White	GFR8200HWLU	GFR8300HWLU



GFR8300HWLU

GFCI LED Tamper and Weather Resistant “Buy American” Compliant, “U.S.A. Domestic End Product”



Description	Rating	Color	Catalog Number	
Tamper and Weather Resistant, impact resistant flush nylon face, back and side wired, automatic grounding clip, LED, assembled in the U.S.A.	15 and 20A 125VAC	Almond	GFTR15ALU	GFTR20ALU
		Black	GFTR15BKU	GFTR20BKU
		Brown	GFTR15U	GFTR20U
		Gray	GFTR15GYU	GFTR20GYU
		Ivory	GFTR15IU	GFTR20IU
		Light Almond	GFTR15LAU	GFTR20LAU
		Red	GFTR15RU	GFTR20RU
		White	GFTR15WU	GFTR20WU



GFTR20IU

GFCI LED Hospital Grade ● Tamper and Weather Resistant “Buy American” Compliant, “U.S.A. Domestic End Product”



Description	Rating	Color	Catalog Number	
Hospital Grade ●, Tamper and Weather Resistant, impact resistant flush nylon face, back and side wired, automatic grounding clip, LED, assembled in the U.S.A.	15 and 20A 125VAC	Almond	GFR8200HALTRU	GFR8300HALTRU
		Black	GFR8200HBKTRU	GFR8300HBKTRU
		Brown	GFR8200HTRU	GFR8300HTRU
		Gray	GFR8200HGYTRU	GFR8300HGYTRU
		Ivory	GFR8200HITRU	GFR8300HITRU
		Light Almond	GFR8200HLATRU	GFR8300HLATRU
		Red	GFR8200HRTRU	GFR8300HRTRU
		White	GFR8200HWTRU	GFR8300HWTRU



GFR8300HLATRU

