

Locking and Corrosion Resistant Devices

INDEX

A.

-

(

(4)

.

Industrial Specification Grade Locking Devices
Overview
15 Amp Devices
20 Amp Devices
30 Amp Devices
Wetguard [®] Devices
15 Amp
20 Amp
30 Amp
Corrosion Resistant Devices
15 Amp
20 Amp
30 Amp
50 Amp
Non-NEMA Devices
15 Amp
20 Amp
30 Amp
50 Amp
50 Amp "California Style"
Weather Resistant Boots
Power Interrupting Devices
Midget Straight Blade and Locking Devices N29
Combination Locking and
Straight Blade Devices
Integrated Inlets and Outlets with
Weather Resistant Covers

Locking and Corrosion Resistant Devices Index



(B)




LOCKING DEVICE FEATURES

Industrial Grade Locking Devices

LOCKING DEVICES FOR THE ENTIRE SPECTRUM OF INDUSTRIAL APPLICATIONS

Leviton's Industrial Grade Locking Devices are built to provide unparalleled quality and superior performance in the most severe industrial settings. The Locking Devices line represents a broad selection of plugs and connectors, locking receptacles, flanged inlets and outlets, California-style devices, midget locking devices, power interrupting devices, and non-NEMA devices. Leviton combines the best materials available with superior production standards to produce a broad selection of Locking Devices of unmatched flexibility and dependability.





Shrouded pockets in cord clamp prevents slippage of screwdriver blade when tightening clamp screws.



Wire clamps move within individual chambers to provide positive clamp lock without cutting wire strands.



Captive terminal screws eliminate nuisance dropping and searching for missing screws



Deep-funnelled, large wire wells guide conductors into termination position



Stability ribs

Uni-body face Triple-combo

Mechanically-secured

all-brass ground path





Specifically developed for wet or damp locations. EPTR thermoplastic rubber body and rugged design resists water, acids, alkalies, grease, oils and solvents. 24W47 shown

Industrial Grade Locking Devices

Extra thick .050" nickel-plated brass mounting strap ÷ Stamped-in agency certifications Amperage & voltage rating NEMA line number Color-coded voltage rating Manufacturer


mounting screws 0 344484436EEEE Molded-in terminal identification letters Multi-termination design Accepts #8°#14 solid or stranded conductors **AAAAAAAAAAAAAAA**

One-piece ,040" thick brass, high-copper content contacts with nickel-plated clamp type terminals

N

For answers to technical questions, call Leviton's Techline at 1-800-824-3005

Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.co



Heavy-duty, impactresistant, super tough ST801 all-nylon body WEATHER RESISTANT BOOTS AND COVERS construction, with sure grip fluted design Weather-resistant boots and covers for plugs and connectors are available for Nylon plug and con-15Ă, 20A, 30A and 50A straight and nector body is distinlocking plugs and connectors. The tough, rubber triple-seal design protects guished by a bright vellow color for easy devices against the harmful effects of Wiring module keyed identification as dirt and moisture. Thermoplastic covers for 15A, 20A and 30A flush receptacles to body for easy corrosion resistant assembly and tight fit 52CM-66C have close-fitting, spring-loaded lids to shown Mill-slotted, stainless protect outlets against the elements in Wire clamp provides steel cord clamp harsh environments. Boots and covers positive crimp lock withscrews set in deepare listed after their appropriate device. out cutting wire strands funneled wells

LEVITON® To learn more about Leviton's outstanding offering of devices visit our Website at: www.leviton.com

Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com

FOR CORROSION RESISTANT DEVICES

15 AMP 125V



Ø 1.53 (38.9)

BLACK & WHITE

Industrial Grade Locking Devices

NEMA CONFIG.

15 AMP 125V 2-Pole 3-Wire Grounding 🖲 🏵

DESCRIPTION	CAT. NO.	
Dustguard [™] Locking Plug, Yellow EPTR Body	2447	
Dustguard [™] Locking Connector, Yellow EPTR Body	2547	
Duplex Flush Receptacle, Self Grounding, Back and Side Wired	4700	
Duplex Flush Receptacle w/2 Hot Feeds and 1 Neutral Return, Self Grounding, Back and Side Wired	4702-IIR	
Duplex Flush Receptacle w/Split Feed — 2 Hot Feeds and 2 Neutral Returns, Self Grounding, Back and Side Wired	4703-IIR	
Duplex Flush Receptacle, Isolated Ground, Back and Side Wired	4700-IG	
Single Flush Receptacle	4710	
Single Flush Receptacle, w/Short Strap	4710-SS	
Single Flush Receptacle, Isolated Ground	4710-IG	
Locking Flanged Outlet	4715-C	L5-15P
Locking Flanged Inlet	4716-C	
Locking Plug, Black & White Nylon Body	4720-C	
Power Indication™ Locking Plug, Black & White Nylon Body	4720-PLC	
Angle Locking Plug, Black & White Nylon Body	4720-CA	
Locking Plug, All Black Nylon for Stage and Studio	4720-CB	
Locking Plug, Yellow Nylon Body	4720-CY	
Locking Connector, Black & White Nylon Body	4729-C	
Power Indication™ Locking Connector, Black Nylon Body	4729-PLC	
Locking Connector, All Black Nylon for Stage and Studio	4729-CB	
Locking Connector, Yellow Nylon Body	4729-CY	-
Weather-Resistant Boots for 15A Locking Plugs and Connectors are	e listed on pa	nge N27







4720-CA



WEATHER-RESISTANT FLIP LID COVER

FOR INLETS AND OUTLETS

IP64 Rated—Includes Gasket and Screws

WP1

4716-C

Locking Flush Receptacles

Wallplates and Covers **302 STAINLESS STEEL**

SINGLE RECEPTACLE

1.41" Dia. Opening

Ο ٥ 84004-40

For complete wallplate selection, see Section E.

- Rugged nylon body and cover for outstanding resist-ance to impact and harsh chemicals
- · Double-wipe phosphor-bronze power contacts
- Locking Plugs and Connectors
- Super tough Nylon body resists damage from severe impact, abrasion and chemicals
- · Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
- · Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
- · One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long service life
- Power Indication™ 15A Locking Plugs & Connectors equipped with green neon bulb rated at 30,000 hours (24/7) for 3.5 years

Flanged Inlets and Outlets

Cord Clamp Range—Black & White Plugs and Connectors: .240"-.700" #18-#10 AWG Dustguard Plugs and Connectors: .240"-.655" #18-#12 AWG

302 STAINLESS STEEL

DUPLEX RECEPTACLE

84003-40

SPECIFICATIONS AND FEATURES

- · Rugged nylon flange fits flush and won't crack in highabuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- Wire clamps provide positive crimp lock without cutting wire strands

Dustguard Plugs and Connectors

- IEC IP44 Rated
- Developed to withstand dusty and dirty environments, cracking and fading, temperature extremes
- · Rugged wiring modules have high performance singlepiece brass triple-wipe contacts, solid brass plug blades

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed. Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94 Operating Temperature: -40°C to 60°C

LEVITON For answers to technical questions, call Leviton's Techline at 1-800-824-3005





.09 (53.2)

.39 (35.3)

Ø 1.53 (38.9)

1.47 (35.7) 4570-CA

1.98 (50.4)

2.76 (70.0) 4579-CY

Cord Clamp Range—Black & White Plugs and Connectors: .240"-.700"

#18ॅ–#10 AWG

4570-CY

15 AMP 250V, 277V and 3Ø 250V

Industrial Grade Locking Devices



(38. 53 Ø

15 AMD 250V 2 Data 2 Wire Crounding I a



DESCRIPTION	CAT. NO.	NEMA CONFIG.
Duplex Flush Receptacle, Self Grounding, Back and Side Wired	4550	
Duplex Flush Receptacle, Isolated Ground, Back and Side Wired	4550-IG	
Single Flush Receptacle	4560	
Single Flush Receptacle, Isolated Ground	4560-IG	
Locking Plug, Black & White Nylon Body	4570-C	
Power Indication™ Locking Plug, Black & White Nylon Body	4570-PLC	
Angle Locking Plug, Black & White Nylon Body	4570-CA	L6-15P
Locking Plug, Yellow Nylon Body	4570-CY	
Locking Connector, Black & White Nylon Body	4579-C	
Power Indication [™] Locking Connector, Black & White Nylon Body	4579-PLC	
Locking Connector, Yellow Nylon Body	4579-CY	
Locking Flanged Outlet	4585-C	
Locking Flanged Inlet	4586-C	
15 AMP 277V 2-Pole 3-Wire Grounding 🖲 🗐		
DESCRIPTION	CAT. NO.	NEMA CONFIG.
Duplex Flush Receptacle, Self Grounding, Back and Side Wired	4750	
Duplex Flush Receptacle, Isolated Ground, Back and Side Wired	4570-IG	
Single Flush Receptacle	4760	
Single Flush Receptacle, Isolated Ground	4760-IG	
Locking Plug, Black & White Nylon Body	4770-C	
Power Indication [™] Locking Plug, Black & White Nylon Body	4770-PLC	
Angle Locking Plug, Black & White Nylon Body	4770-CA	L7-15P
Locking Plug, Yellow Nylon Body	4770-CY	
Locking Connector, Black & White Nylon Body	4779-C	
Locking Connector, Yellow Nylon Body	4779-CY	
Power Indication [™] Locking Connector, Black & White Nylon Body	4779-PLC	
Locking Flanged Outlet	4785-C	
Locking Flanged Inlet	4786-C	
15 AMP 3Ø 250V 3-Pole 3-Wire Non-Grounding 🖲		
DESCRIPTION	CAT. NO.	NEMA CONFIG.
Single Flush Receptacle	4870	

_	DESCRIPTION	CAT. NO.	NEMA CONFIG.
	Single Flush Receptacle	4870	
	Locking Plug, Black & White Nylon Body	4880-C	L11-15P (z) L11-15R (*())
	Locking Connector, Black & White Nylon Body	4889-C	

Weather-Resistant Boots for 15A Locking Plugs and Connectors are listed on page N27

Wallplates and Covers

wallplates and covers		
302 STAINLESS STEEL SINGLE RECEPTACLE	302 STAINLESS STEEL DUPLEX RECEPTACLE	WEATHER-RESISTANT FLIP LID COVER FOR INLETS AND OUTLETS
1.41" Dia. Opening		IP64 Rated—Includes Gasket and Screws
° ° 84004-40	84003-40	WP1

For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

Locking Flush Receptacles

- · Rugged nylon body and cover for outstanding resistance to impact and harsh chemicals
- · Double-wipe phosphor-bronze power contacts
- Locking Plugs and Connectors
- Super tough Nylon body resists damage from severe impact, abrasion and chemicals
- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
- Cord clamp does not have to be disassembled from body for wiring-accepts all wire mesh strain reliefs
- conductivity and long service life • Power Indication™ 15A Locking Plugs & Connectors equipped with green neon bulb rated at 30,000 hours (24/7) for 3.5 years

 One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum

Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- · Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- · Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94 Operating Temperature: -40°C to 60°C

N

LEVITON® To learn more about Leviton's outstanding offering of devices visit our Website at: www.leviton.com Courtes of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com

20 AMP 125V, 250V and 277V



Industrial Grade Locking Devices

L5-20R

NEMA CONFIG.

L6-20R

<u>ی</u>،

NEMA CONFIG.

20 AMP 125V 2-Pole 3-Wire Grounding 🗓 🕮

BLACK WHITE

DESCRIPTION	CAT. NO.	
V-0-MAX [®] Single Flush Receptacle	2310	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2310-IG	
Locking Plug, Black & White Nylon Body	2311	
Power Indication™ Locking Plug, Black & White Nylon Body	2311-PLC	
Locking Plug, all Black for Stage and Studio	2311-B	
Power Indication™ Locking Plug, All-Black Nylon Body	2311-PLB	
Locking Plug, Yellow Nylon Body	2311-CY	L5-
Locking Connector, Black & White Nylon Body	2313	
Power Indication [™] Locking Connector, Black & White Nylon Body	2313-PLC	
Locking Connector, all Black for Stage and Studio	2313-B	
Power Indication [™] Locking Connector, All-Black Nylon Body	2313-PLB	
Locking Connector, Yellow Nylon Body	2313-CY	
Locking Flanged Inlet	2315	
Locking Flanged Outlet	2316	

20 AMP 250V 2-Pole 3-Wire Grounding 🗓 🕮

DESCRIPTION	CAT. NO.	
V-0-MAX [®] Single Flush Receptacle	2320	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2320-IG	
Locking Plug, Black & White Nylon Body	2321	
Power Indication [™] Locking Plug, Black & White Nylon Body	2321-PLC	
Power Indication [™] Locking Plug, All-Black Nylon Body	2321-PLB	
Locking Plug, Yellow Nylon Body	2321-CY	L
Locking Connector, Black & White Nylon Body	2323	
Power Indication [™] Locking Connector, Black & White Nylon Body	2323-PLC	
Power Indication™ Locking Connector, All-Black Nylon Body	2323-PLB	
Locking Connector, Yellow Nylon Body	2323-CY	
Locking Flanged Inlet	2325	
Locking Flanged Outlet	2326	

20 AMP 277V 2-Pole 3-Wire Grounding 🗓 🕮

CAT. NO.	NEMA CONFIG.
2330	
2330-IG	
2331	
2331-PLC	L7-20P
2333	
2333-PLC	
2335	
2336	
-	2330 2330-IG 2331 2331-PLC 2333 2333-PLC 2335

Weather-Resistant Boots for 20A Locking Plugs and Connectors are listed on page N27

For recommended Wallplates and Covers, see page N8. For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

V-O-Max® Locking Flush Receptacles

- UL 94 V-O Flammability Rating, the best rating of any material used in Industrial Locking Flush Receptacles available today
- Extra-thick .050" nickel-plated brass mounting strap for high-abuse applications
- Designed for maximum durability: One-piece .040" brass, high copper-content contacts with nickelplated clamp-type terminals
- Color-coded voltage rating on face for easy identification


Locking Plugs and Connectors

- Super tough Nylon body resists damage from severe impact, abrasion and chemicals
- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling

- Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
- One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long sonico life
- conductivity and long service life ¹ • Power Indication™ 20A Locking Plugs & Connectors equipped with green LED rated at 100,000 hours (24/7) for 11.5 years


Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- Wire clamps provide positive crimp lock without cutting wire strands





2311



2313

Ø 2.08 (52.8)

Locking Devices



Cord Clamp Range—Black & White Plugs and Connectors: .385"-.780" #16-#10 AWG

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated V0 Operating Temperature: -40°C to 60°C


For answers to technical questions, call Leviton's Techline at 1-800-824-3005 LEVITON. Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com



20 AMP 347V, 480V, 600V and 125/250V

Industrial Grade Locking Devices

BLACK & WHITE



2340







DESCRIPTION		CAT.	NO.	NEMA CONFIG.
V-O-MAX [®] Single Flush R	Receptacle	3720	-	
Locking Plug, Black & Wi		3721		L24-20P
Locking Connector, Black		3723		
Locking Flanged Inlet		3755	5	0 0
Locking Flanged Outlet		3756	6	
20 AMP 480V 2-Pole	e 3-Wire Grounding 🗓 🔀			
DESCRIPTION	3	CAT.	NO.	NEMA CONFIG.
V-O-MAX [®] Single Flush R	Receptacle	2340)	
V-O-MAX [®] Single Flush R	Receptacle, Isolated Ground	2340)-IG	
Locking Plug, Black & Wi	hite Nylon Body	2341		L8-20P () L8-20R ()
Locking Connector, Black	& White Nylon Body	2343	3	\mathbf{O}
Locking Flanged Inlet		2345	5	
Locking Flanged Outlet		2346	ò	
20 AMP 600V 2-Pole	e 3-Wire Grounding 🗓 🚱			
DESCRIPTION		CAT.	NO.	NEMA CONFIG.
V-O-MAX [®] Single Flush R	Receptacle	2350)	
V-O-MAX [®] Single Flush R	Receptacle, Isolated Ground	2350)-IG	
Locking Plug, Black & Wi	hite Nylon Body	2351		L9-20P
Locking Connector, Black	& White Nylon Body	2353	3	
Locking Flanged Inlet		2355	5	
Locking Flanged Outlet		2356	b	
20 AMP 125/250V 3	-Pole 3-Wire Non-Grounding 🞚			
DESCRIPTION		CAT.	NO.	NEMA CONFIG.
Single Flush Receptacle		2360)	
Locking Plug, Black & Wl	hite Nylon Body	2361		L10-20P
Locking Connector, Black	& White Nylon Body	2363	3	
Locking Flanged Inlet		2365	5	
Locking Flanged Outlet		2366	ò	
Weather-Resistant Boots I	for 20A Locking Plugs and Connectors ar	e listed	l on pa	ge N27
Cord Clamp R	ange—Black & White Plugs and Connecto	ors: .38	5"–.78	0" #16-#10 AWG
Wallplates and Cove	rs			,
302 STAINLESS STEEL SINGLE RECEPTACLE	WEATHER-RESISTANT FLIP LID COVER For 20A Inlets/outlets and 20A Receptad		WEATH	HER-RESISTANT THERMOPLASTIC COVER FOR RECEPTACLES

302 STAINLESS STEEL SINGLE RECEPTACLE	WEATHER-RESISTANT FLIP LID COVER FOR 20A INLETS/OUTLETS AND 20A RECEPTACLES		WEATHER-RESISTANT THERMOPLASTIC COVER FOR RECEPTACLES
1.60" Dia. Opening	IP64 Rated—Includes (Gasket and Screws	Self-Closing Lid—Includes Gasket and Screws
°			
84020-40	WP2 for Inlets/Outlets	7420-CR for Receptacles	4980-GY

For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
 - Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
 - One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long service life

Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- · Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated VO Operating Temperature: -40°C to 60°C

V-O-Max[®] Locking Flush Receptacles

for high-abuse applications

plated clamp-type terminals

Locking Plugs and Connectors

available today

identification

N

UL 94 V-O Flammability Rating, the best rating of any material used in Industrial Locking Flush Receptacles

Extra-thick .050" nickel-plated brass mounting strap

Designed for maximum durability: One-piece .040"

Super tough Nylon body resists damage from severe impact, abrasion and chemicals

brass, high copper-content contacts with nickel-

Color-coded voltage rating on face for easy

20 AMP 3Ø 250V, 480V and 125/250V

NEMA CONFIG.

BLACK AWHITE DUUSTRIAL GRADE PLUGS & CONNECTORS

DESCRIPTION

Locking Flanged Inlet

Locking Flanged Outlet

V-0-MAX[®] Single Flush Receptacle

Locking Plug, Black & White Nylon Body

Locking Connector, Black & White Nylon Body

Industrial Grade Locking Devices



20 AMP 3Ø 250V 3-Pole 3-Wire Non-Grounding

DESCRIPTION	CAT. NO.	NEMA CONFIG.
Single Flush Receptacle	2370	
Locking Plug, Black & White Nylon Body	2371	
Locking Connector, Black & White Nylon Body	2373	L11-20P
Locking Flanged Inlet	2375	
Locking Flanged Outlet	2376	

20 AMP 3Ø 480V 3-Pole 3-Wire Non-Grounding		
DESCRIPTION	CAT. NO.	NEMA CONFIG.
Single Flush Receptacle	2380	
Locking Plug, Black & White Nylon Body	2381	
Locking Connector, Black & White Nylon Body	2383	$ = L12-20P \left(\begin{array}{c} \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\$
Locking Flanged Inlet	2385	
Locking Flanged Outlet	2386	_

CAT. NO.

2410-IG


2410

2411

2413

2415

2416





3.78 (96.0) **2413**

Ø 3.03 (77.0)

Ø 2.22 (56.4) **2416**

20 AMP 3Ø 250V 3-Pole 4-Wire Grounding 🗓 🕮

20 AMP 125/250V 3-Pole 4-Wire Grounding 🗓 🏵

V-0-MAX® Single Flush Receptacle, Isolated Ground

DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2420†	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2420-IG†	~ ~
Locking Plug, Black & White Nylon Body	2421	115-20P
Locking Connector, Black & White Nylon Body	2423	
Locking Flanged Inlet	2425	
Locking Flanged Outlet	2426	

Weather-Resistant Boots for 20A Locking Plugs and Connectors are listed on page N27

Cord Clamp Range—Black & White Plugs and Connectors 3-Wire: .385"-.780" #16-#10 AWG 4-Wire: .595"-.895" #14-#10 AWG

Wallplates and Covers

Tranplatos ana ooro	10		
302 STAINLESS STEEL SINGLE RECEPTACLE	WEATHER-RESISTANT FLIP LID COVER For 20A Inlets/outlets and 20A receptacles		WEATHER-RESISTANT THERMOPLASTIC COVER FOR RECEPTACLES
1.60" Dia. Opening	IP64 Rated—Include	s Gasket and Screws	Self-Closing Lid—Includes Gasket and Screws
° °			<u> </u>
84020-40	WP2 for Inlets/Outlets	7420-CR for Receptacles	4980-GY

For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

V-O-Max® Locking Flush Receptacles

- UL 94 V-O Flammability Rating, the best rating of any material used in Industrial Locking Flush Receptacles available today
- Extra-thick .050" nickel-plated brass mounting strap for high-abuse applications
- Designed for maximum durability: One-piece .040' brass, high copper-content contacts with nickelplated clamp-type terminals
- Color-coded voltage rating on face for easy identification

Locking Plugs and Connectors

Super tough Nylon body resists damage from severe impact, abrasion and chemicals

- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
- Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
- One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum
- tacts and solid brass plug blades provide maximum conductivity and long service life Flanged Inlets and Outlets
- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and
- Flanged Outlets (File #E-13399)

31 (58.7)

- CSA Certified (File #LR-406)
- NOM Certified (#057)Backed by a Lifetime Warranty

97 (50.

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated V0 Operating Temperature: -40°C to 60°C

N

(56.4)

Ø 2.22





20 AMP 30 480V; 30Y 120/208V, 277/480V and 347/600V

Industrial Grade Locking Devices

BLACK WHITE











20 AMP 3Ø 480V 3	-Pole 4-Wire Grounding 🗓 🕲	8	
DESCRIPTION		CAT. N	0. NEMA CONFIG.
V-0-MAX [®] Single Flush	Receptacle	2430	
V-0-MAX [®] Single Flush	Receptacle, Isolated Ground	2430-	IG
Locking Plug, Black & V	Vhite Nylon Body	2431	L16-20P
Locking Connector, Blac	ck & White Nylon Body	2433	
Locking Flanged Inlet		2435	
Locking Flanged Outlet		2436	
20 AMP 3ØY 120/2	08V 4-Pole 4-Wire Non-Grou	nding	
DESCRIPTION		CAT. N	0. NEMA CONFIG.
Single Flush Receptacle	<u>}</u>	2440	
Locking Plug, Black & V	Vhite Nylon Body	2441	
Locking Connector, Blac	ck & White Nylon Body	2443	L18-20P (* L18-20R (*() 1 0)
Locking Flanged Inlet		2445	
Locking Flanged Outlet		2446	
20 AMP 3ØY 277/4	80V 4-Pole 4-Wire Non-Grou	nding	
DESCRIPTION		CAT. N	0. NEMA CONFIG.
Single Flush Receptacle	2	2450	
Locking Plug, Black & V	Vhite Nylon Body	2451	
Locking Connector, Blac	ck & White Nylon Body	2453	L19-20P (() L19-20R ())
Locking Flanged Inlet		2455	
Locking Flanged Outlet		2456	
20 AMP 3ØY 347/6	00V 4-Pole 4-Wire Non-Grou	nding	
DESCRIPTION		CAT. N	0. NEMA CONFIG.
Single Flush Receptacle	2	2460	
Locking Plug, Black & V	Vhite Nylon Body	2461	
Locking Connector, Blac	ck & White Nylon Body	2463	L20-20P ((()) L20-20R (())
Locking Flanged Inlet		2465	
Locking Flanged Outlet		2466	
Weather-Resistant Boots	for 20A Locking Plugs and Connect	ors are listed o	on page N27
Cord Clamp	Range—Black & White Plugs and Co	nnectors: .595'	'895" #14-#10 AWG
Wallplates and Cov	ers		
302 STAINLESS STEEL	WEATHER-RESISTANT FLIP LID CO		NEATHER-RESISTANT THERMOPLASTIC
1.60" Dia. Opening	FOR 20A INLETS/OUTLETS AND 20A REC IP64 Rated—Includes Gasket and Sc		COVER FOR RECEPTACLES elf-Closing Lid—Includes Gasket and Screws
84020-40	WP2 for Inlets/Outlets 7420-CR for F		4980-GY
For complete wellplate	·		

For complete wallplate selection, see Section E.

V-O-Max[®] Locking Flush Receptacles

- UL 94 V-O Flammability Rating, the best rating of any material used in Industrial Locking Flush Receptacles available today
- Extra-thick .050" nickel-plated brass mounting strap for high-abuse applications
- Designed for maximum durability: One-piece .040" brass, high copper-content contacts with nickelplated clamp-type terminals
- Color-coded voltage rating on face for easy identification

Locking Plugs and Connectors

· Super tough Nylon body resists damage from severe impact, abrasion and chemicals

- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
- Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
- One-piece, rivetless .035" thick brass connector con-tacts and solid brass plug blades provide maximum conductivity and long service life

Flanged Inlets and Outlets

SPECIFICATIONS AND FEATURES

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- · Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated VO Operating Temperature: -40°C to 60°C

N

20 AMP 3ØY 120/208V, 277/480V and 347/600V



90

1.13 (28.6)

 \leq

27

Ø 2.22 (56.4)

2510

2.70 (68.7) 2511

3.78 (96.0)

2513

1.70 (43.3)

0.75 19.1

3.62 (92.1) (83.3)

Ø 1.97 (50.0)

Ø 1.97 (50.0)

3.28

Industrial Grade Locking Devices

20 AMP 3ØY 120/208V 4-Pole 5-Wire Grounding 🖲 🏵

DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2510	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2510-IG	
Locking Plug, Black & White Nylon Body	2511	
Locking Connector, Black & White Nylon Body	2513	
Locking Flanged Inlet	2515	
Locking Flanged Outlet	2516	

20 AMP 3ØY 277/480V 4-Pole 5-Wire Groundina 🖲 🏵

DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2520	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2520-IG	
Locking Plug, Black & White Nylon Body	2521	.22-20P (()) L22-20R (())
Locking Connector, Black & White Nylon Body	2523	
Locking Flanged Inlet	2525	
Locking Flanged Outlet	2526	

20 AMP 3ØY 347/600V 4-Pole 5-Wire Grounding 🖤 🏵

DESCRIPTION	CAT. NO.	NEMA CONFIG.
Single Flush Receptacle	2530	
Single Flush Receptacle, Isolated Ground	2530-IG	_
Locking Plug, Black & White Nylon Body	2531	L23-20P
Locking Connector, Black & White Nylon Body	2533	
Locking Flanged Inlet	2545	
Locking Flanged Outlet	2546	
Weather Pesistant Boots for 201 Locking Plugs and Conn	actors are listed on na	ao N27

Weather-Resistant Boots for 20A Locking Plugs and Connectors are listed on page N27

Cord Clamp Range—Black & White Plugs and Connectors: .595"-.895" #14-#10 AWG

Wallplates and Covers

BLACK WHITE

	-		
302 STAINLESS STEEL SINGLE RECEPTACLE	WEATHER-RESISTANT FLIP LID COVER FOR 20A INLETS/OUTLETS AND 20A RECEPTACLES		WEATHER-RESISTANT THERMOPLASTIC COVER FOR RECEPTACLES
1.60" Dia. Opening	IP64 Rated—Include	s Gasket and Screws	Self-Closing Lid—Includes Gasket and Screws
°			
84020-40	WP2 for Inlets/Outlets	7420-CR for Receptacles	4980-GY

For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
- Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
- One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long service life

Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- · Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated VO Operating Temperature: -40°C to 60°C

N

For answers to technical questions, call Leviton's Techline at 1-800-824-3005

Locking Flush Receptacles

- UL 94 V-O Flammability Rating, the best rating of any material used in Industrial Locking Flush Receptacles available today
- Extra-thick .050" nickel-plated brass mounting strap for high-abuse applications
- Designed for maximum durability: One-piece .040" brass, high copper-content contacts with nickel-plated clamp-type terminals
- Color-coded voltage rating on face for easy identification

Locking Plugs and Connectors

· Super tough Nylon body resists damage from severe impact, abrasion and chemicals

Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.



30 AMP 125V, 250V and 277V

Industrial Grade Locking Devices









2625F

Cord Clamp Range—Black & White
Plugs and Connectors: .385"860"
#16-#8 AWG

30 AMP	9 125V 2-Pole	3-Wire	Grounding	$(\! \! \ \! \ \! \!)$	\$₽₀	
--------	---------------	--------	-----------	--------------------------	------	--

DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2610	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2610-IG	
Locking Plug, Black & White Nylon Body	2611	
Power Indication [™] Locking Plug, Black & White Nylon Body	2611-PLC	
Locking Plug, All Black for Stage and Studio	2611-B	
Power Indication™ Locking Plug, All-Black Nylon Body	2611-PLB	
Locking Plug, Yellow Nylon Body	2611-CY	
Locking Connector, Black & White Nylon Body	2613	L5-30P
Power Indication [™] Locking Connector, Black & White Nylon Body	2613-PLC	
Locking Connector, All Black for Stage and Studio	2613-B	
Power Indication [™] Locking Connector, All-Black Nylon Body	2613-PLB	
Locking Connector, Yellow Nylon Body	2613-CY	
Locking Flanged Inlet	2615	
Locking Flanged Outlet	2616	
30 AMP 250V 2-Pole 3-Wire Grounding 🖲 🕄		

DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2620	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2620-IG	
Locking Plug, Black & White Nylon Body	2621	
Power Indication™ Locking Plug, Black & White Nylon Body	2621-PLC	
Locking Plug, All Black for Stage and Studio	2621-B	_
Locking Plug, Yellow Nylon Body	2621-CY	L6-30P
Locking Connector, Black & White Nylon Body	C2623	
Power Indication [™] Locking Connector, Black & White Nylon Body	2623-PLC	
Locking Connector, All Black for Stage and Studio	C2623-B	
Locking Connector, Yellow Nylon Body	C2623-CY	
Locking Flanged Inlet	2625F	
Locking Flanged Outlet	2626F	

30 AMP 277V 2-Pole 3-Wire Grounding 🖤 🏵

DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2630	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2630-IG	
Locking Plug, Black & White Nylon Body	2631	
Power Indication [™] Locking Plug, Black & White Nylon Body	2631-PLC	LT-30P
Locking Connector, Black & White Nylon Body	2633	
Power Indication [™] Locking Connector, Black& White Nylon Body	2633-PLC	
Locking Flanged Inlet	2635	
Locking Flanged Outlet	2636	

Weather-Resistant Boots for 30A Locking Plugs and Connectors are listed on page N27

For recommended Wallplates and Covers, see page N13. For complete wallplate selection, see Section E.

Tor complete wanplate selection,

SPECIFICATIONS AND FEATURES

- V-O-Max[®] Locking Flush Receptacles
- UL 94 V-O Flammability Rating, the best rating of any material used in Industrial Locking Flush Receptacles available today
- Extra-thick .050" nickel-plated brass mounting strap for high-abuse applications
- Designed for maximum durability: One-piece .040" brass, high copper-content contacts with nickelplated clamp-type terminals
- Color-coded voltage rating on face for easy identification

Locking Plugs and Connectors

Super tough Nylon body resists damage from severe impact, abrasion and chemicals

- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
- Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
 One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum
- conductivity and long service life Power Indication™ 30A Locking Plugs & Connectors equipped with green LED rated at 100,000 hours

(2'4/7) for 11.5 years Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated V0 Operating Temperature: -40°C to 60°C

Locking Devices

N

LEVITON To learn more about Leviton's outstanding offering of devices visit our Website at: www.leviton.com

30 AMP 480V, 600V, 125/250V and 3Ø 250V



Industrial Grade Locking Devices

30 AMP 480V 2-Pole 3-Wire Grounding 🖤 🏵

BLACK WHITE

DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2640	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2640-IG	_
Locking Plug, Black & White Nylon Body	2641	- L8-30P
Locking Connector, Black & White Nylon Body	2643	
Locking Flanged Inlet	2645	
Locking Flanged Outlet	2646	-

30 AMP 600V 2-Pole 3-Wire Grounding 🖤 🏵

DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2650	
V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2650-IG	
Locking Plug, Black & White Nylon Body	C2651	L9-30P
Locking Connector, Black & White Nylon Body	C2653	
Locking Flanged Inlet	2655	
Locking Flanged Outlet	2656	

30 AMP 125/250V 3-Pole 3-Wire Non-Grounding 🚇

	<u>v</u>	
DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2660	
Locking Plug, Black & White Nylon Body	2661	
Locking Connector, Black & White Nylon Body	2663	「L10-30P (、】) L10-30R (低)、
Locking Flanged Inlet	2665	
Locking Flanged Outlet	2666	-





N

30 AMP 3Ø 250V 3-Pole 3-Wire Non-Grounding

	3	
DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX [®] Single Flush Receptacle	2670	
Locking Plug, Black & White Nylon Body	2671	
Locking Connector, Black & White Nylon Body	2673	「L11-30P (、 」)、 L11-30R (*(、 ノ)
Locking Flanged Inlet	2675	
Locking Flanged Outlet	2676	-

Weather-Resistant Boots for 30A Locking Plugs and Connectors are listed on page N27

Cord Clamp Range-Black & White Plugs and Connectors: .385"-.860" #16-#8 AWG

Wallplates and Covers

maniplatos alla soro					
302 STAINLESS STEEL SINGLE RECEPTACLE	WEATHER-RESISTANT FLIP LID COVER FOR 30A INLETS/OUTLETS AND 30A RECEPTACLES		WEATHER-RESISTANT THERMOPLASTI COVER FOR RECEPTACLES		
1.60" Dia. Opening	IP64 Rated—Includes Gasket and Screws		Self-Closing Lid—Includes Gasket and Screws		
°					
84020-40	WP2 for Inlets/Outlets	7420-CR for Receptacles	4980-GY		

For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

Locking Flush Receptacles

- UL 94 V-O Flammability Rating, the best rating of any material used in Industrial Locking Flush Receptacles available today
- Extra-thick .050" nickel-plated brass mounting strap for high-abuse applications
- Designed for maximum durability: One-piece .040" brass, high copper-content contacts with nickel-plated clamp-type terminals
- Color-coded voltage rating on face for easy identification

Locking Plugs and Connectors

Super tough Nylon body resists damage from severe impact, abrasion and chemicals

- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
- Cord clamp does not have to be disassembled from
- body for wiring-accepts all wire mesh strain reliefs
- One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long service life

Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX[®] Receptacles Rated VO Operating Temperature: -40°C to 60°C




For answers to technical questions, call Leviton's Techline at 1-800-824-3005 Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com



30 AMP 3Ø 480V, 3Ø 600V, 3Ø 250V and 125/250V

Industrial Grade Locking Devices

BLACK WHITE









plated clamp-type terminals

Locking Plugs and Connectors

identification

1.69 (42.8)	30 AMP 3Ø 480V 3-Pole 3-Wire Non-Groundin	ng	
(19.1)	DESCRIPTION	CAT. NO.	NEMA CONFIG.
	Single Flush Receptacle	2680	
	Locking Plug, Black & White Nylon Body	2681	
	Locking Connector, Black & White Nylon Body	2683	L12-30P
130	Locking Flanged Inlet	2685	$ \odot$ \bigcirc
63 (92.1) 28 (83.30 2.67 (67.8	Locking Flanged Outlet	2686	
3.63 (92.1) 3.28 (83.30 2.67 (67.6	30 AMP 3Ø 600V 3-Pole 3-Wire Non-Groundin	na 🕪	
	DESCRIPTION	CAT. NO.	NEMA CONFIG.
• • •	Single Flush Receptacle	2690	
	Locking Plug, Black & White Nylon Body	2691	
1.06 (26.8)	Locking Connector, Black & White Nylon Body	2693	— L13-30P
2710	Locking Flanged Inlet	2695	- 🕑 🔮
	Locking Flanged Outlet	2696	
0.2.22 (56.4)	30 AMP 125/250V 3-Pole 4-Wire Grounding		
31	DESCRIPTION	CAT. NO.	NEMA CONFIG.
0 0 0 0	V-0-MAX [®] Single Flush Receptacle	2710	
2.70 (68.7)	V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2710-IG	_
	Locking Plug, Black & White Nylon Body	2711	
2711	Locking Plug, Yellow Nylon Body	2711-CY	- L14-30P (1) L14-30R (
	Locking Connector, Black & White Nylon Body	2713	
	Locking Connector, Yellow Nylon Body	2713-CY	·
	Locking Flanged Inlet	2715	
	Locking Flanged Outlet	2716	
	30 AMP 3Ø 250V 3-Pole 4-Wire Grounding 🖲) 🕀 🛛	
	DESCRIPTION	CAT. NO.	NEMA CONFIG.
3.78 (96.0)	V-0-MAX [®] Single Flush Receptacle	2720	
2713	V-0-MAX [®] Single Flush Receptacle, Isolated Ground	2720-IG	
	Locking Plug, Black & White Nylon Body	2721	
	Locking Connector, Black & White Nylon Body	2723	— L15-30P (() L15-30R (()
Ø 3.03 (77.0)	Locking Flanged Inlet	2725	- 0 0
-	Locking Flanged Outlet	2726	
1 10.	Weather-Resistant Boots for 30A Locking Plugs and Conn	nectors are listed on	page N27
	Cord Clamp Range —Black & White Plugs and Co	nnectors 3-Wire: .385	5"–.860" #16–#8 AWG
(58.7)	4-Wire: .595"-1.150" #14-#8 AWG Wallplates and Covers		
(28)	302 STAINLESS STEEL WEATHER-RESISTANT FLIP LI	D COVER WF	ATHER-RESISTANT THERMOPLASTIC
5.31	SINGLE RECEPTACLE FOR 30A INLETS/OUTLETS AND 30A	RECEPTACLES	COVER FOR RECEPTACLES
Ø 2.22 (56.3)	1.60" Dia. Opening IP64 Rated—Includes Gasket ar	nd Screws Self-	Closing Lid—Includes Gasket and Screws
2715		SE)	
		for Receptacles	4980-GY
	For complete wallplate selection, see Section E.		
SF	ECIFICATIONS AND FEATURES		AND CODE COMPLIANCE
Nax® Locking Flush Receptacles	 Ergonomic, fluted body design with radial grip ridge i ideal for gripping, turning and pulling 		lugs, connectors, inlets and outlets neet NEMA WD-6, and ANSI C-73,
94 V-O Flammability Rating, the best aterial used in Industrial Locking Flush	Tallig of any 5 1 5		eed UL 498 standards
ailable today	body for wiring—accepts all wire mesh strain reliefs		ted WC-596 – Plugs, Connectors and
tra-thick .050" nickel-plated brass mou high-abuse applications	 One-piece, rivetless .035" thick brass connector con tacts and solid brass plug blades provide maximum 	Flanged Outlets (ile #E-13393), Receptacles and (File #E-13399)
esigned for maximum durability. One-n		 CSA Certified (Fil 	e #I P. 106)

tacts and solid brass plug blades provide maximum conductivity and long service life

Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- · Wire clamps provide positive crimp lock without cutting wire strands
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated V0 Operating Temperature: -40°C to 60°C

Locking Devices

N

LEVITON® To learn more about Leviton's outstanding offering of devices visit our Website at: www.leviton.com LE VII VIII I learn more about Leviton's outstariung of jering of devices visit our website at. www.tevicon.com Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com

 Super tough Nylon body resists damage from severe impact, abrasion and chemicals

Designed for maximum durability: One-piece .040" brass, high copper-content contacts with nickel-

Color-coded voltage rating on face for easy

BLACK WHITE

Industrial Grade Locking Devices

D,



30 AMP 3Ø 480V 3-Pole 4-Wire Grounding 🗓 🏵

ESCRIPTION	CAT. NO. NEMA CONFIG.
0-MAX [®] Single Flush Receptacle	2730
0-MAX [®] Single Flush Receptacle, Isolated Ground	2730-IG
ocking Plug, Black & White Nylon Body	2731 2733 L16-30P
ocking Connector, Black & White Nylon Body	2733
ocking Flanged Inlet	2735
ocking Flanged Outlet	2736
ocking Flanged Inlet	2735


30 AMP 3Ø 600V 3-Pole 4-Wire Grounding 🗓 🏵

<u></u>		
DESCRIPTION	CAT. NO.	NEMA CONFIG.
Single Flush Receptacle	2740	
Single Flush Receptacle, Isolated Ground	2740-IG	_
Locking Plug, Black & White Nylon Body	2741	
Locking Connector, Black & White Nylon Body	2743	
Locking Flanged Inlet	2745	
Locking Flanged Outlet	2746	

30 AMP 3ØY 120/208V 4-Pole 4-Wire Non-Grounding 🕒

30 AMP 3ØY 277/480V 4-Pole 4-Wire Non-Grounding 🖲

	V	
DESCRIPTION	CAT. NO.	NEMA CONFIG.
Single Flush Receptacle	2750	
Locking Plug, Black & White Nylon Body	2751	
Locking Connector, Black & White Nylon Body	2753	L18-30P
Locking Flanged Inlet	2755	
Locking Flanged Outlet	2756	









Weather-Resistant Boots for 30A Locking Plugs and Connectors are listed on page N27

Cord Clamp Range-Black & White Plugs and Connectors: .595"-1.150" #14-#8 AWG

Wallplates and Covers

DESCRIPTION

Single Flush Receptacle

Locking Flanged Inlet

Locking Flanged Outlet

Locking Plug, Black & White Nylon Body

Locking Connector, Black & White Nylon Body

302 STAINLESS STEEL SINGLE RECEPTACLE	WEATHER-RESISTANT FLIP LID COVER FOR 30A INLETS/OUTLETS AND 30A RECEPTACLES		WEATHER-RESISTANT THERMOPLASTIC COVER FOR RECEPTACLES
1.60" Dia. Opening	IP64 Rated—Includes Gasket and Screws		Self-Closing Lid—Includes Gasket and Screws
°			
84020-40	WP2 for Inlets/Outlets	7420-CR for Receptacles	4980-GY

For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

V-O-Max[®] Locking Flush Receptacles

- UL 94 V-O Flammability Rating, the best rating of any material used in Industrial Locking Flush Receptacles available today
- Extra-thick .050" nickel-plated brass mounting strap for high-abuse applications
- Designed for maximum durability: One-piece .040' brass, high copper-content contacts with nickelplated clamp-type terminals
- Color-coded voltage rating on face for easy identification

Locking Plugs and Connectors

- · Super tough Nylon body resists damage from severe impact, abrasion and chemicals
- · Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling

CAT. NO

2760

2761

2763

2765

2766

NEMA CONFIG

- Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
- One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long service life

Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- · Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- · Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCI

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated VO Operating Temperature: -40°C to 60°C

ocking Devices



30 AMP 3ØY 347/600V, 3ØY 120/208V and 3ØY 277/480V

Industrial Grade Locking Devices

BLACK & WHITE









Extra-thick .050" nickel-plated brass mounting strap for high-abuse applications

· Designed for maximum durability: One-piece .040"

Color-coded voltage rating on face for easy

brass, high copper-content contacts with nickel-plated

clamp-type terminals

Locking Plugs and Connectors

identification

 1.70 (43.3) ↓ 0.75 ↓ 	30 AMP 30Y 347/60	OV 4-Pole 4-Wire Non-Groun	ding	
(19.1)	DESCRIPTION		CAT. N	O. NEMA CONFIG.
	Single Flush Receptacle		2770	
	Locking Plug, Black & W	hite Nylon Body	2771	
	Locking Connector, Black		2773	L20-30P (*() L20-30R (*()))
<u>8.3</u>) 60.7	Locking Flanged Inlet		2775	
3.62 (92.1) 3.28 (63.3) 2.39 (60.7	Locking Flanged Outlet		2776	
3.6	30 AMP 30Y 120/20	8V 4-Pole 5-Wire Grounding	(h) (f .	
	DESCRIPTION	<u>.</u>	CAT. N	O. NEMA CONFIG.
	V-0-MAX [®] Single Flush R	Receptacle	2810	
1.13 (28.6)	V-0-MAX [®] Single Flush R	Receptacle, Isolated Ground	2810-	IG
2810	Locking Plug, Black & W	hite Nylon Body	2811	
	Locking Connector, Black	< & White Nylon Body	2813	L21-30P
7	Locking Flanged Inlet		2815	
[50.0] 2 [56.4]	Locking Flanged Outlet		2816	
<u>8</u> 1.97 (50.0) 8.2.22 (56.4)	30 AMP 3ØY 277/48	OV 4-Pole 5-Wire Grounding	(L) (L)	
2.70 (68.7)	DESCRIPTION		CAT. N	O. NEMA CONFIG.
P P	Single Flush Receptacle		2820	
2811	Single Flush Receptacle,	Isolated Ground	2820-	IG
	Locking Plug, Black & W	hite Nylon Body	2821	
	Locking Connector, Black	< & White Nylon Body	2823	
(56.4)	Locking Flanged Inlet		2825	
0 1.97 (50.0) 0 2.22 (56.4)	Locking Flanged Outlet		2826	
	30 AMP 3ØY 347/60	OV 4-Pole 5-Wire Grounding	(L) (L)	
3.78 (96.0)	DESCRIPTION		CAT. N	O. NEMA CONFIG.
2813	Single Flush Receptacle		2830	
	Single Flush Receptacle,	Isolated Ground	2830-	IG
Ø 3.03 (77.0)	Locking Plug, Black & W	hite Nylon Body	2831	
40	Locking Connector, Black	< & White Nylon Body	2833	
(15-)	Locking Flanged Inlet		2835	
	Locking Flanged Outlet		2836	
	Weather-Resistant Boots	for 30A Locking Plugs and Connecto	rs are listed o	on page N27
(58.7)	Wallplates and Cove	rs		
31 (2)	302 STAINLESS STEEL SINGLE RECEPTACLE	WEATHER-RESISTANT FLIP LID CON FOR 30A INLETS/OUTLETS AND 30A RECI		NEATHER-RESISTANT THERMOPLASTIC COVER FOR RECEPTACLES
2.31	1.60" Dia. Opening	IP64 Rated—Includes Gasket and Scree		elf-Closing Lid—Includes Gasket and Screws
 ✓ 2.22 (56.4) 2816 	\bigcirc			Ó
Cord Clamp Range—Black & White	84020-40	WP2 for Inlets/Outlets 7420-CR for Re	ceptacles	4980-GY
Plugs and Connectors: .595"–1.150" #14–#8 AWG	For complete wallplate se	election, see Section E.		
117-110 AWG				
SP	ECIFICATIONS AND FEATURES		TEST	ING AND CODE COMPLIANCE
Locking Flush Receptacles		ed body design with radial grip ridge is		s, plugs, connectors, inlets and outlets
• UL 94 V-O Flammability Rating, the best	rating of any ideal for grippin	g, turning and pulling	are designed	to meet NEMA WD-6, and ANSI C-73, exceed UL 498 standards
material used in Industrial Locking Flush available today		es not have to be disassembled from —accepts all wire mesh strain reliefs	UL Fed Spec.	Listed WC-596 – Plugs, Connectors and
Extra-thick 050" nickel-plated brass mou		tless 035" thick brass connector	Flanged Inlets	s (File #E-13393), Receptacles and

 One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long service life

Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- · Wire clamps provide positive crimp lock without cutting wire strands
- and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX® Receptacles Rated VO Operating Temperature: -40°C to 60°C

16 Control Control

Industrial Grade Wetguard® Locking Devices



Werguard Wetguard [®] Devices Engineered to IP66 & IP67 Watertight Standards				
Wetguard Locking Plugs and Connectors 🖲 🗐				
DESCRIPTION	CAT. NO. PLUG	CAT. NO. CONNECTOR		
Yellow EPTR, 15A-125V 2-Pole, 3-Wire	24W47	25W47 ^{L5-15R} (ريم		
Black EPTR	24W47-B	25W47-B		
Yellow EPTR, 15A-250V 2-Pole, 3-Wire	24W49 L6-15P	25W49 L6-15R		
Yellow EPTR, 15A-277V 2-Pole, 3-Wire	24W34	25W34		
Yellow EPTR, 20A-125V 2-Pole, 3-Wire	26W47	27W47 L5-20R (رج)		
Black EPTR	26W47B	27W47B		
Yellow EPTR, 20A-250V 2-Pole, 3-Wire	26W48	27W48		
Black EPTR	26W48-B	27W48-B		
Yellow EPTR, 20A-277V 2-Pole, 3-Wire	26W49 L7-20P	27W49		
Replacement Closure Cap				



Replacement Closure Cap

CAT. NO. YELLOW	CAT. NO. BLACK
50W50	50W50-B
50W52	50W52-B
14W	14W-B
26W	26W-B
	50W50 50W52 14W

Cord Clamp Range—Wetguard® Locking Plugs and Connectors 15A: .375"-.655" #18–#10 AWG 20A: .375"-.875" #18-#10 AWG

2.31 (58.7 3.58 (91.0) 26W47

Locking Devices

Wetguard

SPECIFICATIONS AND FEATURES

- · IEC IP66 and IP 67 Rated, in accordance with IEC 529 as evaluated by UL and CSA
- NEMA Type 4, 4X, 6 and 6P Ratings in accordance with UL 50 and CSA 94

• EPTR rubber parts provide outstanding resistance to wet and damp environments, extreme temperature variations, acids, alkalis, grease, oils and solvents

- Interlocking "tongue and groove" construction seals out water, moisture, dirt when plugs are mated with connectors
- Multi-point sealing system utilizes nut, strain relief washer and rubber bushing to form a watertight cord grip seal
- · Non-magnetic stainless steel fast-threading assembly screws won't interfere with sensitive equipment
- · Connector "hood" closure cap seals device when not in use

TESTING AND CODE COMPLIANCE

- · Meet NEMA WD 1 & 6, ANSI requirements
- UL Listed & meets Fed. Spec. requirements: (File #13393)
- CSA Certified (File #LR-406) NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated V2 Operating Temperature: -40°C to 60°C



LEVITON

For answers to technical questions, call Leviton's Techline at 1-800-824-3005 Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com



Industrial Grade Wetguard® Locking Devices



26W81



27W81



26W81-B

 •	LEVIIUII							
ata	llard ®	Motauard®	Douiooo	Engineeroo	0	ID47	Watertight S	tondordo
лу	juaru	weiguaru	Devices	Engineered	ά	IP07	watertight 5	lanuarus
		-		-			-	

Wetguard Locking Plugs and Connectors 🗓 🗐

DESCRIPTION	CAT. NO. PLUG	CAT. NO. CONNECTOR
Yellow EPTR, 20A-125/250V 3-Pole, 4-Wire	26W74 L14-20P	27W74
Yellow EPTR, 20A-3Ø 250V 3-Pole, 4-Wire Black EPTR	26W75 L15-20P 26W75-B	27W75 L15-20R 27W75-B
Yellow EPTR, 20A-3Ø 480V 3-Pole, 4-Wire Black EPTR	26W76 L16-20P 26W76-B	27W76 L16-20R 27W76-B
Yellow EPTR, 20A-3ØY 120/208V 4-Pole, 5-Wire Black EPTR	26W81 L21-20P 26W81-B	27W81 L21-20R 27W81-B
Yellow EPTR, 20A-3ØY 277/480V 4-Pole, 5-Wire	26W82 L22-20P	27W82
Yellow EPTR, 20A-3ØY 347/600V 4-Pole, 5-Wire	26W83 L23-20P	27W83

Wetguard Non-NEMA, Non-Grounding Devices (Not UL Listed–For Replacement Use Only)						
DESCRIPTION	CAT. NO. PLUG	CAT. NO. CONNECTOR				
Yellow EPTR, 20A-125/250V 3-Pole, 3-Wire	26W08 NON-NEMA	27W08 NON- NEMA				
Yellow EPTR, 20A-3ØY 120/208V 4-Pole, 4-Wire	26W09	27W09				

Replacement Closure Cap

DESCRIPTION	CAT. NO. YELLOW	CAT. NO. BLACK
Connector Cap for 20A devices	50W52	50W52-B
Plug Cap for 20A devices	26W	26W-B

Cord Clamp Range-Wetguard® 20A Locking Plugs and Connectors: .375"-.875" #18-#10 AWG

SPECIFICATIONS AND FEATURES

Wetguard

- · IEC IP66 and IP 67 Rated, in accordance with IEC 529 as evaluated by UL and CSA
- NEMA Type 4, 4X, 6 and 6P Ratings in accordance with UL 50 and CSA 94
- EPTR rubber part provide outstanding resistance to wet and damp environments, extreme temperature variations, acids, alkalis, grease, oils and solvents
- · Interlocking "tongue and groove" construction seals out water, moisture, dirt when plugs are mated with connectors
- Multi-point sealing system utilizes nut, strain relief washer and rubber bushing to form a watertight cord grip seal
- · Non-magnetic stainless steel fast-threading assembly screws won't interfere with sensitive equipment
- · Connector "hood" closure cap seals device when not in use

TESTING AND CODE COMPLIANCE

- · Meet NEMA WD 1 & 6, ANSI requirements
- UL Listed & meets Fed. Spec. requirements: (File #13393)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated V2 Operating Temperature: -40°C to 60°C

Locking Devices

To learn more about Leviton's outstanding offering of devices visit our Website at: www.leviton.com

LE VII VIN 10 learn more about Levitoris outstanding of jening of devices visit our website at www.evitoric.com Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com

Industrial Grade Wetguard® Locking Devices



3.62 (92.0)

28W47

Ø 2.75 (69.9) 29W47

DESCRIPTION Yellow EPTR, 30A-125V 2-Pole, 3-Wire Black EPTR Yellow EPTR, 30A-250V 2-Pole, 3-Wire Yellow EPTR, 30A-277V 2-Pole, 3-Wire Yellow EPTR, 30A-125/250V 3-Pole, 4-Wire Black EPTR, 30A-3Ø 250V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 480V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 7120/208V 4-Pole, 5-Wire	CAT. NO. PLUG 28W47 28W47-B 28W47-B 28W48 L6-30P 28W49 L7-30P 28W74 L14-30P 28W75-B 28W75-B 28W76-B 28W76-B 28W77-B 28W77-B 28W77-B 28W77-B 28W77-B 28W71 L17-30P (************************************	CAT. NO. CONNECTOR 29W47 29W47-B 29W48 L6-30R 29W49 L7-30R 29W74 L14-30R 29W75 29W75-B 29W76-B 29W76-B 29W77-B 29W77-B 29W81	-
2-Pole, 3-Wire Black EPTR Yellow EPTR, 30A-250V 2-Pole, 3-Wire Yellow EPTR, 30A-277V 2-Pole, 3-Wire Yellow EPTR, 30A-125/250V 3-Pole, 4-Wire Black EPTR, 30A-3Ø 250V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 480V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 120/208V	28W47-B 28W47-B 28W47-B 28W48 L6-30P 28W49 L7-30P 28W74 L14-30P 28W75-B 28W75-B 28W76-B 28W76-B 28W77-B 28W77-B 28W71 L17-30P 28W77-B 28W71 L15-30P 28W77-B 28W71 L15-30P	29W47-B 29W48 L6-30R 29W49 L7-30R 29W74 L14-30R 29W75 29W75-B 29W75-B 29W76-B 29W76-B 29W76-B 29W76-B 29W77-B 29W77-B	-
Yellow EPTR, 30A-250V 2-Pole, 3-Wire Yellow EPTR, 30A-277V 2-Pole, 3-Wire Yellow EPTR, 30A-125/250V 3-Pole, 4-Wire Black EPTR, 30A-3Ø 250V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 480V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR	28W48 L6-30P 28W49 L7-30P 28W74 L14-30P 28W75 28W75-B 28W75-B 28W76-B 28W76-B 28W77-B 28W77-B	29W48 L6-30R 29W49 L7-30R 29W74 L14-30R 29W75 29W75-B 29W75-B 29W76-B 29W76-B 29W76-B 29W77-B 29W77-B	-
2-Pole, 3-Wire Yellow EPTR, 30A-125/250V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 250V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 480V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3ØY 120/208V	28W75 28W75 L15-30P 28W75- 28W76-B 28W76-B 28W76-B 28W77-B 28W77-B	29W74 L14-30R (29W75 L15-30R (29W75-B 29W76-B 29W76-B 29W76-B 29W76-B	-
3-Pole, 4-Wire Yellow EPTR, 30A-3Ø 250V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 480V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3ØY 120/208V	28W75-B 28W76-B 28W76-B 28W76-B 28W76-B 28W76-B 28W77-B 28W77-B	L14-30R (29W75 29W75-B 29W76-B 29W76-B 29W76-B 29W76-B 29W77-B 29W77-B	-
3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 480V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3ØY 120/208V	28W75-B 28W76-B 28W76-B 28W77-B 28W77-B 28W81	29W75-B 29W76-B 29W76-B 29W77-B 29W77-B	-
3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3Ø 600V 3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3ØY 120/208V	28W76-B 28W77-B 28W81	29W76-B 29W77-B 29W77-B	-
3-Pole, 4-Wire Black EPTR Yellow EPTR, 30A-3ØY 120/208V	28W77-B	29W77-B	-
		29W81	
		L21-30R (((O I))	-
Yellow EPTR, 30A-3ØY 277/480V 4-Pole, 5-Wire	28W82 L22-30P	29W82	-
Yellow EPTR, 30A-3ØY 347/600V 4-Pole, 5-Wire	28W83 L23-30P	29W83	-
Wetguard Non-NEMA, Non-Grounding Device	Ces (Not UL Listed-For Repl	acement Use Only)	_
DESCRIPTION	CAT. NO. PLUG	CAT. NO. CONNECTOR	
Yellow EPTR, 30A-125/250V 3-Pole, 3-Wire	28W08 NON-NEMA	29W08 NON-NEMA	-
Yellow EPTR, 30A-3ØY 120/208V 4-Pole, 4-Wire	28W09 NON-NEMA	29W09 NON-NEMA	_
Replacement Closure Cap			
DESCRIPTION	CAT. NO. YELLOW	CAT. NO. BLACK	
Connector Cap for 30A devices Plug Cap for 30A devices	50W54 28W	50W54-B 28W-B	-

Cord Clamp Range—Wetguard® 30A Locking Plugs and Connectors: .625"-1.125" #12-#8 AWG

Wetguard

- · IEC IP66 and IP 67 Rated, in accordance with IEC 529 as evaluated by UL and CSA
- NEMA Type 4, 4X, 6 and 6P Ratings in accordance with UL 50 and CSA 94
- · EPTR rubber parts provide outstanding resistance to wet and damp environments, extreme temperature variations, acids, alkalis, grease, oils and solvents
- · Interlocking "tongue and groove" construction seals out water, moisture, dirt when plugs are mated with connectors
- Multi-point sealing system utilizes nut, strain relief washer and rubber bushing to form a watertight cord grip seal

SPECIFICATIONS AND FEATURES

- · Non-magnetic stainless steel fast-threading assembly screws won't interfere with sensitive equipment
- · Connector "hood" closure cap seals device when not in use

TESTING AND CODE COMPLIANCE

Ø 2.75 (69.9)

29W47-B

- · Meet NEMA WD 1 & 6, ANSI requirements
- UL Listed & meets Fed. Spec. requirements: (File #13393)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated V2 Operating Temperature: -40°C to 60°C

N

LEVITON For answers to technical questions, call Leviton's Techline at 1-800-824-3005

Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.



15 AMP 125V, 250V and 277V

Industrial Grade Corrosion Resistant Devices



52CM-66C





47CM-29C

Cord Clamp Range-15A St. Blade/Locking Plugs and Connectors: .240"-.700" #18-#10 AWG

405V 0 D.1 0.14/2 15

DESCRIPTION	CAT. NO.	NEMA CO	NFIG.	
Straight Blade Plug, Yellow Nylon Body and Cord Clamp	52CM-66C	5-15P	_	_
Straight Blade Connector, Yellow Nylon Body and Cord Clamp	52CM-69C	5-15R		
Duplex Receptacle, Smooth Face. One-Piece Electroless Nickel-Plated Brass Strap	52CM-62	5-15R	5-15P	5-15R
Single Receptacle, Smooth Face, Yellow Nylon Body	5261-CR	5-15R		
Locking Plug, Yellow Nylon Body and Cord Clamp	47CM-20C	L5-15P		65
Locking Connector, Yellow Nylon Body and Cord Clamp	47CM-29C	L5-15R		(G <i>J</i>)
Single Locking Flush Receptacle	47CM-10	L5-15R	L5-15P	L5-15R
15 AMP 250V 2-Pole 3-Wire Grounding 🗓 🚱				
DESCRIPTION	CAT. NO.	NEMA CO	NFIG.	
Single Receptacle, Smooth Face, Yellow Nylon Body	5661-CR	6-15R		
Locking Plug, Yellow Nylon Body and Cord Clamp	45CM-70C	L6-15P	6-15P	6-15R
Locking Connector, Yellow Nylon Body and Cord Clamp	45CM-79C	L6-15R		(\mathbb{N}^{2})
Single Locking Flush Receptacle†	45CM-60	L6-15R	16-15P	16-15R
15 AMP 277V AC 2-Pole 3-Wire Grounding 🕸 🚳				
DESCRIPTION	CAT. NO.	NEMA CO	NFIG.	
Single Locking Flush Receptacle	47CM-60	L7-15R		(C)
			17-15P	L 7-15R

Wallplates and Covers		
302 STAINLESS STEEL FOR 15A/20A ST. BLADE/15A SINGLE LOCKING RECEPTACLE	302 STAINLESS STEEL For 15a/20a ST. Blade DUPLEX RECEPTACLE	WEATHER-RESISTANT FLIP LID COVER FOR 15A/20A ST. BLADE/15A LOCKING DEVICES
1.41" Dia. Opening		IP64 Rated—Includes Gasket and Screws
° O °	0	
84004-40	84003-40	WP1
WETGUARD COVER AND GASKET FOR 15A/20A ST. BLADE/15A LOCKING DEVICES	BLANK PLATE W/GASKET	FD BOX GLASS-FILLED POLYESTER (2 KO OPENINGS)
IP66 Rated		
<u>s</u>		
60W03 Yellow, 60W03-B Black	WP459 Yellow	452CR Yellow 1/2", 453CR Yellow 3/4", 454CR Yellow 1'

For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

Plugs and Connectors

- · All current-carrying metal parts (blades, contacts, terminals and screws) are electroless nickel-coated
- Captive, brass #8 terminal screws are color coded for easy wiring identification: green (ground), brass (hot) and silver (neutral)
- Super tough nylon plug and connector body is bright yellow for easy corrosion resistant identification
- Connector power contacts are heavy-duty, solid, one-piece brass, triple-wipe, set in deep pockets to resist rough use
- Heavy-duty, impact-resistant, super tough ST801 all-nylon body construction; fluted body design provides sure grip
- Wire clamp moves in individual chamber to provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- Plugs and connectors pass the ASTM B117-13 five-hundred hour Salt Spray (Fog) Test with no visible corrosion
- Designed to meet or exceed UL Fed Spec. Listing WC-596. UL Listed (File #E-13399 for Receptacles; File #E-13393 for Plugs and Connectors)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- Meets NEMA WD1 & WD6 requirements
- · NEMA configuration and rating molded on front
- · Backed by a Limited 10-Year Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL 94 Operating Temperature: -40°C (without impact) to 60°C maximum continuous

N

20 AMP 125V, 250V, 277V, 125/250V and 3Ø 250V, 480V

Industrial Grade Corrosion Resistant Devices



Ð (53.0)Ø 2.08 (6

2.47 (63.0)

20 AMP 125V 2-Pole 3-Wire Grounding 🗓 🕮

20 AMP 125V 2-Pole 3-Wire	e Grounding 🖤 🕲					(8)	
DESCRIPTION		CAT. NO		ONFIG.		4 (46.8)	4
Straight Blade Plug, Yellow Nylon E Straight Blade Connector, Yellow N	,					g 1.8	
Duplex Receptacle, smooth face.	yion body and cord	53CM-0				<u> </u>	1 -
One Piece Electroless Nickel-Plate				5-20P	5-20R		2.47 (6
Single Receptacle, Smooth Face, Y		5361-0					23CM-11
Locking Plug, Yellow Nylon Body a		23CM-1			$(C^{\tilde{a}})$	La	1.69 (42.8)
Locking Connector, Yellow Nylon B		23CM- 23CM-		$\mathbf{\bigcirc}$	\bigcirc		0.75
V-0-MAX [®] Single Locking Flush Re			10 L5-20R	L5-20P	L5-20R		
20 AMP 250V 2-Pole 3-Wire	e Grounding 🖤 🕲						1
DESCRIPTION	(allaw Natara Daala	CAT. NO		ONFIG.			
Single Receptacle, Smooth Face, Y	'ellow Nylon Body	5461-0	R 6-20R	6-20P	6-20R	<u>3.63 (92.1)</u> 3.28 (83.3)	0
V-0-MAX [®] Single Locking Flush Re	eceptacle	23CM-2	20 L6-20R	L6-20P	(1-20R		1.
20 AMP 277V AC 2-Pole 3-V	Vire Grounding () ()				_	23CM-10
DESCRIPTION	g -	CAT. NO). NEMA CO	ONFIG.			230IVI-10
V-0-MAX [®] Single Locking Flush Re	eceptacle	23CM-3	30 L7-20R			Cord Clamp I 20A St. Blade	/3-Wire Locki
20 AMP 125/250V 3-Pole 4	-Wire Grounding			L7-20P	L7-20R	Connectors: .2 20A 4-Wire Lo Connectors: .5	ocking Plugs a
DESCRIPTION		CAT. NO					
V-0-MAX [®] Single Locking Flush Re	eceptacle	24CM-1	10 L14-20R			SPECIFIC/ Plugs and Conn • All current-cal	
20 AMP 3Ø 250V 3-Pole 4-V	Vire Grounding () (F .,		L14-20P	L14-20R	 Contacts, term troless nickel- Captive, brass 	niñals and scr coated
DESCRIPTION		CAT. NO				coded for eas (ground), bras	y wiring identi ss (hot) and si
V-0-MAX [®] Single Locking Flush Re	eceptacle	24CM-2	20 L15-20R			 Super tough r body is bright resistant ident 	ylon plug and yellow for eas
20 AMP 3Ø 480V 3-Pole 4-V	Vire Grounding () 🚱		L15-20P	L15-20R	Connector por solid, one-pied deep pockets	ce brass, triple to resist roug
DESCRIPTION		CAT. NO). NEMA CO	ONFIG.		 Heavy-duty, in body construct 	ction; fluted bo
V-0-MAX [®] Single Locking Flush Re	eceptacle	24CM-3	30 L16-20F	R (16-20P	L16-20R	 vides sure grip Wire clamp m provide positiv wire strands 	oves in indivio ve crimp lock
Weather-Resistant Boots for 20A Lo	cking Plugs and Con	nectors are listed	l on page N27				ND CODE CO
Wallplates and Covers						Plugs and co B117-13 five	-hundred ho
302 STAINLESS STEEL 20A SINGLE LOCKING RECEPTACLE	WEATHER-RESISTAN 20A SINGLE LOCKIN	NG RECEPTACLE	WETGUARD CO 20A SINGLE LOC	KING RECE		 (Fog) Test wit Designed to r Spec. Listing 	neet or excee WC-596, UL
1.60" Dia. Opening	IP64 Rated—Includes	7420-CR				#E-13399 for #E-13393 for • CSA Certified • NOM Certifie • Meets NEMA • NEMA config on front • Backed by a	Plugs and C (File #LR-40 d (#057) WD1 & WD6 uration and r
			<u></u>				AL CHARACTE Flammability (® Receptacle
WP459 Yellow		452CR Yellow	1/2", 453CR Yellow 3/4", 4	54CR Yellow 1		impact) to 60°C	maximum co

For complete wallplate selection, see Section E.

nge— -Wire Locking Plugs and

06 (26.8

0"-.700" #18-#10 AWG king Plugs and 5"-.895" #14-#10 AWG

IONS AND FEATURES

Corrosion Resistant Devices

N

ctors

- ing metal parts (blades, als and screws) are elecated
- 8 terminal screws are color wiring identification: green (hot) and silver (neutral)
- on plug and connector ellow for easy corrosion cation
- er contacts are heavy-duty, brass, triple-wipe, set in resist rough use
- pact-resistant, all-nylon on; fluted body design pro-
- es in individual chamber to crimp lock without cutting

D CODE COMPLIANCE

- nectors pass the ASTM undred hour Salt Spray no visible corrosion
- eet or exceed UL Fed /C-596. UL Listed (File Receptacles; File Plugs and Connectors)
- lie #LR-406)
- (#057)
- VD1 & WD6 requirements
- ation and rating molded
 - mited 10-Year Warranty

CHARACTERISTICS

ammability Rated V2 per Receptacles Rated V0 rature: -40°C (without naximum continuous

LEVITON For answers to technical questions, call Leviton's Techline at 1-800-824-3005

Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com




30 AMP 125V, 250V, 125/250V and 3Ø 250V

Industrial Grade Corrosion Resistant Devices




26CM-11



30 AMP 125V 2-Pole 3-Wire Grounding 🏵		
DESCRIPTION	CAT. NO.	NEMA CONFIG.
Locking Plug, Yellow Nylon Body and Cord Clamp	26CM-11	L5-30P
Locking Connector, Yellow Nylon Body and Cord Clamp	26CM-13	L5-30R (いり) (いり
V-0-MAX [®] Single Locking Flush Receptacle	26CM-10	L5-30R L5-30P L5-30R
30 AMP 250V 2-Pole 3-Wire Grounding 🞚 🖲		
DESCRIPTION	CAT. NO.	NEMA CONFIG.
Locking Plug, Yellow Nylon Body and Cord Clamp	26CM-21	L6-30P
Locking Connector, Yellow Nylon Body and Cord Clamp	26CM-23	L6-30R () (C)
Single Locking Flush Receptacle	26CM-20	L6-30R L6-30P L6-30R
30 AMP 125/250V 3-Pole 4-Wire Grounding 🛞 🔇	₽ ∘	
DESCRIPTION	CAT. NO.	NEMA CONFIG.
V-0-MAX® Single Locking Flush Receptacle	27CM-10	L14-30R
30 AMP 3Ø 250V 3-Pole 4-Wire Grounding 🕲	0	
DESCRIPTION	CAT. NO.	NEMA CONFIG.
	27CM-20	L15-30R

Weather-Resistant Boots for 30A Locking Plugs and Connectors are listed on page N27

Cord Clamp Range—30A 3-Wire Locking Plugs and Connectors: .385"-.860" #16-#8 AWG 30A 4-Wire Locking Plugs and Connectors: .595"-1.150" #14-#8 AWG



For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

Plugs and Connectors

(hot) and silver (neutral)

Captive, brass #8 terminal screws are color coded

Nylon plug and connector body is bright yellow for easy corrosion resistant identification

easy wiring identification: green (ground), brass

- · Connector power contacts are heavy-duty, solid, one-piece brass, triple-wipe, set in deep pockets to resist rough use All current-carrying metal parts (blades, contacts, terminals and screws) are electroless nickel-coated
 - Heavy-duty, impact-resistant, all-nylon body con-struction; fluted body design provides sure grip
 - · Wire clamp moves in individual chamber to provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- Plugs and connectors pass the ASTM B117-13 fivehundred hour Salt Spray (Fog) Test with no visible corrosion
- · Designed to meet or exceed UL Fed Spec. Listing WC-596. UL Listed (File #E-13399 for Receptacles; File #E-13393 for Plugs and Connectors)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- Meets NEMA WD1 & WD6 requirements
- · NEMA configuration and rating molded on front
- · Backed by a Limited 10-Year Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94, V-O-MAX[®] Receptacles Rated V0

Operating Temperature: -40°C (without impact) to 60°C maximum continuous

N

LEVITON® To learn more about Leviton's outstanding offering of devices visit our Website at: www.leviton.com

222000 Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.com

50 AMP 125V, 125/250V



Industrial Grade Corrosion Resistant Devices

50 AMP 125V 2-Pole 3-Wire Grounding 🚇 🏵

BLACK

DESCRIPTION	CAT. NO.	NEMA CONFIG.	
Locking Plug, Yellow Nylon Body and Cord Clamp	6361-CR	\frown	
Locking Connector, Yellow Nylon Body and Cord Clamp	6360-CR		
Single Locking Flush Receptacle	6370-CR		
Power Inlet, 316 Stainless Steel w/Threaded Cap	6372-CR		4.97 (126.2)
50 AMP 125/250V 3-Pole 4-Wire Grounding 🛞 🔇	₽ ∞		≤ 6364-CR
DESCRIPTION	CAT. NO.	NEMA CONFIG.	
Locking Plug, Yellow Nylon Body and Cord Clamp	6365-CR		Contract in the second
Locking Connector, Yellow Nylon Body and Cord Clamp	6364-CR		× 4
Single Locking Flush Receptacle	6369-CR		
Power Inlet, 316 Stainless Steel w/Threaded Cap	6374-CR		
Boots and Covers for 50 AMP Corrosion Resistant	Devices		
DESCRIPTION	CAT. NO.		
50A Locking Plug Boot, High Visibility Yellow	7715-CRY		
50A Locking Plug Boot, Black	7715-CR		7788-CR
50A Locking Connector Boot, High Visibility Yellow	7717-CRY		
50A Locking Connector Boot, High Visibility Yellow	7717-CR		
Weather-Resistant Receptacle Flip Lid Cover, IP64 rated, Yellow Lexan	7788-CR		
Cast Aluminum Grey Flip Lid Cover, IP64 rated	7770		

Cord Clamp Range—50A CR Locking Plugs and Connectors: .650"-1.125" #10-#4 AWG

SPECIFICATIONS AND FEATURES

- · All current-carrying metal parts (blades, contacts, terminals and screws) are electroless nickel-coated
- · Color coded wire entrance holes for simple and easy wiring
- · Nylon plug and connector body are bright yellow for easy corrosion resistant identification
- Nylon housing for excellent impact resistance and secure gripping
- · Boots are IP55 Rated

- · Longer contacts inside connector assure stronger, tighter fitting contact points
- · Backed by a lifetime warranty
- · External cord clamp with cable insert accomodates from smallest to largest wire size
- · Covers are IP64 rated for wet location with cover closed

TESTING AND CODE COMPLIANCE

- NOM Certified (#057)
- CSA Certified (File# 152105)
- Receptacles
- UL Listed (File #E-111198)
- Plugs & Connectors and Inlets
- UL Listed (File #E-57672)

MATERIAL CHARACTERISTICS

Operating Temperature: -40°C to 75°C

LEVITON

N

For answers to technical questions, call Leviton's Techline at 1-800-824-3005 .2.3 Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering



15 AMP 125V/10A-250; 20 AMP 250V, 125/250V and 3ØY 120/208V

Industrial Grade Non-NEMA Locking Devices





7310-B





Cord Clamp Range

Non-NEMA Locking Plugs and Connectors— 15A: .240"-.700" #18-#10 AWG 20A 3-Wire: .385"-.780" #16-#10 AWG 20A 4- & 5-Wire: .595"-.895" #14-#10 AWG

15 AMP 125V/10A-250V 3-Pole 3-Wire Non-Grounding Non-NEMA†

DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Flush Receptacle†	7582	
Locking Plug	7567-C*	
Locking Connector†	7565-C*	NON-
Locking Flanged Inlet	7556	
Locking Flanged Outlet	7557	

¹These devices are no longer UL Listed and are for replacement use only. Add (-G) for grounding version. *Grounding (-G) version not available. For grounding connector, use Cat. No. 7555-G

"Grounding (-G) version not available. For grounding connector, use Cat. N **Uses stainless steel wallplate, Cat. No. 84004-40.

20 AMP 250V AC/DC / 10 AMP 600V AC 4-Pole 5-Wire Grounding Non-NEMA

			•
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.	
Single Flush Receptacle	3520		
Locking Plug, Black Nylon Body	3521-C		
Locking Connector, Black Nylon Body	3523-C	NON- NEMA	NON- NEMA
Locking Flanged Inlet	3524-C		
Locking Flanged Outlet	3525-C		

20 AMP 125V/250V 3-Pole 3-Wire Non-Grounding Non-NEMA††

DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.	
Single Flush Receptacle	7310-В		
Locking Plug	9965-C		()×5)
Locking Connector	7314-C	NON-	NON-
Locking Flanged Inlet	3325-C		
Locking Flanged Outlet	3326-C		


20 AMP 3ØY 120V/208V 4-Pole 4-Wire Non-Grounding Non-NEMA††

	3	
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Flush Receptacle	7410-B	
Locking Plug	7411-C	NON- NEMA
Locking Connector	7413-C	
Locking Flanged Inlet	7408-C	NON-
Locking Flanged Outlet	7409-C	NEMA
tt Effective July 1 1081 rating for non-grounding vers	ions was changed from 20A-250V AC/D	C 10A-600V AC to comply with

⁺⁺Effective July 1, 1981, rating for non-grounding versions was changed from 20A-250V AC/DC, 10A-600V AC to comply with UL requirements. Add (-G) for grounding devices: (-G) devices are rated 20A-250V AC/DC, 10A-600V AC and are no longer UL Listed — for replacement use only.

Weather-Resistant Boots for 15A and 20A Locking Plugs and Connectors are listed on page N27

Wallplates and Covers



For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

Locking Flush Receptacles

- Rugged nylon body and cover for outstanding resistance to impact and harsh chemicals
- Double-wipe phosphor-bronze power contacts

Locking Plugs and Connectors

- Super tough Nylon body resists damage from severe impact, abrasion and chemicals
- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
 Cord clamp does not have to be disassembled from
- Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
 One-piece, rivetless .035" thick brass connector
- One-piece, rivetiess. U35" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long service life

Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- Wire clamps provide positive crimp lock without cutting wire strands

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- Most non-NEMA locking devices are not UL Listed and are intended for replacement use only. Consult your Leviton representative for more information on UL Listing for Non-NEMA devices
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94 Operating Temperature: -40°C to 60°C

Locking Devices

N



Industrial Grade Non-NEMA Locking Devices

30 AMP 125V/250 3-Pole 3-Wire Non-Grounding Non-NEMA†

BLACK & WHITE

DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Flush Receptacle	3330	
Locking Plug	3331-C	
Locking Connector	3333-C	
Locking Flanged Inlet	3334-C	NON-NEMA
Locking Flanged Outlet	3335-C	

*Effective July 1, 1981, rating for non-grounding versions was changed from 30A-250V to comply with UL requirements. Add (-G) for grounding devices: (-G) devices are rated 30A-250V and are no longer UL Listed - for replacement use only.

30 AMP 3ØY 120V/208V 4-Pole 4-Wire Non-Grounding Non-NEMA††

	J	
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Flush Receptacle	3430	
Locking Plug	3431-C	
Locking Connector	3433-C	
Locking Flanged Inlet	3434-C	NON-NEMA
Locking Flanged Outlet	3435-C	

th Effective July 1, 1981, rating for non-grounding versions was changed from 30A-250V AC/DC, 30A-600V AC to comply with UL requirements. Add (-G) for grounding devices: (-G) devices are rated 30A-250V AC/DC, 30A-600V AC and are no longer UL Listed—for replacement use only.

50 AMP 250V DC/600V AC 2-Pole 3-Wire Grounding Non-NEMA 🖤 🏵

	<u> </u>		
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.	
Single Locking Receptacle	3771	\frown \frown	
Locking Plug	3763-C	GR W	
Locking Connector	3762-C		
Locking Flanged Inlet	3777	NON-NEMA	
CO AND DECK DECK OON AC 2 Date & Wire Cremeting New NEMA IN C			

DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
50 AMP 250V DC/600V AC 3-Pole 4-Wire Grounding	Non-NEMA	

Single Locking Receptacle	7379*	$ \frown $
Locking Plug	7765-C*	$\begin{pmatrix} \hat{r} \\ \hat{r} \end{pmatrix} \begin{pmatrix} z_0 \end{pmatrix}$
Locking Connector	7764-C*	
Locking Flanged Inlet	7958*	NON-NEMA
	-	-

50 AMP 250V DC/600V AC 3-Pole 4-Wire Grounding Non-NEMA 🕲 🏵 DESCRIPTION CAT. NO. NON-NEMA CONFIG. Single Locking Receptacle 3769

Locking Plug	3765-C	
Locking Connector	3764-C	GR Z Z
Locking Flanged Inlet	3775	NON-NEMA
Weather Desistant Poets for 201 Locking Dlugs	and Connectors are listed on page	N27

Weather Resistant Boots for 30A Locking Plugs and Connectors are listed on page N27. Weather Resistant Boots for 50A Locking Plugs and Connectors are listed on page N23.

Wallplates and Covers

WEATHER-RESISTANT FLIP LID COVER FOR 30A INLETS AND OUTLETS AND 30A RECEPTACLES	WEATHER-RESISTANT FLIP LID COVER FOR 50A RECEPTACLES
IP64 Rated—Includes Gasket and Screws	IP64 Rated—Includes Gasket and Screws
WP2 for Inlets/Outlets 7420-CR for Receptacles	7788-CR Yellow Lexan 7770 Gray Metal
For complete wellplate calection, can Section F	· · · · · · · · · · · · · · · · · · ·


For complete wallplate selection, see Section E. * For replacement use in existing installations only.

SPECIFICATIONS AND FEATURES

- **30A Locking Flush Receptacles**
- Rugged nylon body and cover for outstanding resist ance to impact and harsh chemicals
- Double-wipe phosphor-bronze power contacts
- **30A Locking Plugs and Connectors**
- Super tough Nylon body resists damage from severe impact, abrasion and chemicals
- Ergonomic, fluted body design with radial grip ridge is ideal for gripping, turning and pulling
- Cord clamp does not have to be disassembled from body for wiring—accepts all wire mesh strain reliefs
- One-piece, rivetless .035" thick brass connector contacts and solid brass plug blades provide maximum conductivity and long service life

30A Flanged Inlets and Outlets

- Rugged nylon flange fits flush and won't crack in high-abuse applications
- Individual deep-funneled chamfered wire wells guide each wire into rectangular chambers
- Wire clamps provide positive crimp lock without cutting wire strands
- **50A Locking Plugs and Connectors**
- · Nylon housing for excellent impact and chemical resistance
- 50A Locking Receptacles and Flanged Inlets
- Heavy-duty Nylon construction for excellent impact and chemical resistance
- · Clamp-type wire terminals





3331-C



Ocking Devices

.25

Cord Clamp Range Non-NEMA Locking Plugs and Connectors 30A 3-Wire: .385"-.860" #16-#8 AWG 30A 4-Wire: .595"-1.150" #14-#10 AWG

50A 4-Wire: .650"-1.20" #10-#4 AWG

STING AND CODE COMPLIANCE

- ceptacles, plugs, connectors, inlets buildes and ansi C-73, and to /exceed UL 498 standards
- non-NEMA locking devices are not sted and are intended for replaceuse only. Consult your Leviton representative for more information on UL Listing for Non-NEMA devices

50A Devices

D)

- UL Listed Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles (File #F-13399)
- CSA Certified (File #LR-81290
- NOM certified (#057)

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated VO per UL94 Operating Temperature: 30A Devices: -40°C to 60°C 50A Devices: -40°C to 75°C



50 AMP 125V, 250V, 125/250V, 480V and 3Ø 480V

Industrial Grade "California Style" CS Non-NEMA Locking Devices





2.12 (53.8) 0.63 3.28 (83.3) Ø 1.98 (50.3) (22.6)CS83-69

Locking Devices

SPECIFICATIONS AND FEATURES

50A CS Locking Plugs and Connectors · Nylon housing for excellent impact resistance and secure gripping

· Color-coded wire entrance holes for simple, easy wiring

50A CS Locking Receptacles and Flanged Inlets

- Heavy-duty nylon construction for excellent impact and chemical resistance
- · Clamp-type wire terminals

TESTING AND CODE COMPLIANCE

- UL Listed Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles (File #E-13399)
- CSA Certified (File #LR-15105)
- NOM Certified (#057)

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated VO per UL94 Operating Temperature: -40°C to 75°C

50 AMP 125V 2-Pole 3-Wire Grounding Non-NEMA	. ⊕ € ∘	BLACK & WHITE DIDUSTRIAL GRADE PLUGS & CONNECTORS
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Locking Receptacle	CS63-70	\bigcirc
Locking Plug	CS63-61C	
Locking Connector	CS63-60C	
Locking Flanged Inlet	CS63-77	NON-NEMA
50 AMP 250V 2-Pole 3-Wire Grounding Non-NEMA		
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Locking Receptacle	CS82-69	
Locking Plug	CS82-65C	
Locking Connector	CS82-64C	
Locking Flanged Inlet	CS82-75	NON-NEMA
50 AMP 125/250V 3-Pole 4-Wire Grounding Non-M	IEMA 🖫 🏵	
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Locking Receptacle	CS63-69	
Locking Plug	CS63-65C	
Locking Connector	CS63-64C	G
Locking Flanged Inlet	CS63-75	NON-NEMA
50 AMP 3Ø 250V AC 3-Pole 4-Wire Grounding Non	-NEMA 🗓 🏵	
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Locking Receptacle	CS83-69	
Locking Plug	CS83-65C	
Locking Connector	CS83-64C	G Z Z G
Locking Flanged Inlet	CS83-75	NON-NEMA
50 AMP 480V 2-Pole 3-Wire Grounding Non-NEMA		
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Locking Receptacle	CS84-69	
Locking Plug	CS84-65C	(▲ ○ ▲ ×) (×(〔 ● [∞])
Locking Connector	CS84-64C	
Locking Flanged Inlet	CS84-75	NON-NEMA
50 AMP 3Ø 480V AC 3-Pole 4-Wire Grounding Non	I-NEMA 🗓 🚱	
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Locking Receptacle	CS81-69	
Locking Plug	CS81-65C	(() ×) (×(())
Locking Connector	CS81-64C	
Locking Flanged Inlet	CS8175	NON-NEMA
Weather Resistant Boots for 50A Locking Plugs and Connectors	are listed on page	N23

nt Boots for 50A locking Plugs and Connectors are listed on page N23

Cord Clamp Range—50A CS Locking Plugs and Connectors: .680"-1.125" #10-#4 AWG

Wallplates and Covers

WEATHER-RESISTA For 50A Re			
IP64 Rated—Include:	s Gasket and Screws		
7788-CR Yellow Lexan	7770 Gray Metal		
		-	

For complete wallplate selection, see Section E.



To learn more about Leviton's outstanding offering of devices visit our Website at: www.leviton.com

WEATHER-RESISTANT BOOTS

Industrial Grade Locking Devices

Locking Plug and Connector Boots—Thermoplastic Elastomer Construction

Boots for 15 AMP Industrial Locking Plugs and Connectors

DESCRIPTION	CAT. NO.
Locking Plug Boot, Black	6017-L
Locking Plug Boot, High-Visibility Yellow	6017-LY
Locking Connector Boot, Black	6018-L
Locking Connector Boot, High Visibility Yellow	6018-LY

Boots for 3-Wire 20 AMP & 30 AMP Industrial Locking Plugs and Connectors DESCRIPTION CAT. NO. 3-wire Locking Plug Boot, Black 6031 3-wire Locking Plug Boot, High Visibility Yellow 6031-Y 3-wire Locking Connector Boot, Black 6032 3-wire Locking Connector Boot, High Visibility Yellow 6032-Y

Boots for 4 and 5-Wire 20 AMP & 30 AMP Industrial Locking Plugs and Connectors

DESCRIPTION	CAT. NO.
4 & 5-wire Locking Plug Boot, black	6033
4 & 5-wire Locking Plug Boot, High Visibility Yellow	6033-Y
4 & 5-wire Locking Connector Boot, black	6034
4 & 5-wire Locking Connector Boot, High Visibility Yellow	6034-Y

For Weather-Resistant Boots for 50A Locking Plugs and Connectors see page N23









SPECIFICATIONS AND FEATURES

- Feature a triple seal action to protect straight blade and locking plugs and connectors against dirt and moisture in harsh applications
- Plug and connector boots available in black and high-visibility yellow
- Fluted surface and grip-ring design provide a non-slip grip even in wet conditions

WARRANTY

· Backed by a Limited Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability, Rated HB Operating Temperature: -40°C to 90°C



For answers to technical questions, call Leviton's Techline at 1-800-824-3005 LEVITON® Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering.



20 AMP 125V and 30A-600VAC / 20 AMP-250V DC

Industrial Grade Locking Power Interrupting Devices—Non-NEMA



20 AMP 125V 2-Pole 3-Wire Grounding D 🖲

DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Flush Receptacle with a Thermoset body	23000-HG*	
Locking Connector	23001-HG*	
Locking Plug	23004-HG*	RECEPTACLE

DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Flush Receptacle	23030	
Locking Connector	23031-A	
Locking Plug	23034-A	RECEPTACLE
	0	

<u>30A-600VAC / 20AMP – 250V DC 3-Pole 4-Wir</u>	re Grounding 🖤	
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Flush Receptacle	20403	
Locking Connector	21414-B	
Locking Plug	21415-B	RECEPTACLE

30A-600VAC / 20AMP – 250V DC 4-Pole 5-Wire Grounding		
DESCRIPTION	CAT. NO.	NON-NEMA CONFIG.
Single Receptacle with Fiberglass Reinforced Nylon Interior with Cast Iron and Steel Shell. Fits FS or FD boxes	25403	
Locking Connector	25414-B	
Locking Plug	25415-B	RECEPTACLE

For complete wallplate selection, see Section E.

N



15 AMP 125V and 125/250V



Industrial Grade Midget Locking Devices



SPECIFICATIONS AND FEATURES

- · Offer a smaller form factor for limited-space applications
- Locking Plugs and Connectors feature heavy-duty construction for top performance in the environ-mental extremes of grueling industrial settings
- · Flanged Inlets and Outlets are built to endure hard use with rugged nylon flanges that assure a smooth, flush fit and outstanding resistance to cracking and breaking

TESTING AND CODE COMPLIANCE

- All receptacles, plugs, connectors, inlets and outlets are designed to meet NEMA WD-6, and ANSI C-73, and to meet/exceed UL 498 standards
- UL Fed. Spec. Listed WC-596 Plugs, Connectors and Flanged Inlets (File #E-13393), Receptacles and Flanged Outlets (File #E-13399)
- CSA Certified (File No. LR-406)
- NOM Certified (#057)
- · Backed by a Lifetime Warranty

MATERIAL CHARACTERISTICS

Environmental: Flammability Rated V2 per UL94 Operating Temperature: -40°C to 60°C


N

For answers to technical questions, call Leviton's Techline at 1-800-824-3005 LEVITON


.29 Courtesy of Steven Engineering, Inc. • 230 Ryan Way, South San Francisco, CA 94080-6370 • General Inquiries: (800) 670-4183 • www.stevenengineering




Industrial Grade Locking Devices



4792



4715-FWP



4716-FWP

2.84 (72.2

Combination Locking and Straight Blade Duplex Receptacle

15 AMP 125V 2-Pole 3-Wire Grounding Back and Side Wired 🖲 🏵

DESCRIPTION	CAT. NO.	NEMA CONFIG.
Duplex Combination Locking & Straight Blade Receptacle with Common Feed	4792	L5-15R
Duplex Combination Locking & Straight Blade Receptacle with 2 Hot Feeds, 1 Neutral Return	4794-1R	
Duplex Combination Locking & Straight Blade Receptacle with Split Feed — 2 Hot Feeds, 2 Neutral Returns	4795-2R	5-15R

Integrated Power Inlets and Outlets with Weather-Resistant Covers


- Engineered to IP 64 and NEMA 3R Protection Ratings
- Suitable for Industrial Indoor and Outdoor Use

Integrated Power Inlets and Outlets with Weather-Resistant Covers (1) (Gray, Glass-Filled Thermoplastic Cover and White, Nylon Device



Note: For straight blade configurations, please see page M7.

Wallplates



For complete wallplate selection, see Section E.

SPECIFICATIONS AND FEATURES

Combination Devices

- Impact-resistant black thermoplastic nylon face and body
 Smooth face does not collect dirt
- Smooth face does not collect dirt
- Large, triple-wipe brass "T" contacts for superior contact and conductivity
- Triple-combination terminal screws
- Back and side wire options accept #10–#14 AWG stranded or solid wire

Integrated Devices

- Glass-filled thermoplastic cover and plate provide outstanding impact resistance and durability
- Dual gaskets, one under plate and one under lid, for weather-resistant fit
- Stainless steel external hardware resists corrosive effects of moisture
- Large thumb-tab makes it easy to open cover with gloved hand
- Mounts to panels or FS/FD boxes
- UL Listed and CSA Certified for wet locations with cover closed

TESTING AND CODE COMPLIANCE

Combination Devices

- UL Listed (File #E-13393)
- CSA Certified (File #LR-406)
- NOM Certified (#057)
- Backed by a Limited 10-Year Warranty

Integrated Devices

- UL Listed (File #E-13397)
- CSA Certified (File #LR-16347)
- NOM Certified (#057)
- IP 64 Suitability Rating (protected against dust and splashing water)
- NEMA Type 3R Enclosure Rating when properly installed (protected against rain, sleet and damage from external ice formations)
- Backed by a Limited 2-Year Warranty

MATERIAL CHARACTERISTICS

Combination Devices

Environmental: Flammability, Rated V2

Operating Temperature: -40°C (without impact) to 60°C maximum continuous

Integrated Devices

Environmental: VO Flammability Rating per UL 94 Operating Temperature: -40°C to 60°C

Locking Devices