



Straight Blade Receptacles

Pass & Seymour



PlugTail™. The fastest, most consistent and reliable wiring devices – ever! Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. The connector simply snaps into the back of the device – no preparing, stripping or looping conductors, no exposed terminals to tighten or tape, and no mistakes mean no costly callbacks! Now device installation is a snap!



Device	Rating	Page Number
PlugTail™ Extra Heavy-Duty Receptacles	15 & 20A, 125V	B-2 – B-5
Extra Heavy-Duty Hospital Grade Receptacles	15 & 20A, 125V; 20A, 250V	B-6, B-7
Heavy-Duty Hospital Grade Receptacles	15 & 20A, 125V; 20A, 250V	B-8, B-9
Industrial Extra Heavy-Duty Specification Grade Receptacles	15 & 20A, 125 & 250V	B-10, B-11
Heavy-Duty Specification Grade Receptacles	15 & 20A, 125 & 250V	B-12
PlugTail™ Specification Grade Receptacles	15 & 20A, 125V	B-13
Hard Use Specification Grade Receptacles	15A, 125, 125/250 & 250V; 20A, 125 & 125/250V	B-14
Construction Specification Grade Receptacles	15 & 20A, 125V	B-15, B-16
Commercial Specification Grade Receptacles	15 & 20A, 125V	B-17
Hospital & Specification Grade Single Receptacles	15 & 20A, 125 & 250V	B-18 – B-20
Tamper-Resistant Receptacles	15 & 20A, 125V	B-21 – B-24
Weather-Resistant Receptacles	15 & 20A, 125 & 250V	B-25
Isolated Ground Receptacles	15 & 20A, 125V; 20A, 250V	B-26
PlugTail™ Decorator Receptacles	15 & 20A, 125V	B-27
Hospital & Specification Grade Decorator Receptacles	15 & 20A, 120/125, 125 & 250V	B-28 – B-31
TradeMaster® Tamper-Resistant Receptacles	15A, 125V	B-32, B-33
Weather-Resistant Receptacles	15A, 125V	B-34
TradeMaster® Receptacles	15A, 125V	B-35, B-36
TradeMaster® Decorator Hallway Lights & Combinations	15A, 120/125VAC	B-37
Recessed TV Boxes		B-38
Specification & Hospital Grade GFCI Receptacles	15 & 20A, 125VAC	B-39 – B-43
Decorator Combination GFCI Receptacles	15A, 125VAC	B-44, B-45
Weather-Resistant & DuraShield™ GFCI Receptacles	15 & 20A, 125VAC	B-46, B-47
PlugTail™ GFCIs	15 & 20A, 125VAC	B-48 – B-51
TVSS Hospital & Specification Grade Receptacles	15 & 20A, 125VAC	B-52, B-53
Quad Receptacles & Specifications & Accessories	15 & 20A, 125V	B-54, B-55
Dust & Moisture Resistant & Clock Hanger Receptacles	15 & 20A, 125V	B-56
Power Outlet Receptacles & Plugs	20, 30, 50 & 60A	B-57 – B-59
Miscellaneous Configurations		B-60
Power & TVSS Strips & Device Specifications		B-61, B-62

Pass & Seymour



Straight Blade Receptacles PlugTail™ Extra Heavy-Duty Specification Grade Receptacles

Auto-ground clip
assures positive ground.

Two drive screws anchor strap
to back body and face.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.


Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

No exposed terminals create a finger-safe application before, during, and after installation.


Large crimped and welded brass contacts snugly terminate on device blade terminals.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.



PT5362AW




Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Straight Blade Receptacles


PlugTail™ Extra Heavy-Duty Specification Grade Receptacles

15 & 20A, 125V



Pass & Seymour



PT5362AW



PTTR63W



PTR66STR PTR66STRBP PTR66STRG

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL UL498	FSUL WC596
Duplex Receptacles					
PT5262AI	15 125	Ivory	5-15R	•	•
PT5262AW	15 125	White	5-15R	•	•
PT5262A	15 125	Brown	5-15R	•	•
PT5262AGRY	15 125	Gray	5-15R	•	•
PT5262ABK	15 125	Black	5-15R	•	•
PT5262ABL	15 125	Blue	5-15R	•	•
PT5262ARED	15 125	Red	5-15R	•	•
PT5262ALA	15 125	Light Almond	5-15R	•	•
PT5362AI	20 125	Ivory	5-20R	•	•
PT5362AW	20 125	White	5-20R	•	•
PT5362A	20 125	Brown	5-20R	•	•
PT5362AGRY	20 125	Gray	5-20R	•	•
PT5362ABK	20 125	Black	5-20R	•	•
PT5362ABL	20 125	Blue	5-20R	•	•
PT5362ARED	20 125	Red	5-20R	•	•
PT5362ALA	20 125	Light Almond	5-20R	•	•
Tamper-Resistant Duplex Receptacles					
PTTR62I	15 125	Ivory	5-15R	•	•
PTTR62W	15 125	White	5-15R	•	•
PTTR62	15 125	Brown	5-15R	•	•
PTTR62GRY	15 125	Gray	5-15R	•	•
PTTR62BK	15 125	Black	5-15R	•	•
PTTR62BL	15 125	Blue	5-15R	•	•
PTTR62RED	15 125	Red	5-15R	•	•
PTTR62LA	15 125	Light Almond	5-15R	•	•
PTTR63I	20 125	Ivory	5-20R	•	•
PTTR63W	20 125	White	5-20R	•	•
PTTR63	20 125	Brown	5-20R	•	•
PTTR63GRY	20 125	Gray	5-20R	•	•
PTTR63BK	20 125	Black	5-20R	•	•
PTTR63BL	20 125	Blue	5-20R	•	•
PTTR63RED	20 125	Red	5-20R	•	•
PTTR63LA	20 125	Light Almond	5-20R	•	•

Catalog Number	Wire Type	Wire Length
PlugTail Connectors – Right Angle		
PTRA6SOL	Solid	6"
PTRA6STR	Stranded	6"
PTRA6SOLB25	Solid	25"
PTRA6STRB25	Stranded	25"
PlugTail Connectors – Right Angle with WAGO Connectors		
PTRA6SOLBP	Solid	6"
PTRA6STRBP	Stranded	6"
PlugTail Connectors – Right Angle with Ground Screw		
PTRA6SOLG	Solid	6"
PTRA6STRG	Stranded	6"

All Plugtail Connectors are available in any wire length up to 25 inches, use Configurables Solutions to order.


Configurable Solutions and Metal Box Kits for PlugTail Receptacles and Connectors, see Pages U-1–U-3.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Straight Blade Receptacles

PlugTail™ EHD Specification Grade Receptacles

Pass & Seymour



PT8300W



PTTR63HW



2 Pole, 3 Wire

NEMA
5-15RNEMA
5-20R

Straight Blade Receptacles PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles

15 & 20A, 125V

Features

- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	FSUL WC596
Duplex Receptacles					
PT8200I	15 125	Ivory	5-15R	•	•
PT8200W	15 125	White	5-15R	•	•
PT8200	15 125	Brown	5-15R	•	•
PT8200GRY	15 125	Gray	5-15R	•	•
PT8200BK	15 125	Black	5-15R	•	•
PT8200BL	15 125	Blue	5-15R	•	•
PT8200RED	15 125	Red	5-15R	•	•
PT8200LA	15 125	Light Almond	5-15R	•	•
PT8300I	20 125	Ivory	5-20R	•	•
PT8300W	20 125	White	5-20R	•	•
PT8300	20 125	Brown	5-20R	•	•
PT8300GRY	20 125	Gray	5-20R	•	•
PT8300BK	20 125	Black	5-20R	•	•
PT8300BL	20 125	Blue	5-20R	•	•
PT8300RED	20 125	Red	5-20R	•	•
PT8300LA	20 125	Light Almond	5-20R	•	•
Tamper-Resistant Duplex Receptacles					
PTTR62HI	15 125	Ivory	5-15R	•	•
PTTR62HW	15 125	White	5-15R	•	•
PTTR62H	15 125	Brown	5-15R	•	•
PTTR62HGRY	15 125	Gray	5-15R	•	•
PTTR62HBK	15 125	Black	5-15R	•	•
PTTR62HBL	15 125	Blue	5-15R	•	•
PTTR62HRED	15 125	Red	5-15R	•	•
PTTR62HLA	15 125	Light Almond	5-15R	•	•
PTTR63HI	20 125	Ivory	5-20R	•	•
PTTR63HW	20 125	White	5-20R	•	•
PTTR63H	20 125	Brown	5-20R	•	•
PTTR63HGRY	20 125	Gray	5-20R	•	•
PTTR63HBK	20 125	Black	5-20R	•	•
PTTR63HBL	20 125	Blue	5-20R	•	•
PTTR63HRED	20 125	Red	5-20R	•	•
PTTR63HLA	20 125	Light Almond	5-20R	•	•

For PlugTail Connectors, see Page B-3.

Configurable Solutions and Metal Box Kits for PlugTail Receptacles and Connectors, see Pages U-1-U-3.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Straight Blade Receptacles

PlugTail™ Extra Heavy-Duty

Hospital Grade Illuminated Receptacles

15 & 20A, 125V

Pass & Seymour



PT8300ILLA




Illuminated face indicates power to receptacle and makes it easy to identify receptacle in dark applications.

Features

- Molded-in "IL" markings on face of product.
- Illuminated face indicates power to receptacle and makes it easy to identify receptacle in dark applications.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	FSUL WC596
Illuminated Duplex Receptacles					
PT8200ILI	15 125	Ivory	5-15R	•	•
PT8200ILW	15 125	White	5-15R	•	•
PT8200ILGRY	15 125	Gray	5-15R	•	•
PT8200ILBK	15 125	Black	5-15R	•	•
PT8200ILRED	15 125	Red	5-15R	•	•
PT8200ILLA	15 125	Light Almond	5-15R	•	•
PT8300ILI	20 125	Ivory	5-20R	•	•
PT8300ILW	20 125	White	5-20R	•	•
PT8300IL	20 125	Brown	5-20R	•	•
PT8300ILGRY	20 125	Gray	5-20R	•	•
PT8300ILBK	20 125	Black	5-20R	•	•
PT8300ILRED	20 125	Red	5-20R	•	•
PT8300ILLA	20 125	Light Almond	5-20R	•	•

2 Pole, 3 Wire



For PlugTail Connectors, see Page B-3.

Configurable Solutions and Metal Box Kits for PlugTail Receptacles and Connectors, see Pages U-1-U-3.

Features

- Ensures proper connections and power presence at both rough-in and device-out stages during P&S PlugTail Device installation.
- Fast, easy identification of circuit connections.
- Easy-to-see indicator lights.
- Sturdy construction for long-term dependability.
- Helps prevent call backs.
- Ensures proper wiring.


Catalog Number	Description
P&S PlugTail™ Tester	
PTTESTER	Red PlugTail Tester for Receptacles and Tails




PTTESTER

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



8300I



8300ILI

Straight Blade Receptacles Extra Heavy-Duty Hospital Grade Receptacles

15 & 20A, 125V; 20A, 250V

Features

- One-piece nickel-plated brass mounting strap with integral ground.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.
- Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External nickel-plated screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 – #10 AWG stranded or solid copper clad conductors.
- Auto-ground clip assures positive ground.
- Illuminated version features exclusive LED lamp with solder connection for long durable life (10-12 years).

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 C22.2 No. 42
Duplex Receptacles Back & Side Wire						
8200I	15 125	Ivory	5-15R	•	•	•
8200W	15 125	White	5-15R	•	•	•
8200	15 125	Brown	5-15R	•	•	•
8200GRY	15 125	Gray	5-15R	•	•	•
8200BK	15 125	Black	5-15R	•	•	•
8200RED	15 125	Red	5-15R	•	•	•
8200LA	15 125	Light Almond	5-15R	•	•	•
8300I	20 125	Ivory	5-20R	•	•	•
8300W	20 125	White	5-20R	•	•	•
8300	20 125	Brown	5-20R	•	•	•
8300GRY	20 125	Gray	5-20R	•	•	•
8300BK	20 125	Black	5-20R	•	•	•
8300RED	20 125	Red	5-20R	•	•	•
8300LA	20 125	Light Almond	5-20R	•	•	•
8800I	20 250	Ivory	6-20R	•	•	•
8800W	20 250	White	6-20R	•	•	•
8800	20 250	Brown	6-20R	•	•	•
8800GRY	20 250	Gray	6-20R	•	•	•
8800BK	20 250	Black	6-20R	•	•	•
8800LA	20 250	Light Almond	6-20R	•	•	•
8800RED	20 250	Red	6-20R	•	•	•
LED Illuminated Face Duplex Receptacles Back & Side Wire						
8200ILI	15 125	Ivory	5-15R	•	•	•
8200ILRED	15 125	Red	5-15R	•	•	•
8200ILW	15 125	White	5-15R	•	•	•
8300ILI	20 125	Ivory	5-20R	•	•	•
8300ILRED	20 125	Red	5-20R	•	•	•
8300ILLA	20 125	Light Almond	5-20R	•	•	•
8300ILGRY	20 125	Gray	5-20R	•	•	•

2 Pole, 3 Wire

NEMA
5-15RNEMA
5-20RNEMA
6-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles Extra Heavy-Duty Hospital Grade MRI Receptacles

15 & 20A, 125V


Pass & Seymour



Receptacles designed expressly for MRI applications – We build these exclusive P&S receptacles with no ferrous metal, so they are perfect for high-magnetic-field environments such as magnetic-resonance imaging (MRI) suites. With the same basic design as our standard Extra Heavy-Duty Receptacles, they are extremely durable.

Features


- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty, one-piece nickel-plated brass mounting strap with integral ground for superior structural integrity and long-term performance.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.




8200LAMRI

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 C22.2 No. 42
Hospital Grade Duplex Receptacles Back & Side Wire						
8200IMRI	15 125	Ivory	5-15R	•	•	•
8200WMRI	15 125	White	5-15R	•	•	•
8200MRI	15 125	Brown	5-15R	•	•	•
8200GRYMRI	15 125	Gray	5-15R	•	•	•
8200BKMRI	15 125	Black	5-15R	•	•	•
8200REDMRI	15 125	Red	5-15R	•	•	•
8200LAMRI	15 125	Light Almond	5-15R	•	•	•
8300IMRI	20 125	Ivory	5-20R	•	•	•
8300WMRI	20 125	White	5-20R	•	•	•
8300MRI	20 125	Brown	5-20R	•	•	•
8300GRYMRI	20 125	Gray	5-20R	•	•	•
8300BKMRI	20 125	Black	5-20R	•	•	•
8300REDMRI	20 125	Red	5-20R	•	•	•
8300LAMRI	20 125	Light Almond	5-20R	•	•	•


2 Pole, 3 Wire



Pass & Seymour



PS8200HI



PS8300HSLA

Straight Blade Receptacles
Heavy-Duty Hospital Grade Receptacles
15 & 20A, 125V

Features

- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-ripe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Tri-drive brass terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for more wiring flexibility.
- Auto-ground clip assures positive ground.
- Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	 C22.2 No. 42
Duplex Receptacles Back & Side Wire						
PS8200HI	15 125	Ivory	5-15R	•	•	•
PS8200HW	15 125	White	5-15R	•	•	•
PS8200H	15 125	Brown	5-15R	•	•	•
PS8200HGRY	15 125	Gray	5-15R	•	•	•
PS8200HRED	15 125	Red	5-15R	•	•	•
PS8200HLA	15 125	Light Almond	5-15R	•	•	•
PS8300HI	20 125	Ivory	5-20R	•	•	•
PS8300HW	20 125	White	5-20R	•	•	•
PS8300H	20 125	Brown	5-20R	•	•	•
PS8300HGRY	20 125	Gray	5-20R	•	•	•
PS8300HRED	20 125	Red	5-20R	•	•	•
PS8300HLA	20 125	Light Almond	5-20R	•	•	•
Duplex Receptacles – Smooth Face Back & Side Wire						
PS8200HSI	15 125	Ivory	5-15R	•	•	•
PS8200HSW	15 125	White	5-15R	•	•	•
PS8200HS	15 125	Brown	5-15R	•	•	•
PS8200HSGRY	15 125	Gray	5-15R	•	•	•
PS8200HSBK	15 125	Black	5-15R	•	•	•
PS8200HSRED	15 125	Red	5-15R	•	•	•
PS8200HSLA	15 125	Light Almond	5-15R	•	•	•
PS8300HSI	20 125	Ivory	5-20R	•	•	•
PS8300HSW	20 125	White	5-20R	•	•	•
PS8300HS	20 125	Brown	5-20R	•	•	•
PS8300HSGRY	20 125	Gray	5-20R	•	•	•
PS8300HSBK	20 125	Black	5-20R	•	•	•
PS8300HSRED	20 125	Red	5-20R	•	•	•
PS8300HSLA	20 125	Light Almond	5-20R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles Heavy-Duty Hospital Grade Compact Design Receptacles

15 & 20A, 125V; 20A, 250V

Pass & Seymour




Straight Blade Receptacles


Heavy-Duty Hospital Grade Receptacles

Features

- Impact-resistant nylon face.
- One-piece heat-treated triple-wipe brass power contacts.
- Easily accessible break-off line contact connecting tab for split circuit wiring.
- Terminal compartments isolated from each other for positive conductor containment.
- Corrosion-resistant, zinc-plated steel strap is locked in.
- Internal screw-pressure-plate back wire and side wire line terminals accept #14 – #10 AWG copper or copper-clad conductors.
- High strength thermoplastic back body.
- Back wire holes allow entry of conductor insulation partially into body but not into wiring compartment.
- Auto-ground clip assures positive ground.
- Compact design for easy installation.
- Tri-drive terminal and mounting screws.



8200HI



IG8300

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 C22.2 No. 42
Duplex Receptacles – Compact Design Back & Side Wire						
8200HI	15 125	Ivory	5-15R	•	•	•
8200HW	15 125	White	5-15R	•	•	•
8200H	15 125	Brown	5-15R	•	•	•
8200HGRY	15 125	Gray	5-15R	•	•	•
8200HRED	15 125	Red	5-15R	•	•	•
8200HLA	15 125	Light Almond	5-15R	•	•	•
8300HI	20 125	Ivory	5-20R	•	•	•
8300HW	20 125	White	5-20R	•	•	•
8300H	20 125	Brown	5-20R	•	•	•
8300HGRY	20 125	Gray	5-20R	•	•	•
8300HBK	20 125	Black	5-20R	•	•	•
8300HRED	20 125	Red	5-20R	•	•	•
8300HLA	20 125	Light Almond	5-20R	•	•	•
Isolated Ground Duplex Receptacles Back & Side Wire						
IG8200I	15 125	Ivory	5-15R	•	•	•
IG8200	15 125	Orange	5-15R	•	•	•
IG8200RED	15 125	Red	5-15R	•	•	•
IG8300I	20 125	Ivory	5-20R	•	•	•
IG8300W	20 125	White	5-20R	•	•	•
IG8300	20 125	Orange	5-20R	•	•	•
IG8300RED	20 125	Red	5-20R	•	•	•
IG8300LA	20 125	Light Almond	5-20R	•	•	•
IG8800	20 250	Orange	6-20R	•	•	•
IG8800LA	20 250	Light Almond	6-20R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-20R

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



Straight Blade Receptacles Industrial Extra Heavy-Duty Specification Grade Receptacles

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Exclusive, patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.


External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

5362AI

Auto-ground clip assures positive ground.

Heavy-duty, one-piece brass strap and integral ground for added strength and safety.



Straight Blade Receptacles Industrial Extra Heavy-Duty Specification Grade Receptacles

15 & 20A, 125 & 250V

Pass & Seymour




Straight Blade Receptacles

Industrial EHD Spec Grade Receptacles

Features

- One-piece brass mounting strap with integral ground.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.
- Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 – #10 AWG stranded or solid copper clad conductors.
- Auto-ground clip assures positive ground.
- Corrosion-resistant models have nickel-plated straps and contacts.



Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance		
	A.	V.			 UL498	 FSUL WC596	 C22.2 No. 42
Duplex Receptacles Back & Side Wire							
5262AI	15	125	Ivory	5-15R	•	•	•
5262AW	15	125	White	5-15R	•	•	•
5262A	15	125	Brown	5-15R	•	•	•
5262AGRY	15	125	Gray	5-15R	•	•	•
5262ABK	15	125	Black	5-15R	•	•	•
5262ARED	15	125	Red	5-15R	•	•	•
5262ALA	15	125	Light Almond	5-15R	•	•	•
CR6200*	15	125	Yellow	5-15R	•	•	•
5362AI	20	125	Ivory	5-20R	•	•	•
5362AW	20	125	White	5-20R	•	•	•
5362A	20	125	Brown	5-20R	•	•	•
5362AGRY	20	125	Gray	5-20R	•	•	•
5362ABK	20	125	Black	5-20R	•	•	•
5362ARED	20	125	Red	5-20R	•	•	•
5362ALA	20	125	Light Almond	5-20R	•	•	•
5362ABL	20	125	Blue	5-20R	•	•	•
CR6300BR*	20	125	Brown	5-20R	•	•	•
CR6300*	20	125	Yellow	5-20R	•	•	•
5662AI	15	250	Ivory	6-15R	•	•	•
5662AW	15	250	White	6-15R	•	•	•
5662A	15	250	Brown	6-15R	•	•	•
5662AGRY	15	250	Gray	6-15R	•	•	•
5662ABK	15	250	Black	6-15R	•	•	•
5662ARED	15	250	Red	6-15R	•	•	•
5862AI	20	250	Ivory	6-20R	•	•	•
5862AW	20	250	White	6-20R	•	•	•
5862A	20	250	Brown	6-20R	•	•	•
5862AGRY	20	250	Gray	6-20R	•	•	•
5862ABK	20	250	Black	6-20R	•	•	•
5862ARED	20	250	Red	6-20R	•	•	•
5862ALA	20	250	Light Almond	6-20R	•	•	•

*Corrosion-Resistant.

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-15R




NEMA
6-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



PS5262I

Straight Blade Receptacles
Heavy-Duty Specification Grade Receptacles
15 & 20A, 125 & 250V

Features

- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face.
- Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors. Eight back wire holes.
- Auto-ground clip assures positive ground.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 C22.2 No. 42
Duplex Receptacles Back & Side Wire						
PS5262I	15 125	Ivory	5-15R	•	•	•
PS5262W	15 125	White	5-15R	•	•	•
PS5262	15 125	Brown	5-15R	•	•	•
PS5262GRY	15 125	Gray	5-15R	•	•	•
PS5262BK	15 125	Black	5-15R	•	•	•
PS5262RED	15 125	Red	5-15R	•	•	•
PS5262LA	15 125	Light Almond	5-15R	•	•	•
PS5262BL	15 125	Blue	5-15R	•	•	•
PS5362I	20 125	Ivory	5-20R	•	•	•
PS5362W	20 125	White	5-20R	•	•	•
PS5362	20 125	Brown	5-20R	•	•	•
PS5362GRY	20 125	Gray	5-20R	•	•	•
PS5362BK	20 125	Black	5-20R	•	•	•
PS5362RED	20 125	Red	5-20R	•	•	•
PS5362LA	20 125	Light Almond	5-20R	•	•	•
PS5362BL	20 125	Blue	5-20R	•	•	•
5662I	15 250	Ivory	6-15R	•	•	•
5662W	15 250	White	6-15R	•	•	•
5662	15 250	Brown	6-15R	•	•	•
5862I	20 250	Ivory	6-20R	•	•	•
5862W	20 250	White	6-20R	•	•	•
5862	20 250	Brown	6-20R	•	•	•
5862GRY	20 250	Gray	6-20R	•	•	•
5862BK	20 250	Black	6-20R	•	•	•
5862RED	20 250	Red	6-20R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-15R



NEMA
6-20R

For Configurable Solutions, see Page U-1.

Straight Blade Receptacles PlugTail™ Specification Grade Receptacles

15 & 20A, 125V

Pass & Seymour





Features


- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Crimped and welded contacts.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- Isolated ground version features a plastic barrier that isolates grounding terminal from mounting strap and metal boxes.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 US UL498	FSUL WC596
Duplex Receptacles					
PT5262I	15 125	Ivory	5-15R	•	•
PT5262W	15 125	White	5-15R	•	•
PT5262	15 125	Brown	5-15R	•	•
PT5262GRY	15 125	Gray	5-15R	•	•
PT5262BK	15 125	Black	5-15R	•	•
PT5262RED	15 125	Red	5-15R	•	•
PT5262LA	15 125	Light Almond	5-15R	•	•
PT5262BL	15 125	Blue	5-15R	•	•
PT5362I	20 125	Ivory	5-20R	•	•
PT5362W	20 125	White	5-20R	•	•
PT5362	20 125	Brown	5-20R	•	•
PT5362GRY	20 125	Gray	5-20R	•	•
PT5362BK	20 125	Black	5-20R	•	•
PT5362RED	20 125	Red	5-20R	•	•
PT5362LA	20 125	Light Almond	5-20R	•	•
PT5362BL	20 125	Blue	5-20R	•	•
Isolated Ground Duplex Receptacles					
PTIG5262I	15 125	Ivory	5-15R	•	•
PTIG5262W	15 125	White	5-15R	•	•
PTIG5262	15 125	Orange	5-15R	•	•
PTIG5262GRY	15 125	Gray	5-15R	•	•
PTIG5262RED	15 125	Red	5-15R	•	•
PTIG5262LA	15 125	Light Almond	5-15R	•	•
PTIG5362I	20 125	Ivory	5-20R	•	•
PTIG5362W	20 125	White	5-20R	•	•
PTIG5362	20 125	Orange	5-20R	•	•
PTIG5362GRY	20 125	Gray	5-20R	•	•
PTIG5362RED	20 125	Red	5-20R	•	•
PTIG5362LA	20 125	Light Almond	5-20R	•	•

2 Pole, 3 Wire



PT5362LA




PTIG5362LA

For PlugTail Connectors, see Page B-3.

Configurable Solutions and Metal Box Kits for PlugTail Receptacles and Connectors, see Page U-1-U-3.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



5262I

Straight Blade Receptacles Hard Use Specification Grade Receptacles

15A, 125V, 125/250 & 250V; 20A, 125 & 125/250V

Features

- Corrosion-resistant, plated and tabbed steel strap is locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 – 14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 C22.2 No. 42
Duplex Receptacles Back & Side Wire						
5262I	15 125	Ivory	5-15R	•	•	•
5262W	15 125	White	5-15R	•	•	•
5262	15 125	Brown	5-15R	•	•	•
5262GRY	15 125	Gray	5-15R	•	•	•
5262BK	15 125	Black	5-15R	•	•	•
5262RED	15 125	Red	5-15R	•	•	•
5262LA	15 125	Light Almond	5-15R	•	•	•
5262BL	15 125	Blue	5-15R	•	•	•
5362I	20 125	Ivory	5-20R	•	•	•
5362W	20 125	White	5-20R	•	•	•
5362	20 125	Brown	5-20R	•	•	•
5362GRY	20 125	Gray	5-20R	•	•	•
5362BK	20 125	Black	5-20R	•	•	•
5362RED	20 125	Red	5-20R	•	•	•
5362LA	20 125	Light Almond	5-20R	•	•	•
5362BL	20 125	Blue	5-20R	•	•	•
5652I	15 250	Ivory	6-15R	•	•	•
5652	15 250	Brown	6-15R	•	•	•
5652BK	15 250	Black	6-15R	•	•	•
5652LA	15 250	Light Almond	6-15R	•	•	•
Duplex Receptacles Side Wire						
5642I	15 250	Ivory	6-15R	•	•	•
5642	15 250	Brown	6-15R	•	•	•
Combination Duplex Receptacles Side Wire						
5290I	15 125/250	Ivory	5/6-15R	•	•	•
5290	15 125/250	Brown	5/6-15R	•	•	•
5890I	20 125/250	Ivory	5/6-20R	•	•	
5890W	20 125/250	White	5/6-20R	•	•	
5890	20 125/250	Brown	5/6-20R	•	•	

2 Pole, 3 Wire

NEMA
5-15RNEMA
5-20RNEMA
6-15RNEMA
6-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles Construction Specification Grade Receptacles


15 & 20A, 125V

Pass & Seymour




Features

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 – 14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.



CRB5362I



CRB5362SLA

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance		
	A.	V.			 UL498	 FSUL WC596	 C22.2 No. 42
Duplex Receptacles Back & Side Wire							
CRB5262I	15	125	Ivory	5-15R	•	•	•
CRB5262W	15	125	White	5-15R	•	•	•
CRB5262	15	125	Brown	5-15R	•	•	•
CRB5262GRY	15	125	Gray	5-15R	•	•	•
CRB5262BK	15	125	Black	5-15R	•	•	•
CRB5262RED	15	125	Red	5-15R	•	•	•
CRB5262LA	15	125	Light Almond	5-15R	•	•	•
CRB5362I	20	125	Ivory	5-20R	•	•	•
CRB5362W	20	125	White	5-20R	•	•	•
CRB5362	20	125	Brown	5-20R	•	•	•
CRB5362GRY	20	125	Gray	5-20R	•	•	•
CRB5362BK	20	125	Black	5-20R	•	•	•
CRB5362RED	20	125	Red	5-20R	•	•	•
CRB5362LA	20	125	Light Almond	5-20R	•	•	•
Duplex Receptacles – Smooth Face Back & Side Wire							
CRB5262SI	15	125	Ivory	5-15R	•	•	•
CRB5262SW	15	125	White	5-15R	•	•	•
CRB5262S	15	125	Brown	5-15R	•	•	•
CRB5262SGRY	15	125	Gray	5-15R	•	•	•
CRB5262SRED	15	125	Red	5-15R	•	•	•
CRB5262SLA	15	125	Light Almond	5-15R	•	•	•
CRB5362SI	20	125	Ivory	5-20R	•	•	•
CRB5362SW	20	125	White	5-20R	•	•	•
CRB5362S	20	125	Brown	5-20R	•	•	•
CRB5362SGRY	20	125	Gray	5-20R	•	•	•
CRB5362SRED	20	125	Red	5-20R	•	•	•
CRB5362SLA	20	125	Light Almond	5-20R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R




NEMA
5-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



Straight Blade Receptacles Construction Specification Grade Receptacles

15 & 20A, 125V

Features

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-ripe power contacts for lasting retention.
- Impact-resistant nylon face and thermoplastic back body.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- Pre-wired with welded wire leads that create faster, more reliable connections. Split circuit capable types have four leads – 2 hot, 1 neutral, and 1 ground. (Non-split circuit types have a total of three leads – 1 hot, 1 neutral, and 1 ground.)
- Pre-stripped leads fasten to conductors, faster than standard pigtails.

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance		
	A.	V.			 UL498	 FSUL WC596	 C22.2 No. 42
Duplex Receptacles with 6" Leads							
CRL5262IB	15	125	Ivory	5-15R	•	•	•
CRL5262WB	15	125	White	5-15R	•	•	•
CRL5262B	15	125	Brown	5-15R	•	•	•
CRL5262GRYB	15	125	Gray	5-15R	•	•	•
CRL5262BKB	15	125	Black	5-15R	•	•	•
CRL5262REDB	15	125	Red	5-15R	•	•	•
CRL5262LAB	15	125	Light Almond	5-15R	•	•	•
CRL5362IB	20	125	Ivory	5-20R	•	•	•
CRL5362WB	20	125	White	5-20R	•	•	•
CRL5362B	20	125	Brown	5-20R	•	•	•
CRL5362GRYB	20	125	Gray	5-20R	•	•	•
CRL5362BKB	20	125	Black	5-20R	•	•	•
CRL5362REDB	20	125	Red	5-20R	•	•	•
CRL5362LAB	20	125	Light Almond	5-20R	•	•	•
Duplex Receptacles with 6" Leads – Split Circuit Capable							
CRL5262SCIB	15	125	Ivory	5-15R	•	•	•
CRL5262SCWB	15	125	White	5-15R	•	•	•
CRL5262SCB	15	125	Brown	5-15R	•	•	•
CRL5262SCGRYB	15	125	Gray	5-15R	•	•	•
CRL5262SCBKB	15	125	Black	5-15R	•	•	•
CRL5262SCREDB	15	125	Red	5-15R	•	•	•
CRL5262SCLAB	15	125	Light Almond	5-15R	•	•	•
CRL5362SCIB	20	125	Ivory	5-20R	•	•	•
CRL5362SCWB	20	125	White	5-20R	•	•	•
CRL5362SCB	20	125	Brown	5-20R	•	•	•
CRL5362SCGRYB	20	125	Gray	5-20R	•	•	•
CRL5362SCBKB	20	125	Black	5-20R	•	•	•
CRL5362SCREDB	20	125	Red	5-20R	•	•	•
CRL5362SCLAB	20	125	Light Almond	5-20R	•	•	•

2 Pole, 3 Wire

NEMA
5-15RNEMA
5-20R

Available in Bulk Packs of 100.

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles Commercial Specification Grade Receptacles


15A, 125V; 20A, 125 & 250V

Pass & Seymour



Features

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- CR and 5850 Series: #14 – #10 AWG solid side wire only. BR Series: side and internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.



CR151

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 C22.2 No. 42
Duplex Receptacles Side Wire					
CR15I	15 125	Ivory	5-15R	•	•
CR15W	15 125	White	5-15R	•	•
CR15	15 125	Brown	5-15R	•	•
CR15GRY	15 125	Gray	5-15R	•	•
CR15LA	15 125	Light Almond	5-15R	•	•
CR20I	20 125	Ivory	5-20R	•	•
CR20W	20 125	White	5-20R	•	•
CR20	20 125	Brown	5-20R	•	•
CR20GRY	20 125	Gray	5-20R	•	•
CR20BK	20 125	Black	5-20R	•	•
CR20RED	20 125	Red	5-20R	•	•
CR20LA	20 125	Light Almond	5-20R	•	•
Duplex Receptacles Back & Side Wire					
BR15I	15 125	Ivory	5-15R	•	•
BR15W	15 125	White	5-15R	•	•
BR15	15 125	Brown	5-15R	•	•
BR15GRY	15 125	Gray	5-15R	•	•
BR15LA	15 125	Light Almond	5-15R	•	•
BR20I	20 125	Ivory	5-20R	•	•
BR20W	20 125	White	5-20R	•	•
BR20	20 125	Brown	5-20R	•	•
BR20GRY	20 125	Gray	5-20R	•	•
BR20BK	20 125	Black	5-20R	•	•
BR20LA	20 125	Light Almond	5-20R	•	•
Duplex Receptacles Side Wire					
5850I	20 250	Ivory	6-20R	•	•
5850W	20 250	White	6-20R	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-20R

For Configurable Solutions, see Page U-1.


All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour




Straight Blade Receptacles
Hospital Grade Single Receptacles

15 & 20A, 125V; 20A, 250V



8201-I



8284-I

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	cUL/CSA
Single Receptacles Back & Side Wire						
8201I	15 125	Ivory	5-15R	•	•	•
8201W	15 125	White	5-15R	•	•	•
8201	15 125	Brown	5-15R	•	•	•
8201GRY	15 125	Gray	5-15R	•	•	•
8201BK	15 125	Black	5-15R	•	•	•
8201RED	15 125	Red	5-15R	•	•	•
8201LA	15 125	Light Almond	5-15R	•	•	•
8301I	20 125	Ivory	5-20R	•	•	•
8301W	20 125	White	5-20R	•	•	•
8301	20 125	Brown	5-20R	•	•	•
8301GRY	20 125	Gray	5-20R	•	•	•
8301RED	20 125	Red	5-20R	•	•	•
8801I	20 250	Ivory	6-20R	•	•	•
8801W	20 250	White	6-20R	•	•	•
8801	20 250	Brown	6-20R	•	•	•
8801GRY	20 250	Gray	6-20R	•	•	•
8801RED	20 250	Red	6-20R	•	•	•
Short Strap Single Receptacles 1.937" Screw Spacing, Back & Side Wire						
8284I	15 125	Ivory	5-15R	•	•	•
8284	15 125	Brown	5-15R	•	•	•
8384I	20 125	Ivory	5-20R	•	•	
8384	20 125	Brown	5-20R	•	•	

For Hospital Use Power Interrupting Device consult Turnlok® Section I.

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-20R

Straight Blade Receptacles Heavy-Duty Specification Grade Single Receptacles


15 & 20A, 125 & 250V

Pass & Seymour



Features

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-ripe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.



5361I

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 C22.2 No. 42
Single Receptacles Back & Side Wire						
5261I	15 125	Ivory	5-15R	•	•	•
5261W	15 125	White	5-15R	•	•	•
5261	15 125	Brown	5-15R	•	•	•
5261GRY	15 125	Gray	5-15R	•	•	•
5261BK	15 125	Black	5-15R	•	•	•
5261RED	15 125	Red	5-15R	•	•	•
5261LA	15 125	Light Almond	5-15R	•	•	•
5361I	20 125	Ivory	5-20R	•	•	•
5361W	20 125	White	5-20R	•	•	•
5361	20 125	Brown	5-20R	•	•	•
5361GRY	20 125	Gray	5-20R	•	•	•
5361BK	20 125	Black	5-20R	•	•	•
5361RED	20 125	Red	5-20R	•	•	•
5361LA	20 125	Light Almond	5-20R	•	•	•
5671I	15 250	Ivory	6-15R	•	•	•
5671	15 250	Brown	6-15R	•	•	•
5671LA	15 250	Light Almond	6-15R	•	•	•
5871I	20 250	Ivory	6-20R	•	•	•
5871W	20 250	White	6-20R	•	•	•
5871	20 250	Brown	6-20R	•	•	•
5871GRY	20 250	Gray	6-20R	•	•	•
5871BK	20 250	Black	6-20R	•	•	•
5871RED	20 250	Red	6-20R	•	•	•
5871LA	20 250	Light Almond	6-20R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-15R






NEMA
6-20R

Pass & Seymour



Straight Blade Receptacles
Specification Grade Single Receptacles
15 & 20A, 125 & 250V



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 C22.2 No. 42
Single Receptacles Side Wire					
5251I	15 125	Ivory	5-15R	•	•
5251W	15 125	White	5-15R	•	•
5251	15 125	Brown	5-15R	•	•
5251LA	15 125	Light Almond	5-15R	•	•
5351I	20 125	Ivory	5-20R	•	•
5351W	20 125	White	5-20R	•	•
5351	20 125	Brown	5-20R	•	•
5351LA	20 125	Light Almond	5-20R	•	•
5651I	15 250	Ivory	6-15R	•	•
5651W	15 250	White	6-15R	•	•
5651	15 250	Brown	6-15R	•	•
5651LA	15 250	Light Almond	6-15R	•	•
5851I	20 250	Ivory	6-20R	•	•
5851W	20 250	White	6-20R	•	•
5851	20 250	Brown	6-20R	•	•
5851LA	20 250	Light Almond	6-20R	•	•
Single Receptacles Side Wire Right Angle Slots					
5371I	20 125	Ivory	Non-NEMA	•	•
5371W	20 125	White	Non-NEMA	•	•
5371	20 125	Brown	Non-NEMA	•	•

Short Strap Single Receptacles Screw Spacing 1.750"					
5258I	15 125	Ivory	5-15R	•	•
5258W	15 125	White	5-15R	•	•
5258	15 125	Brown	5-15R	•	•
5358I	20 125	Ivory	5-20R	•	•
5358W	20 125	White	5-20R	•	•
5358	20 125	Brown	5-20R	•	•
5358BK	20 125	Black	5-20R	•	•
5658I	15 250	Ivory	6-15R	•	•
5658	15 250	Brown	6-15R	•	•
5858I	20 250	Ivory	6-20R	•	•
5858W	20 250	White	6-20R	•	•
5858	20 250	Brown	6-20R	•	•
Supplied with mounting screws.					

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-15R



NEMA
6-20R

Straight Blade Receptacles Tamper-Resistant Specification Grade Receptacles


15 & 20A, 125V

Pass & Seymour



Features


- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.



TR621


Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	 C22.2 No. 42
Duplex Receptacles Back & Side Wire						
TR62I	15 125	Ivory	5-15R	•	•	•
TR62W	15 125	White	5-15R	•	•	•
TR62	15 125	Brown	5-15R	•	•	•
TR62GRY	15 125	Gray	5-15R	•	•	•
TR62BK	15 125	Black	5-15R	•	•	•
TR62RED	15 125	Red	5-15R	•	•	•
TR62LA	15 125	Light Almond	5-15R	•	•	•
TR62BL	15 125	Blue	5-15R	•	•	•
TR63I	20 125	Ivory	5-20R	•	•	•
TR63W	20 125	White	5-20R	•	•	•
TR63	20 125	Brown	5-20R	•	•	•
TR63GRY	20 125	Gray	5-20R	•	•	•
TR63BK	20 125	Black	5-20R	•	•	•
TR63RED	20 125	Red	5-20R	•	•	•
TR63LA	20 125	Light Almond	5-20R	•	•	•

2 Pole, 3 Wire




For PlugTail™ Tamper-Resistant Receptacles, see Pages B-3, B-4, and F-3.


The Mechanical Shutter System



Thermoplastic shutter in closed position covers access to contacts.



Insertion of object in any one side does not open shutter.



Two-bladed plug or grounding plug compresses spring and simultaneously opens both shutters.


This tamper-resistant receptacle, like all others, can be defeated by actions such as inserting foreign objects in both sides of the slots simultaneously.

2008 NEC® section 517.18(C) Pediatric Locations.

Receptacles located within the rooms, bathrooms, playrooms, activity rooms, and patient care areas of pediatric wards shall be listed under tamper resistant or employ a listed tamper resistant cover.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



TR62HI

Straight Blade Receptacles
Tamper-Resistant
Hospital Grade Receptacles

15 & 20A, 125V

Features

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.

NEW	Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
					 UL498	 FSUL WC596	 C22.2 No. 42
	Hospital Grade Duplex Receptacles Back & Side Wire						
	TR62HI	15 125	Ivory	5-15R	•	•	•
	TR62HW	15 125	White	5-15R	•	•	•
	TR62H	15 125	Brown	5-15R	•	•	•
	TR62HGRY	15 125	Gray	5-15R	•	•	•
	TR62HRED	15 125	Red	5-15R	•	•	•
	TR62HLA	15 125	Light Almond	5-15R	•	•	•
	NEW	TR63HI	20 125	Ivory	5-20R	•	•
TR63HW		20 125	White	5-20R	•	•	•
TR63H		20 125	Brown	5-20R	•	•	•
TR63HGRY		20 125	Gray	5-20R	•	•	•
TR63HRED		20 125	Red	5-20R	•	•	•
TR63HLA		20 125	Light Almond	5-20R	•	•	•
TR63HBL		20 125	Blue	5-20R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R

For PlugTail™ Tamper-Resistant Receptacles, see Pages B-3, B-4, and F-3.

Straight Blade Receptacles Tamper-Resistant Hard Use & Commercial Grade Receptacles

15 & 20A, 125V


Pass & Seymour



Straight Blade Receptacles

Features

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation. Internal screw-pressure-plate back and side wire capability. Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-ripe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.




TR5362LA

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 C22.2 No. 42
Tamper-Resistant Duplex Receptacles – Back & Side Wire						
TR5262I	15 125	Ivory	5-15R	•	•	•
TR5262W	15 125	White	5-15R	•	•	•
TR5262	15 125	Brown	5-15R	•	•	•
TR5262GRY	15 125	Gray	5-15R	•	•	•
TR5262BK	15 125	Black	5-15R	•	•	•
TR5262RED	15 125	Red	5-15R	•	•	•
TR5262LA	15 125	Light Almond	5-15R	•	•	•
TR5362I	20 125	Ivory	5-20R	•	•	•
TR5362W	20 125	White	5-20R	•	•	•
TR5362	20 125	Brown	5-20R	•	•	•
TR5362GRY	20 125	Gray	5-20R	•	•	•
TR5362BK	20 125	Black	5-20R	•	•	•
TR5362RED	20 125	Red	5-20R	•	•	•
TR5362LA	20 125	Light Almond	5-20R	•	•	•


Features

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-ripe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.



TR15LA

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 cULus	 C22.2 No. 42
Tamper-Resistant Duplex Receptacles – Side Wire						
TR15I	15 125	Ivory	5-15R	•	•	•
TR15W	15 125	White	5-15R	•	•	•
TR15	15 125	Brown	5-15R	•	•	•
TR15GRY	15 125	Gray	5-15R	•	•	•
TR15LA	15 125	Light Almond	5-15R	•	•	•
TR20I	20 125	Ivory	5-20R	•	•	•
TR20W	20 125	White	5-20R	•	•	•
TR20	20 125	Brown	5-20R	•	•	•
TR20GRY	20 125	Gray	5-20R	•	•	•
TR20BK	20 125	Black	5-20R	•	•	•
TR20LA	20 125	Light Almond	5-20R	•	•	•




NEMA
5-15R

NEMA
5-20R

All devices listed on this page conform to NEMA WD-1 and WD-6.

TR Hard Use & Commercial Grade Recept.

Pass & Seymour



TR5351LA



NEMA
5-15R



NEMA
5-20R

Straight Blade Receptacles
Tamper-Resistant Construction Grade
Receptacles & Shim-Lock

15 & 20A, 125V

Features

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.
- One-piece brass triple-wipe power contacts for lasting retention.

NEW

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	 C22.2 No. 42
+ Tamper-Resistant Single Receptacles – Back & Side Wire						
TR5251I	15 125	Ivory	5-15R	•	•	•
TR5251W	15 125	White	5-15R	•	•	•
TR5251	15 125	Brown	5-15R	•	•	•
TR5251LA	15 125	Light Almond	5-15R	•	•	•
TR5351I	20 125	Ivory	5-20R	•	•	•
TR5351W	20 125	White	5-20R	•	•	•
TR5351	20 125	Brown	5-20R	•	•	•
TR5351LA	20 125	Light Almond	5-20R	•	•	•



Shim-Lock

Features

- One Shim-Lock provides a device adjustment depth range between 1/8" and 3/4".
- Provides a perfect flush mount every time, regardless of the wallboard, tile or panel condition.
- An inexpensive and quick fix for floating installations.
- Made of steel and finished with clear zinc chromate plating.



Catalog Number	Dimensions	Qty. Per Package
Shim-Lock		
SHL20	Length: .310", Screw Opening: #6	20
SHL100	Length: .310", Screw Opening: #6	100

Straight Blade Receptacles Weather-Resistant Heavy-Duty & Commercial Grade Receptacles

15 & 20A, 125 & 250V


Pass & Seymour




Straight Blade Receptacles

Features

- Auto-ground clip assures positive ground.
- WR marking on face as required by UL Standard.
- Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Tri-drive brass terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for more wiring flexibility.
- Heavy-duty, brass strap for added strength and ground conductivity.
- UV-resistant nylon face for longer life under adverse environmental conditions.
- Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- .032 inch thick brass triple-ripe power contacts for lasting retention.



WR5262W



WR20TRW

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	 C22.2 No. 42
Weather-Resistant Duplex Receptacles Back & Side Wire						
WR5262I	15 125	Ivory	5-15R	•	•	•
WR5262W	15 125	White	5-15R	•	•	•
WR5262GRY	15 125	Gray	5-15R	•	•	•
WR5362I	20 125	Ivory	5-20R	•	•	•
WR5362W	20 125	White	5-20R	•	•	•
WR5362GRY	20 125	Gray	5-20R	•	•	•
WR5662I	15 250	Ivory	6-15R	•	•	•
WR5662W	15 250	White	6-15R	•	•	•
WR5662GRY	15 250	Gray	6-15R	•	•	•
WR5862I	20 250	Ivory	6-20R	•	•	•
WR5862W	20 250	White	6-20R	•	•	•
WR5862GRY	20 250	Gray	6-20R	•	•	•

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 C22.2 No. 42
Weather-Resistant Duplex Receptacles Side Wire					
WR20TRI	20 125	Ivory	5-20R	•	•
WR20TRW	20 125	White	5-20R	•	•
WR20TR	20 125	Brown	5-20R	•	•
WR20TRGRY	20 125	Gray	5-20R	•	•
WR20TRLA	20 125	Light Almond	5-20R	•	•

WR20TR models are Tamper-Resistant.

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R

2008 National Electrical Code® Section 406.8 Receptacles in Wet or Damp Locations.

Requires that all 15- and 20-amp, 125- and 250-volt non-locking receptacles installed in wet or damp locations shall be weather-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Weather-Resistant Receptacles

Pass & Seymour




Straight Blade Receptacles
Isolated Ground Receptacles


15 & 20A, 125V; 20A, 250V



IG8300





IG26262I



IG5261
IG5361
IG8301


2 Pole, 3 Wire



Catalog Number		Rating A. V.	NEMA Config. No.	Color	3rd Party Compliance				
Spec Grade	Hospital Grade				UL498	FSUL WC596	CS® C22.2 No. 42		
Duplex Receptacles Back & Side Wire*									
IG5262I	IG8200I	NEW	15 125	5-15R	Ivory	•	•	•	
IG5262W	IG8200RED		15 125	5-15R	White	•	•	•	
IG5262GRY			15 125	5-15R	Gray	•	•	•	
IG5262RED			15 125	5-15R	Red	•	•	•	
IG5262LA			15 125	5-15R	Light Almond	•	•	•	
IG5262		IG8200	15 125	5-15R	Orange	•	•	•	
IG5362I	IG8300I	NEW	20 125	5-20R	Ivory	•	•	•	
IG5362W	IG8300W	NEW	20 125	5-20R	White	•	•	•	
IG5362GRY	IG8300RED	20 125	5-20R	Gray	•	•	•		
IG5362RED		20 125	5-20R	Red	•	•	•		
IG5362BK		20 125	5-20R	Black	•	•	•		
IG5362LA		IG8300LA	20 125	5-20R	Light Almond	•	•	•	
IG5362		IG8300	20 125	5-20R	Orange	•	•	•	
IG5362BL			20 125	5-20R	Blue	•	•	•	
IG5662		NEW	15 250	6-15R	Orange	•	•	•	
	IG8800LA		20 250	6-20R	Light Almond	•	•	•	
IG5862	IG8800		20 250	6-20R	Orange	•	•	•	
Decorator Duplex Receptacles Back & Side Wire									
IG26262I	IG26262HGW	NEW	15 125	5-15R	Ivory	•	•	•	
IG26262W			15 125	5-15R	White	•	•	•	
IG26262GRY			15 125	5-15R	Gray	•	•	•	
IG26262RED			IG26262HGRED	15 125	5-15R	Red	•	•	•
IG26262BK			15 125	5-15R	Black	•	•	•	
IG26262LA			15 125	5-15R	Light Almond	•	•	•	
IG26262	IG26262HG		15 125	5-15R	Orange	•	•	•	
IG26362I	IG26362HGW		20 125	5-20R	Ivory	•	•	•	
IG26362W		20 125	5-20R	White	•	•	•		
IG26362GRY		IG26362HGGRY	20 125	5-20R	Gray	•	•	•	
IG26362RED		IG26362HGRED	20 125	5-20R	Red	•	•	•	
IG26362BK		IG26362HGBK	20 125	5-20R	Black	•	•	•	
IG26362LA			20 125	5-20R	Light Almond	•	•	•	
IG26362	IG26362HG		20 125	5-20R	Orange	•	•	•	
Single Receptacles Back & Side Wire									
IG5261			15 125	5-15R	Orange	•	•	•	
IG5361	IG8301		20 125	5-20R	Orange	•	•	•	

For Wall Plates for Isolated Ground Systems, consult Wall Plates Section S.

*For Configurable Solutions, see Page U-1.




All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles


PlugTail™ Decorator Receptacles

15 & 20A, 125V


Pass & Seymour



PT26352LA



PT26362HGI




PTIG26362LA

Features

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- Isolated ground version features nylon isolator plate for isolating ground from strap and box system.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 US UL498	FSUL WC596
Duplex Receptacles					
PT26252I	15 125	Ivory	5-15R	•	•
PT26252W	15 125	White	5-15R	•	•
PT26252	15 125	Brown	5-15R	•	•
PT26252GRY	15 125	Gray	5-15R	•	•
PT26252BK	15 125	Black	5-15R	•	•
PT26252RED	15 125	Red	5-15R	•	•
PT26252LA	15 125	Light Almond	5-15R	•	•
PT26352I	20 125	Ivory	5-20R	•	•
PT26352W	20 125	White	5-20R	•	•
PT26352	20 125	Brown	5-20R	•	•
PT26352GRY	20 125	Gray	5-20R	•	•
PT26352BK	20 125	Black	5-20R	•	•
PT26352RED	20 125	Red	5-20R	•	•
PT26352LA	20 125	Light Almond	5-20R	•	•
Hospital Grade Duplex Receptacles					
PT26262HGI	15 125	Ivory	5-15R	•	•
PT26262HGW	15 125	White	5-15R	•	•
PT26262HGGRY	15 125	Gray	5-15R	•	•
PT26262HGRED	15 125	Red	5-15R	•	•
PT26362HGI	20 125	Ivory	5-20R	•	•
PT26362HGW	20 125	White	5-20R	•	•
PT26362HGGRY	20 125	Gray	5-20R	•	•
PT26362HGRED	20 125	Red	5-20R	•	•
PT26362HGLA	20 125	Light Almond	5-20R	•	•
Isolated Ground Duplex Receptacles					
PTIG26262I	15 125	Ivory	5-15R	•	•
PTIG26262W	15 125	White	5-15R	•	•
PTIG26262	15 125	Orange	5-15R	•	•
PTIG26262GRY	15 125	Gray	5-15R	•	•
PTIG26262RED	15 125	Red	5-15R	•	•
PTIG26262LA	15 125	Light Almond	5-15R	•	•
PTIG26362I	20 125	Ivory	5-20R	•	•
PTIG26362W	20 125	White	5-20R	•	•
PTIG26362	20 125	Orange	5-20R	•	•
PTIG26362GRY	20 125	Gray	5-20R	•	•
PTIG26362RED	20 125	Red	5-20R	•	•
PTIG26362LA	20 125	Light Almond	5-20R	•	•

2 Pole, 3 Wire



NEMA
5-15R


NEMA
5-20R

For PlugTail Connectors, see Page B-3.


Configurable Solutions and Metal Box Kits for PlugTail Receptacles and Connectors, see Pages U-1-U-3.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Pass & Seymour



26262HGI



IG26262HGI



26252I

2 Pole, 3 Wire

NEMA
5-15RNEMA
5-20R

For Configurable
Solutions, see Page U-1.

Straight Blade Receptacles Heavy-Duty Hospital Grade & Specification Grade Decorator Receptacles 15 & 20A, 125V

Features

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 – #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	cUL/CSA
Hospital Grade Duplex Receptacles Back & Side Wire						
26262HGI	15 125	Ivory	5-15R	•	•	•
26262HGW	15 125	White	5-15R	•	•	•
26262HGGRY	15 125	Gray	5-15R	•	•	•
26262HGRED	15 125	Red	5-15R	•	•	•
26362HGI	20 125	Ivory	5-20R	•	•	•
26362HGW	20 125	White	5-20R	•	•	•
26362HG	20 125	Brown	5-20R	•	•	•
26362HGGRY	20 125	Gray	5-20R	•	•	•
26362HGRED	20 125	Red	5-20R	•	•	•
26362HGLA	20 125	Light Almond	5-20R	•	•	•
Hospital Grade Isolated Ground Duplex Receptacles Back & Side Wire						
IG26262HGW	15 125	White	5-15R	•		•
IG26262HG	15 125	Orange	5-15R	•		•
IG26262HGRED	15 125	Red	5-15R	•		•
IG26362HGW	20 125	White	5-20R	•		•
IG26362HG	20 125	Orange	5-20R	•		•
IG26362HGGRY	20 125	Gray	5-20R	•		•
IG26362HGBK	20 125	Black	5-20R	•		•
IG26362HGRED	20 125	Red	5-20R	•		•
Hospital Grade Illuminated Duplex Receptacles Back & Side Wire						
26222HGI	15 125	Ivory	5-15R	•		•
26322HGI	20 125	Ivory	5-20R	•		•
26322HGW	20 125	White	5-20R	•		•
26322HGRED	20 125	Red	5-20R	•		•

Specification Grade Duplex Receptacles Back & Side Wire


26252I	15 125	Ivory	5-15R	•	•	•
26252W	15 125	White	5-15R	•	•	•
26252	15 125	Brown	5-15R	•	•	•
26252GRY	15 125	Gray	5-15R	•	•	•
26252BK	15 125	Black	5-15R	•	•	•
26252RED	15 125	Red	5-15R	•	•	•
26252LA	15 125	Light Almond	5-15R	•	•	•
26352I	20 125	Ivory	5-20R	•	•	•
26352W	20 125	White	5-20R	•	•	•
26352	20 125	Brown	5-20R	•	•	•
26352GRY	20 125	Gray	5-20R	•	•	•
26352BK	20 125	Black	5-20R	•	•	•
26352RED	20 125	Red	5-20R	•	•	•
26352LA	20 125	Light Almond	5-20R	•	•	•

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles Specification Grade Decorator Receptacles

15 & 20A, 125 & 250V

Pass & Seymour



26242I

Features

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 – #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	cUL/CSA
Duplex Receptacles Back & Side Wire						
26652I	15 250	Ivory	6-15R	•	•	•
26652W	15 250	White	6-15R	•	•	•
26652	15 250	Brown	6-15R	•	•	•
26652GRY	15 250	Gray	6-15R	•	•	•
26652BK	15 250	Black	6-15R	•	•	•
26652RED	15 250	Red	6-15R	•	•	•
26852I	20 250	Ivory	6-20R	•	•	•
26852W	20 250	White	6-20R	•	•	•
26852	20 250	Brown	6-20R	•	•	•
26852GRY	20 250	Gray	6-20R	•	•	•
26852BK	20 250	Black	6-20R	•	•	•
26852RED	20 250	Red	6-20R	•	•	•
26852LA	20 250	Light Almond	6-20R	•	•	•
Duplex Receptacles Side Wire Only						
26242I	15 125	Ivory	5-15R	•	•	•
26242W	15 125	White	5-15R	•	•	•
26242	15 125	Brown	5-15R	•	•	•
26242GRY	15 125	Gray	5-15R	•	•	•
26242BK	15 125	Black	5-15R	•	•	•
26242RED	15 125	Red	5-15R	•	•	•
26342I	20 125	Ivory	5-20R	•	•	•
26342W	20 125	White	5-20R	•	•	•
26342	20 125	Brown	5-20R	•	•	•
26342GRY	20 125	Gray	5-20R	•	•	•
26342BK	20 125	Black	5-20R	•	•	•
26342RED	20 125	Red	5-20R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-15R




NEMA
6-20R


For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



TR26362I



TR26362HGI

Straight Blade Receptacles Heavy-Duty Tamper-Resistant Decorator Receptacles

15 & 20A, 125V

Features

- Auto-ground clip assures positive ground.
- Dual mechanical shutter system to help prevent insertion of foreign objects.
- One-piece brass triple-wipe power contacts for reliable plug retention.
- Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.
- Patented external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- One-piece plated steel mounting strap with integral ground for superior long-term performance.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 cUL/CSA
▶ Tamper-Resistant Decorator Duplex Receptacles – Back & Side Wire						
TR26262I	15 125	Ivory	5-15R	•	•	•
TR26262W	15 125	White	5-15R	•	•	•
TR26262	15 125	Brown	5-15R	•	•	•
TR26262GRY	15 125	Gray	5-15R	•	•	•
TR26262BK	15 125	Black	5-15R	•	•	•
TR26262RED	15 125	Red	5-15R	•	•	•
TR26262LA	15 125	Light Almond	5-15R	•	•	•
TR26362I	20 125	Ivory	5-20R	•	•	•
TR26362W	20 125	White	5-20R	•	•	•
TR26362	20 125	Brown	5-20R	•	•	•
TR26362GRY	20 125	Gray	5-20R	•	•	•
TR26362BK	20 125	Black	5-20R	•	•	•
TR26362RED	20 125	Red	5-20R	•	•	•
TR26362LA	20 125	Light Almond	5-20R	•	•	•
▶ Tamper-Resistant Hospital Grade Duplex Receptacles – Back & Side Wire						
TR26262HGI	15 125	Ivory	5-15R	•	•	•
TR26262HGW	15 125	White	5-15R	•	•	•
TR26262HG	15 125	Brown	5-15R	•	•	•
TR26262HGGRY	15 125	Gray	5-15R	•	•	•
TR26262HGBK	15 125	Black	5-15R	•	•	•
TR26262HGRED	15 125	Red	5-15R	•	•	•
TR26262HGLA	15 125	Light Almond	5-15R	•	•	•
TR26362HGI	20 125	Ivory	5-20R	•	•	•
TR26362HGW	20 125	White	5-20R	•	•	•
TR26362HG	20 125	Brown	5-20R	•	•	•
TR26362HGGRY	20 125	Gray	5-20R	•	•	•
TR26362HGBK	20 125	Black	5-20R	•	•	•
TR26362HGRED	20 125	Red	5-20R	•	•	•
TR26362HGLA	20 125	Light Almond	5-20R	•	•	•

NEMA
5-15RNEMA
5-20R

Straight Blade Receptacles Specification Grade Combination & Decorator Receptacles

15 & 20A, 125 & 250V; 20A, 120/125VAC

Features

- Impact-resistant face and body.
- GE Lexan™ high impact-resistant lens.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.
- Sensor automatically turns light ON in the dark.
- Increased light output for better illumination.
- Light sensor for enhanced sensitivity.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance
					 UL498
Specification Grade Decorator Hallway Light & Single Receptacle					
PS8HWLI	20 120/125	0.2561	Ivory	5-20R	•
PS8HWLW	20 120/125	0.2561	White	5-20R	•
PS8HWLLA	20 120/125	0.2561	Light Almond	5-20R	•


*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See Page U-55 for more information.

Features


- Corrosion-resistant, plated wraparound steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 – #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	cUL/CSA
Heavy-Duty Specification Grade Single Receptacles				Back & Side Wire		
26261I	15 125	Ivory	5-15R	•	•	•
26261W	15 125	White	5-15R	•	•	•
26261	15 125	Brown	5-15R	•	•	•
26261GRY	15 125	Gray	5-15R	•	•	•
26261BK	15 125	Black	5-15R	•	•	•
26361I	20 125	Ivory	5-20R	•	•	
26361W	20 125	White	5-20R	•	•	
26361	20 125	Brown	5-20R	•	•	
26361GRY	20 125	Gray	5-20R	•	•	
26361BK	20 125	Black	5-20R	•	•	
26361LA	20 125	Light Almond	5-20R	•	•	
26661I	15 250	Ivory	6-15R	•	•	•
26661W	15 250	White	6-15R	•	•	•
26661GRY	15 250	Gray	6-15R	•	•	•
26661BK	15 250	Black	6-15R	•	•	•
26861I	20 250	Ivory	6-20R	•	•	
26861W	20 250	White	6-20R	•	•	
26861	20 250	Brown	6-20R	•	•	
26861GRY	20 250	Gray	6-20R	•	•	
26861BK	20 250	Black	6-20R	•	•	
26861LA	20 250	Light Almond	6-20R	•	•	

Pass & Seymour





PS8HWLLA



26261I

2 Pole, 3 Wire




All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



Straight Blade Receptacles TradeMaster® Tamper-Resistant Receptacles

Meets 2008 National Electrical Code®
Tamper-Resistant requirements.



2008 National Electrical Code® Section 406.11 Tamper-Resistant Receptacles in Dwelling Units.

In all areas specified in 210.52 all 125-volt, 15- and 20-amp receptacles shall be listed tamper-resistant receptacles.

Straight Blade Receptacles TradeMaster® Tamper-Resistant Receptacles

15A, 125V

Pass & Seymour






Straight Blade Receptacles


TradeMaster® Tamper-Resistant Receptacles

Features

- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet “caps” or “protection plates.”
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.



2 Pole, 3 Wire



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 C22.2 No. 42	 cULus
Tamper-Resistant Duplex Receptacles – Grounding						
3232TRI	15 125	Ivory	5-15R	•	•	•
3232TRW	15 125	White	5-15R	•	•	•
3232TR	15 125	Brown	5-15R	•	•	•
3232TRBK	15 125	Black	5-15R	•	•	•
3232TRLA	15 125	Light Almond	5-15R	•	•	•
Self-Grounding Tamper-Resistant Duplex Receptacles						
3232TRSI	15 125	Ivory	5-15R	•	•	•
3232TRSW	15 125	White	5-15R	•	•	•
3232TRS	15 125	Brown	5-15R	•	•	•
3232TRSLA	15 125	Light Almond	5-15R	•	•	•
Decorator Tamper-Resistant Receptacles						
885TRI	15 125	Ivory	5-15R	•	•	•
885TRW	15 125	White	5-15R	•	•	•
885TR	15 125	Brown	5-15R	•	•	•
885TRGRY	15 125	Gray	5-15R	•	•	•
885TRBK	15 125	Black	5-15R	•	•	•
885TRLA	15 125	Light Almond	5-15R	•	•	•
Self-Grounding Decorator Tamper-Resistant Receptacles						
885TRSI	15 125	Ivory	5-15R	•	•	•
885TRSW	15 125	White	5-15R	•	•	•
885TRSLA	15 125	Light Almond	5-15R	•	•	•

Features

- Impact-resistant face and body.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- GE Lexan™ high impact-resistant lens.
- Tri-drive screws.
- Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.
- Sensor automatically turns light ON in the dark.
- Increased light output for better illumination.
- Light sensor for enhanced sensitivity.
- UL tested shutter mechanism for protection against improper object insertion per UL498.
- Specially designed for increased protection of children in their homes.
- Superior protection than traditional outlet “caps” or “protection plates.”

Catalog Number	Rating A. VAC	Light Output in 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance
					 UL498
Decorator Hallway Light with High Output Light & Tamper-Resistant Single Receptacle					
TM8HWLTRICC	15 125	0.2561	Ivory	5-15R	•
TM8HWLTRWCC	15 125	0.2561	White	5-15R	•
TM8HWLTRBKCC	15 125	0.2561	Black	5-15R	•
TM8HWLTRCC	15 125	0.2561	Brown	5-15R	•
TM8HWLTRLACC	15 125	0.2561	Light Almond	5-15R	•

* FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See Page U-55 for more information.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour





Straight Blade Receptacles

Weather-Resistant Receptacles

Residential Weather-Resistant Receptacles are Tamper-Resistant as required by 2008 National Electrical Code®


Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including:

- Ultraviolet light exposure test
- Cold impact test
- Accelerated aging test
- Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.



Features

- Specifically designed for increased protection of children in the home.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 C22.2 No. 42	 cULus
Weather-Resistant Duplex Receptacles						
3232TRWRI	15 125	Ivory	5-15R	•	•	•
3232TRWRW	15 125	White	5-15R	•	•	•
3232TRWR	15 125	Brown	5-15R	•	•	•
3232TRWRLA	15 125	Light Almond	5-15R	•	•	•
3232TRWRBK	15 125	Black	5-15R	•	•	•
Decorator Weather-Resistant Duplex Receptacles						
885TRWRI	15 125	Ivory	5-15R	•	•	•
885TRWRW	15 125	White	5-15R	•	•	•
885TRWR	15 125	Brown	5-15R	•	•	•
885TRWRLA	15 125	Light Almond	5-15R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R

2008 National Electrical Code® Section 406.8 Receptacles in Wet or Damp Locations.

Requires that all 15- and 20-amp, 125- and 250-volt non-locking receptacles installed in wet or damp locations shall be weather-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles

TradeMaster® Decorator Receptacles

15A, 125V


Pass & Seymour



Straight Blade Receptacles

Features

- High impact-resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Tri-drive screws.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid.
- Push wire accepts #14 AWG solid only.
- Self-grounding models provide automatic ground clip.




885I

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 C22.2 42
Decorator Duplex Receptacles					
885I	15 125	Ivory	5-15R	•	•
885W	15 125	White	5-15R	•	•
885	15 125	Brown	5-15R	•	•
885BK	15 125	Black	5-15R	•	•
885LA	15 125	Light Almond	5-15R	•	•
Self-Grounding Decorator Duplex Receptacles					
885SI	15 125	Ivory	5-15R	•	•
885SW	15 125	White	5-15R	•	•
885SLA	15 125	Light Almond	5-15R	•	•

For Configurable Solutions, see Page U-1.

Features

- Longer steel straps than competitive devices, still fits under a standard wall plate.
- High-impact thermoplastic face and back body eliminate cracks, breaks and callbacks.
- Ultrasonic welding of face to back body.
- Patented design provides better plug retention.
- External screw-pressure-plate back wire on all four terminal screws and ground screw eliminates wrapping.
- Accepts #12 and #14 stranded and solid wire.
- Break-off tabs that are big enough to grab hold of – even if the contact screws are backed-out. Scored deeper, for fast, clean breaks every time.
- All four contact screws and the ground screw are backed-out.
- All screws are tri-drive.



TM885W

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance
				 UL498
Decorator Duplex Receptacles with Pressure Plates				
TM885I	15 125	Ivory	5-15R	•
TM885W	15 125	White	5-15R	•
TM885	15 125	Brown	5-15R	•
TM885GRY	15 125	Gray	5-15R	•
TM885BK	15 125	Black	5-15R	•
TM885LA	15 125	Light Almond	5-15R	•
Decorator Duplex Receptacles with Pressure Plates Self-Grounding				
TM885SI	15 125	Ivory	5-15R	•
TM885SW	15 125	White	5-15R	•
TM885SLA	15 125	Light Almond	5-15R	•
Decorator Duplex Receptacles with Pressure Plates Bulk Pack of 150				
TM885I150	15 125	Ivory	5-15R	•
TM885W150	15 125	White	5-15R	•
TM885LA150	15 125	Light Almond	5-15R	•

2 Pole, 3 Wire







NEMA
5-15R

All devices listed on this page conform to NEMA WD-1 and WD-6.

TradeMaster® Receptacles

Straight Blade Receptacles TradeMaster® Receptacles

15A, 125V



Features

- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Low profile face.
- Traditional contoured face. (3232 models.)
- Self-grounding models provide automatic ground clip.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 C22.2 No. 42
Duplex Receptacles – Grounding					
3232I*	15 125	Ivory	5-15R	•	•
3232W*	15 125	White	5-15R	•	•
3232*	15 125	Brown	5-15R	•	•
3232BK	15 125	Black	5-15R	•	•
3232LA*	15 125	Light Almond	5-15R	•	•
Self-Grounding Duplex Receptacles					
3232SI	15 125	Ivory	5-15R	•	•
3232SW	15 125	White	5-15R	•	•
3232S	15 125	Brown	5-15R	•	•
3232SLA	15 125	Light Almond	5-15R	•	•
4 Terminal, Screws In					
3232I4	15 125	Ivory	5-15R	•	•
3232W4	15 125	White	5-15R	•	•
32324	15 125	Brown	5-15R	•	•
Duplex Receptacles – Without Ears					
3232IMH	15 125	Ivory	5-15R	•	•
3232WMH	15 125	White	5-15R	•	•
3232MH	15 125	Brown	5-15R	•	•


*Available in bulk packs of 150. Add "U" to end of Catalog Number. Example: 3232LAU.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 C22.2 No. 42
8 Hole Push Wire Without Terminal Screws					
880I	15 125	Ivory	5-15R	•	•
880W	15 125	White	5-15R	•	•
880	15 125	Brown	5-15R	•	•
8 Hole Push Wire – Without Ears Without Terminal Screws					
880IMH	15 125	Ivory	5-15R	•	•
880WMH	15 125	White	5-15R	•	•
880MH	15 125	Brown	5-15R	•	•


Straight Blade Receptacles

TradeMaster® Decorator Hallway Lights & Combination Devices


Pass & Seymour




TMHWLCC



TMHWLECC



TM8HWLWCC



TM8HWLEWCC4

Features

- Impact-resistant face and body.
- GE Lexan™ high impact-resistant lens.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.
- Sensor automatically turns light ON in the dark.
- Increased light output for better illumination.
- Light sensor for enhanced sensitivity.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	3rd Party Compliance
				 UL1598
TradeMaster® Decorator Full Hallway Light				
TMHWLCC	— 120	0.1328	Clear	•
Enhanced Decorator Full Hallway Light with Light Sensor				
TMHWLECC	— 120	1.079	Clear	•
Enhanced Decorator Full Hallway Light without Light Sensor				
TMHWLENSCC	— 120	1.113	Clear	•
Full Hallway Decorator Light for use with P&S Metal Louver Plates**				
TMHWLLOUVCC	— 120	0.0843	Clear	•

*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See Page U-55 for more information.

**For Louver Plates, see Page S-20.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance
					 UL498
TradeMaster® Decorator Hallway Light & Single Receptacle					
TM8HWLICCC	15 120/125	0.1442	Ivory	5-15R	•
TM8HWLWCC	15 120/125	0.1442	White	5-15R	•
TM8HWLBKCC	15 120/125	0.1442	Black	5-15R	•
TM8HWLCC	15 120/125	0.1442	Brown	5-15R	•
TM8HWLLACC	15 120/125	0.1442	Light Almond	5-15R	•
Enhanced Decorator Hallway Light & Single Receptacle					
TM8HWLEICC	15 120/125	0.2561	Ivory	5-15R	•
TM8HWLEWCC	15 120/125	0.2561	White	5-15R	•
TM8HWLELACC	15 120/125	0.2561	Light Almond	5-15R	•

*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See Page U-55 for more information.

2 Pole, 3 Wire



NEMA
5-15R

For complete line of Decorator Combination Devices and Hallway Lights, see Pages E-7 – E-11, E-17, E-18, E-21, E-30, E-36 and E-72.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles Recessed TV Boxes

Ideal for flat-screen TVs, home office, kitchen counter tops, and behind furniture to allow snug-to-wall placement.

Today's homeowners have more multimedia choices than ever — including flat panel, wall-mounted televisions. P&S Recessed TV Boxes offer a clean installation with the versatility to handle up to 12 multimedia connections, while providing surge protected power.

Their recessed design saves space and simplifies connections to cable or satellite boxes, DVRs, DVD players, surround-sound systems and more.

And they're available with or without TVSS receptacles to protect costly electronics from potentially damaging surges.



TV3WTVSSWLA



TV1WW



TV1WTVSSBK

Features

- Clean, flush-mount appearance — snap-on end caps hide mounting screws.
- Flexible — position either line voltage or low-voltage in all three openings.
- Low-voltage connectors offer both terminated and pull-through capability.
- Plugs and multimedia connections stay recessed behind the wall surface.
- Molded-in template and rectangular cut-out.
- Accepts standard TP wall plates.
- Metal swing brackets ensure a solid mounting.
- Uses old-work-style boxes for line voltage.
- Accepts all P&S keystone low-voltage connectors, including Cat 5e and F-connectors (both supplied with TVSS kit), as well as RCA and audio binding posts.

Catalog Number	Description	Color
Recessed TV Boxes		
TV1WW TV1WBK TV1WLA	Single Gang Recessed TV Box — Frame Only.	White Black Light Almond
TV1WTVSSW TV1WTVSSBK TV1WTVSSLA	Single Gang Recessed TV Box with TVSS & Low-Voltage Kit. Includes TVSS Duplex Receptacle, Cat 5e Jack, F-Connector, Blanks, & Wall Plates.	White Black Light Almond
TV3WW TV3WBK TV3WLA	3 Gang Recessed TV Box — Frame Only.	White Black Light Almond
TV3WTVSSW TV3WTVSSBK TV3WTVSSLA	Single Gang Recessed TV Box with TVSS & Low-Voltage Kit. Includes TVSS Duplex Receptacle, Cat 5e Jack, F-Connector, Blanks, & Wall Plates.	White Black Light Almond

Single gang dimensions: 7.25" L x 4.875" W x 2.25" D

Three gang dimensions: 8.5" L x 4.875" W x 2.25" D

Straight Blade Receptacles Tamper-Resistant GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour




Features


- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity



1595TRW



2095TRSW


Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI						
1595TRI	15 125	Ivory	5-15R	•	•	•
1595TRW	15 125	White	5-15R	•	•	•
1595TR	15 125	Brown	5-15R	•	•	•
1595TRBK	15 125	Black	5-15R	•	•	•
1595TRLA	15 125	Light Almond	5-15R	•	•	•
TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI with Auto-Ground						
1595TRSI	15 125	Ivory	5-15R	•	•	•
1595TRSW	15 125	White	5-15R	•	•	•
1595TRSLA	15 125	Light Almond	5-15R	•	•	•
Specification Grade Tamper-Resistant 20 Amp Duplex GFCI						
2095TRI	20 125	Ivory	5-20R	•	•	•
2095TRW	20 125	White	5-20R	•	•	•
2095TR	20 125	Brown	5-20R	•	•	•
2095TRGRY	20 125	Gray	5-20R	•	•	•
2095TRBK	20 125	Black	5-20R	•	•	•
2095TRRED	20 125	Red	5-20R	•	•	•
2095TRLA	20 125	Light Almond	5-20R	•	•	•
Specification Grade Tamper-Resistant 20 Amp Duplex GFCI with Auto-Ground						
2095TRSI	20 125	Ivory	5-20R	•	•	•
2095TRSW	20 125	White	5-20R	•	•	•
2095TRSLA	20 125	Light Almond	5-20R	•	•	•

For Configurable Solutions, see Page U-1.

2008 National Electrical Code® Section 406.11 Tamper-Resistant Receptacles in Dwelling Units.

In all areas specified in 210.52 all 125-volt, 15- and 20-amp receptacles shall be listed tamper-resistant receptacles.


All devices listed on this page conform to NEMA WD-1 and WD-6.




NEMA
5-15R

NEMA
5-20R

Pass & Seymour



1595HGTRW



2095HGTRW

Straight Blade Receptacles

Hospital Grade Tamper-Resistant GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC


Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
Hospital Grade Tamper-Resistant 15 Amp Duplex GFCI						
1595HGTRI	15 125	Ivory	5-15R	•	•	•
1595HGTRW	15 125	White	5-15R	•	•	•
1595HGTR	15 125	Brown	5-15R	•	•	•
1595HGTRGRY	15 125	Gray	5-15R	•	•	•
1595HGTRRED	15 125	Red	5-15R	•	•	•
1595HGTRLA	15 125	Light Almond	5-15R	•	•	•
Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI						
2095HGTRI	20 125	Ivory	5-20R	•	•	•
2095HGTRW	20 125	White	5-20R	•	•	•
2095HGTR	20 125	Brown	5-20R	•	•	•
2095HGTRGRY	20 125	Gray	5-20R	•	•	•
2095HGTRRED	20 125	Red	5-20R	•	•	•
2095HGTRLA	20 125	Light Almond	5-20R	•	•	•



For Configurable Solutions, see Page U-1.

Straight Blade Receptacles TradeMaster® & Specification Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour



Straight Blade Receptacles


TradeMaster® & Spec Grade GFCI Receptacles

Features


- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.

Specifications


- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity




1595W



1595SW



2095W



NEMA
5-15R



NEMA
5-20R


Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
TradeMaster®/Spec Grade 15 Amp Duplex GFCI							
1595I	15	125	Ivory	5-15R	•	•	•
1595W	15	125	White	5-15R	•	•	•
1595	15	125	Brown	5-15R	•	•	•
1595GRY	15	125	Gray	5-15R	•	•	•
1595BK	15	125	Black	5-15R	•	•	•
1595RED	15	125	Red	5-15R	•	•	•
1595LA	15	125	Light Almond	5-15R	•	•	•
TradeMaster®/Spec Grade 15 Amp Duplex GFCI with Auto-Ground							
1595SI	15	125	Ivory	5-15R	•	•	•
1595SW	15	125	White	5-15R	•	•	•
1595SLA	15	125	Light Almond	5-15R	•	•	•
Specification Grade 20 Amp Duplex GFCI							
2095I	20	125	Ivory	5-20R	•	•	•
2095W	20	125	White	5-20R	•	•	•
2095	20	125	Brown	5-20R	•	•	•
2095GRY	20	125	Gray	5-20R	•	•	•
2095BK	20	125	Black	5-20R	•	•	•
2095RED	20	125	Red	5-20R	•	•	•
2095LA	20	125	Light Almond	5-20R	•	•	•
Specification Grade 20 Amp Duplex GFCI with Auto-Ground							
2095SI	20	125	Ivory	5-20R	•	•	•
2095SW	20	125	White	5-20R	•	•	•
2095SLA	20	125	Light Almond	5-20R	•	•	•

For Configurable Solutions, see Page U-1.


Available in Bulk Packaging, i.e. 1595W20 is 20 pack, 1595W100 is 100 pack.
Please contact Customer Support at 1-800-223-4189.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



1595HGW



2095HGW

Straight Blade Receptacles Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



Features

- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
Hospital Grade 15 Amp Duplex GFCI						
1595HGI	15 125	Ivory	5-15R	•	•	•
1595HGW	15 125	White	5-15R	•	•	•
1595HG	15 125	Brown	5-15R	•	•	•
1595HGGRY	15 125	Gray	5-15R	•	•	•
1595HGRED	15 125	Red	5-15R	•	•	•
1595HGLA	15 125	Light Almond	5-15R	•	•	•
Hospital Grade 20 Amp Duplex GFCI						
2095HGI	20 125	Ivory	5-20R	•	•	•
2095HGW	20 125	White	5-20R	•	•	•
2095HG	20 125	Brown	5-20R	•	•	•
2095HGGRY	20 125	Gray	5-20R	•	•	•
2095HGRED	20 125	Red	5-20R	•	•	•
2095HGLA	20 125	Light Almond	5-20R	•	•	•



For Configurable Solutions, see Page U-1.

Straight Blade Receptacles Illuminated GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour




Features


- Green indicator light (LED) is ON when power is available. Helps identify emergency power branch circuits.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity




1595WL



2095HGWL

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	 FSUL WC59
TradeMaster®/Spec Grade Illuminated 15 Amp Duplex GFCI							
1595IL	15	125	Ivory	5-15R	•	•	•
1595WL	15	125	White	5-15R	•	•	•
1595L	15	125	Brown	5-15R	•	•	•
1595LAL	15	125	Light Almond	5-15R	•	•	•
Specification Grade Illuminated 20 Amp Duplex GFCI							
2095IL	20	125	Ivory	5-20R	•	•	•
2095WL	20	125	White	5-20R	•	•	•
2095L	20	125	Brown	5-20R	•	•	•
2095GRYL	20	125	Gray	5-20R	•	•	•
2095LAL	20	125	Light Almond	5-20R	•	•	•
Hospital Grade Illuminated 15 Amp Duplex GFCI							
1595HGIL	15	125	Ivory	5-15R	•	•	•
1595HGWL	15	125	White	5-15R	•	•	•
1595HGL	15	125	Brown	5-15R	•	•	•
1595HGGRYL	15	125	Gray	5-15R	•	•	•
1595HGREDL	15	125	Red	5-15R	•	•	•
1595HGLAL	15	125	Light Almond	5-15R	•	•	•
Hospital Grade Illuminated 20 Amp Duplex GFCI							
2095HGIL	20	125	Ivory	5-20R	•	•	•
2095HGWL	20	125	White	5-20R	•	•	•
2095HGL	20	125	Brown	5-20R	•	•	•
2095HGGRYL	20	125	Gray	5-20R	•	•	•
2095HGREDL	20	125	Red	5-20R	•	•	•
2095HGLAL	20	125	Light Almond	5-20R	•	•	•



NEMA 5-15R




NEMA 5-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



1595SWTTRWCC4

Straight Blade Receptacles Decorator Combination Tamper-Resistant Switch/GFCI Receptacles

15A, 125VAC

Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Up-down switching.
- 15 Amp single pole switch rated for 1/2 HP motor loads – perfect for bath or kitchen vents and garbage disposals.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Two back wire holes per terminal.
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Switch Rating A. VAC	Receptacle Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance			
					 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	 UL20 C22.2 No. 111	
	Combination Tamper-Resistant Single Pole Switch/GFCI							
	1595SWTTRICC4	15 120	15 125	Ivory	5-15R	•	•	•
	1595SWTTRWCC4	15 120	15 125	White	5-15R	•	•	•
	1595SWTTRBKCC4	15 120	15 125	Black	5-15R	•	•	•
	1595SWTTRLACC4	15 120	15 125	Light Almond	5-15R	•	•	•


NEMA
5-15R

Straight Blade Receptacles


Decorator Combination Tamper-Resistant Nightlight/GFCI Receptacles

15 & 20A, 125VAC

Pass & Seymour



1595NTLTRWCC4



2095HGNTLTRW

Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Two receptacles.
- Photocell turns nightlight ON in dark, OFF in daylight.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity


	Catalog Number	Rating A.	VAC	Light Output in 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance		
							 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
	Combination Tamper-Resistant 15 Amp Nightlight/GFCI								
	1595NTLTRICC4	15	125	0.180	Ivory	5-15R	•	•	•
	1595NTLTRWCC4	15	125	0.180	White	5-15R	•	•	•
	1595NTLTRBKCC4	15	125	0.180	Black	5-15R	•	•	•
	1595NTLTRLACC4	15	125	0.180	Light Almond	5-15R	•	•	•
	Combination Tamper-Resistant 20 Amp Nightlight/GFCI								
	2095NTLTRI	20	125	0.180	Ivory	5-20R	•	•	•
	2095NTLTRW	20	125	0.180	White	5-20R	•	•	•
	2095NTLTRGRY	20	125	0.180	Gray	5-20R	•	•	•
	2095NTLTRRED	20	125	0.180	Red	5-20R	•	•	•
	2095NTLTRLA	20	125	0.180	Light Almond	5-20R	•	•	•
	Hospital Grade Combination Tamper-Resistant 15 Amp Nightlight/GFCI								
	1595HGNTLTRI	15	125	0.180	Ivory	5-15R	•	•	•
	1595HGNTLTRW	15	125	0.180	White	5-15R	•	•	•
	1595HGNTLTR	15	125	0.180	Brown	5-15R	•	•	•
	1595HGNTLTRGRY	15	125	0.180	Gray	5-15R	•	•	•
	1595HGNTLTRRED	15	125	0.180	Red	5-15R	•	•	•
	1595HGNTLTRLA	15	125	0.180	Light Almond	5-15R	•	•	•
	Hospital Grade Combination Tamper-Resistant 20 Amp Nightlight/GFCI								
	2095HGNTLTRI	20	125	0.180	Ivory	5-20R	•	•	•
	2095HGNTLTRW	20	125	0.180	White	5-20R	•	•	•
	2095HGNTLTR	20	125	0.180	Brown	5-20R	•	•	•
	2095HGNTLTRGRY	20	125	0.180	Gray	5-20R	•	•	•
	2095HGNTLTRRED	20	125	0.180	Red	5-20R	•	•	•
	2095HGNTLTRLA	20	125	0.180	Light Almond	5-20R	•	•	•

*FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See Page U-55 for more information.


All devices listed on this page conform to NEMA WD-1 and WD-6.



Pass & Seymour



1595TRWRW



2095TRWRW

Straight Blade Receptacles

Weather-Resistant GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Features

- Weather-Resistant: Meets 2008 National Electrical Code® Weather-Resistant requirements.
- Tamper-Resistant: Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including:
 - Ultraviolet light exposure test
 - Cold impact test
 - Accelerated aging test
 - Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long nickel post-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

	Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance			
					 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	 FSUL WC596	
NEW	TradeMaster®/Spec Grade Weather-Resistant 15 Amp Duplex GFCI							
	1595TRWRI	15	125	Ivory	5-15R	•	•	•
	1595TRWRW	15	125	White	5-15R	•	•	•
	1595TRWR	15	125	Brown	5-15R	•	•	•
	1595TRWRLA	15	125	Light Almond	5-15R	•	•	•
NEW	Specification Grade Weather-Resistant 20 Amp Duplex GFCI							
	2095TRWRI	20	125	Ivory	5-20R	•	•	•
	2095TRWRW	20	125	White	5-20R	•	•	•
	2095TRWR	20	125	Brown	5-20R	•	•	•
	2095TRWRGRY	20	125	Gray	5-20R	•	•	•
	2095TRWRLA	20	125	Light Almond	5-20R	•	•	•

NEMA
5-15RNEMA
5-20R

For Configurable Solutions, see Page U-1.

2008 National Electrical Code® Section 406.8 Receptacles in Wet or Damp Locations.

Requires that all 15- and 20-amp, 125- and 250-volt non-locking receptacles installed in wet or damp locations shall be weather-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles Weather-Resistant DuraShield™ GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC


Features

- Designed for extra durability and a long service life when installed in harsh environments: outdoor, garages, workshops, wash down areas, commercial kitchens, and labs.
- Weather-Resistant: Meets 2008 National Electrical Code® Weather-Resistant requirements.
- Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including:
 - Ultraviolet light exposure test
 - Cold impact test
 - Accelerated aging test
 - Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.
- Dust- and insect-resistant.
- Rubber curtains let plug blades in; keep dust, water and insects out.
- Integral gasket seals receptacle, protecting critical electronic components.
- Exceeds UL corrosion requirements – survives 4X the required corrosion test cycles.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long nickel post-plated steel mounting strap.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Pass & Seymour



1595DSWRBKCC4



Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance	
				 UL 18 UL943	 UL 18 UL498
				C22.2 No. 144	C22.2 No. 42
Specification Grade Weather-Resistant DuraShield™ 15 Amp Duplex GFCI					
1595DSWRBKCC4	15 125	Black	5-15R	•	•
Specification Grade Weather-Resistant DuraShield™ 20 Amp Duplex GFCI					
2095DSWRBK	20 125	Black	5-20R	•	•



NEMA
5-15R



NEMA
5-20R


For Configurable Solutions, see Page U-1.

2008 National Electrical Code® Section 406.8 Receptacles in Wet or Damp Locations.


Requires that all 15- and 20-amp, 125- and 250-volt non-locking receptacles installed in wet or damp locations shall be weather-resistant receptacles.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



PT2095W



PTR6STR

Straight Blade Receptacles PlugTail™ Specification Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Features

- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

NEW

NEW

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
Specification Grade 15 Amp Duplex GFCI						
PT1595I	15 125	Ivory	5-15R	•	•	•
PT1595W	15 125	White	5-15R	•	•	•
PT1595	15 125	Brown	5-15R	•	•	•
PT1595GRY	15 125	Gray	5-15R	•	•	•
PT1595BK	15 125	Black	5-15R	•	•	•
PT1595RED	15 125	Red	5-15R	•	•	•
PT1595LA	15 125	Light Almond	5-15R	•	•	•
Specification Grade 20 Amp Duplex GFCI						
PT2095I	20 125	Ivory	5-20R	•	•	•
PT2095W	20 125	White	5-20R	•	•	•
PT2095	20 125	Brown	5-20R	•	•	•
PT2095GRY	20 125	Gray	5-20R	•	•	•
PT2095BK	20 125	Black	5-20R	•	•	•
PT2095RED	20 125	Red	5-20R	•	•	•
PT2095LA	20 125	Light Almond	5-20R	•	•	•

Catalog Number	Wire Type	Wire Length
PlugTail Connectors – Right Angle		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"

NEMA
5-15RNEMA
5-20R

For additional PlugTail Connectors,
see Page B-3.

All PlugTail Connectors are available
in any wire length up to 25 inches,
use Configurable Solutions to order.

Configurable Solutions and Metal Box Kits for PlugTail Receptacles and Connectors,
see Pages U-1 – U-3.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles PlugTail™ Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour




Features

- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity



PT2095HGW



Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
Hospital Grade 15 Amp Duplex GFCI						
PT1595HGI	15 125	Ivory	5-15R	•	•	•
PT1595HGW	15 125	White	5-15R	•	•	•
PT1595HG	15 125	Brown	5-15R	•	•	•
PT1595HGGRY	15 125	Gray	5-15R	•	•	•
PT1595HGRED	15 125	Red	5-15R	•	•	•
PT1595HGLA	15 125	Light Almond	5-15R	•	•	•
Hospital Grade 20 Amp Duplex GFCI						
PT2095HGI	20 125	Ivory	5-20R	•	•	•
PT2095HGW	20 125	White	5-20R	•	•	•
PT2095HG	20 125	Brown	5-20R	•	•	•
PT2095HGGRY	20 125	Gray	5-20R	•	•	•
PT2095HGRED	20 125	Red	5-20R	•	•	•
PT2095HGLA	20 125	Light Almond	5-20R	•	•	•

Catalog Number	Wire Type	Wire Length
PlugTail Connectors – Right Angle		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"

For additional PlugTail Connectors, see Page B-3.


All PlugTail Connectors are available in any wire length up to 25 inches, use Configurable Solutions to order.



NEMA
5-15R



NEMA
5-20R




PTRA6STR


Configurable Solutions and Metal Box Kits for PlugTail Receptacles and Connectors, see Pages U-1 – U-3.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Pass & Seymour



PT2095TRW



PT2095HGTRW



PTR6STR

For PlugTail Connector
catalog numbers,
see Page B-3.

NEMA
5-15RNEMA
5-20R

Straight Blade Receptacles PlugTail™ Specification & Hospital Grade Tamper-Resistant GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Features

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
Specification Grade Tamper-Resistant 15 Amp Duplex GFCI						
PT1595TRI	15 125	Ivory	5-15R	•	•	•
PT1595TRW	15 125	White	5-15R	•	•	•
PT1595TR	15 125	Brown	5-15R	•	•	•
PT1595TRGRY	15 125	Gray	5-15R	•	•	•
PT1595TRBK	15 125	Black	5-15R	•	•	•
PT1595TRRED	15 125	Red	5-15R	•	•	•
PT1595TRLA	15 125	Light Almond	5-15R	•	•	•
Specification Grade Tamper-Resistant 20 Amp Duplex GFCI						
PT2095TRI	20 125	Ivory	5-20R	•	•	•
PT2095TRW	20 125	White	5-20R	•	•	•
PT2095TR	20 125	Brown	5-20R	•	•	•
PT2095TRGRY	20 125	Gray	5-20R	•	•	•
PT2095TRBK	20 125	Black	5-20R	•	•	•
PT2095TRRED	20 125	Red	5-20R	•	•	•
PT2095TRLA	20 125	Light Almond	5-20R	•	•	•
Hospital Grade Tamper-Resistant 15 Amp Duplex GFCI						
PT1595HGTRI	15 125	Ivory	5-15R	•	•	•
PT1595HGTRW	15 125	White	5-15R	•	•	•
PT1595HGTRGRY	15 125	Gray	5-15R	•	•	•
PT1595HGTRRED	15 125	Red	5-15R	•	•	•
PT1595HGTRLA	15 125	Light Almond	5-15R	•	•	•
Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI						
PT2095HGTRI	20 125	Ivory	5-20R	•	•	•
PT2095HGTRW	20 125	White	5-20R	•	•	•
PT2095HGTRGRY	20 125	Gray	5-20R	•	•	•
PT2095HGTRRED	20 125	Red	5-20R	•	•	•
PT2095HGTRLA	20 125	Light Almond	5-20R	•	•	•

Configurable Solutions and Metal Box Kits for PlugTail Receptacles and Connectors,
see Pages U-1 – U-3.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles PlugTail™ Specification & Hospital Grade Nightlight/GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC


Features

- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Photocell turns nightlight ON in dark, OFF in daylight.
- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.


Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity


Pass & Seymour



PT1595NTLLA




PT1595HGNTLLA



PTR6STR

For PlugTail Connector catalog numbers, see Page B-3.




NEMA 5-15R




NEMA 5-20R

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
-Specification Grade 15 Amp Combination Nightlight/GFCI						
PT1595NTLI	15 125	Ivory	5-15R	•	•	•
PT1595NTLW	15 125	White	5-15R	•	•	•
PT1595NTLGRY	15 125	Gray	5-15R	•	•	•
PT1595NTLBK	15 125	Black	5-15R	•	•	•
PT1595NTLRED	15 125	Red	5-15R	•	•	•
PT1595NTLLA	15 125	Light Almond	5-15R	•	•	•
-Specification Grade 20 Amp Combination Nightlight/GFCI						
PT2095NTLI	20 125	Ivory	5-20R	•	•	•
PT2095NTLW	20 125	White	5-20R	•	•	•
PT2095NTLGRY	20 125	Gray	5-20R	•	•	•
PT2095NTLBK	20 125	Black	5-20R	•	•	•
PT2095NTLRED	20 125	Red	5-20R	•	•	•
PT2095NTLLA	20 125	Light Almond	5-20R	•	•	•
-Hospital Grade 15 Amp Combination Nightlight/GFCI						
PT1595HGNTLI	15 125	Ivory	5-15R	•	•	•
PT1595HGNTLW	15 125	White	5-15R	•	•	•
PT1595HGNTLGRY	15 125	Gray	5-15R	•	•	•
PT1595HGNTLRED	15 125	Red	5-15R	•	•	•
PT1595HGNTLLA	15 125	Light Almond	5-15R	•	•	•
-Hospital Grade 20 Amp Combination Nightlight/GFCI						
PT2095HGNTLI	20 125	Ivory	5-20R	•	•	•
PT2095HGNTLW	20 125	White	5-20R	•	•	•
PT2095HGNTLGRY	20 125	Gray	5-20R	•	•	•
PT2095HGNTLRED	20 125	Red	5-20R	•	•	•
PT2095HGNTLLA	20 125	Light Almond	5-20R	•	•	•

Pass & Seymour



8200ISP



IG8300ISP

NEMA
5-15RNEMA
5-20R

Straight Blade Receptacles

Hospital Grade TVSS Duplex Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Specifications

- UL1449 (latest revision). (1.2 x 50 μ s 6000V, 8 x 20 μ s 3000A).
- 1 filtering capacitor for 7 to 1 average noise reduction.
- Nominal let-through (suppressed) voltage in all 3 modes, 500V.
- Response time less than 1 nanosecond for unmounted MOV.
- Overcurrent protection in all 3 modes.
- Electronic components potted for electrical, mechanical and thermal stability.
- Thermal protection in all 3 modes.
- Leakage current: 0.5mA at 25°C/120VAC.
- 3 18mm dual pack MOVs to suppress transients in all modes – equally.
- Common mode noise attenuation: 500 KHz to 30 MHz; up to 35dB (50 ohm source impedance)
- Varistor voltage: 150V RMS.
- Back and side wire capability including ground terminal.
- Operating temperature: -40°C to 85°C (-40°F to 185°F)
- Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

Specification, Hospital and Isolated Ground Receptacles

- Audible alarm able to be turned on/off.
- LED indicator light.
- 280 joules of energy absorption in each of the three modes.
- 18,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.
- Isolated Ground version complies with NEC 410-56 (C) and 250-74 exception 4.

Commercial Receptacles

- LED indicator light.
- 140 joules of energy absorption in each of the three modes.
- 9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.

Audible Alarm with LED Indicator

Catalog Number	Rating A. VAC		NEMA Config. No.	Color	3rd Party Compliance			
					 UL1449	 UL498	FSUL WC596	cUL/CSA
Duplex Receptacles Back & Side Wire								
8200ISP	15	125	5-15R	Ivory	•	•	•	•
8200WSP	15	125	5-15R	White	•	•	•	•
8200SP	15	125	5-15R	Brown	•	•	•	•
8200GRYSP	15	125	5-15R	Gray	•	•	•	•
8200REDSP	15	125	5-15R	Red	•	•	•	•
8200LASP	15	125	5-15R	Light Almond	•	•	•	•
8200BLSP	15	125	5-15R	Blue	•	•	•	•
8300ISP	20	125	5-20R	Ivory	•	•	•	•
8300WSP	20	125	5-20R	White	•	•	•	•
8300SP	20	125	5-20R	Brown	•	•	•	•
8300GRYSP	20	125	5-20R	Gray	•	•	•	•
8300REDSP	20	125	5-20R	Red	•	•	•	•
8300LASP	20	125	5-20R	Light Almond	•	•	•	•
8300BLSP	20	125	5-20R	Blue	•	•	•	•
Isolated Ground Duplex Receptacles Back & Side Wire								
IG8200ISP	15	125	5-15R	Ivory	•	•		•
IG8200WSP	15	125	5-15R	White	•	•		•
IG8200GRYSP	15	125	5-15R	Gray	•	•		•
IG8200LASP	15	125	5-15R	Light Almond	•	•		•
IG8200BLSP	15	125	5-15R	Blue	•	•		•
IG8200OSP	15	125	5-15R	Orange	•	•		•
IG8300ISP	20	125	5-20R	Ivory	•	•		•
IG8300WSP	20	125	5-20R	White	•	•		•
IG8300GRYSP	20	125	5-20R	Gray	•	•		•
IG8300LASP	20	125	5-20R	Light Almond	•	•		•
IG8300BLSP	20	125	5-20R	Blue	•	•		•
IG8300OSP	20	125	5-20R	Orange	•	•		•

Straight Blade Receptacles Specification Grade TVSS Duplex Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour




Straight Blade Receptacles

Spec Grade TVSS Duplex Receptacles


Audible Alarm with LED Indicator

Catalog Number	Rating A. VAC	NEMA Config. No.	Color	3rd Party Compliance			
				 UL1449	 UL498	FSUL WC596	cUL/CSA
Extra Heavy-Duty Duplex Receptacles Back & Side Wire*							
5262ISP	15 125	5-15R	Ivory	•	•	•	•
5262WSP	15 125	5-15R	White	•	•	•	•
5262SP	15 125	5-15R	Brown	•	•	•	•
5262GRYSP	15 125	5-15R	Gray	•	•	•	•
5262REDSP	15 125	5-15R	Red	•	•	•	•
5262LASP	15 125	5-15R	Light Almond	•	•	•	•
5262BLSP	15 125	5-15R	Blue	•	•	•	•
5262BKSP	15 125	5-15R	Black	•	•	•	•
5362ISP	20 125	5-20R	Ivory	•	•	•	•
5362WSP	20 125	5-20R	White	•	•	•	•
5362SP	20 125	5-20R	Brown	•	•	•	•
5362GRYSP	20 125	5-20R	Gray	•	•	•	•
5362REDSP	20 125	5-20R	Red	•	•	•	•
5362LASP	20 125	5-20R	Light Almond	•	•	•	•
5362BLSP	20 125	5-20R	Blue	•	•	•	•
Isolated Ground Duplex Receptacles Back & Side Wire							
IG5262ISP	15 125	5-15R	Ivory	•	•	•	•
IG5262WSP	15 125	5-15R	White	•	•	•	•
IG5262GRYSP	15 125	5-15R	Gray	•	•	•	•
IG5262BLSP	15 125	5-15R	Blue	•	•	•	•
IG5262OSP	15 125	5-15R	Orange	•	•	•	•
IG5362ISP	20 125	5-20R	Ivory	•	•	•	•
IG5362WSP	20 125	5-20R	White	•	•	•	•
IG5362SP	20 125	5-20R	Brown	•	•	•	•
IG5362GRYSP	20 125	5-20R	Gray	•	•	•	•
IG5362LASP	20 125	5-20R	Light Almond	•	•	•	•
IG5362BLSP	20 125	5-20R	Blue	•	•	•	•
IG5362OSP	20 125	5-20R	Orange	•	•	•	•



LED Indicator Only

Catalog Number	Rating A. VAC	NEMA Config. No.	Color	3rd Party Compliance			
				 UL1449	 UL498	FSUL WC596	cUL/CSA
Duplex Receptacles Back & Side Wire*							
5252ISP	15 125	5-15R	Ivory	•	•	•	•
5252WSP	15 125	5-15R	White	•	•	•	•
5252GRYSP	15 125	5-15R	Gray	•	•	•	•
5252LASP	15 125	5-15R	Light Almond	•	•	•	•
5252BLSP	15 125	5-15R	Blue	•	•	•	•
5352ISP	20 125	5-20R	Ivory	•	•	•	•
5352WSP	20 125	5-20R	White	•	•	•	•
5352GRYSP	20 125	5-20R	Gray	•	•	•	•
5352LASP	20 125	5-20R	Light Almond	•	•	•	•
5352BLSP	20 125	5-20R	Blue	•	•	•	•



NEMA
5-15R




NEMA
5-20R

*For Configurable Solutions, see Page U-1.

Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE587), ANSI/IEEE C62.45.

All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



Quad Receptacle

Straight Blade Receptacles
Quad Receptacles & Accessories

15 & 20A, 125V

Application

Pass & Seymour/Legrand's quad receptacles are designed for dense, multiple-outlet applications such as personal computers and peripherals, office equipment, and home entertainment centers. The bidirectional outlet configuration allows use of up to four oversized plugs, in close proximity. The clean, contemporary design of the quad receptacle allows for surface mounting with minimal protrusion from the wall. No wall plate is required.

Features

- Rugged nylon face and body withstands impacts and hard use.
- Built-in wire stripping gauge.
- Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.
- Heavy-duty, phosphor bronze contacts.
- Shielding walls guard against live-circuit-to-ground shorts.
- Split circuit break-off tabs.
- UL and CSA listed.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				 UL498	 UL1449  CSA
Hospital Grade Isolated TVSS Quads					
IG420HISP	20 125	Ivory	5-20R	•	•
IG420HGRYSP	20 125	Gray	5-20R	•	•
IG420HBLSP	20 125	Blue	5-20R	•	•
Hospital Grade Quads					
420HI	20 125	Ivory	5-20R	•	•
420HW	20 125	White	5-20R	•	•
420H	20 125	Brown	5-20R	•	•
420HGRY	20 125	Gray	5-20R	•	•
420HRED	20 125	Red	5-20R	•	•
Specification Grade TVSS Quads					
420ISP	20 125	Ivory	5-20R	•	•
420BLSP	20 125	Blue	5-20R	•	•
Specification Isolated Grade Quads					
IG415	15 125	Orange	5-15R	•	•
IG420	20 125	Orange	5-20R	•	•
Specification Grade Quads					
415I	15 125	Ivory	5-15R	•	•
415W	15 125	White	5-15R	•	•
415GRY	15 125	Gray	5-15R	•	•
420I	20 125	Ivory	5-20R	•	•
420W	20 125	White	5-20R	•	•
420GRY	20 125	Gray	5-20R	•	•
Quad Adapter Plates					
4API		Ivory		•	•
4APW		White		•	•
4AP		Brown		•	•
4APGRY		Gray		•	•
4APRED		Red		•	•
4APBL		Blue		•	•
4APORG		Orange		•	•

2 Pole, 3 Wire



NEMA
5-15R




NEMA
5-20R

Straight Blade Receptacles Quad Receptacles Specifications


Pass & Seymour



Hard Use Spec Grade & Hard Use TVSS Spec Grade Quads	
- Isolated ground complied with NEC® 410-56(c) and 250-74 exception 4 - Conforms to NEMA WD-1, WD-6.	
Electrical	
Frequency	60Hz
Voltage	125V
Mechanical	
Terminal Identification	Brass = Hot, Nickel = Neutral, Green = Ground
Terminal Accommodation	#14 –12 AWG copper and copper-clad
Product Identification	Ratings are permanent part of device
Weight	10.75 oz.
Environmental	
Flammability	UL94 V2
Operating Temperature	-40°C to 65°C (-40°F to 150°F) continuous without impact
Materials	
Face	Nylon
Body	Nylon
Line Terminals	.035" T-type Triple-Wipe Phosphor Bronze
Terminal Screws	Brass #8-32
Hex Head Grounding Screw	Steel (Green)
Mounting Screws	Zinc-plated steel
Additional Specifications for Hard Use TVSS Spec Grade Quads	
- ANSI /IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45 - Installation Categories "A" (ring wave) and "B" (unidirectional impulse)	
Electrical	
MOV Rating	18mm
UL1449 Suppressed Voltage Rating	500V (L-N, L-G, N-G)
Noise Attenuation	-35db Noise Filtering at 5kHz-50MHz
Thermal Protection	Fused
Green LED Indicator	ON when protection is active, OFF when protection is inactive




Quad Receptacle



Adapter Plate

Pass & Seymour



6207
shown with neoprene
sealing mat

Straight Blade Receptacles
Dust & Moisture Resistant &
Clock Hanger Receptacles


15 & 20A, 125V

Features – Dust & Moisture Resistant

- Duplex receptacle has face backed by neoprene gasket which is slit to provide wiping action on plug blades and to provide positive closure when not in use.
- Cellular neoprene sealing mat fits under wall plate.

Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	 C22.2 No. 42
Dust & Moisture Resistant						
6207	15 125	Duplex, Dust and Moisture Resistant, Gray	5-15R	•	•	•
CR6207	15 125	Duplex, Corrosion, Dust and Moisture Resistant, Yellow	5-15R	•	•	•
6307	20 125	Duplex, Dust and Moisture Resistant, Gray	5-20R	•	•	
6307RED	20 125	Duplex, Dust and Moisture Resistant, Red	5-20R	•	•	
CR6307	20 125	Duplex, Corrosion, Dust and Moisture Resistant, Yellow	5-20R	•	•	

NEW



S3713I

Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance		
				 UL498	FSUL WC596	 C22.2 No. 42
Clock Hangers						
S3713I	15 125	Recessed Receptacle with Ivory Smooth Wall Plate	5-15R	•	•	•
S3713W	15 125	Recessed Receptacle with White Smooth Wall Plate	5-15R	•	•	•
S3713BK	15 125	Recessed Receptacle with Black Smooth Wall Plate	5-15R	•	•	•
S3713LA	15 125	Recessed Receptacle with Light Almond Smooth Wall Plate	5-15R	•	•	•
S3733SS	15 125	Recessed Receptacle with Stainless Steel Wall Plate	5-15R	•	•	•
S3733	15 125	Recessed Receptacle with Brass Wall Plate	5-15R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R

Straight Blade Receptacles Power Outlet Receptacles & Plugs

20, 30, 50, & 60A

Pass & Seymour



Straight Blade Receptacles

Power Outlet Receptacles & Plugs

Rating A. V.	Receptacle/Plug Configuration & NEMA No.						
		Flush Receptacle	Wall Plate	Surface Receptacle	Plug	Angle Plug	Connector
				Catalog Nos.			
30 125	5-30  	3802 \$ AL/CU	1-Gang: TP724 ** 2-Gang: SS702 ** 2-Gang: TP703 †		D0531 .57"-1.26"		D0533 .57"-1.26"
30 125	NEMA TT30  	3830 AL/CU*	1-Gang: TP724 ** 2-Gang: SS702 ** 2-Gang: TP703 †				
30 250	6-30  	3801 AL/CU	1-Gang: TP724 ** 2-Gang: SS702 ** 2-Gang: TP703 †		D0631 .57"-1.26"	3869	D0633 .57"-1.26"
50 125	5-50  				D0551 .57"-1.26"		D0553 .57"-1.26"
50 250	6-50  	3804 \$ AL/CU	1-Gang: TP724 ** 2-Gang: SS702 ** 2-Gang: TP703 †	3852 # AL/CU	D0651 .57"-1.26"	3869	D0653 .57"-1.26"
30 125/250 Dryer	10-30  	3860 AL/CU	1-Gang: TP724 ** 2-Gang: SS702 ** 2-Gang: TP703 †	388 AL/CU	1031	3861	
50 125/250 Range	10-50  	3890 \$ AL/CU	1-Gang: TP724 ** 2-Gang: SS702 ** 2-Gang: TP703 †	385 AL/CU	1051 .57"-1.26"	3861	1053 .32"-.91"
20 125/250	14-20  	3820	1-Gang: SS7 **				
30 125/250 Dryer	14-30  	3864 AL/CU	2-Gang: SS702 ** 2-Gang: TP703 †	3884 #/388440† AL/CU	1431 .57"-1.26"	5746AN 3867	
30 3ø, 250	15-30  	5740 AL/CU	2-Gang: SS702 ** 2-Gang: TP703 †			5741AN	
50 125/250 Range	14-50  	3894 \$ AL/CU	2-Gang: SS702 ** 2-Gang: TP703 †	3854 #/385440† AL/CU	1451 .57"-1.26"	5745AN 3867	
50 3ø, 250	15-50  	5750 AL/CU	2-Gang: SS702 ** 2-Gang: TP703 †			5751AN	
60 3ø, 250	15-60  	5760 AL/CU	2-Gang: SS702 ** 2-Gang: TP703 †			5761AN	
20 3øY, 120/208	18-20  	3822	1-Gang: SS7 **		7251DF .35"-1.05"		
60 3øY, 120/208	18-60  	3870 \$ AL/CU	2-Gang: SS701 †		D1861 .57"-1.26"	8302AN	

*For recreational vehicles. **For 2 screw mounting. †For 4 screw mounting. ‡In bulk pack of 40 with plastic snap-in wire clamp.

\$Up to #3 AWG aluminum conductors. #Up to #4 AWG aluminum conductors.

For further information consult Wall Plate Section S (for Stainless Steel versions of TP724 and TP703, refer to pages S-12 and S-13).











All devices listed on this page conform to NEMA WD-1 and WD-6.

Pass & Seymour



Straight Blade Receptacles Power Outlet Receptacles & Plugs

20, 30, 50, & 60A



Straight Blade Receptacles

Power Outlet Receptacles & Plugs

20, 30, 50 & 60A

Pass & Seymour



Application

Power devices are for use in industrial, institutional, commercial, and certain residential applications to provide higher amperage power to equipment such as air conditioners, copiers, small welders, ranges, and dryers.

Features

- Flush receptacle bodies are molded of arc-resistant plastic.
- All devices are of dead front design.
- Receptacles have double-wipe contacts of high performance copper-based alloy.
- Recommended stainless steel wall plates are listed with each flush receptacle.
- UL Listed for use with aluminum wiring.

Receptacle Amp. Rating	AWG Size	Material
Conductor Size & Material for Power Outlet Receptacles		
20A	#14 – #10	Copper/Copper-clad
30A	#10 – #6	Copper/Copper-clad/Aluminum
50A	#10 – #6	Copper/Copper-clad/Aluminum
60A	#8 – #4	Copper/Copper-clad/Aluminum

Ampere Rating	With Non-Metallic Sheathed Cable	With Conduit
Recommended Box Sizes for Flush Receptacles		
30A	4" sq. x 2-1/8" deep	4-11/16" sq. x 2-1/8" deep
50A	4-11/16" sq. x 2-1/8" deep	2-g deep box (4" sq. x 2-1/2" deep)
60A	4-11/16" sq. x 2-1/8" deep with 1/2" raised ring	2-g deep box (4" sq. x 2-1/2" deep)

Description	Color	Nylon	Metal	Wall Plates Recommended for the Following Flush Receptacles	
		TradeMaster®	Material		
Accessories – Flush Receptacle Wall Plates					
	• 2.156" hole for 2.125" dia. device • 2 mtg. holes	Ivory White Brown Gray Black Light Almond	TP724I TP724W TP724 TP724GRY TP724BK TP724LA	Chrome S384C 302S/S SS724	2 Pole, 3 Wire Grounded 3801 3804 3802 3830
	• 2-5/32" hole for 2-1/8" dia. device • 2 mtg. holes			302S/S SS702	3 Pole, 3 Wire Ungrounded 3860 3860
	• 2.1563" hole for 2.125" dia. device • 4 mtg. holes	Ivory White Brown Gray Black Light Almond	TP703I TP703W TP703 TP703GRY TP703BK TP703LA	Chrome S3862C 302S/S SS703	3 Pole, 4 Wire Ungrounded 3864 5740 3894 5750 5760


New Installations require 4 wire range and dryer outlets. Ref: 2002 NEC 250-134, 250-138
Existing Installations permitted to use 3 wire range and dryer outlets. Ref: 2002 NEC 250-140




Flush Receptacle




Surface Receptacle



Angle Plug



Plug




Wall Plate


Straight Blade Receptacles
Miscellaneous Configurations

Straight Blade Receptacles, 3 Wire, Specification Grade



Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance		
				 FSUL UL498 WC596	 C22.2 No. 42	
2 Pole, 3 Wire Grounding						
5762	15 277	Duplex Receptacle, Self-Grounding	7-15R	•		
D0711	15 277	Plug, Yellow	7-15P	•	•	
7621	20 277	Single Receptacle	7-20R	•		
D0721	20 277	Plug, Yellow	7-20P			
3 Pole, 3 Wire Non-Grounding						
6810I	20 125/250	Receptacle, Ivory	10-20R	•		
6810	20 125/250	Receptacle, Black	10-20R	•		
9977	20 125/250	Plug, Nylon	10-20P			
9750DF	10 250	Plug, with Nylon Insert	NON-NEMA			
7088	20 125/250	Connector, Armored	10-20R			




5762




6810I



7621



7088



9750DF



9977

Straight Blade Receptacles Power & TVSS Strips

Pass & Seymour



Features

- UL1449 listed.
- Heavy-duty cord from 3' to 15', depending on device.
- Circuit breaker switch.

Catalog Number	Rating A.	Rating V.	Type of Housing	# of Outlets	Cord Length	Color
Power Strips without Surge Protection						
PNS6	15	125	Strip	6	3'	Black
PNS7L	15	125	Strip	7	8'	Black
PNS10	15	125	Block	10	15'	Black

Application

There are an average of over 250 power disturbances per year in each home or office in the United States. Over 8% data loss is a direct result from lightning and the value of equipment and data is sometimes much greater than that of equipment.

Surges and spikes can come through power lines as well as phone and coax lines. So choose a protector which includes phone and/or coax protection.


Features

- 400V clamping voltage.
- UL1449 listed.
- Heavy-duty cord from 3' to 15', depending on device.
- Multiple function protection available for power, phone, fax, modem, coax or data.
- Extremely long life with dependable protection.
- Surge protection indicator on surge devices.
- Circuit breaker switch.
- Heavy-duty high-energy MOVs.
- Ground continuity indicator.


Protection Specifications

- Line protection modes: L-N, L-G, N-G.
- Spike protection for sudden, dramatic surges, over 400V.
- Surge protection lasts for 1/120 of a second, for moderate short term overvoltage.
- EMI/RFI noise attenuation.


Catalog Number	Rating A.	Rating V.	Type of Housing	# of Outlets	Cord Length	Joule Rating Range	Max. Spike Current (Amps)	Type of Protection Phone/Fax	Coax	Color
Power Strips with Surge Protection										
PS1	15	125	Tap	1		740J	48K			PC Gray
PS1P	15	125	Tap	1		740J	48K	X		PC Gray
PS6	15	125	Strip	6	3'	555J	36K			PC Gray
PS7	15	125	Strip	7	6'	740J	48K			PC Gray
PS7P	15	125	Strip	7	6'	740J	48K	X		PC Gray
PS7L	15	125	Strip	7	15'	740J	48K			PC Gray
PS8C	15	125	Block	8	8'	1100J	72K		X	PC Gray
PS8P	15	125	Block	8	8'	1100J	72K	X		PC Gray
PS10PC	15	125	Block	10	8'	1100J	72K	X	X	PC Gray



TAP - PS1



STRIP - PNS7L



BLOCK - PS10PC

All devices listed on this page conform to NEMA WD-1 and WD-6.

Straight Blade Receptacles Power & TVSS Device Specifications

Power Devices – Ratings

Catalog Number	PNS6	PNS7L	PNS10
Type of Housing	Strip	Strip	Strip
Total Outlets	6	7	10
Standard Grounded Outlets	6	6	6
Transformer Ready Outlets	0	1	4
Power Indicator			X
Circuit Breaker Switch	Unlighted	Lighted	Lighted
Cord Length (exposed) ft.	3'	8'	15'
Plug	Straight	Straight	Straight
Molded Add-On Safety Covers	0	0	5
Molded Housing Color	Black	Black	Black

Power & TVSS Devices – Ratings

Catalog Number	PS1	PS1P	PS6	PS7	PS7P	PS7L	PS8C	PS8P	PS10PC
Type of Housing	Tap	Tap	Strip	Strip	Strip	Strip	Block	Block	Block
Number of Outlets	1	1	6	7	7	7	8	8	10
Standard Grounded Outlets	1	1	6	6	6	6	0	0	6
Transformer Ready Outlets	1	1	0	1	1	1	8	8	4
Joule Rating Range	740J	740J	555J	740J	740J	740J	1100J	1100J	1100J
MOV Configuration	4-20mm	4-20mm	3-20mm	4-20mm	4-20mm	4-20mm	6-20mm	6-20mm	6-20mm
Clamping Voltage	400V	400V	400V	400V	400V	400V	400V	400V	400V
Max. Spike Current (Amps)	48K	48K	36K	48K	48K	48K	72K	72K	72K
EMI Filter Capacitors	X	X		X	X	X	X	X	X
Protection (L-N, L-G, N-G)	X	X	X	X	X	X	X	X	X
Surge Protection Indicator	X	X	X	X	X	X	X	X	X
Ground/Wiring Indicator				X	X	X	X	X	X
Circuit Breaker Switch			Unlighted	Lighted	Lighted	Lighted	Lighted	Lighted	Lighted
Cord Length (exposed) ft.			3'	6'	6'	15'	8'	8'	8'
Plug			Straight	Straight	Straight	Straight	Rt. Angle	Rt. Angle	Rt. Angle
Phone/Fax Protection		X			X			X	X
Phone Line(s) Configuration					1 in/1 out			1 in/2 out	1 in/1 out
Phone Jack Spec		RJ-11			RJ-11			RJ-45	RJ-45
Nickel-Coaxial Jack Protection							X		X
6' Phone Cable (6P2C)		X			X			X	X
6' Coax Cable (Nickel Plated)							X		X
Molded Add-On Safety Covers	0	0	0	2	2	2	4	4	5
Molded Housing Color	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray
UL1449 2nd Edition	X	X	X	X	X	X	X	X	X

Devices & Wall Plates Color Selection Chart

Pass & Seymour



Devices & Plastic Wall Plate Colors




Ivory



Light Almond



White



Black



Blue



Brown



Gray



Orange



Red

See specific device and wall plate catalog charts for particular color availabilities.

Metal Wall Plates



Aluminum



Brass (Brushed)



Polished Brass



Stainless Steel




Brushed Bronze



Chrome

Custom Metal Wall Plates Paint Finish Colors



Paint Color Light Blue



Orange



Navy




Peach




Hunter Green



Gray



Yellow



Paint Color Glossy Black




Brown (Dark)



Brown (NEMA)



Burgundy




White



Primer



Red



Paint Color Beige



Pink



Flat Black



Ivory



Light Almond



Medium Blue

To order custom metal wall plates, see Pages S-42 – S-44.