

Type SOOW-2-40 Conductor, EPDM Insulation-CPE Jacket, 90°C-600 Volt



Product Construction

Conductor:

- Fully annealed stranded bare copper

Insulation:

- Ethylene Propylene Diene Monomer (EPDM)

Jacket

- Chlorinated Polyethylene (CPE)

Applications

- Portable tools and equipment
- Portable appliances
- Small motors and associated machinery

Standards

- UL Flexible Cord-Subject 62
- MSHA Approved

COLOR CODE CHART	
Cond. #	Color
1	Black
2	White
3	Green
4	Red

Flexible and Portable Cord



Part #	AWG	Conductors	Insulation Thickness	Nom. O.D.	Lbs./M'
B11802	18	2	.030"	.345"	65
B11803	18	3	.030"	.365"	80
B11804	18	4	.030"	.390"	94
B11602	16	2	.030"	.370"	77
B11603	16	3	.030"	.390"	94
B11604	16	4	.030"	.420"	114
B11402	14	2	.045"	.510"	154
B11403	14	3	.045"	.535"	171
B11404	14	4	.045"	.575"	209
B11202	12	2	.045"	.570"	168
B11203	12	3	.045"	.595"	223
B11204	12	4	.045"	.650"	276
B11002	10	2	.045"	.620"	230
B11003	10	3	.045"	.660"	289
B11004	10	4	.045"	.715"	351

*Fittings are available for these products

Note: The information in this specification sheet is approximate and subject to standard industry and manufacturer tolerances. Please verify specific requirements with your Omni Cable account manager.