












ELECTRICAL ACCESSORIES

Incandescent Lampholders

METAL SHELL LAMPHOLDERS

|  | CATALOG NUMBER | RATING | | DESCRIPTION | COLOR | UL | CSA | cULus |
|---|----------------|--------|------|------------------------------------|-------|----|-----|-------|
| | 975ABDCC10 | 660W | 250V | Medium base, metal shell, keyless. | | • | • | |

MEDIUM BASE LAMPHOLDERS

| | | | | | | | | |
|---|-----------|------|------|--|-------|---|---|---|
|  | 8101 | 660W | 250V | Medium base, porcelain, keyless, single circuit, 2 piece ring with leads. 1-3/8" to 1-1/2" hole. | White | • | | |
|  | 201 | 660W | 600V | Medium base, rubber, keyless, for temporary lighting, 2 wire leads 6" long. | Black | • | | • |
|  | 31528 | 660W | 250V | Medium base, porcelain, screw terminals, keyless, single circuit, fixture pan with 1/8" IPS hickey. | White | • | • | W |
|  | 3352F | 660W | 250V | Medium base, porcelain, keyless, screw terminals, short base. | White | • | • | |
|  | 8052CC10 | 660W | 250V | Medium base, porcelain, bracket mount. | | • | • | |
|  | 9814 | 250W | 250V | Medium base, porcelain, 2-piece pull chain, ring type, screw terminals, gasket furnished. | White | | | |
|  | 9880 | 660W | 250V | Medium base, porcelain, surface mount type, 2-piece. | White | • | • | |
|  | 10045 | 660W | 250V | Medium base, porcelain, keyless, single circuit with screw terminals, aluminum screw shell with set. | White | • | • | |
| | 10085 | 660W | 250V | Medium base, porcelain, keyless, single circuit with 2-18 AWG leads 6" long. | White | • | • | |
|  | 19062 | 660W | 250V | Medium base, porcelain, pony cleat type, terminal screws. | White | • | • | |
|  | S752WCC10 | 660W | 250V | Medium base, cleat sockets, front wire. | White | | | • |
|  | 61 | 660W | 125V | Medium base, outlet to lampholder, 2 Pole, 2 Wire. | Brown | | | |

All devices listed on this page conform to NEMA WD-1 and WD-6.