Mini Inverter Series

Interruptible unit equipment 125W, 250W, 400W or 720W



Housing

- · 14-gauge steel
- · White semi-gloss powered-coat paint finish

Mounting

- · Surface mount
- Optional recessed T-bar (125W unit only)

Lamp types operated

- LED
- Incandescent
- Fluorescent
- Operating switched, normally-on or normally-off fixture types
- Incandescent, LED, fluorescent lamps and ballast combinations, including triac dimmable ballasts (consult factory if DALI dimming)

Load capacity

- 125W, 250W, 400W or 720W
- Line voltage allows for remote mounting of the emergency fixtures at distances up to 1000 feet
- May accept load to it's full capacity when load feature power factor of 0.9 for 250W model and 0.8 for 125, 400 and 720W model

Electronics

- High-efficiency pure sine wave inverter at 250W capacity or higher
- Temperature compensated charger
- Replaceable output fuse protection
- Low battery voltage disconnect
- Unit comes standard with electronic lockout and brownout circuits

Controls

- Standard with a non-audible self diagnostic/charger is fully self-contained, fully automatic microcontrollerbased system
- Optional audible auto diagnostic available
- Standard lighting control override for 0-10V dimming systems

Nexus® Option

 Units equipped with Nexus® self-testing monitoring system circuitry shall selftest, in accordance with NFPA101, Life Safety Code minimum 30 seconds every 30 days, 30 minutes every six months and 90 minutes annually as well as keep a history of all testing logs, plus feature a real-time diagnoses, as well as, be able to locate exact fixture location while notifying service personnel to the status of the fixture via email notification. Nexus® system interface with an improved minimum load lost detection of 10%

Sealed maintenance-free battery

- 12V oversized valve regulated lead-calcium (VRLA) battery
- Provides 90 minutes of emergency operation

Power requirements

 Choice of voltage 120V in/120V out or 277V in/277V out operation, 60Hz

Approvals

- UL 924 Standard
- Meets or exceeds all National Electric Code and Life Safety Code Emergency Lighting Requirements

Warranty (subject to proper installation and maintenance)

- Battery has a 3-year full, plus 7-year pro-rata warranty
- Unit has a three-year warranty (excluding lamps and fuses)
 Detailed warranty terms located on page 178 or online at: www.emergi-lite.com/usa/files/EL_Warranty.pdf

All Emergi-Lite® inverter products receive 100% quality inspection before shipment to insure proper and satisfactory operation.





MINI INVERTER SERIES

Specifications

Transfer time	Voltage regulation on emergency	Frequency reglation on emergency	Load power factor range	Operating temperature
Less than 1 second	+/ -5%	60 Hz +/- 1%	250W model: .9 leading to .9 lagging	68° to 86°F (20° to 30°C)
-	-	_	125, 400 & 720W models: 8 leading to	_

Replacement battery

Description	Suffix
EMIU-125	860.0024-E
EMIU-250	2X 860.0024-E
EMIU-400	2X 860.0043-E
EMIU-720	2X 860.0096-E

Electrical characteristics and dimensions

			Cabinet dimensions		No. of	Total weight	Weight w/o battery	
Power rating	Sine wave	Installation	Width	Height	Depth	battery	120V & 277V	120V & 277V
125W	Modified	T-bar	24"	6.5"	8"	1	50 lbs	22 lbs
125W	Modified	Wall	16.5"	12.2"	7.3"	1	50 lbs	22 lbs
250W	Pure	Wall	27"	12.2"	7.3"	2	100 lbs	45 lbs
400W	Pure	Wall	24"	20"	10.5"	2	150 lbs	65 lbs
720W	Pure	Wall	24"	20"	14.5"	2	220 lbs	95 lbs

Note: For wiring diagram, please refer to the specification sheets

Power consumption and unit rating

						Emergency power available for load		
Model number		AC specs	90 Min	2H	3H	4H		
EMIU-125	120/277VAC	1.15 / 0.70 Amps	125W	83W	62W	47W		
EMIU-250		2.75 / 1.20 Amps	250W	167W	125W	94W		
EMIU-400		4.60 / 2.00 Amps	400W	300W	200W	150W		
EMIU-720		9.60 / 4.00 Amps	720W	480W	360W	270W		

How to order

Series	Capacity	Voltage	Diagnostic feature	Options
EMIU	-125= 125W -250= 250W -400= 400W -720= 720W	Blank = 120/120VAC or 277/277VAC	-Blank= Advanced Diagnostic, non-audible ¹ -AD= Advanced Diagnostic, audible ¹ -NAD= No auto test/ Advanced Diagnostics -NEX= Nexus® wired -NEXRF= Nexus® wireless	-D3= Time delay (15 minutes) -SAC= Service alarm contact ² -T= Recessed T-bar mounting (125W unit only)
Exampl	e: EMIU-720			

¹ Minimum load required: 10% of unit capacity ² Service alarm contact (SAC) shall provide a 24V signal, the charger board will indicate a fault by choosing a contact. Not available with 720 capacity