

Refit Solutions from GE



Application illustration only, subject lamps not used in photo.

Type C LED Tubes - 2, 3 and 4 foot

Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall. LED tubes are ideal for those seeking high energy savings with minimal installation time. Each LED tube is operated by a GE Lightech™ driver. See reverse for LED tubes and Lightech driver product details.

FEATURES

- 2', 3' & 4' tubes
- 900 – 2,200 lumens
- >100 total system lumens per watt (LPW)
- 3000K, 3500K, 4000K, 5000K and 6500K color temperatures
- 50,000-hour rated life
- UL and CUL-approved technologies
 - in compliance with UL 1598 certification
- Open or Enclosed Fixtures
- NSF Rated for food application (shatter resistant)
- Damp rating
- 5 year warranty
- DLC listed

BENEFITS

- Fast and Easy LED upgrade
- Low energy LFL replacement
- 66% longer life than LFL (50,000 vs. 30,000 hours)
- Better quality of light
 - instant on
- Shatter resistant
 - prevents breakage and downtime
- Easy disposal, non-hazardous waste

To learn more about saving money and energy, go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.

ecomaginationSM



imagination at work

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

Product Specifications - 2-3-4 Foot LED Tubes

Refit LED Tubes

| Grainger Item # | GE Product Code | Description | Bulb Shape | Base | Watts | Case Quantity | Length (in) | Initial Lumens | Color Temp (K°) | CRI | *Rated Life L70 (Hrs) |
|---------------------|-----------------|---------------|------------------|------------------|-------|---------------|-------------|----------------|-----------------|--------|-----------------------|
| 2ft LED Tube | | | | | | | | | | | |
| 65706 | LED9T8/2/835 | T8 | Med Bi-Pin (G13) | 8 | 20 | 24" | 1000 | 3500 | 80 | 50,000 | |
| 65707 | LED9T8/2/840 | T8 | Med Bi-Pin (G13) | 8 | 20 | 24" | 1100 | 4000 | 80 | 50,000 | |
| 65711 | LED9T8/2/850 | T8 | Med Bi-Pin (G13) | 8 | 20 | 24" | 1100 | 5000 | 80 | 50,000 | |
| 39CC80 | 92997 | LED9T8/2/865 | T8 | Med Bi-Pin (G13) | 8 | 20 | 24" | 1100 | 6500 | 80 | 50,000 |
| 3ft LED Tube | | | | | | | | | | | |
| 40CP64 | 82343 | LED18T8/3/835 | T8 | Med Bi-Pin (G13) | 16 | 10 | 36" | 1800 | 3500 | 80 | 50,000 |
| 40CP66 | 82345 | LED18T8/3/840 | T8 | Med Bi-Pin (G13) | 16 | 10 | 36" | 1800 | 4000 | 80 | 50,000 |
| 40CP63 | 82346 | LED18T8/3/850 | T8 | Med Bi-Pin (G13) | 16 | 10 | 36" | 1800 | 5000 | 80 | 50,000 |
| 4ft LED Tube | | | | | | | | | | | |
| 38954 | LED15T8/4/830 | T8 | Med Bi-Pin (G13) | 13 | 10 | 48" | 1700 | 3000 | 80 | 50,000 | |
| 38957 | LED15T8/4/835 | T8 | Med Bi-Pin (G13) | 13 | 10 | 48" | 1750 | 3500 | 80 | 50,000 | |
| 38958 | LED15T8/4/840 | T8 | Med Bi-Pin (G13) | 13 | 10 | 48" | 1800 | 4000 | 80 | 50,000 | |
| 38962 | LED15T8/4/850 | T8 | Med Bi-Pin (G13) | 13 | 10 | 48" | 1800 | 5000 | 80 | 50,000 | |
| 38964 | LED15T8/4/865 | T8 | Med Bi-Pin (G13) | 13 | 10 | 48" | 1800 | 6500 | 80 | 50,000 | |
| 31CA75 | 94381 | LED21T8/4/835 | T8 | Med Bi-Pin (G13) | 18 | 10 | 48" | 2100 | 3500 | 80 | 50,000 |
| 31CA76 | 94382 | LED21T8/4/840 | T8 | Med Bi-Pin (G13) | 18 | 10 | 48" | 2100 | 4000 | 80 | 50,000 |
| 31CA77 | 94383 | LED21T8/4/850 | T8 | Med Bi-Pin (G13) | 18 | 10 | 48" | 2200 | 5000 | 80 | 50,000 |
| 39CC83 | 26059 | LED21T8/4/865 | T8 | Med Bi-Pin (G13) | 18 | 10 | 48" | 2200 | 6500 | 80 | 50,000 |

Lightech Drivers - Non Dimming

| Grainger Item # | GE Product Code | Description | # of Lamps |
|-----------------|-----------------|------------------|------------|
| 39CC87 | 93100 | LED9T8/DR/UN/2L | 2 |
| | 38970 | LED15T8/DR/UN/2L | 2 |
| 40CP65 | 82347 | LED18T8/DR/UN/2L | 2 |
| 31LA57 | 94384 | LED21T8/DR/1L | 1 |
| 31LA58 | 94385 | LED21T8/DR/2L | 2 |

General Characteristics - Non Dimming

| GE Product Code | 38970 | 94384 | 94385 |
|----------------------|----------|-------|--------|
| Output Current (A) | 0.44*2 | 0.62 | 0.62*2 |
| Input Watt (Max) | 30 | 21 | 42 |
| Input Voltage (V) | 120-277V | | |
| Input Frequency (Hz) | 50/60Hz | | |
| Efficiency (%) | > .9% | | |
| Output Type | DC | | |
| Output Volt Range | 27-33V | | |
| Dimmability | None | | |
| Ambient Temp Min | -4°F | | |
| Ambient Temp Max | 104°F | | |
| Case Temperature | 158°F | | |

Dimensions - Non Dimming

| GE Product Code | 38970 | 94384 | 94385 |
|-------------------------|-------|-------|-------|
| Weight | 1.01 | 1.01 | 1.08 |
| Casing Length (in) | 9.5 | | |
| Casing Width (in) | 1.3 | | |
| Casing Height (in) | 1 | | |
| Lead Exit Length (in) | 26 | | |
| Input Wire Length (in) | 36 | | |
| Output Wire Length (in) | 38 | | |

Lightech Drivers - Dimming

| Grainger Item # | GE Product Code | Description | # of Lamps |
|-----------------|-----------------|-----------------|------------|
| | 38974 | LED15T8/DR/D2L | 2 |
| | 38975 | LED15T8/DR/4DL | 4 |
| 39CC84 | 60041 | LED21T8/DR/D/2L | 2 |
| 39CC85 | 62030 | LED21T8/DR/D/4L | 4 |

General Characteristics - Dimming

| GE Product Code | 38974 | 60041 | 38975 | 62030 |
|----------------------|----------|--------|--------|--------|
| Output Current (A) | 0.44*2 | 0.62*2 | 0.44*4 | 0.62*4 |
| Input Watt (Max) | 30 | 42 | 60 | 84 |
| Input Voltage (V) | 120-277V | | | |
| Input Frequency (Hz) | 50/60Hz | | | |
| Efficiency (%) | > .9% | | | |
| Output Type | DC | | | |
| Output Volt Range | 27-33V | | | |
| Dimmability | 0-10V | | | |
| Ambient Temp Min | -4°F | | | |
| Ambient Temp Max | 104°F | | | |
| Case Temperature | 158°F | | | |

Dimensions - Dimming

| GE Product Code | 38974 | 60041 | 38975 | 62030 |
|-------------------------|-------|-------|-------|-------|
| Weight | 1.01 | | 1.08 | |
| Casing Length (in) | 9.5 | | | |
| Casing Width (in) | 1.3 | | | 1.7 |
| Casing Height (in) | 1 | | | 1 |
| Lead Exit Length (in) | 26 | | | |
| Input Wire Length (in) | 36 | | | |
| Output Wire Length (in) | 38 | | | 42 |



Product is compliant with material restriction requirements of RoHS



www.gelighting.com

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2016 GE.

LEDL016-G (Rev5/6/16)

Distributor:

