


**TYPE
PBTD**
Features

- Broad wire range: 750kcmil-14
- UL Listed and CSA Certified for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size
			L	W	H	
PBTD-2-4	2	4-14	1.24	1.25	1.42	1/8
PBTD-3-4	3	4-14	1.70	1.25	1.42	1/8
PBTD-4-4	4	4-14	2.16	1.25	1.42	1/8
PBTD-5-4	5	4-14	2.61	1.25	1.42	1/8
PBTD-6-4	6	4-14	3.07	1.25	1.42	1/8
PBTD-7-4	7	4-14	3.53	1.25	1.42	1/8
PBTD-8-4	8	4-14	3.99	1.25	1.42	1/8
PBTD-9-4	9	4-14	4.45	1.25	1.42	1/8
PBTD-10-4	10	4-14	4.90	1.25	1.42	1/8
PBTD-11-4	11	4-14	5.36	1.25	1.42	1/8
PBTD-12-4	12	4-14	5.82	1.25	1.42	1/8
PBTD-13-4	13	4-14	6.28	1.25	1.42	1/8
PBTD-14-4	14	4-14	6.74	1.25	1.42	1/8
PBTD-2-1/0	2	1/0-14	1.67	1.63	1.63	3/16
PBTD-3-1/0	3	1/0-14	2.29	1.63	1.63	3/16
PBTD-4-1/0	4	1/0-14	2.92	1.63	1.63	3/16
PBTD-5-1/0	5	1/0-14	3.54	1.63	1.63	3/16
PBTD-6-1/0	6	1/0-14	4.17	1.63	1.63	3/16
PBTD-7-1/0	7	1/0-14	4.79	1.63	1.63	3/16
PBTD-8-1/0	8	1/0-14	5.42	1.63	1.63	3/16
PBTD-9-1/0	9	1/0-14	6.04	1.63	1.63	3/16
PBTD-10-1/0	10	1/0-14	6.67	1.63	1.63	3/16
PBTD-11-1/0	11	1/0-14	7.29	1.63	1.63	3/16
PBTD-12-1/0	12	1/0-14	7.92	1.63	1.63	3/16
PBTD-13-1/0	13	1/0-14	8.54	1.63	1.63	3/16
PBTD-14-1/0	14	1/0-14	9.17	1.63	1.63	3/16
PBTD-2-3/0	2	3/0-6	1.89	1.68	1.86	1/4
PBTD-3-3/0	3	3/0-6	2.65	1.68	1.86	1/4
PBTD-4-3/0	4	3/0-6	3.42	1.68	1.86	1/4
PBTD-5-3/0	5	3/0-6	4.18	1.68	1.86	1/4
PBTD-6-3/0	6	3/0-6	4.95	1.68	1.86	1/4
PBTD-7-3/0	7	3/0-6	5.71	1.68	1.86	1/4
PBTD-8-3/0	8	3/0-6	6.48	1.68	1.86	1/4
PBTD-9-3/0	9	3/0-6	7.24	1.68	1.86	1/4

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Per NEC Article 310-316, allowable ampacities are as follows: #4-95 Amps, 1/0-170 Amps, 3/0-225 Amps, 250-290 Amps, 350-350 Amps, 600-475 Amps, 750-535 Amps

Replacement caps & plugs available. Consult Factory Tested to UL 486A/B, UL File E6207


TYPE PBTD

Features

- Broad wire range: 750kcmil-14
- UL Listed and CSA Certified for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size
			L	W	H	
PBTD-10-3/0	10	3/0-6	8.01	1.68	1.86	1/4
PBTD-11-3/0	11	3/0-6	8.77	1.68	1.86	1/4
PBTD-12-3/0	12	3/0-6	9.54	1.68	1.86	1/4
PBTD-13-3/0	13	3/0-6	10.30	1.68	1.86	1/4
PBTD-14-3/0	14	3/0-6	11.07	1.68	1.86	1/4
PBTD-2-250	2	250kcmil-6	2.17	2.13	2.17	5/16
PBTD-3-250	3	250kcmil-6	3.07	2.13	2.17	5/16
PBTD-4-250	4	250kcmil-6	3.96	2.13	2.17	5/16
PBTD-5-250	5	250kcmil-6	4.85	2.13	2.17	5/16
PBTD-6-250	6	250kcmil-6	5.75	2.13	2.17	5/16
PBTD-7-250	7	250kcmil-6	6.64	2.13	2.17	5/16
PBTD-8-250	8	250kcmil-6	7.53	2.13	2.17	5/16
PBTD-9-250	9	250kcmil-6	8.42	2.13	2.17	5/16
PBTD-10-250	10	250kcmil-6	9.32	2.13	2.17	5/16
PBTD-11-250	11	250kcmil-6	10.21	2.13	2.17	5/16
PBTD-12-250	12	250kcmil-6	11.10	2.13	2.17	5/16
PBTD-13-250	13	250kcmil-6	12.00	2.13	2.17	5/16
PBTD-14-250	14	250kcmil-6	12.89	2.13	2.17	5/16
PBTD-2-350	2	350kcmil-6	2.51	2.25	2.62	5/16
PBTD-3-350	3	350kcmil-6	3.56	2.25	2.62	5/16
PBTD-4-350	4	350kcmil-6	4.61	2.25	2.62	5/16
PBTD-5-350	5	350kcmil-6	5.67	2.25	2.62	5/16
PBTD-6-350	6	350kcmil-6	6.71	2.25	2.62	5/16
PBTD-7-350	7	350kcmil-6	7.76	2.25	2.62	5/16
PBTD-8-350	8	350kcmil-6	8.81	2.25	2.62	5/16
PBTD-9-350	9	350kcmil-6	9.86	2.25	2.62	5/16
PBTD-10-350	10	350kcmil-6	10.91	2.25	2.62	5/16
PBTD-11-350	11	350kcmil-6	11.96	2.25	2.62	5/16
PBTD-12-350	12	350kcmil-6	13.01	2.25	2.62	5/16
PBTD-13-350	13	350kcmil-6	14.06	2.25	2.62	5/16
PBTD-14-350	14	350kcmil-6	15.11	2.25	2.62	5/16
PBTD-2-500	2	600kcmil-4	2.97	2.63	3.04	3/8
PBTD-3-500	3	600kcmil-4	4.12	2.63	3.04	3/8
PBTD-4-500	4	600kcmil-4	5.28	2.63	3.04	3/8

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Per NEC Article 310-316, allowable ampacities are as follows: #4-95 Amps, 1/0-170 Amps, 3/0-225 Amps, 250-290 Amps, 350-350 Amps, 600-475 Amps, 750-535 Amps

Replacement caps & plugs available. Consult Factory Tested to UL 486A/B, UL File E6207


TYPE PBTD

Features

- Broad wire range: 750kcmil-14
- UL Listed and CSA Certified for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size
			L	W	H	
PBTD-5-500	5	600kcmil-4	6.44	2.63	3.04	3/8
PBTD-6-500	6	600kcmil-4	7.59	2.63	3.04	3/8
PBTD-7-500	7	600kcmil-4	8.75	2.63	3.04	3/8
PBTD-8-500	8	600kcmil-4	9.90	2.63	3.04	3/8
PBTD-9-500	9	600kcmil-4	11.06	2.63	3.04	3/8
PBTD-10-500	10	600kcmil-4	12.22	2.63	3.04	3/8
PBTD-11-500	11	600kcmil-4	13.37	2.63	3.04	3/8
PBTD-12-500	12	600kcmil-4	14.53	2.63	3.04	3/8
PBTD-13-500	13	600kcmil-4	15.68	2.63	3.04	3/8
PBTD-14-500	14	600kcmil-4	16.84	2.63	3.04	3/8
PBTD-2-750	2	750kcmil-250kcmil	3.47	3.25	3.31	1/2
PBTD-3-750	3	750kcmil-250kcmil	4.89	3.25	3.31	1/2
PBTD-4-750	4	750kcmil-250kcmil	6.32	3.25	3.31	1/2
PBTD-5-750	5	750kcmil-250kcmil	7.74	3.25	3.31	1/2
PBTD-6-750	6	750kcmil-250kcmil	9.16	3.25	3.31	1/2
PBTD-7-750	7	750kcmil-250kcmil	10.58	3.25	3.31	1/2
PBTD-8-750	8	750kcmil-250kcmil	12.00	3.25	3.31	1/2
PBTD-9-750	9	750kcmil-250kcmil	13.43	3.25	3.31	1/2
PBTD-10-750	10	750kcmil-250kcmil	14.85	3.25	3.31	1/2
PBTD-11-750	11	750kcmil-250kcmil	16.27	3.25	3.31	1/2
PBTD-12-750	12	750kcmil-250kcmil	17.69	3.25	3.31	1/2
PBTD-13-750	13	750kcmil-250kcmil	19.11	3.25	3.31	1/2
PBTD-14-750	14	750kcmil-250kcmil	20.54	3.25	3.31	1/2

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Per NEC Article 310-316, allowable ampacities are as follows: #4-95 Amps, 1/0-170 Amps, 3/0-225 Amps, 250-290 Amps, 350-350 Amps, 600-475 Amps, 750-535 Amps

Replacement caps & plugs available. Consult Factory

Tested to UL 486A/B, UL File E6207


TYPE PBTS

Features

- Broad wire range: 750kcmil-14
- UL Listed and CSA Certified for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size
			L	W	H	
PBTS-2-4	2	4-14	1.24	1.22	1.42	1/8
PBTS-3-4	3	4-14	1.70	1.22	1.42	1/8
PBTS-4-4	4	4-14	2.16	1.22	1.42	1/8
PBTS-5-4	5	4-14	2.61	1.22	1.42	1/8
PBTS-6-4	6	4-14	3.07	1.22	1.42	1/8
PBTS-7-4	7	4-14	3.53	1.22	1.42	1/8
PBTS-8-4	8	4-14	3.99	1.22	1.42	1/8
PBTS-9-4	9	4-14	4.45	1.22	1.42	1/8
PBTS-10-4	10	4-14	4.90	1.22	1.42	1/8
PBTS-11-4	11	4-14	5.36	1.22	1.42	1/8
PBTS-12-4	12	4-14	5.82	1.22	1.42	1/8
PBTS-13-4	13	4-14	6.28	1.22	1.42	1/8
PBTS-14-4	14	4-14	6.74	1.22	1.42	1/8
PBTS-2-1/0	2	1/0-14	1.67	1.53	1.63	3/16
PBTS-3-1/0	3	1/0-14	2.29	1.53	1.63	3/16
PBTS-4-1/0	4	1/0-14	2.92	1.53	1.63	3/16
PBTS-5-1/0	5	1/0-14	3.54	1.53	1.63	3/16
PBTS-6-1/0	6	1/0-14	4.17	1.53	1.63	3/16
PBTS-7-1/0	7	1/0-14	4.79	1.53	1.63	3/16
PBTS-8-1/0	8	1/0-14	5.42	1.53	1.63	3/16
PBTS-9-1/0	9	1/0-14	6.04	1.53	1.63	3/16
PBTS-10-1/0	10	1/0-14	6.67	1.53	1.63	3/16
PBTS-11-1/0	11	1/0-14	7.29	1.53	1.63	3/16
PBTS-12-1/0	12	1/0-14	7.92	1.53	1.63	3/16
PBTS-13-1/0	13	1/0-14	8.54	1.53	1.63	3/16
PBTS-14-1/0	14	1/0-14	9.17	1.53	1.63	3/16
PBTS-2-3/0	2	3/0-6	1.89	1.58	1.86	1/4
PBTS-3-3/0	3	3/0-6	2.65	1.58	1.86	1/4
PBTS-4-3/0	4	3/0-6	3.42	1.58	1.86	1/4
PBTS-5-3/0	5	3/0-6	4.18	1.58	1.86	1/4
PBTS-6-3/0	6	3/0-6	4.95	1.58	1.86	1/4
PBTS-7-3/0	7	3/0-6	5.71	1.58	1.86	1/4
PBTS-8-3/0	8	3/0-6	6.48	1.58	1.86	1/4
PBTS-9-3/0	9	3/0-6	7.24	1.58	1.86	1/4

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Per NEC Article 310-316, allowable ampacities are as follows: #4-95 Amps, 1/0-170 Amps, 3/0-225 Amps, 250-290 Amps, 350-350 Amps, 600-475 Amps, 750-535 Amps

Replacement caps & plugs available. Consult Factory Tested to UL 486A/B, UL File E6207


TYPE PBTS

Features

- Broad wire range: 750kcmil-14
- UL Listed and CSA Certified for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size
			L	W	H	
PBTS-10-3/0	10	3/0-6	8.00	1.58	1.86	1/4
PBTS-11-3/0	11	3/0-6	8.77	1.58	1.86	1/4
PBTS-12-3/0	12	3/0-6	9.54	1.58	1.86	1/4
PBTS-13-3/0	13	3/0-6	10.30	1.58	1.86	1/4
PBTS-14-3/0	14	3/0-6	11.07	1.58	1.86	1/4
PBTS-2-250	2	250kcmil-6	2.17	1.91	2.17	5/16
PBTS-3-250	3	250kcmil-6	3.07	1.91	2.17	5/16
PBTS-4-250	4	250kcmil-6	3.96	1.91	2.17	5/16
PBTS-5-250	5	250kcmil-6	4.85	1.91	2.17	5/16
PBTS-6-250	6	250kcmil-6	5.75	1.91	2.17	5/16
PBTS-7-250	7	250kcmil-6	6.64	1.91	2.17	5/16
PBTS-8-250	8	250kcmil-6	7.53	1.91	2.17	5/16
PBTS-9-250	9	250kcmil-6	8.42	1.91	2.17	5/16
PBTS-10-250	10	250kcmil-6	9.32	1.91	2.17	5/16
PBTS-11-250	11	250kcmil-6	10.21	1.91	2.17	5/16
PBTS-12-250	12	250kcmil-6	11.10	1.91	2.17	5/16
PBTS-13-250	13	250kcmil-6	12.00	1.91	2.17	5/16
PBTS-14-250	14	250kcmil-6	12.89	1.91	2.17	5/16
PBTS-2-350	2	350kcmil-6	2.51	2.03	2.62	5/16
PBTS-3-350	3	350kcmil-6	3.56	2.03	2.62	5/16
PBTS-4-350	4	350kcmil-6	4.61	2.03	2.62	5/16
PBTS-5-350	5	350kcmil-6	5.66	2.03	2.62	5/16
PBTS-6-350	6	350kcmil-6	6.71	2.03	2.62	5/16
PBTS-7-350	7	350kcmil-6	7.76	2.03	2.62	5/16
PBTS-8-350	8	350kcmil-6	8.81	2.03	2.62	5/16
PBTS-9-350	9	350kcmil-6	9.86	2.03	2.62	5/16
PBTS-10-350	10	350kcmil-6	10.91	2.03	2.62	5/16
PBTS-11-350	11	350kcmil-6	11.96	2.03	2.62	5/16
PBTS-12-350	12	350kcmil-6	13.01	2.03	2.62	5/16
PBTS-13-350	13	350kcmil-6	14.06	2.03	2.62	5/16
PBTS-14-350	14	350kcmil-6	15.11	2.03	2.62	5/16
PBTS-2-500	2	600kcmil-4	2.97	2.28	3.04	3/8
PBTS-3-500	3	600kcmil-4	4.12	2.28	3.04	3/8
PBTS-4-500	4	600kcmil-4	5.28	2.28	3.04	3/8

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Per NEC Article 310-316, allowable ampacities are as follows: #4-95 Amps, 1/0-170 Amps, 3/0-225 Amps, 250-290 Amps, 350-350 Amps, 600-475 Amps, 750-535 Amps

Replacement caps & plugs available. Consult Factory Tested to UL 486A/B, UL File E6207


TYPE PBTS

Features

- Broad wire range: 750kcmil-14
- UL Listed and CSA Certified for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size
			L	W	H	
PBTS-5-500	5	600kcmil-4	6.44	2.28	3.04	3/8
PBTS-6-500	6	600kcmil-4	7.59	2.28	3.04	3/8
PBTS-7-500	7	600kcmil-4	8.75	2.28	3.04	3/8
PBTS-8-500	8	600kcmil-4	9.90	2.28	3.04	3/8
PBTS-9-500	9	600kcmil-4	11.06	2.28	3.04	3/8
PBTS-10-500	10	600kcmil-4	12.22	2.28	3.04	3/8
PBTS-11-500	11	600kcmil-4	13.37	2.28	3.04	3/8
PBTS-12-500	12	600kcmil-4	14.53	2.28	3.04	3/8
PBTS-13-500	13	600kcmil-4	15.68	2.28	3.04	3/8
PBTS-14-500	14	600kcmil-4	16.84	2.28	3.04	3/8
PBTS-2-750	2	750kcmil-250kcmil	3.47	2.75	3.31	1/2
PBTS-3-750	3	750kcmil-250kcmil	4.89	2.75	3.31	1/2
PBTS-4-750	4	750kcmil-250kcmil	6.32	2.75	3.31	1/2
PBTS-5-750	5	750kcmil-250kcmil	7.74	2.75	3.31	1/2
PBTS-6-750	6	750kcmil-250kcmil	9.16	2.75	3.31	1/2
PBTS-7-750	7	750kcmil-250kcmil	10.58	2.75	3.31	1/2
PBTS-8-750	8	750kcmil-250kcmil	12.00	2.75	3.31	1/2
PBTS-9-750	9	750kcmil-250kcmil	13.43	2.75	3.31	1/2
PBTS-10-750	10	750kcmil-250kcmil	14.85	2.75	3.31	1/2
PBTS-11-750	11	750kcmil-250kcmil	16.27	2.75	3.31	1/2
PBTS-12-750	12	750kcmil-250kcmil	17.69	2.75	3.31	1/2
PBTS-13-750	13	750kcmil-250kcmil	19.11	2.75	3.31	1/2
PBTS-14-750	14	750kcmil-250kcmil	20.54	2.75	3.31	1/2

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Per NEC Article 310-316, allowable ampacities are as follows: #4-95 Amps, 1/0-170 Amps, 3/0-225 Amps, 250-290 Amps, 350-350 Amps, 600-475 Amps, 750-535 Amps

Replacement caps & plugs available. Consult Factory

Tested to UL 486A/B, UL File E6207



TYPE PBTM

Features

- Mountable
- Broad wire range: 750kcmil-6
- UL Listed and CSA Certified for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Isolated mounting in trough, wire way or panels
- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size	Mounting Holes
			L	W	H		
PBTD-2-3/0-M	2	3/0-6	3.42	1.68	1.86	3/16	1/4
PBTD-3-3/0-M	3	3/0-6	4.18	1.68	1.86	3/16	1/4
PBTD-4-3/0-M	4	3/0-6	4.95	1.68	1.86	3/16	1/4
PBTD-5-3/0-M	5	3/0-6	5.71	1.68	1.86	3/16	1/4
PBTD-6-3/0-M	6	3/0-6	6.48	1.68	1.86	3/16	1/4
PBTD-7-3/0-M	7	3/0-6	7.24	1.68	1.86	3/16	1/4
PBTD-8-3/0-M	8	3/0-6	8.01	1.68	1.86	3/16	1/4
PBTD-9-3/0-M	9	3/0-6	8.77	1.68	1.86	3/16	1/4
PBTD-10-3/0-M	10	3/0-6	9.54	1.68	1.86	3/16	1/4
PBTD-11-3/0-M	11	3/0-6	10.30	1.68	1.86	3/16	1/4
PBTD-12-3/0-M	12	3/0-6	11.07	1.68	1.86	3/16	1/4
PBTD-2-250-M	2	250kcmil-6	3.96	2.13	2.17	5/16	1/4
PBTD-3-250-M	3	250kcmil-6	4.85	2.13	2.17	5/16	1/4
PBTD-4-250-M	4	250kcmil-6	5.75	2.13	2.17	5/16	1/4
PBTD-5-250-M	5	250kcmil-6	6.64	2.13	2.17	5/16	1/4
PBTD-6-250-M	6	250kcmil-6	7.53	2.13	2.17	5/16	1/4
PBTD-7-250-M	7	250kcmil-6	8.42	2.13	2.17	5/16	1/4
PBTD-8-250-M	8	250kcmil-6	9.32	2.13	2.17	5/16	1/4
PBTD-9-250-M	9	250kcmil-6	10.21	2.13	2.17	5/16	1/4
PBTD-10-250-M	10	250kcmil-6	11.10	2.13	2.17	5/16	1/4
PBTD-11-250-M	11	250kcmil-6	12.00	2.13	2.17	5/16	1/4
PBTD-12-250-M	12	250kcmil-6	12.89	2.13	2.17	5/16	1/4
PBTD-2-350-M	2	350kcmil-6	4.61	2.25	2.62	5/16	5/16
PBTD-3-350-M	3	350kcmil-6	5.67	2.25	2.62	5/16	5/16
PBTD-4-350-M	4	350kcmil-6	6.71	2.25	2.62	5/16	5/16
PBTD-5-350-M	5	350kcmil-6	7.76	2.25	2.62	5/16	5/16
PBTD-6-350-M	6	350kcmil-6	8.81	2.25	2.62	5/16	5/16
PBTD-7-350-M	7	350kcmil-6	9.86	2.25	2.62	5/16	5/16
PBTD-8-350-M	8	350kcmil-6	10.91	2.25	2.62	5/16	5/16
PBTD-9-350-M	9	350kcmil-6	11.96	2.25	2.62	5/16	5/16
PBTD-10-350-M	10	350kcmil-6	13.01	2.25	2.62	5/16	5/16
PBTD-11-350-M	11	350kcmil-6	14.06	2.25	2.62	5/16	5/16
PBTD-12-350-M	12	350kcmil-6	15.11	2.25	2.62	5/16	5/16

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Per NEC Article 310-316, allowable ampacities are as follows: #4-95 Amps, 1/0-170 Amps, 3/0-225 Amps, 250-290 Amps, 350-350 Amps, 600-475 Amps, 750-535 Amps

Replacement caps & plugs available. Consult Factory. Tested to UL 486A/B, UL File E6207

NIMBUS® Mountable Insulated Multi-Tap Connectors Dual Sided Entry



TYPE PBTM

Features

- Mountable
- Broad wire range: 750kcmil-6
- UL Listed and CSA Certified for 600 volts, 90° C
- Dual rated
- Cold temperature rated to -45° C
- High dielectric strength plastisol
- Black cover
- Removable plugs
- Prefilled with De-ox®

Benefits

- Isolated mounting in trough, wire way or panels
- Flexibility in the field
- Ensures reliability
- For copper or aluminum conductor
- Application variability
- Chemical resistant
- UV Rated
- Entry port closure
- Prevents oxides from forming



Catalog Number	No. Of Ports	Wire Range	Dimensions			Hex Size	Mounting Holes
			L	W	H		
PBTD-2-500-M	2	600kcmil-4	5.28	2.63	3.04	3/8	5/16
PBTD-3-500-M	3	600kcmil-4	6.44	2.63	3.04	3/8	5/16
PBTD-4-500-M	4	600kcmil-4	7.59	2.63	3.04	3/8	5/16
PBTD-5-500-M	5	600kcmil-4	8.75	2.63	3.04	3/8	5/16
PBTD-6-500-M	6	600kcmil-4	9.90	2.63	3.04	3/8	5/16
PBTD-7-500-M	7	600kcmil-4	11.06	2.63	3.04	3/8	5/16
PBTD-8-500-M	8	600kcmil-4	12.22	2.63	3.04	3/8	5/16
PBTD-9-500-M	9	600kcmil-4	13.37	2.63	3.04	3/8	5/16
PBTD-10-500-M	10	600kcmil-4	14.53	2.63	3.04	3/8	5/16
PBTD-11-500-M	11	600kcmil-4	15.68	2.63	3.04	3/8	5/16
PBTD-12-500-M	12	600kcmil-4	16.84	2.63	3.04	3/8	5/16
PBTD-2-750-M*	2	750kcmil-250kcmil	6.32	3.25	3.31	1/2	3/8
PBTD-3-750-M*	3	750kcmil-250kcmil	7.74	3.25	3.31	1/2	3/8
PBTD-4-750-M*	4	750kcmil-250kcmil	9.16	3.25	3.31	1/2	3/8
PBTD-5-750-M*	5	750kcmil-250kcmil	10.58	3.25	3.31	1/2	3/8
PBTD-6-750-M*	6	750kcmil-250kcmil	12.00	3.25	3.31	1/2	3/8
PBTD-7-750-M*	7	750kcmil-250kcmil	13.43	3.25	3.31	1/2	3/8
PBTD-8-750-M*	8	750kcmil-250kcmil	14.85	3.25	3.31	1/2	3/8
PBTD-9-750-M*	9	750kcmil-250kcmil	16.27	3.25	3.31	1/2	3/8
PBTD-10-750-M*	10	750kcmil-250kcmil	17.69	3.25	3.31	1/2	3/8
PBTD-11-750-M*	11	750kcmil-250kcmil	19.11	3.25	3.31	1/2	3/8
PBTD-12-750-M*	12	750kcmil-250kcmil	20.54	3.25	3.31	1/2	3/8

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

Per NEC Article 310-316, allowable ampacities are as follows: #4-95 Amps, 1/0-170 Amps, 3/0-225 Amps, 250-290 Amps, 350-350 Amps, 600-475 Amps, 750-535 Amps

Replacement caps & plugs available. Consult Factory.

* Not UL Listed

Tested to UL 486A/B, UL File E6207