

Ordinary Location Fittings — Liquidtight Fittings

The ultimate liquidtight solution for corrosive environments!

Ocal PVC-Coated Liquidtight Conduit Connectors



Ocal PVC-Coated Liquidtight Fittings — Straight (top left), 45° Angled (above) and 90° Angled (left).

- Nominal .040" (40 mil) PVC coating bonded to exterior — available in gray, white, blue or custom colors
- Pressure-sealing sleeves protect the connection
- Ocal uses only genuine T&B® liquidtight fittings to ensure quality installations

PVC-COATED STEEL STRAIGHT CAT. NO.	PVC-COATED ALUMINUM STRAIGHT CAT. NO.	PVC-COATED STEEL 45° CAT. NO.	PVC-COATED STEEL 90° CAT. NO.	PVC-COATED ALUMINUM 90° CAT. NO.	PIPE SIZE IN. METRIC SIZE DESIGNATOR*
ST3/8-	ST3/8SA-	ST3/845-	ST3/890-	ST3/890SA-	3/8
ST1/2-	ST1/2SA-	ST1/245-	ST1/290-	ST1/290SA-	1/2
ST3/4-	ST3/4SA-	ST3/445-	ST3/490-	ST3/490SA-	3/4
ST1-	ST1SA-	ST145-	ST190-	ST190SA-	1
ST1-1/4-	ST1-1/4SA-	ST1-1/445-	ST1-1/490-	ST1-1/490SA-	1 1/4
ST1-1/2-	ST1-1/2SA-	ST1-1/245-	ST1-1/290-	ST1-1/290SA-	1 1/2
ST2-	ST2SA-	ST245-	ST290-	ST290SA-	2
ST2-1/2-	ST2-1/2SA-	ST2-1/245-	ST2-1/290-	ST2-1/290SA-	2 1/2
ST3-	ST3SA-	ST345-	ST390-	ST390SA-	3
ST4-	ST4SA-	ST445-	ST490-	ST490SA-	4
					103

* Metric size designator (ANSI C80.1-1994).

Cat. No.	Material	Color
ST3/4	Blank = Steel/Iron	G = Gray
	SA = Aluminum	W = White
		B = Blue
		Custom colors also available.

T&B 304 Stainless Steel Liquidtight Conduit Connectors



T&B 304 Stainless Steel Liquidtight Fittings — Straight (top left), 45° Angled (bottom left) and 90° Angled (top right). 5262 Series Sealing Ring Gasket (bottom right) sold separately.

STAINLESS STEEL STRAIGHT CAT. NO.	STAINLESS STEEL 45° CAT. NO.	STAINLESS STEEL 90° CAT. NO.	SEALING RING GASKET CAT. NO.	PIPE SIZE IN. METRIC SIZE DESIGNATOR*
5331SST	5341SST	5351SST	5261	3/8
5332SST	5342SST	5352SST	5262	1/2
5333SST	5343SST	5353SST	5263	3/4
5334SST	5344SST	5354SST	5264	1
5335SST	5345SST	5355SST	5265	1 1/4
5336SST	5346SST	5356SST	5266	1 1/2
5337SST	5347SST	5357SST	5267	2
				53

* Metric size designator (ANSI C80.1-1994).